

GOT2000 Series UV Protective Sheet (for Rugged Models)

User's Manual

GT25T-07WPSVC

Thank you for purchasing Mitsubishi Electric Graphic Operation Terminal

Prior to use, please read both this manual and detailed manual thoroughly to fully understand the product.



MODEL	GT25T-PS-U-JE	
MODEL CODE	1D7MU1	
IB(NA)-0800612-B(2307)MEE		

© 2018 MITSUBISHI ELECTRIC CORPORATION

●SAFETY PRECAUTIONS●

(Always read these precautions before using this equipment.)

Before using this product, please read this manual and the relevant manuals introduced in this manual carefully and pay full attention to safety to handle the product correctly.

The precautions given in this manual are concerned with this product. In this manual, the safety precautions are ranked as "WARNING" and "CAUTION".



Indicates that incorrect handling may cause hazardous conditions, resulting in death or severe injury.



Indicates that incorrect handling may cause hazardous conditions, resulting in medium or slight personal injury or physical damage.

Note that the A CAUTION level may lead to a serious accident according to the

Always follow the precautions of both levels because they are important to

Please save this manual to make it accessible when required and always forward it

IINSTALLATION PRECAUTIONS

⚠ CAUTION

- When attaching the protective sheet onto the GOT display section, make sure to fit the protective sheet onto the section closely without leaving any air between them. Failure to do so may cause a malfunction.

- ramure u oo so may cause a mathunction.

 Do not operate or store the GOT in the environment exposed to direct sunlight, rain, high temperature, dust, humidity, or vibrations.

 Do not operate the GOT with its display section frozen.

 The water droplets on the display section may freeze at a low temperature.

 Touch switches and other input objects may malfunction if the display section is frozen.

[STARTUP AND MAINTENANCE PRECAUTIONS]

⚠ CAUTION

Daily check the protective sheet with eyes. When you find extreme dirt or scratches of the surface, immediately replace it with new one.

Using the productive sheet of decreased visibility may cause a malfunction.

[DISPOSAL PRECAUTIONS]

⚠ CAUTION

Dispose of this product as industrial waste

[TRANSPORTATION PRECAUTIONS]

⚠ CAUTION

When furnigants that contain halogen materials such as fluorine, chlorine, bromine, and iodine are used for disinfecting and protecting wooden packaging from insects, they cause malfunction when entering our products Please take necessary precautions to ensure that remaining materials from furnigant do not enter our products, or treat packaging with methods other than furnigation (heat method).

Additionally, disinfect and protect wood from insects before packing products

<u>Manuals</u>

The following shows manuals relevant to this product.

Manual name	Manual number (Model code)	
GOT2000 Series User's Manual (Hardware)	SH-081194ENG	
(Sold separately)	(1D7MJ5)	

For the latest e-Manuals and PDF manuals, consult your local sales office.

Packing List

the box, check that the following products are included.

Model	Product	Quantity
GT25T-07WPSVC	UV protective sheet (for the rugged model)	1
	GOT2000 Series UV Protective Sheet (for Rugged Models) User's Manual (This manual)	1

eferenced Standard: GB/T15969.2 Requirement of Chinese standardiz

1. OVERVIEW

This user's manual describes the GOT2000 series UV protective sheet for the rugged model (hereinafter referred to as the protective sheet). The protective sheet protects the GOT front face from damage and soil. The protective sheet also helps protect the GOT front face from UV-induced deterioration.

2. SPECIFICATIONS


The following shows the performance specifications and models of the protective sheets, and applicable GOT screen sizes.

The general specifications for the protective sheet are the same as those of the

For the general specifications of the GOT, refer to the GOT2000 Series User's Manual (Hardware).

Product	Model	Description	
UV protective sheet (for the rugged model)	GT25T-07WPSVC	UV protective sheet for 7" rugged model	Antiglare (UV-resistant) type Transparent Without a hole for the USB environmental protection cover 1 sheet


3. EXTERNAL DIMENSIONS



Model	Α	В
GT25T-07WPSVC	205 (8.07)	149 (5.87)
		Unit: mm (inch)

4. INSTALLATION AND REMOVAL

1) If the old protective sheet is attached, slowly remove the sheet from the finger grip part of the lower right of the GOT. Clean the GOT surface.



Peel the release paper off the back of the new protective sheet.
 If the protective sheet without the hole for the USB environmental part cover is attached, position the sheet from the upper left of the GOT.



3) To attach the protective sheet, attach it from one direction gradually. Make sure to fit the protective sheet onto the joining surface closely without leaving any air between them.

Attach the protective sheet with adding additional pressure sufficiently to the adhesive side of the outer circumference.

To hold adequate strength of the adhesive joining, use the GOT after a lapse of about 24 hours.



5. PRECAUTIONS FOR USE

- 1) The protective sheet is consumable supplies.
- If you find scratches or extreme dirt by the periodic check, replace it with new
- 2) Do not push the protective sheet with something whose the point is sharp, such
- as a mechanical pencil or screwdriver
- as a mechanical pencil or screwdriver.

 Doing so may cause scratches or be damaged.

 3) Do not wash the protective sheet with using bleach, thinner, organic solvent, caustic chemical, and others.

 Doing so may change in shape or color.

 4) If the protective sheet gets dust, wipe the sheet with a damp cloth.

 5) When using the protective sheet, remove the protective film from the sheet

Warranty

Mitsubishi Electric will not be held liable for damage caused by factors found not to be the cause of Mitsubishi Electric; machine damage or lost profits caused by faults in the Mitsubishi Electric products; damage, secondary damage, accident compensation caused by special factors unpredictable by Mitsubishi Electric; damages to products other than Mitsubishi Electric products; and to other duties.

♠ For safe use

- This product has been manufactured as a general-purpose part for general industries, and has not been designed or manufactured to be incorporated in a device or system used in purposes related to human life.
- Before using the product for special purposes such as nuclear power, electric power, aerospace, medicine or passenger movement vehicles, consult with Mitsubishi Electric.

 This product has been manufactured under strict quality control.
- However, when installing the product where major accidents or losses could occur if the product fails, install appropriate backup or failsafe functions in the system.

Sales office/Tel

Sales office/Tol
Americas
Mitsubish Electric Automation, Inc.
500 Corporate Woods Parkway, Vernon Hills, IL 60061, U.S.A.
Tci: +1-847-778-2100
Mitsubish Electric do Brasil Comercio e Servicos Ltda.
Avenida Adelino Cardana, 293, 21 andar, Bethaville, Barueri SP, Brazil
Tci: +55-11-4698-3001
Mitsubish Electric Automation, Inc. Mexico Branch
Boulevard Miguel de Cervantes Saavedra 301. Torre Norte Piso 5, Ampliacion Granada,
Miguel Hidalgo, Outded de Mexico, Mexico, C.P.11520
Tci: +52-25-3007-7512

Europe

Mitsubishi Electric Europe B.V. German Branch
Mitsubishi-Electric-Piatz 1, 40822 Ratingen, Germany
Tei: +482-102-486-0
Mitsubishi Electric Europe B.V. UK Branch
Travellers Lane, UK-Hatfleid, Hertfordshire, AL10 8XB, U.K.
Tei: +44-1707-28-8-780

Milsubishi Electric Europe B.V. Italian Branch Centro Direzionale Colleoni - Palazzo Sirio, Viale Colleoni 7, 20864 Agrate Brianza (MB), Italy Tel: +39-039-60531

Mitsubishi Electric Europe B.V. Spanish Branch Carretera de Rubi, 76-80-Apdo. 420, E-08190 Sant Cugat del Valles (Barcelona), Spain Tel: +34-935-65-3131

Mitsubishi Electric Europe B.V. French Branch 25, Boulevard des Bouvets, 92741 Nanterre Cedex, France Tel: +33-1-55-68-55-68

Mitsubishi Electric Turkey A.S. Umraniye Branch Serifali Mahallesi Nutuk Sokak No:5, TR-34775 Umraniye / Istanbul, Turkey Tel: +90-216-526-3990

Mitsubishi Electric Europe B.V. Polish Branch ul. Krakowska 48, 32-083 Balice, Poland Tel: +48-12-347-65-00

Africa

Adroit Technologies 20 Waterford Office Park, 189 Witkoppen Road, Fourways, South Africa Tel: +27-11-658-8100

Asia-Pacific Mitsubishi Electric Automation (China) Ltd. Mitsubishi Electric Automation Center, No.1386 Hongqiao Road, Shanghai, China Tei: +86-21-2322-3030

SETSUYO ENTERPRISE CO., LTD.
6F, No.105, Wugong 3rd Road, Wugu District, New Taipei City 24889, Taiwan Tel: +886-2-2299-2499

Mitsubishi Electric Automation Korea Co., Ltd.
7F to 9F, Gangseo Hangang XI-tower A, 401, Yangcheon-ro, Gangseo-Gu, Seoul 07528, Korea
7E: +82-2-3860-9569

Mitsubishi Electric Asia Pte. Ltd. 307 Alexandra Road, Mitsubishi Electric Building, Singapore 159943 Tel: +65-6473-2308

Nitsubish Electric Factory Automation (Thailand) Co., Ltd. 12th Floor, SV.City Building, Office Tower 1, No. 896/19 and 20 Rama 3 Road, Kwaeng Bangpongpang, Khet Yannawa, Bangkok 10120, Thailand Tel: +662-882-6522 to 31

PT. Mitsubishi Electric Indonesia Gedung Jaya 8th Floor, JL. MH. Thamrin No.12, Jakarta Pusat 10340, Indonesia Tel: +62-21 3192-6461

Mitsubishi Electric Vietnam Company Limited 11th & 12th Floor, Viettel Tower B, 285 Cach Mang Thang 8 Street, Ward 12, District 10,

Mitsubihi Electric India Pvt. Ltd. Pune Branch Emerald House, EL-3, J Block, M.I.D.C., Bhosari, Pune - 411026, Maharashtra, India Tel: +91-20-2710-2000

MITSUBISHI ELECTRIC AUSTRALIA PTY. LTD. 348 Victoria Road, P.O. Box 11, Rydalmere, N.S.W 2116, Australia Tel: +61-2-9684-7777

MITSUBISHI ELECTRIC CORPORATION

HEAD OFFICE: TOKYO BLDG., 2-7-3, MARUNOUCHI, CHIYODA-KU, TOKYO 100-8310, JAPAN NAGOYA WORKS: 1-14, YADA-MINAMI 5-CHOME, HIGASHI-KU, NAGOYA 461-8670, JAPAN When exported from Japan, this manual does not require application to the Ministry of Economy, Trade and Industry for service transaction permission

Specifications subject to change without notice. Printed in Japan, July 2023.