

BCN-P5999-0874-C(2403)	QRコード <div></div>
------------------------	--

MI Configuratorインストール手順書

ご使用の前にお読みください

ご使用になる前に、本資料をお読みください。お読みになった後は、いつでも使用できるように大切に保管してください。また、本製品のユーザが代わる場合も、必ず最終ユーザのお手元に届くようお願いいたします。使用時の注意事項については、下記を参照してください。

モデル名称	マニュアル番号
MI Configuratorオペレーティングマニュアル	SH-081937

本書に関するご注意

- 本書の内容の一部または全部を当社に断りなく、いかなる形でも転載または複製することは、固くお断りします。
- 本書の記述内容はソフトウェア、ハードウェアの改訂に追従するように努力しておりますが、やむなく同期できない場合も生じます。
- 本書に記載されている内容は断りなしに変更することがありますのでご了承ください。

1. 動作環境

項目	内容
パソコン本体	Microsoft®Windows®が動作するパーソナルコンピュータ
CPU	Intel® Core™ 2 Duo 2GHz以上推奨
必要メモリ	OSが64ビット版の場合: 2GB以上推奨 <p>OSが32ビット版の場合: 1GB以上推奨</p>
ハードディスク空き容量	2GB以上
ディスプレイ	解像度1024×768ドット以上
OS <p>(日本語版、英語版、中国語簡体字版)</p>	<ul style="list-style-type: none">Windows 10 (Home, Pro, Enterprise, Education, IoT Enterprise 2016 LTSB¹) Windows 8.1, Windows 8.1 (Pro, Enterprise) Windows 8, Windows 8 (Pro, Enterprise) Windows 7 (Home Basic, Premium, Professional, Ultimate, Enterprise)

*1 64ビット版にのみ対応しています。

- MI Configuratorをインストールするパソコンに、.NET Framework 2.0、.NET Framework 4.0、Windows Installer 3.0 がインストール済みでない場合、それらをインストールするために、システムドライブに約500MBの空き容量が必要です。
- Windows 10では、.NET Framework 3.5(.NET 2.0および3.0を含む)および.NET Framework 4.6Advanced Servicesを有効化する必要があります。下記いずれかを参照してください。
 - LIJMI Configuratorオペレーティングマニュアル[SH-081937]
 - テクニカルニュースNo. FA-D-0207
- Windows 8、Windows 8.1では、.NET Framework 3.5(.NET 2.0および3.0を含む)および.NET Framework 4.5 Advanced Servicesを有効化する必要があります。テクニカルニュースNo. FA-D-0153を参照してください。
- Windows 7では、.NET Framework 3.5(.NET 2.0および3.0を含む)を有効化する必要があります。
- 下記の機能を使用した場合、本製品は正常に動作しない可能性があります。
 - Windows互換モードでのアプリケーション起動
 - ユーザ簡易切替
 - リモートデスクトップ
 - Windows XP Mode
 - タッチ機能
 - Modern UI
 - クライアントHyper-V
 - タブレットモード
 - 仮想デスクトップ
- 下記の場合、本製品の画面が正常に動作しない可能性があります。
 - 画面上のテキストやその他の項目のサイズを既定値(96 DPI、100%、9ptなど)以外に変更した場合
 - 詳細は、下記を参照してください。
 - LIJMI Configuratorオペレーティングマニュアル[SH-081937]
 - 動作中に画面の解像度を変更した場合
 - 動作中にWindowsのテーマを変更した場合
 - マルチディスプレイに設定した場合
- MI Configuratorでは、「標準ユーザ」または「管理者」で使用してください。
- Windowsファイアウォールの設定が有効な場合、「ユニット検索機能」、「直接接続機能」が正常に動作しない可能性があります。Windowsファイアウォールの設定を無効にしてください。
- 本製品では小数点を表す記号としてピリオド(.)を使用します。コントロールパネルの「小数点の記号」の設定にかかわらず、小数点を入力するときはピリオドを入力してください。

MI Configuratorインストール手順書

使用前请务必阅读

使用前请务必阅读本资料。阅读后请妥善保管，以便随时使用。此外，本产品的用户发生变更时，请务必将本资料转交给最终用户。关于使用时的注意事项，请参照以下手册。	
手册名称	手册编号
MI Configurator操作手册	SH-081961CHN

本说明书相关注意事项

- 未经三菱电机株式会社许可，禁止以任何形式转载或复制本说明书的部分或全部内容。
- 本说明书的记载内容尽量跟随软件、硬件的改版进程，但仍有可能无法完全同步。
- 本说明书中记载的内容可能在事先未知情的情况下进行更改，敬请谅解。

1. 运行环境

項目	内容
个人计算机	基于Microsoft® Windows® 下运行的个人计算机
CPU	建议Intel® Core™ 2 Duo 2GHz以上
必要内存	64位版操作系统时：建议2GB以上 <p>32位版操作系统时：建议1GB以上</p>
硬盘可用空间	2GB以上
显示器	分辨率1024×768像素以上
OS <p>(日语版、英语版、简体中文版)</p>	<ul style="list-style-type: none">Windows 10(Home、Pro、Enterprise、Education、IoT Enterprise 2016 LTSB¹) Windows 8.1、Windows 8.1 (Pro、Enterprise) Windows 8、Windows 8 (Pro、Enterprise) Windows 7 (Home Basic、Home Premium、Professional、Ultimate、Enterprise)

*1 仅支持64位版。

- 安装MI Configurator的个人计算机中未安装.NET Framework 2.0、.NET Framework 4.0、Windows Installer 3.0时，系统驱动器需要有约500MB的可用空间用于安装 .NET Framework 2.0、.NET Framework 4.0、Windows Installer 3.0。
- Windows 10环境下，需启用.NET Framework 3.5（包括.NET 2.0和3.0）及.NET Framework 4.6 Advanced Services。请参照以下其中一项。
 - LIJMI Configurator操作手册 [SH-081961CHN]
 - 技术简讯No. FA-A-0207（英文版）
- Windows 8、Windows 8.1环境下，需启用.NET Framework 3.5（包括.NET 2.0和3.0）及.NET Framework 4.5 Advanced Services。请参照技术简讯No. FA-A-0153（英文版）。
- Windows 7环境下，需启用.NET Framework 3.5（包括.NET 2.0和3.0）。
- 如果使用下述功能，有可能导致本产品无法正常运行。
 - Windows兼容模式下的应用程序启动
 - 用户简易切换
 - 远程桌面
 - Windows XP Mode
 - 触控功能
 - Modern UI
 - 客户端Hyper-V
 - 平板模式
 - 虚拟桌面
- 下述情况下，有可能导致本产品的画面无法正常运行。
 - 画面中的文本与其他项目等的尺寸为默认值（96 DPI、100%、9pt等）以外时
 - 详细内容，请参照以下手册。
 - LIJMI Configurator操作手册 [SH-081961CHN]
 - 在运行中更改了画面的分辨率时
 - 在运行中更改了Windows的主题时
 - 设置为多屏显示时
- 请以“标准用户”或“管理员”权限使用MI Configurator。
- 启用Windows防火墙的设置时，“模块搜索功能”、“直接连接功能”有可能无法正常运行。应禁用Windows防火墙的设置。
- 本产品中表示小数点的符号使用（.）。无论控制面板的“小数点”的设置如何，输入小数点时请输入（.）。

2. インストール手順

2.1 インストール前に確認してください。

- MELIPCまたはパソコンへは、「管理者」または「Administrator」のユーザとしてログインしてください。
- インストールを行う前に、動作させているすべてのアプリケーションを終了させてください。他のアプリケーションが動作している状態でインストールすると、製品が正常に動作しない場合があります。

2.2 手順

- 入手した圧縮ファイルを解凍します。
- 解凍されたフォルダー内の「setup.exe」をダブルクリックし、インストーラを起動します。
- 画面の指示に従って必要事項を選択または入力します。

2.3 ご注意

- 弊社が紹介するMicrosoft Windows Operating System対応の市販ソフトウェア製品について各製品に対する保証は致しませんので、ご了承ください。
- 本製品のソフトウェアの著作権は三菱電機株式会社にあります。
- 本製品(マニュアル含む)は、ソフトウェア使用契約のもとでのみ使用することができます。
- 本製品(マニュアル含む)を運用した結果の影響については、いっさい責任を負いかねますのでご了承ください。

3. アンインストール手順

Windowsのコントロールパネルからアンインストールしてください。

Intelは、米国およびその他の国におけるIntel Corporationの登録商標または商標です。MicrosoftおよびWindowsは、マイクロソフトグループの企業の商標です。本文中における会社名、システム名、製品名などは、一般に各社の登録商標または商標です。本文中で、商標記号(®)は明記していない場合があります。

MI Configurator Installation Instructions

Before Using the Product

Please read this document before use. Keep the document in a safe place for future reference. Make sure that the end users read the document.

For the precautions on using MI Configurator, refer to the following manual.

Manual name	Manual number
MI Configurator Operating Manual	SH-081938ENG

Notice

- Reprinting or reproducing the part or all of the contents of this document in any form for any purpose without the permission of Mitsubishi Electric Corporation is strictly forbidden.
- Although we have made the utmost effort to follow the revisions of the software and hardware, in some cases, unsynchronized matter may occur.
- The information in this document may be subject to change without notice.

1. Operating Environment

Item	Contents
Personal computer	A personal computer on which Microsoft® Windows® operates
CPU	Intel® Core™ 2 Duo Processor 2GHz or more
Required memory	64-bit OS: Recommended 2GB or more <p>32-bit OS: Recommended 1GB or more</p>
Available hard disk capacity	2GB or more
Monitor	Resolution 1024 x 768 pixels or higher
OS <p>(English version, Japanese version, Simplified Chinese version)</p>	<ul style="list-style-type: none">Windows 10 (Home, Pro, Enterprise, Education, IoT Enterprise 2016 LTSB¹) Windows 8.1, Windows 8.1 (Pro, Enterprise) Windows 8, Windows 8 (Pro, Enterprise) Windows 7 (Home Basic, Home Premium, Professional, Ultimate, Enterprise)

*1 64-bit version only

- If .NET Framework 2.0、.NET Framework 4.0 and Windows Installer 3.0 are not installed to thepersonal computer to which MI Configurator is to be installed, approximately 500MB of memory is required in the system drive to install them.
- For Windows 10, .NET Framework 3.5 (including .NET 2.0 and 3.0) or .NET Framework 4.6 Advanced Services needs to be enabled. Refer to either of the following documents.
 - LIJMI Configurator Operating Manual [SH-081938ENG]
 - TECHNICAL BULLETIN No. FA-A-0207.
- For Windows 8 and Windows 8.1, if .NET Framework 3.5 (including .NET 2.0 and 3.0) or .NET Framework 4.5 Advanced Services needs to be enabled. Refer to TECHNICAL BULLETIN No. FA-A-0153.
- For Windows 7, if .NET Framework 3.5 (including .NET 2.0 and 3.0) needs to be enabled.
- When the following functions are used, this product may not run properly.
 - Application start-up in Windows compatibility mode
 - Fast user switching
 - Remote desktop
 - Windows XP Mode
 - Touch function
 - Modern UI
 - Client Hyper-V
 - Tablet mode
 - Virtual Desktops
- In the following cases, the screen of this product may not work properly.
 - The size of the text and/or other items on the screen are changed to values other than default values (such as 96 DPI, 100%, and 9 pt). For details, refer to the following manual
 - LIJMI Configurator Operating Manual [SH-081938ENG]
 - The resolution of the screen is changed in operation.
 - Windows theme is changed in operation.
 - The multi-display is set.
- Use MI Configurator as a standard user or an administrator.
- If the Windows firewall setting is enabled, the "Find Module function" and "Direct connection function" may not operate correctly. Disable the Windows firewall setting.
- In this product, the period (.) is used as the symbol of the decimal point. Regardless of the setting of "Decimal symbol" on the control panel, use the period when enter the decimal point.

2. Installation

2.1 Confirm before installation.

- Log on to MELIPC or Personal computer as an administrator.
- Close all running applications before installation. If the product is installed while other applications are running, it may not operate normally.

2.2 Procedure

- Unzip the compressed folder.
- Double-click 'setup.exe' in the unzipped folder to start installation.
- Select or enter the necessary information by following the on-screen instructions.

2.3 Acknowledgements

- We do not guarantee those commercially available Microsoft Windows Operating System products that are introduced in this manual.
- This software's copyright is owned by Mitsubishi Electric Corporation.
- This product (including manual) can be used under the Software License Agreement only.
- We do not take any responsibilities for the consequences of operating this product (including manual).

3. Uninstallation

Uninstall MI Configurator from the control panel of Windows.

Intel is either a registered trademark or a trademark of Intel Corporation in the United States and/or other countries. Microsoft and Windows are trademarks of the Microsoft group of companies. The company names, system names and product names mentioned in this manual are either registered trademarks or trademarks of their respective companies. In some cases, trademark symbols such as "™" or "®" are not specified in this manual.

三菱電機株式会社

〒100-8310 東京都千代田区丸の内2-7-3 (東京ビル)

MITSUBISHI ELECTRIC CORPORATION

HEAD OFFICE: TOKYO BLDG. 2-7-3, MARUNOUCHI, CHYODOKU, TOKYO 100-8310, JAPAN
NAGOYA WORKS: 1-14, YADA-MINAMI 5-CHOME, HIGASHI-KU, NAGOYA 461-8670, JAPAN

SW1DNN-MICONF-O-INSTL-M