MELSOFT

#### GX Works3

# Installation Instructions

# Before Using the Product

Please read this document before use. Keep the document in a safe place for future reference. Make sure that the end users read the document.

For the precautions on using GX Works3, refer to the following:

GX Works3 Operating Manual [SH-081215ENG]

#### A Notice

- Reprinting or reproducing the part or all of the contents of this document in any form for any purpose without the permission of Mitsubishi Electric Corporation is strictly forbidden. Although we have made the utmost effort to follow the revisions of the software and
- hardware, in some cases, unsynchronized matter may occur.
- The information in this document may be subject to change without notice

# **Operating Environment**

ltem	Contents	
Personal computer	A personal computer on which Microsoft <sup>®</sup> Windows <sup>®</sup> operates	
CPU <sup>*1</sup>	Windows 11	2 or more cores on a compatible 64-bit processor or System on a Chip (SoC)
	Windows 10	Intel <sup>®</sup> Core <sup>™</sup> 2 Duo Processor 2 GHz or more recommended
Required memory*1	Windows 11	Recommended 4 GB or more
	Windows 10	64-bit OS: Recommended 2 GB or more 32-bit OS: Recommended 1 GB or more
Available hard disk capacity	For installation: 22 GB or more free hard disk capacity For operation: 512 MB or more free virtual memory capacity	
Monitor	Resolution 1024 × 768 pixels or higher	
.NET Framework <sup>*2</sup>	Microsoft .NET Framework 4.8 or later	
OS (English version)	Windows 11 (Home, Pro, Enterprise, Education)     Windows 10 version 1607 or later(Home, Pro, Enterprise, Education, IoT     Enterprise 2016 LTSB <sup>*3</sup> , IoT Enterprise 2019 LTSC <sup>*3</sup> )	
Communication interface (When a CPU module is directly connected)	USB port, Ethernet port	

\*1 For a project including 20,000 or more labels, a 64-bit operating system with Intel Core i7 processor and 8 GB or more memory is recommended. \*2 If .NET Framework 4.8 is not installed, approximately 500 MB of memory is required in the system drive to

install it. \*3 64-bit version only

 Use GX Works3 as a standard user or an administrator.
 For Windows 11 and Windows 10, .NET Framework 3.5 (including .NET 2.0 and 3.0) or .NET Framework 4.8 Advanced Services needs to be enabled. For details, refer to TECHNICAL BULLETIN No. FA-A-0207.

When the following functions are used, this product may not run properly.
 Application start-up in Windows compatibility mode

- Fast user switching
- Remote desktop
- Touch function
- Virtual environment such as Client Hyper-V
- Tablet mode
- Virtual Desktops Unified Write Filter
- Text cursor indicator
- · In the following cases, the screen of this product may not work properly
  - The size of the text and other items in the screen is other than 100% (96 DPI, 9 pt etc.).
    - For details, refer to the following:
    - GX Works3 Operating Manual [SH-081215ENG]
    - · The resolution of the screen is changed in operation
    - The Windows theme is changed in operation.
  - The multi-display is set.
- · If the Windows firewall setting is enabled, the 'module search function' and 'direct connection function' may not run correctly. Disable the Windows firewall setting. • In this product, the period (.) is used as the symbol of the decimal point. Regardless of the
- setting of "Decimal symbol" on the control panel, use the period when enter the decimal point

# Installation

#### ■ Confirm before installation

- · Log on to the personal computer as an administrator. Close all running applications before installation. If the product is installed while other
- applications are running, it may not operate normally. Install this product to a folder to which the administrator authority is given. The default installation folder is recommended to enhance the security

#### ■ Procedure

- 1. Insert the GX Works3 DVD to the DVD drive. Double-click "setup.exe" in the Disk1 folder on the DVD.
- 2. Select or enter the necessary information by following the on-screen instructions.\*1
- \*1 Product ID is written on 'License certificate' included with the product. Enter the 12-digit number divided into 3 and 9 digits

### Packing List

Model name	Product name	Quantity
SW1DND-GXW3-EC (English version package)	GX Works3 DVD	1
	Installation Instructions (This document)	1
(Site license product)	End-user software license agreement	1
	Software registration notice	1
	License certificate	1

#### Applications on the DVD

Application	Storage location of "setup.exe"
GX Works3 <sup>*1</sup>	Disk1\GXW3
PX Developer*2	Disk1\FBDQ
CPU Module Logging Configuration Tool	Disk1\LLUTL
GX LogViewer	Disk1\VIEWER
GX VideoViewer <sup>*3</sup>	Disk1\REPROA
GX Works2	Disk2
GX Works2 Help (for FXCPU)	Disk3\DocFX

\*1 When GX Works3 is installed, MR Configurator2 is installed automatically

- \*2 Cannot be installed together with GX Works3. Double-click the "setup.exe" of each product to install it individually.
- \*3 Can be installed only on a personal computer with Windows 10 version 1703 or later

#### Acknowledgements

- We do not guarantee those commercially available Microsoft Windows Operating System
  products that are introduced in this manual.
- This software's copyright is owned by Mitsubishi Electric Corporation.
  This product (including manual) can be used under the software license agreement only.
- · We do not take any responsibilities for the consequences of operating this product (including manual).

# Uninstallation

Uninstall GX Works3 from the control panel of Windows.

# Installation of a USB driver

In order to communicate with a CPU module via USB, a USB driver needs to be installed. When a CPU module can not communicate via USB, refer to the following manual to install a USB drive

GX Works3 Operating Manual [SH-081215ENG]

Microsoft and Windows are trademarks of the Microsoft group of companies. Intel is either a registered trademark or a trademark of Intel Corporation in the United States and/or other countries.

The company names, system names and product names mentioned in this manual are either registered trademarks or trademarks of their respective companies

In some cases, trademark symbols such as "<sup>TM</sup> or <sup>(®)</sup> are not specified in this manual