

CW Configurator

Installation Instructions

Before Using the Product

Before using the product, please read this document. Make sure that the end users read this document and then keep the document in a safe place for future reference.

For the precautions on using CW Configurator, refer to the following manual.

[CW Configurator Operating Manual \[SH-081382ENG\]](#)

Notice

- Reprinting or reproducing the part or all of the contents of this document in any form for any purpose without the permission of Mitsubishi Electric Corporation is strictly forbidden.
- Although we have made the utmost effort to follow the revisions of the software and hardware, in some cases, unsynchronized matter may occur.
- The information in this document may be subject to change without notice.

Operating Environment

Item	Contents	
Personal computer	A personal computer on which Microsoft® Windows® operates	
CPU	Windows 11	2 or more cores on a compatible 64-bit processor or System on a Chip (SoC)
	Windows 10	Intel® Core™ 2 Duo Processor 2GHz or more
Required memory	Windows 11	Recommended 4 GB or more
	Windows 10	64-bit OS: Recommended 2GB or more 32-bit OS: Recommended 1GB or more
Available hard disk capacity	For installation: 5GB or more free hard disk capacity For operation: 512MB or more free virtual memory capacity	
Monitor	Resolution 1024 × 768 pixels or higher	
OS (English version)	<ul style="list-style-type: none"> • Windows 11 (Home, Pro, Enterprise, Education) • Windows 10 (Home, Pro, Enterprise, Education, IoT Enterprise 2016 LTSC^{*1}, IoT Enterprise LTSC 2019^{*1}) 	
Communication interface (When a CPU module is directly connected.)	Ethernet port	

*1 64-bit version only

- Use CW Configurator as a standard user or an administrator.
- If .NET Framework 4.0 is not installed to the personal computer to which CW Configurator is to be installed, approximately 500MB of memory is required in the system drive to install it.
- For Windows 10 and Windows 11, .NET Framework 3.5 (including .NET 2.0 and 3.0) or .NETFramework 4.8 Advanced Services needs to be enabled. For details, refer to TECHNICALBULLETIN No. FA-A-0207.
- When the following functions are used, this product may not run properly.
 - Application start-up in Windows compatibility mode
 - Fast user switching
 - Remote desktop
 - Touch function
 - Virtual environment such as Client Hyper-V
 - Tablet mode
 - Virtual Desktops
 - Unified Write Filter
 - Text cursor indicator
- In the following cases, the screen of this product may not work properly.
 - The size of the text and other items on the screen is other than 100% (96 DPI, 9 pt etc.).
For details, refer to the following manual.
[CW Configurator Operating Manual \[SH-081382ENG\]](#)
 - The resolution of the screen is changed in operation.
 - Windows theme is changed in operation.
 - The multi-display is set.
- If the Windows firewall setting is enabled, the "Find Module function" and "Direct connection function" may not operate correctly. Disable the Windows firewall setting.
- In this product, the period (.) is used as the symbol of the decimal point. Regardless of the setting of "Decimal symbol" on the control panel, use the period when enter the decimal point.

Installation

Confirm before installation

- Log on to the personal computer as a user having the Administrator authority.
- Close all running applications before installation. If the product is installed while other applications are running, it may not operate normally.

Procedure

1. Insert the CW Configurator DVD to the DVD drive. Double-click "setup.exe" in the Disk1 folder on the DVD.
 2. Select or enter the necessary information by following the on-screen instructions.*1
- *1 Product ID is written on the "License certificate" included with the product. Enter the 12-digit number divided into 3 and 9 digits.

Product Makeup

Model name	Product name	Quantity
SW1DND-RCCPU-E (English version package)	CW Configurator DVD	1
	Installation Instructions (This document)	1
	End-user software license agreement	1
	License certificate	1

Applications on the DVD

Application	Storage location of "setup.exe"
CW Configurator	Disk1 folder

Acknowledgements

- We do not guarantee those commercially available Microsoft Windows Operating System products that are introduced in this manual.
- This software's copyright is owned by Mitsubishi Electric Corporation.
- This product (including manual) can be used under the Software License Agreement only.
- We do not take any responsibilities for the consequences of operating this product (including manual).

Uninstallation

Uninstall CW Configurator from the control panel of Windows.

Microsoft, and Windows are trademarks of the Microsoft group of companies.
Intel is either registered trademarks or trademarks of Intel Corporation in the United States and/or other countries.
The company names, system names and product names mentioned in this manual are either registered trademarks or trademarks of their respective companies.
In some cases, trademark symbols such as ® or ™, are not specified in this manual.