

Before Using the Product

Before using the product, please read this manual. Make sure that the end users read this manual and then keep the manual in a safe place for future reference.

This product is a cover for an AD75CK cable clamp. The MELSEC iQ-R series system using an AD75CK cable clamp will be compliant with ship classification standards by attaching this cover.

Relevant manuals

Before using the product, please read the Safety Guidelines included with the base unit used, especially the following sections.

- SAFETY PRECAUTIONS
- CONDITIONS OF USE FOR THE PRODUCT
- EMC AND LOW VOLTAGE DIRECTIVES
- WARRANTY

Manuels correspondants

Avant d'utiliser ce produit, prière de lire les "Safety Guidelines" (directive de sécurité) fournies avec l'unité de base, en particulier dans les sections suivantes.

- PRÉCAUTIONS DE SÉCURITÉ
- CONDITIONS D'UTILISATION DE PRODUIT
- DIRECTIVES CEM ET BASSE TENSION
- GARANTIE

Packing list

Check that the following items are included in the package of the product.

| Item | Quantity |
|---|----------|
| Ship classification compliant cable clamp cover | 4 |
| Before Using the Product (this manual) | 1 |

Operating ambient temperature

Use the product within the following range.

- 0 to 55°C (when an extended temperature range base unit is not used)
- 0 to 60°C (when an extended temperature range base unit is used)


Température ambiante de fonctionnement

Ce produit doit être utilisé dans les conditions suivantes.


- 0 et 55°C (quand une unité de base à gamme de température élargie n'est pas utilisée)
- 0 et 60°C (quand une unité de base à gamme de température élargie est utilisée)

Handling precautions

- To attach/remove a cover to/from an AD75CK cable clamp, keep a distance of 20mm or more between the cable clamp and the walls. (A distance of 10mm or more is required between the cover and the walls.)




- Wire the ground terminal with the AD75CK cable clamp and cables parallel so that the cable clamp cover is mounted.
- Wire the cables so that they do not sag by their own weight and damage the cable clamp cover.



Cable clamp cover

- Wire the cables so that the braided shield part of cables fixed by the AD75CK cable clamp is brought within the cable clamp cover.




Braided shield

Attachment/removal procedure

(a) Attaching a cover


Mount a cover to an AD75CK cable clamp in the direction of the arrow, and push it until it clicks.



(b) Removing a cover


① Pull the hook of the cover outward with your fingers.

② Pull the cover forward.



External dimensions

- When attached to an AD75CK cable clamp



(Unit: mm)

Information and services

For further information and services, please consult your local Mitsubishi representative.