


MX Sheet Version 3

Installation Instructions

Before Using the Product

Please read this document before use. Keep the document in a safe place for future reference. Make sure that the end users read the document.

For the precautions on using MX Sheet, refer to the following manual.

 MX Sheet Version 3 Operating Manual [SH-082390EN]

Notice

- Reprinting or reproducing the part or all of the contents of this document in any form for any purpose without the permission of Mitsubishi Electric Corporation is strictly forbidden.
- Although we have made the utmost effort to follow the revisions of the software and hardware, in some cases, unsynchronized matter may occur.
- The information in this document may be subject to change without notice.

Operating Environment

Item	Contents	
Personal computer	A personal computer on which Microsoft® Windows® operates	
CPU	Windows 11	2 or more cores on a compatible 64-bit processor or System on a Chip (SoC)
	Windows 10	Processor 1.6 GHz with 2 or more cores
Required memory	Windows 11	Recommended 4 GB or more
	Windows 10	Recommended 2 GB or more
Available hard disk capacity	For installation: 2.5 GB or more free hard disk capacity ^{*1} For operation: 512 MB or more free virtual memory capacity	
Monitor	Windows 11	Resolution WXGA (1280 × 720 pixels) or higher
	Windows 10	Resolution 1024 × 768 pixels or higher
OS (English version) (32-bit/64-bit)	<ul style="list-style-type: none"> • Windows 11 (Home, Pro, Enterprise, Education)^{*2} • Windows 10 (Home, Pro, Enterprise, Education, IoT Enterprise 2016 LTSB^{*2}, IoT Enterprise 2019 LTSC^{*2}) 	
Required software (English version) (32-bit/64-bit)	<ul style="list-style-type: none"> • Microsoft Excel® 2019^{*3} • Microsoft Excel 2021^{*3,4} • Microsoft Excel for Microsoft 365^{*2,5} • MX Component Version 5 	

*1 This includes the required free space for installation of MX Component.

*2 64-bit version only

*3 Desktop version only

*4 The operation of this product has been confirmed with the version 2206 (Build 15330.20196).

*5 The operation of this product has been confirmed with the version 2201 (Build 14827.20192).

- .NET Framework 4.6 Advanced Services and .NET Framework 4.8 Advanced Services need to be enabled. For details, refer to TECHNICAL BULLETIN No. FA-A-0207.
- When the following functions are used, this product may not run properly.
 - Application start-up in Windows compatibility mode
 - Fast user switching
 - Remote desktop
 - Touch function
 - Virtual environment such as Client Hyper-V
 - Tablet mode
 - Virtual Desktops
 - Windows Hibernate and Standby
 - Unified Write Filter
 - Text cursor indicator
- In the following cases, the screen of this product may not work properly.
 - The size of the text and other items on the screen is other than 100% (96 DPI, 9 pt etc.).
 - The resolution of the screen is changed in operation.
 - Windows theme is changed in operation.
 - The multi-display is set.
- Excel spreadsheets created in the English environment are applicable to the English environment only. They cannot be used in the other environment.
- In this product, the period (.) is used as the symbol of the decimal point. Regardless of the setting of "Decimal symbol" on the control panel, use the period when entering the decimal point.
- A communication error may occur when communicating with the programmable controller CPU after setting the resume function, suspend setting, power-saving function, and/or standby mode of the personal computer. Therefore, when communicating with the programmable controller CPU, do not set the above functions.
- Surrogate pair characters and environment dependent characters are not available in MX Sheet.

Installation

Confirm before installation

- Log on to the personal computer as an administrator.
- Close all running applications before installation. If the product is installed while other applications are running, it may not operate normally.
- Install this product to a folder to which the administrator authority is given. The default installation folder is recommended to enhance the security.


Procedure

1. Insert the MX Sheet DVD to the DVD drive. Double-click "setup.exe" on the DVD.
2. Select or enter the necessary information by following the on-screen instructions.*1

*1 Product ID is written on the "License certificate" included with the product. Enter the 12-digit number divided into 3 and 9 digits.

Acknowledgements

When starting Excel for the first time after installing MX Sheet, the following screens may appear. If the screens appear, click the [Install] button.



Packing List

Model name	Product name	Quantity
SW3DND-SHEET-E (English version package) (Standard license product)	MX Sheet DVD	1
	Installation Instructions (This document)	1
	License certificate	1
	Software registration notice	1
	End-user software license agreement	1
SW3DND-SHEET-EA (English version package) (Volume license product)	MX Sheet DVD	1
	Installation Instructions (This document)	1
	License certificate	n ^{*1}
	Software registration notice	1
	End-user software license agreement	1
SW3DND-SHEET-EAZ (English version package) (Additional license product)	License certificate	n ^{*1}
	Software registration notice	1
	End-user software license agreement	1
	MX Sheet DVD	1
SW3DND-SHEETSET-E (English version package) (Set product)	MX Component DVD	1
	Installation Instructions	2 ^{*2}
	License certificate	2 ^{*2}
	Software registration notice	2 ^{*2}
	End-user software license agreement	1

*1 Number of licenses

*2 One each for MX Sheet and MX Component

Acknowledgements

- We do not guarantee those commercially available Microsoft Windows Operating System products that are introduced in this manual.
- This software's copyright is owned by Mitsubishi Electric Corporation.
- This product (including manual) can be used under the Software License Agreement only.
- We do not take any responsibilities for the consequences of operating this product (including manual).

Uninstallation

Uninstall MX Sheet from the control panel of Windows.

Microsoft, Windows, and Excel are trademarks of the Microsoft group of companies. The company names, system names and product names mentioned in this manual are either registered trademarks or trademarks of their respective companies. In some cases, trademark symbols such as [™] or [®] are not specified in this manual. The screens (screenshots) are used in accordance with the Microsoft Corporation guideline.