

FACTORY AUTOMATION

NUMERICAL CONTROL (CNC) E80 Series













Our Factory Automation business is focused on "Automating the World" to make it a better, more sustainable environment supporting manufacturing and society, celebrating diversity and contributing towards an active and fulfilling role.

Mitsubishi Electric is involved in many areas including the following:

Energy and Electric Systems

A wide range of power and electrical products from generators to large-scale displays.

Electronic Devices

A wide portfolio of cutting-edge semiconductor devices for systems and products.

Home Appliance

Dependable consumer products like air conditioners and home entertainment systems.

Information and Communication Systems

Commercial and consumer-centric equipment, products and systems.

Industrial Automation Systems

Maximizing productivity and efficiency with cutting-edge automation technology.



The Mitsubishi Electric Group is actively solving social issues, such as decarbonization and labor shortages, by providing production sites with energy-saving equipment and solutions that utilize automation systems, thereby helping towards a sustainable society.


OVERVIEW

E80 Series	03
CNC SYSTEM CONFIGURATIONS	04
LATHE SYSTEM	05
MACHINING CENTER SYSTEM	07
FACTORY-WIDE OPTIMIZATION	09
SPECIFICATIONS	10
DRIVE SYSTEM	11
SOFTWARE TOOLS	13
GLOBAL SALES & SERVICE NETWORK	15
WARRANTY	17

E80 Series


The CNC E80 Series boasts drastic improvements in performance and a higher accuracy than ever before.

The simple and easy-to-use E80 Series helps in achieving a greater cost performance, and fits best with simple machine configurations.




Drastic improvements in performance CNC-dedicated CPU

With Mitsubishi Electric's high-speed CNC-dedicated CPU, the E80 Series reduces cycle times due to a higher program and PLC processing capability. Higher optical communication speeds between the CNC and drive acheive higher accuracy in machining



Models for various machine configurations TypeA/TypeB


TypeA and TypeB models are available for both machining centers and lathes. Select the model with the specifications that suit the machine configuration best.




Leading design Display Units and Keyboards


The E80 Series adopts the M800/M80 Series design. The display unit and keyboard are only 9.5 mm thick, and their flat profile opens up new possibilities for machine design. There are 2 types of keyboard layouts, one for lathes and the other for milling.

CNC SYSTEM CONFIGURATIONS



ENHANCED LATHE SYSTEM






Pursuing usability The Simple Monitor Screen


The simple monitor screen puts all the essential information for mass production on one screen, making it simple to find information immediately.

Information such as the selected tool and the remaining lifetime can be checked by viewing the tool icon




Reduce setup time Workpiece Coordinate System Shift

The same machining program can be used when the workpiece coordinate system does not match the actual workpiece coordinate system, or when the actual workpiece length is different. This function helps to create machining programs easier.




Improved machining accuracy High-accuracy Control


E80 Series high-accuracy control minimizes deviation of the actual tool path from the command path, improving the accuracy of the machining of corners and arcs.



Flexible commands Diameter/Radius Designation Switch

Flexible commands allow the user to switch between diameter/radius designation for each axis with the G-code at any time. Flexible commands are particularly useful for programs where turning and milling coexist.






Applicable to a wide array of machine specifications Synchronous Tapping with Analog I/F Spindle and Spindle Control with Pulse Train Output

Synchronous tapping can be performed with an analog-connected spindle such as an inverter without using a dedicated tool holder. The applicability to a wide array of machine specifications allows for more efficient machining. Higher accuracy can be achieved by connection of a pulse command inverter. (Spindle control with pulse train output)


Easier program creation Interactive Cycle Insertion

Create a machining program automatically simply by inserting a machining shape in a selected machining cycle. Interactive cycle insertion enables the user to create programs intuitively while referring to drawings on the screen, reducing the time required for program creation compared with G-code input



Easier program creation Finish Shape View Programming

The finished shape is displayed in 3D while creating a machining program. Checking the finished shape in real-time during program creation allows the user to correct mistakes as they appear in the finished shape.



Easier program creation Program Check Operation

Check the machining program while viewing the actual operation of the machine. Also, forward run/reverse run operation can be checked meticulously at a desired feedrate (manual handle feed), making prototype checks more accurate and easier than before.





Program finalization 3D Solid Program Check

3D solid program check allows the user to check a finalized machining program against the 3D graphic of the final shape for the program.

Being able to perform a detailed check of the final shape before production on the actual machine is a major advantage.

ENHANCED MACHINING CENTER SYSTEM





Pursuing usability The Simple Monitor Screen


The simple monitor screen puts all the essential information for mass production on one screen, and is easy to view from distance.

The screen configurations (simple/normal), and the types of counters being displayed can be changed using the screen menu, making the customization of displays easier than before.




Reduce setup time Workpiece Position Measurement

The coordinate points can be measured on the workpiece measurement screen, and values automatically calculated from the measured coordinates are set. Manual measurements using jigs or dial gauges are no longer necessary.



Applicable to a wide array of machine specifications Synchronous Tapping with Analog I/F Spindle and Spindle Control with Pulse Train Output

Synchronous tapping can be performed with an analog-connected spindle such as an inverter without using a dedicated tool holder. The applicability to a wide array of machine specifications allows for more efficient machining. Higher accuracy can be achieved by connection of a pulse command inverter. (Spindle control with pulse train output)




Standard model Position control Position contr

Applicable to a wide array of machine specifications Multiple-axis Synchronization Control

This function enables the synchronous control of multiple Z axes. Synchronizing multiple axes enables the controlling of machines that perform the same operation over multiple axes such as multi-head machines. The tool length for each Z axis can be compensated individually, and it improves machining accuracy.

Contribute to high-accuracy machining OMR-FF Control

OMR-FF control adjusts the optimal position loop gain for each axis, leading to smoother and more accurate machining.




Contribute to high-quality machining eSSS Control¹¹

When the tool passes through the corner portion at high acceleration and high speed, eSSS control determines the machining shape comprehensively, suppresses excessive feedrate change and vibration, and smoothens the operation.

This ensures consistent high-quality machining which is not affected by the quality of machining programs.

*1 The control process of this function is equivalent to "SSS Control" (Super Smooth Surface Control) of the M800/M80 Series. Some of the relevant parameters are fixed for this function, however, "SSS Control" can be used by making some simple settings.




Easy operation, high quality Tolerance Control

This function obtains the optimum clamp speed for corners or curves based on the designated tolerance to perform operations. It also ensures smooth passing in corner sections within the tolerance range, which suppresses machine vibrations. The cycle time is reduced because the clamp speed can be increased to a higher speed than

Simply set the amount of tolerance, and the machine operates at the optimal speed and tool path, making it easy to achieve a high-quality machined surface.


FACTORY-WIDE OPTIMIZATION



NC Machine Tool Optimizer visualizes the status of various equipment in multiple factories

NC Machine Tool Optimizer is a software product that collects operation data from NC machine tools and peripherals to support the visualization and analysis of operational status. Besides being connected with controllers (of various makers, of various models) on the shop floor, it can monitor and analyze the operation of equipment in multiple factories, helping to increase productivity.


* Connection with Mitsubishi Electric CNC (old models) and third-party controllers is supported.



Remote confirmation of machine status Email Notification to Operator

This sends you an e-mail about machine condition automatically at the specified timing to a computer, tablet or smartphone. No dedicated line is needed, so you can set up easily.

Machine condition can be monitored at anytime, anywhere. This helps you to deal with emergent situations timely, leading to shorter downtime and higher productivity.



Wider compatibility with peripheral devices Connection to Various of Field Networks

By inserting an optional card in the slot on the back of the display unit, CNC can support CC-Link (master/local), PROFIBUS-DP (master), CC-Link IE Field (Master/Local), EtherNet/IP, FL-net, and CC-Link IE Field Basic connections, making it possible to connect with many peripheral devices through a wide range of field networks.

SPECIFICATIONS

		E80 Series			
		Lathe system Machining center system			
		ТуреА	ТуреВ	ТуреА	ТуреВ
Number of control axes	Max. number of axes (NC axes + Spindles + PLC axes)	8	6	6	4
	Max. number of NC axes (in total for all part systems)	5	4	5 (*1)	3
	Max. number of spindles	3	3	1	1
	Max. number of PLC axes	3	3	2	0
	Number of simultaneous contouring control axes	4	4	4	3
Max. number of part systems		○1	○1	○1	O 1
Display unit-side High-speed program server mode		0	0	0	0
Front-side SD card mode		0	0	0	0
Least command increment		0.1µm	0.1µm	0.1µm	1µm
Least control increment		1nm	1nm	1nm	1nm
Program memory capacity	(number of programs stored)	230KB [600m] (400 programs)	230KB [600m] (400 programs)	500KB [1280m] (1000programs)	500KB [1280m] (1000programs)
Max. number of tool offset	sets	99 sets	99 sets	200 sets	99 sets
Built-in PLC capacity [number	per of steps]	○20000	○20000	○20000	○20000
Multi-program [number of p	programs]	○60	○60	○60	<u></u> 60
Multi-project [number of pr	ojects stored]	<u></u>	○2	○2	○2
Macro program Variable co		600 sets	200 sets	600 sets	200 sets
Machine tool builder macro			0	0	0
Workpiece coordinate syste	em shift		0	-	-
3D solid program check				0	0
	n (program check operation)	0	0	-	-
Interactive cycle insertion	u		0	0	0
Diameter/Radius designation	on switch	0	0	-	-
Synchronous tapping with a			0	0	0
Spindle control with pulse t		0	0	0	0
Workpiece position measur	•	_	-	0	0
PLC skip		0	0	0	0
Torque limitation skip			0	0	0
Simple inclined surface ma	chining command		_	0	-
High-accuracy control (G61			0	0	
eSSS control			0	0	_
Tolerance control			0	0	_
OMR-FF			0	0	0
					0
Spindle-mode servo motor Finish shape view programi		0	0	-	-
	•	0	0		
Email notification to operat		0	0	0	0
Operation history (detailed BiSS encoder I/F	анатт пізногу інтогніаціоп)	0	0	0	0
		0	0	0	0
CC-Link (Master/Local)					
PROFIBUS-DP (Master)					
CC-Link IE Field (Master/Local)					
EtherNet/IP					
FL-net					
CC-Link IE Field Basic					
MES interface library		0	0	0	0
EcoMonitorLight connection	n	0	0	0	0
System lock		0	0	0	0

^(*1) Up to one rotary axis

Ethernet is a registered trademark of Xerox Corporation in the United States and/or other countries.

Microsoft® and Windows® are either trademarks or registered trademarks of Microsoft Corporation in the United States and/or other countries.

SD logo and SDHC logo are either registered trademarks or trademarks of LLC.

PROFIBUS-DP is a trademark of Profibus International

Other company and product names that appear in this manual are trademarks or registered trademarks of the respective companies.

^{*} Trademark

MELSEC, CC-Link, CC-Link/LT and CC-Link IE are either trademarks or registered trademarks of Mitsubishi Electric Corporation in Japan and/or other countries.

DRIVE SYSTEM

Drive units



High-performance Servo/ Spindle Drive Units MDS-E/EH Series

- •The servo control-dedicated core processor realizes improved control speed, leading to enhanced basic performance. When combined with a higher resolution motor sensor and enhanced high-speed optical communication, this drive contributes to high-speed, high-accuracy control. •The motor power connector is
- equipped with an anti-misinsertion mechanism. This helps to eliminate connection errors.
- Improved diagnostic and preventive maintenance features
- •Safe Torque Off (STO) and Safe Brake Control (SBC) are also incorporated as additional safety



Multi-hybrid **Drive Units** MDS-EM/EMH Series

- •Multi-hybrid drive units are capable of driving a maximum of three servo axes and one spindle. This contributes to downsizing machines and offers technical advantages.
- •The motor power connector is equipped with an anti-misinsertion mechanism. This helps to eliminate connection errors. •Safe Torque Off (STO) and Safe
- Brake Control (SBC) are also incorporated as additional safety features •The fan unit facilitates fan exchange. •An MDS-EMH drive unit is available

for 400V systems.



All-in-one **Compact Drive Units** MDS-EJ/EJH Series

- •Ultra-compact drive units with built-in power supply contribute to smaller control panel size.
- •A 2-axis type has been added for further downsizing.
- •The servo control-dedicated core processor realizes improved control speed, leading to improved basic performance. When combined with a higher resolution motor sensor and enhanced high-speed optical communication, this drive contributes to high-speed, high-accuracy control. ·Safe Torque Off (STO) and Safe
- Brake Control (SBC) are also incorporated as additional safety •An MDS-EJH drive unit is available

for 400V systems. (Note 1)



PWM Converter MDS-EX-CVP Series

- Products of the PWM converter series which provides a stabilizing DC voltage function and boost function. The MDS-EX-CVP Series reduces the output deceleration of the spindle motor and improves output in the high-speed range.
- •Available for 400V system power supply units only.

Servo motors



Medium-inertia. High-accuracy. **High-speed Motors HK Series**

- ·Latest servo motor to help increase productivity.
- •Range: 0.5 to 7 [kW] •Maximum rotation speed:
- 2,000 to 6,000 [r/min] •High power density design has improved motor efficiency.
- One-touch lock of the power connector for easy mounting (Note 2). Battery-free encoder helps reduce maintenance costs.



Medium-inertia. High-accuracy. **High-speed Motors HG Series**

- ·Sensor resolution has been significantly improved. These servo motors, which boast smooth rotation and outstanding acceleration capabilities, are well-suited as feed axes of machine tools.
- •Range: 0.2 to 11 [kW] •Maximum rotation speed:
- 2,000 to 6,000 [r/min]
- •Safety support sensors are included as standard specification. Three sensor resolutions (i.e., 1, 4 or 67
- million pulses/rev) are available. •These motors can also be used as a tool spindle motor.
- •The small-sized connector allows horizontal cable connection to save space in machines. (Note 3)



Linear **Servo Motors** LM-F Series

- •These motors can be used in clean environments, since no ball screws are used, eliminating possible grease contamination.
- •Elimination of transmission mechanisms, including backlash, enables smooth, quiet operation even at high speeds.
- Maximum thrust: 900 to 18,000 [N·m]



Direct-drive Servo Motors TM-RB Series

- •High-torque, direct-drive motors combined with high-gain control provide quick acceleration and positioning, making rotation
- •Suitable for rotary axes that drive tables or spindle heads
- Maximum torque: 36 to 1,280 [N·m]

Spindle motors



High-performance **Spindle Motors** SJ-D Series

- •Motor energy loss has been significantly reduced by optimizing the magnetic circuit.
- ·High-speed bearings are incorporated as a standard feature, helping to achieve higher speed, lower vibration and improved durability.
- •Range: 3.7 to 26 [kW]
- •Maximum rotation speed: 8,000 to 12,000 [r/min]

High-output, High-speed **Spindle Motors SJ-DG Series**

- •The addition of S3 rating (%ED rating) has improved output and torque acceleration/deceleration characteristics
- •A balance adjustment ring added to the counter-load side allows for fine tuning.
- S3 rating: 5.5 to 15 [kW]
- •Maximum rotation speed: 10,000 to 12,000 [r/min]

High-torque **Spindle Motors SJ-DN Series**

- •Higher torque characteristics than those of the SJ-D Series with the same output. This series can be driven with a small-capacity multi-hybrid drive
- Suitable for heavy cutting. Helps to improve productivity. •Range: 7.5 to 18.5 [kW]

•Maximum rotation speed: 8,000 [r/min]

Spindle Motors SJ-DL Series

Low-inertia, High-speed

- •This series of spindle motors is dedicated for use in tapping machines that require faster drilling and tapping.
- •The latest design technologies make it possible to attain lower vibration and greater rigidity even with
- •Range: 0.75 to 7.5 [kW]
- •Maximum rotation speed: 10,000 to 24,000 [r/min]

Compact, Lightweight **Spindle Motors SJ-DJ Series**

- •Spindle motors that are smaller and lighter than the SJ-D Series with the same output. This helps to further downsize machines.
- •Range: 5.5 to 15 [kW]
- •Maximum rotation speed: 8,000 to 12,000 [r/min]

High-output High-torque IPM Spindle Motors SJ-DM Series

- •The use of magnets allows for higher output and torque, leading to reduced cycle time.
- •The SJ-DM Series can provide torque characteristics comparable to the former SJ-D Series of the next frame number
- •Maximum rotation speed: 12,000 [r/min]



Built-in **Spindle Motors** SJ-BG Series

•The electrical design has been optimized to increase the continuous rated torque per unit volume, contributing to downsizing spindle units. Options for mold and cooling jacket specifications




Tool Spindle Motors HG-JR Series

- Compact tool spindle motors are designed to have the small, high-output characteristics of servo motors yet offer high-speed rotation (8,000r/min). These motors contribute to downsizing spindle size, like rotary tool spindles. •Range: 0.75 to 1.5 [kW]
- •Maximum rotation speed: 8,000 [r/min]
- •Small-sized connector allows horizontal cable connection to save space in machines. (Note 3)


(Note 1) For servo motors only (Note 2) Available only for flange sizes 90SQ., 130SQ. and 176SQ. (Note 3) Options supported (Flange size 90SQ only) * Use Mitsubishi Electric CNC's dedicated drive unit and motor

SOFTWARE TOOLS


Process flow from machine design and development to operation and maintenance




Machine design



•Electrical circuitry design



Machine assembly and adjustment




[NC Configurator2]

NC parameters required for NC control or machine operation can be edited on a computer. It is also possible to create initial parameters simply by inputting the machine configuration.



For details on each software tool, refer to the software tools catalog (BNP-A1246).

Machine assembly and adjustment




(NC Analyzer2)



Servo parameters can be adjusted automatically by measuring and analyzing machine characteristics. Measurement and analysis can be done by running a servo motor using the machining program for adjustment, or using the vibration signal. This function can sample various types of data.

Operation and maintenance



(NC Trainer2)



NC Trainer2 plus supports customization development; it helps to program the ladder programming of the user PLC to be developed by machine tool builders and debug it and check the operations of customized screens.

(NC Explorer)




CNC machining data can be managed using Windows® Explorer on a computer when the computer is connected to multiple CNCs via Ethernet.

[NC Monitor2]



Taking advantage of connection with a factory network, CNC operation status can be monitored from remote locations. Several CNCs can be connected and monitored simultaneously.


Application development support



Mitsubishi Electric CNC Communication Software (FCSB1224W000)]

This software provides a bunch of API functions. They facilitate development of an Windows application which requires connection and communication with Mitsubishi Electric CNC(1). You can use the common interfaces for any Mitsubishi Electric CNC model, which leads to high efficiency in development.

(*) The compatible model is Mitsubishi Electric CNCs after M700/M70.



GLOBAL SALES Qο **SERVICE NETWORK**

GLOBAL SALES & SERVICE NETWORK

MITSUBISHI ELECTRIC AUTOMATION INC. (AMERICA FA CENTER) **HQ and Central Region Service Center (Chicago)**

500 CORPORATE WOODS PARKWAY, VERNON HILLS, ILLINOIS 60061,U.S.A.

- TEL: +1-847-478-2500 / FAX: +1-847-478-2650 · Minneapolis, MN Service Satellite
- Detroit, MI Service Satellite
- Grand Rapids, MI Service Satellite
- · Cleveland, OH Service Satellite
- . St. Louis, MO Service Satellite · Indianapolis, IN Service Saltellit

South/East Region Service Center (Georgia)

1845 SATELLITE BOULEVARD STE. 450, DULUTH, GEORGIA 30097, U.S.A. TEL +1-678-258-4529 / FAX +1-678-258-4519

- · Charleston, SC Service Satellite
- . Charlotte, NC Service Satellite
- Raleigh, NC Service Satellite Dallas, TX Service Satellite
- Houston, TX Service Satellite . Hartford, CT Service Satellite
- . Knoxville, TN Service Satellite
- Nashville, TN Service Satellite
- · Huntsville, AL Satallite
- Pittsburg, PA Service Satellite
- Tampa, Fl. Service Satellite
- Miami, FL Satelite · Lafayette, LA Service Satellite
- Allentown, PA Satelite

Western Region Service Center (California)

5900-B KATELLA AVE. - 5900-A KATELLA AVE. CYPRESS, CALIFORNIA 90630,

TEL: +1-714-699-2625 / FAX: +1-847-478-2650

- · San Francisco, CA Satelite · Seattle, WA Service Satellite
- · Denver, CO Service Satellite

Canada Region Service Center (Toronto)

4299 14TH AVENUE MARKHAM, ONTARIO I 3R O.I.2, CANADA

TEL: +1-905-475-7728 / FAX: +1-905-475-7935

- · Montreal, QC Service Satellite

Mexico Region Service Center (Queretaro)

Parque Tecnológico Innovación Querétaro, Lateral Carretera Estatal 431, Km 2+200, Lote 91 Modulos 1 y 2 Hacienda la Machorra, CP 76246, El Marqués, Querétaro, México

TEL: +52-442-153-6050

- Monterrey, NL Service Satellite
- . Mexico City, DF Service Satellite

MITSUBISHI ELECTRIC DO BRASIL COMÉRCIO E SERVIÇOS LTDA.

AV. GISELE CONSTANTINO, 1578, PARQUE BELA VISTA, VOTORANTIM-SP, BRAZII CFP:18.110-650

TEL: +55-15-3023-9000

. Blumenau, Santa Catarina Office

MITSUBISHI ELECTRIC EUROPE B.V.

European Service Headquarters (Dusseldorf, GERMANY)

Mitsubishi-Electric-Platz 1 40882 RATINGEN, GERMANY TFI: +49-2102-486-5000 / FAX: +49-2102-486-5910

South Germany Service Center (Stuttgart)

SCHELMENWASENSTRASSE 16-20, 70567 STUTTGART, GERMANY

TEL: +49-711-770598-123 / FAX: +49-711-770598-141

France Service Center (Paris)

2 RUE DE L'UNION, 92565 RUEIL-MALMAISON CEDEX, FRANCE

TEL: +33-1-41-02-83-13 / FAX: +33-1-49-01-07-25 France Service Satellite (Lyon)

240, ALLEE JACQUES MONOD 69800 SAINT PRIFST FRANCE

TEL: +33-1-41-02-83-13 / FAX: +33-1-49-01-07-25

Italy Service Center (Milan)

VIA ENERGY PARK 14, VIMERCATE 20871 (MB) ITALY TEL: +39-039-6053-342 / FAX: +39-039-6053-206

Italy Service Satellite (Padova)

VIA G. SAVELLI, 24 - 35129 PADOVA, ITALY

TEL: +39-039-6053-342 / FAX: +39-039-6053-206

U.K. Service Center

TRAVELLERS LANE HATELELD HERTEORDSHIRE ALIO 8XB LLK

TFI: +44-1707-288-780 / FAX: +44-1707-278-695

CTRA. RUBI, 76-80 8174 SAINT CUGAT DEL VALLES, BARCELONA, SPAIN TEL: +34-935-65-2236 / FAX: +34-935-89-1579

UL.KRAKOWSKA 50, 32-083 BALICE, POLAND

TEL: +48-12-347-6500 / FAX: +48-12-630-4701

Hungary Service Cente MITSUBISHI ELECTRIC EUROPE B.V. HUNGARIAN BRANCH

BUDAÖRS OFFICE PARK, SZABADSÁG ÚT 117., 2040 BUDAÖRS, HUNGARY

MITSUBISHI ELECTRIC TURKEY ELEKTRİK ÜRÜNLERİ A.Ş

SERIFALI MAHALLESI KALE SOKAK. NO.41 34775 UMRANIYE, ISTANBUL,

TEL: +90-216-969-2500 / FAX: +90-216-661-44-47

Czech Republic Service Center

MITSUBISHI ELECTRIC EUROPE B.V. PRAGUE OFFICE

Pekařská 621/7, 155 00 PRAHA 5, CZECH REPUBLIC

Sweden Service Center

HAMMARBACKEN 14, P.O.BOX 750 SE-19127, SOLLENTUNA, SWEDEN TEL: +46-8-6251200 / FAX: +46-8-6251014

Bulgaria Service Center

AKHNATON Ltd. (Service Partner)

4 ANDREJ LJAPCHEV BLVD, POB 21, BG-1756 SOFIA, BULGARIA TEL: +359-2-8176009 / FAX: +359-2-9744061

Ukraine Service Center (Kiev)

CSC Automation Ltd. (Service Partner)

4 B. YEVHENA SVERSTYLIKA STR., 02002 KIEV, LIKRAINE TEL: +380-44-494-3344 / FAX: +380-44-494-3366

South Africa Service Center

Adroit Technologies (Service Partner)

20 WATERFORD OFFICE PARK, WATERFORD DRIVE, CNR OF WITKOPPEN ROAD, FOURWAYS JOHANNESBURG SOUTH AFRICA TEL: +27-11-658-8100 / FAX: +27-11-658-8101

MITSUBISHI ELECTRIC ASIA PTE. LTD. (ASEAN FA CENTER) Singapore Service Center

307 ALEXANDRA ROAD MITSUBISHI ELECTRIC BUILDING SINGAPORE 159943 TEL: +65-6473-2308 / FAX: +65-6476-7439

PHILIPPINES

MELCO FACTORY AUTOMATION PHILIPPINES INC.

128 LOPEZ RIZAL STREET, BRGY., HIGHWAY HILLS, MANDALUYONG CITY, MM PHILIPPINES 1550

TFI: +63-2-8256-8042 / FAX: +632-8637-2294

Philippines Service Center

KM.23 WEST SERVICE ROAD SSH, CUPANG, MUNTINLUPA CITY, PHILIPPINES TEL: +63-2-8807-0420 / FAX: +63-2-8842-5202

MITSUBISHI ELECTRIC VIETNAM CO., LTD.

Vietnam Ho Chi Minh Service Center

11TH & 12TH FLOOR, VIETTEL TOWER B, 285 CACH MANG THANG 8 STREET, WARD 12. DISTRICT 10. HO CHI MINH CITY, VIETNAM

TEL: +84-28-3910-5945 / FAX: +84-28-3910-5947

Vietnam Hanoi Service Center

14TH FLOOR, CAPITAL TOWER, 109 TRAN HUNG DAO STREET, CUA NAM WARD, HOAN KIEM DISTRICT, HA NOI CITY, VIETNAM TFI: +84-24-3937-8075 / FAX: +84-24-3937-8076

INDONESIA

PT. MITSUBISHI ELECTRIC INDONESIA

Indonesia Service Center (Cikarang)

JL. KENARI RAYA BLOK G2-07A, DELTA SILICON 5, LIPPO CIKARANG - BEKASI 17550, INDONESIA

TEL: +62-21-2961-7797 / FAX: +62-21-2961-7794

MAI AYSIA

MITSUBISHI ELECTRIC SALES MALAYSIA SDN. BHD.

Malaysia Service Center (Kuala Lumpur Service Center)

LOT 11, JALAN 219, P.O BOX 1036, 46860 PETALING JAYA, SELANGOR DARUL FHSAN, MAI AYSIA

TEL: +60-3-7626-5032

Johor Bahru Service Center

9, Jalan Perjiranan 4/6, Bandar Dato Onn, 81100 Johor.

TEL: 07-3642250 / 2256

Pulau Pinang Service Center

25-G, Pusat Perniagaan Perdana Jaya, Jalan Permatang Rawa, 14000 Bukit

TEL: +60-4-510-1838 / Fax: +60-4-510-1835

THAILAND

MITSUBISHI ELECTRIC FACTORY AUTOMATION (THAILAND) CO., LTD. Thailand Service Center (Bangkok)

101, TRUE DIGITAL PARK OFFICE, 5TH FLOOR, SUKHUMVIT ROAD, BANGCHAK, PHRA KHANONG, BANGKOK, 10260 THAILAND

TEL: +66-2-092-8600 / FAX: +66-2-043-1231-33

MITSUBISHI ELECTRIC INDIA PVT., LTD.

Service Head office and South India Service Center (Bangalore) CNC eXPerience Park, PLOT NO. 57/A, PEENYA PHASE 3, PEENYA INDUSTRIAL

AREA, BANGALORE 560058, KARNATAKA, INDIA TEL: +91-80-4655-2121

Chennai Service Satellite • Coimbatore Service Satellite • Hyderabad Service Satellite

North India Service Center (Gurgaon) PLOT 517, GROUND FLOOR, UDYOG VIHAR PHASE-III, GURUGRAM 122008, HARYANA, INDIA

TFI: +91-124-463-0300

- Ludhiana Service Satellite
- Panthnagar Service Satellite
- Delhi Service Satellite Jamshednur Service Satellite

Manesar Service Satellite

West India Service Center (Pune)

ICC-Devi GAURAV TECHNOLOGY PARK, UNIT NO.402, FOURTH FLOOR, NORTH WING, SURVEY NUMBER 191-192 (P), NEXT to INDIAN CARD CLOTHING COMPANY Ltd, OPP. VALLABH NAGAR, PIMPRI, PUNE- 411 018, MAHARASHTRA,

TEL: +91-20-6819-2274

- Kolhapur Service Satellite
- Aurangabad Service Satellite
- Mumbai Service Satellite

West India Service Center (Ahmedabad)

204-209, 2ND FLOOR, 31FIVE, CORPORATE ROAD PRAHLADNAGAR, AHMEDABAD -380015, GUJARAT, INDIA

TFI: +91-79-6777-7888

Raikot Service Satellite

MITSUBISHI ELECTRIC AUTOMATION (CHINA) LTD. (CHINA FA CENTER) **CNC Call Cente**

NO.1386 HONG QIAO ROAD, CHANG NING QU, SHANGHAI 200336, CHINA

TEL: +86-400-921-5130 Shanghai Service Center

- TEL: +86-21-2322-3030 / FAX: +86-21-2322-3000*8422
- Qingdao Service Cente Suzhou Service Cente
- Wuhan Service Center Ningbo Service Center
- Hefei Service Center
- Beijing Service Center
- Xian Service Center
- Dalian Service Center Chenadu Service Center

Shenzhen Service Center LEVEL8, GALAXY WORLD TOWER B, 1 YABAO ROAD, LONGGANG DISTRICT,

SHENZHEN 518129, CHINA TEL: +86-755-2399-8272 / FAX: +86-755-8229-3686

- Dongguan Service Center
- Xiamen Service Center

SFOUL 07528 KORFA

MITSUBISHI ELECTRIC AUTOMATION KOREA CO., LTD. (KOREA FA CENTER) Korea Seoul Service Cente 8F GANGSEO HANGANG XI-TOWER A, 401 YANGCHEON-RO, GANGSEO-GU

TEL: +82-2-3660-9631 / FAX: +82-2-3664-8668

Korea Daegu Service Center 2F KT BLDG. 8, HOGUK-RO, BUK-GU, DAEGU 41518, KOREA

TEL: +82-53-382-7401 / FAX: +82-53-382-7412

Korea Changwon Technical Center #205, 888, CHANGWON-DAERO, SEONGSAN-GU, CHANGWON-SI,

TEL: +886-4-2359-0688 / FAX: +886-4-2359-0689

GYEONGSANGNAM-DO 51532 KOREA TEL: +82-55-261-5559 / FAX: +82-55-261-5558

MITSUBISHI ELECTRIC TAIWAN CO., LTD. (TAIWAN FA CENTER) Taiwan Taichung Service Cente

NO.8-1, GONGYEQU 16TH RD., XITUN DIST., TAICHUNG CITY 40768,

Taiwan Taipei Service Cente

Taiwan Tainan Service Cente

11F, NO.88, SEC.6, ZHONGSHAN N. RD., SHILIN DIST., TAIPEI CITY 11155, TEL: +886-2-2833-5430 / FAX: +886-2-2833-5433

11F-1, NO.30, ZHONGZHENG S. RD., YONGKANG DIST., TAINAN CITY 71067,

OCEANIA

MITSUBISHI ELECTRIC AUSTRALIA PTY. LTD.

TEL: +886-6-252-5030 / FAX: +886-6-252-5031

Oceania Service Center 348 VICTORIA ROAD, RYDALMERE, N.S.W. 2116 AUSTRALIA

TFI: +61-2-9684-7269 / FAX: +61-2-9684-7245

WARRANTY

Please confirm the following product warranty details before using MITSUBISHI ELECTRIC CNC.

1. Warranty Period and Coverage

Should any fault or defect (hereafter called "failure") for which we are liable occur in this product during the warranty period, repair services shall be provided at no cost through the distributor from which the product was purchased or through a Mitsubishi Electric service provider. Note, however, that this does not apply if the customer was informed prior to purchasing the product that the product is not covered under warranty. Also note that

we are not responsible for any on-site readiustment and/or trial run that may be required after a defective unit is replaced.

[Warranty Term]

The term of warranty for this product shall be twenty-four (24) months from the date of delivery of the product to the end user, provided the product purchased from Mitsubishi Electric or a distributor in Japan is installed in Japan (but in no event longer than thirty (30) months, including distribution time after shipment from Mitsubishi Electric or a distributor).

Note that, in the case where the product purchased from Mitsubishi Electric or a distributor in or outside Japan is exported and installed in any country other than where it was purchased, please refer to "2. Service in Overseas Countries" below.

[Limitations]

- (1) The machine tool builder is requested to conduct an initial failure diagnosis, as a general rule. The diagnosis may also be carried out by Mitsubishi Electric or our service provider for a fee at the machine tool builder's request.
- (2)This warranty applies only when the conditions, method, environment, etc., of use are in compliance with the terms, conditions and instructions that are set forth in the instruction manual, user's manual, and the caution label affixed to the product.
- (3)Even during the term of warranty, repair costs will be charged to the customer in the following cases:
- (a) a failure caused by improper storage or handling, carelessness or negligence. etc., or a failure caused by a problem with the customer's hardware or software

- (b) a failure caused by any alteration, etc., to the product made by the customer without Mitsubishi Electric's approval
- (c) a failure which could have been avoided if the customer's equipment in which this product is incorporated had been equipped with a safety device required by applicable laws or has any function or structure considered indispensable in the light of industrial common sense
- (d) a failure which could have been avoided if consumable parts designated in the instruction manual, etc. had been duly maintained and replaced
- (e) any replacement of consumable parts (including the battery, relay and fuse)
- (f) a failure caused by external factors such as inevitable accidents, including without limitation fire and abnormal fluctuation of voltage, and acts of God, including without limitation earthquakes, lightning, and natural disasters
- (g) a failure which could not have been foreseen under technologies available at the time of shipment of this product from Mitsubishi Electric
- (h) any other failures which are not attributable to Mitsubishi Electric or which the customer acknowledges are not attributable to Mitsubishi Electric

2. Service in Overseas Countries

If the customer installs a product purchased from Mitsubishi Electric in a machine or equipment and exports it to any country other than where it was purchased, the customer may sign a paid warranty contract with our local FA

This applies in the case where the product purchased from us in or outside Japan is exported and installed in any country other than where it was purchased.

For details please contact the distributor from which the product was purchased.

3. Exclusion of Responsibility for Compensation against Loss of Opportunity, Secondary Loss, etc.

Regardless of the gratis warranty term, Mitsubishi Electric shall not be liable for compensation for:

(1)Damage arising from any cause found not to

be the responsibility of Mitsubishi Electric.

- (2)Lost opportunity or lost profit incurred by the user due to a failure of a Mitsubishi Electric product.
- (3)Special damage or secondary damage, whether foreseeable or not, compensation for accidents, and compensation for damages to products other than Mitsubishi Electric products.
- (4)Replacement by the user, maintenance of on-site equipment, start-up test run and other tasks.

4. Changes in Product Specifications

Specifications shown in our catalogs, manuals or technical documents are subject to change without notice.

5. Product Application

- (1) For use of this product, applications should be those that will not result in a serious damage even if a failure or malfunction occurs in the product, and a backup or failsafe function should operate on an external system when any failure or malfunction occurs to the product.
- (2)Mitsubishi Electric CNC is designed and manufactured solely for applications to machine tools for industrial purposes. Do not use this product in applications other than those specified above, especially those which have substantial influence on public interest or which are expected to have significant influence on human lives or properties.

MELSEC, CC-Link, CC-Link/LT and CC-Link IE are either trademarks or registered trademarks of Mitsubishi Electric Corporation in Japan and/or other

Android is a trademarks of Google LLC. EtherNet/IP is a trademarks of ODVA, Inc.

Microsoft® and Windows® are either trademarks or

registered trademarks of Microsoft Corporation in the United States and/or other countries.

The SD logo and SDHC logo are either registered trademarks or trademarks of SD-3C, LLC.

PROFIBUS-DP is a trademark of Profibus International. OR Code is a trademark of DENSO WAVE Inc.

VNC is a registered trademark of RealVNC Ltd. in the United States and other countries.

Other company and product names that appear in this manual are trademarks or registered

trademarks of the respective companies. In some cases, trademark symbols such as $^{\rm TM}$ or $^{\rm 0}$ are

Creating Solutions Together.















Low-voltage Power Distribution Products

Transformers, Med-voltage Distribution

Power Monitoring and Energy Saving

Power (UPS) and Environmental Product









Edge Computing Products



Numerical Control (NC)



Collaborative and Industrial Robots





Mitsubishi Electric's product lineup, from various controllers and drives to energy-saving devices and processing machines, all help you to automate your world. They are underpinned by software, innovative data monitoring, and modelling systems supported by advanced industrial networking and Edgecross IT/OT connectivity. Together with a worldwide partner ecosystem, Mitsubishi Electric factory automation (FA) has everything to make IoT and Digital Manufacturing a reality.

With a complete portfolio and comprehensive capabilities that combine synergies with diverse business units, Mitsubishi Electric provides a one-stop approach to how companies can tackle the shift to clean energy and energy conservation, carbon neutrality and sustainability, which are now a universal requirement of factories, buildings, and social infrastructure.

We at Mitsubishi Electric FA are your solution partners waiting to work with you as you take a step toward the realization of sustainable manufacturing and society through the application of automation. Let's automate the world together!

Global Partner. Local Friend.





[YouTube logo] is a trademark or registered trademark of Google LLC.

Official Mitsubishi Electric Mechatronics YouTube account

User support videos are available, including how to backup/restore data and replace batteries, and an introduction to our products and technologies.



<u> (</u> Safety Warning

To ensure proper use of the products listed in this catalog, please be sure to read the instruction manual prior to use.









[Facebook logo] is a trademark or registered trademark of Meta Platforms, Inc.

[LinkedIn logo] is a trademark or registered trademark of LinkedIn Corporation.

Official Mitsubishi Electric CNC Facebook/LinkedIn account

Visit our page for information about exhibitions, products, technologies, and FAQ.

MITSUBISHI ELECTRIC CORPORATION HEAD OFFICE: TOKYO BLDG., 2-7-3, MARUNOUCHI, CHIYODA-KU, TOKYO 100-8310, JAPAN