IB-0800385ENG-K-1/2



Do not bundle the control and communication cables with main-circuit, power or other wiring. Run the above cables separately from such wiring and keep them a minimum of 100mm (3.94in,) apart.Not doing so noise can cause a malfunction. Do not press the GOT display section with a pointed material as a pen or driver.Doing so can result in a damage or failure of the display section. Turn on the controllers and the network devices to be ready for communication before they communicate with the GOT.Failure to do so can cause a communication Be sure to shut off all phases of the external power supply used by the system befor mounting or removing the GOT toffrom the panel. Not doing so can cause the unit to fail or malfunction. Use the GOT in the environment that satisfies the general specifications described it this manual. Not doing so can cause an electric shock, fire, malfunction or product described the second described that the second described the second described that the second described described that the second described descri damage or deterioration. When mounting the GOT to the control panel, tighten the mounting screws in the specified torque range. Undertightening can cause the GOT to drop, short circuit or malfunction. Overlightening can cause a drop, short circuit or malfunction due to the damage of the screws or the GOT. When inserting/removing a CF card into/from the GOT, turn the CF card access switch off in advance. Failure to do so may corrupt data within the CF card. When inserting a CF card into the GOT push into the insertion slot until the CF card eject button will pop out. Failure to do so may cause a malfunction due to poor contact. contact. When removing a CF card from the GOT, make sure to support the CF card by hand as it may pop out. Failure to do so may cause the CF card to drop from the GOT and break. break. Remove the protective film of the GOT.When the user continues using the GOT and the protective film, the film may not be removed. Operate and store the GOT in environments without direct sunlight, high temperature, dust, humidity, and vibrations. When using the GOT in the environment of oil or chemicals, use the protective cover for oil. Failure to do so may cause failure or malfunction due to the oil or chemical entering into the GOT. Be sure to shut off all phases of the external power supply used by the system befor wring, Failure to do so may result in an electric shock, product damage or malfunctions. Always ground the FG terminal of the GOT power to the functional groun conductor. Failuer to do so may cause electric shocks and malfunctions. Terminal screws which are not to be used must be tightened always at torque 0.5 to 0.8 N·m. Otherwise there will be a danger of short circuit against the solderless Correctly wire the GOT between the a dariger or short Circuit against the solderless terminals. Use applicable solderless terminals and tighten them with the specified torque. If any solderless spade terminal is used, it may be disconnected when the terminal screw comes loose, resulting in failure.less terminals. Correctly wire the GOT power supply section after confirming the rated voltage and terminal arrangement of the product. Not doing so can cause a fire of failure. Tighten the terminal screws of the GOT power supply section in the specified torque range. Undertightening can cause a short circuit or maffunction due to the damage of the screws or the GOT. Sold foreign matter such as chips and wire offcuts entering the GOT. Not doing so can cause a fire of failure or maffunction. The module has an ingress prevention label on its top to prevent foreign matter, such as wire offcuts, from entering the module during wiring. Do not peel this label during wiring. Before starting system operation, be sure to peel this label because of the dissipation. P Plug the communication cable into the connector of the connected unit and tight

Before performing the test operations of the user creation monitor screen (such as turning ON or OFF bit device, changing the word device current value, changing the settings or current values of the timer or counter, and changing the buffer memory current value, read through the manual carefully and make yourself familiar with the operation method. During test operation, never change the data of the devices which are used to perform significant operation for the system. False output or malfunction can cause an accident.

STARTUP/MAINTENANCE WARNING RECAUTIONS

- When power is on, do not touch the terminals. Doing so can cause an elect
- shock or malfunction. Correctly connect the battery connector. Do not charge, disassemble, heat, short-circuit, solder, or throw the battery into the fire. Doing so will cause the battery to produce heat, explode, or ignite, resulting in injuly and fire. Before starting cleaning or terminal screw retightering, always switch off the power externally in all phases. Not switching the power off in all phases can cause a unit failure or malfunction. Undertightering can cause a short circuit or malfunction. Overtightening can cause a short circuit or malfunction due to the damage of the screws or unit.

TARTUP/MAINTENANCE RECAUTIONS

- Concerning the unit of the unit of the unit development of the unit. Do not drop or give an impact to the battery causing the battery fuel to leak inside the battery. If the battery is dropped or given an impact, dispose of it without using. Before touching the unit a dives touch grounded metal, etc. to discharge static electricity from human body, etc. Not doing so can cause the unit to fail or malination.

- malfunction. Replace battery with GT11-50BAT by Mitsubishi electric Co.only. Use of anoth-battery may present a risk of fire or explosion. Dispose of used battery promptly. Keep away from children. Do not disassemb and do not dispose of in fire.

Manuals

The following manuals are relevant to this product. When these loose manuals are required, please consult with our local distributor

Manual name	Contents	Manual Number (Model Code)
GT11 User's Manual (sold separately)*1	Describes the GT11 hardware-relevant content such as part names, external dimensions, mounting, power supply wiring, specifications, and introduction to option devices.	JY997D17501 (09R815)
GOT1000 Series Connection Manual (Mitsubishi Products) for GT Works3 (sold separately) *1	Describes system configurations of the connection method applicable to GOT1000 series and cable creation method	SH-080868ENG (1D7MC2)
GT Designer3 Version1 Screen Design Manual (Fundamentals) 1/2, 2/2 (sold separately) *1	Describes methods of the GT Designer3 installation operation, basic operation for drawing and transmitting data to GOT1000 series	SH-080866ENG (1D7MB9)
GT Designer3 Version1 Screen Design Manual (Functions) 1/2, 2/2 (sold separately) *1	Describes specifications and settings of the object functions used in GT Designer3	SH-080867ENG (1D7MC1)
GOT1000 Series User's Manual (Extended Functions, Option Functions) for GT Works3 (sold separately) *1	Describes extended functions and option functions applicable to GOT series.	SH-080863ENG (1D7MB3)

*1 For relevant manuals, refer to the PDF manuals stored in the DVD-ROM for the drawing software used. For details of a programmer e controller to be connected, refer to the programmable controller user's manual respectively.

Bundled Items

Product Name	Model Name	Specifications						
	GT1155-QTBDQ		0×240 dots, TFT color LCD (256 colors), built-in battery and backlight, built-in bus interface for connecting to the Q mode) and motion controller CPU (Q series), built-in serial interface					
	GT1155-QTBDA		× 240 dots, TFT color LCD (256 colors), built-in battery and backlightm built-in bus interface for connecting to the ACPU, ACPU, and motion controller CPU (A series), built-in serial interface					
GOT	GT1155-QSBDQ		20 x 240 dots, STN color LCD (256 colors), built-in battery and backlightm, built-in bus interface for connecting to the QCPU and and motion controller CPU (Q series), built-in serial interface					
	GT1155-QSBDA	320 × 240 dots, STN color LCD (256 colors), built-in battery and backlight, built-in bus interface for connecting to the QnACPU, ACPU, and motion controller CPU (A series), built-in serial interface						
	GT1150-QLBDQ	connecting to the QCPU (Q mode) and motion controller CPU (Q series), built-in serial interface						
	GT1150-QLBDA							
	Bundled item		Quantity	Bundled item	Quantity			
ounting brackets			4	GT11 General Description (This manual)	1			

3. SPECIFICATIONS

-Μοι

1 General Specificatio

1. FEATURES 1) Improved monitoring performance and connectivity to FA devices High speed monitoring through high speed communication at maximum of 115.2kbps Multiple languages are displayed using the Unicode2.1-compatible fonts and beautiful characters are drawn using the TrueType and high quality fonts

High speed display and high speed touch switch response


2) More efficient GOT operations including screen design, startup, adjustment, management and maintenance works
 The 3MB user memory is included as standard.

Font installation is available to increase the system fonts.


3) Enhanced support of FA setup tools


Transferring or monitoring the sequence programs using the personal computer connected to GOT, during direct connection to Q, QnA or A series programmable controller CPU (FA Transparent function).
 The USB connector is positioned on the GOT front. This enables the system startup to be performed more efficiently using FA device setup tool, and eliminates the indirect works (opening and closing the control panel, cable replacement, cable rewiring) in order to improve the working efficiency.

2. PART NAME



3)4)





	ltem	Specifications							
Operating ambient temperature	Display section Zone d'affichage	0 to 50°C 0 à 50 ℃							
Température ambiante de fonctionnement	Other than display section Autre que la zone d'affichage		to $55^\circ C^{*5}$ (When mounted horizontaly), 0 to $50^\circ C$ (When mounted verticaly) à $55^\circ C^{*5}$ (montage horizontal), 0 à $50^\circ C$ (montage vertical)						
Storage ambient ter	nperature	-20 to 60°C							
Operating ambient h	numidity*1	10 to 90% RH, non	-condensing						
Storage ambient hu	midity*1	10 to 90% RH, non	-condensing						
				Frequency	Acceleration	Half-amplitude	Sweep Count		
		Conforms to JIS	Under intermittent	5 to 8.4Hz		3.5mm			
Vibration resistance		B3502 and	vibration	8.4 to 150Hz	9.8m/s ²		10 times each in X, Y and Z directions		
		IEC61131-2	Under continuous	5 to 8.4Hz		1.75mm			
		vibration	vibration	8.4 to 150Hz	4.9m/s ²		1		
Shock resistance		Conforms to JIS B3502, IEC 61131-2 (147 m/s ² , 3 times each in X, Y and Z directions)							
Operating atmosphere		No greasy fumes, corrosive gas, flammable gas, excessive conductive dust, and direct sunlight (Same as storage atmosphere)							
Operating altitude ^{*2}		2000 m (6562 ft) max.							
Installation location		Inside control panel							
Overvoltage catego	ry*3	II or less							
Pollution degree*4		2 or less							
Cooling method		Self-cooling							
*1 The wet-bulb ter *2 Do not use or st *3 This indicates th	mperature is 39°C or less for tore the GOT under pressure he section of the power sup n the premises.Category II a ge withstand level for up to th	STN LCDs. higher than the atm ply to which the equ pplies to equipment	ipment is assumed to I or which electrical powe	be connected betwe	een the public elect				

*5 When a protective cover for oil is mounted on the GOT, the maximum operating ambient temperature must be 5°C lower than the one described above. Lors de l'installation du couvercle de protection contre l'huile, la température ambiante de fonctionnement doit être réduite de 5°C par rapport aux valeurs maximales dans les spécifications générales.

3.2 Performance Specifications

		Specifications				
	ltem	GT1155-QTBDQ GT1155-QTBDA	GT1150-QLBDQ GT1150-QLBDA			
	Туре	TFT color liquid crystal	STN color liquid crystal	STN monochrome (white/black) liquid crysta		
	Screen size	5.7"		•		
	Resolution	320×240 dots				
	Display size	W115(4.53)× H86(3.39)[mm](inch)				
	Display character	16-dot standard font: 20 characters × 15 li	nes, 12-dot standard font: 26 characters × 2	0 lines (Horizontal format)		
Display	Display color	256 colors		Monochrome (white/black), 16 scales		
section*1	Display angle	Left/Right: 70 degrees, Top: 70 degrees, Bottom: 50 degrees (Horizontal format)	Left/Right: 50 degrees, Top: 50 degrees, Bottom: 70 degrees (Horizontal format) ^{*6}	Left/Right: 45 degrees, Top: 20 degrees, Bottom: 40 degrees (Horizontal format)		
	Contrast adjustment	-	16-level adjustment			
	Intensity of LCD only	400[cd/m ²]	380[cd/m2]	220[cd/m ²]		
	Intensity adjustment	8-level adjustment	·	•		
	Life*2	Approx. 50,000h (Operating ambient temp	perature of 25°C)			
Backlight		Cold cathode fluorescent tube (irreplaceable by a user) backlight shutoff detection function is included. Backlight off/screen saving time can be set.				
	Life	Approx. 75,000h or longer, Guaranteed: 1 50% at the operating ambient temperature		Approx. 54,000h or longer, Guaranteed: 1 year (Time for display intensity reaches 50% at the operating ambient temperature of 25°C)		
	Number of touch keys	300 keys/screen (Matrix structure of 15 lines × 20 columns)				
Touch	Key size	Minimum 16× 16 dots (per key)				
panel	Number of points touched simultaneously	Maximum of 2 points				
	Life	1 million times or more (operating force 0.98N max.)				
	C drive*3	Flash memory (Internal), for storing project data (3Mbytes) and OS				
Memory	Life (Number of write times)	100,000 times				
D drive		SRAM (Internal), 512kbyes (battery backup)				
		GT11-50BAT lithium battery				
Battery	Backup target	Clock data, alarm history and recipe data				
Life		Approx. 5 years (Operating ambient temperature of 25°C), Guaranteed: 1 year				
Buzzer ou		Single tone (tone length adjustable)				
Invironm	ental protective structure*4	Equivalent to IP67 (JEM1030) (front section) when the USB environmental protective cover is attached				
External of	dimensions	W167(6.57)×H135(5.31)×D65(2.56)[mm](inch)(Excluding USB environmental protect	ctive cover)		
Panel cut	ting dimensions	W153 (6.02)×H121(4.76)[mm] (inch)				
Veight		0.9kg (Excluding mounting fixtures)				
Compatible software package		GT Designer2 Version2 or later*5				

When disposing of the product, handle it as industrial waste. When disposing of batteries, separate them from other wastes according to the local regulations (Refer to the User's Manual of the GOT to be used for details of the batter directive in the EU member states.)

TRANSPORTATION PRECAUTIONS

When transporting lithium batteries, make sure to treat them based on the transport regulations. (Refer to the User's Manual of the GOT to be used for details of the

regulations. (Keter to the User's Manual of the GO1 to be used for details of the regurated models.) Make sure to transport the GOT main unit and/or relevant unit(s) in the manne they will not be exposed to the impact exceeding the impact resistance described in the general specifications of the User's Manual of the GOT to be used, as they an precision devices. Failure to do so may cause the unit to fail. Check if the un operates correctly after transportation.

		liquid crystal, 16 scales			For connecting to a cor
2)	Touch key	For operating the touch switches in the utility screen and the user creation screen	2)	RS-232 interface	computer (OS install, p (D-sub 9-pin male)
3)	USB interface	USB interface for connecting a personal computer (OS installation, project data download, transparent)	3)	Hole for unit installation fitting	Hole for the inserting in the GOT installation to bottom)
4)	USB environmental protection cover	Opens/Closes when the USB interface is used.	4)	Rating plate(nameplate)	-
5)	POWER LED	Lit in green : Power is correctly supplied Lit in orange : Screen saving Blinking in orange/green : Blown backlight bulb	5)	CF card access LED	ON: The CF card is ac accessed.
For t		Not lit : Power is not supplied connection, refer to the following. rsion1 Screen Design Manual (Fundamentals) 1/2, 2/2	6)	CF card access switch	Switch for disabling the removing the CF card ON :The CF card is a prohibited) OFF :The CF card is n available)
			7)	CE card cover	Open or close when in

2)	RS-232 interface	computer (OS install, project data download, transparent) (D-sub 9-pin male)				
3)	Hole for unit installation fitting	Hole for the inserting installation fittings (accessory) during the GOT installation to the panel (4 holes at top and bottom)				
4)	Rating plate(nameplate)	-				
5)	CF card access LED	ON: The CF card is accessed. OFF: The CF card is not accessed.				
6)	CF card access switch	Switch for disabling the access to the CF card before removing the CF card from the GOT ON :The CF card is accessed. (CF card removal prohibited) OFF :The CF card is not accessed. (CF card removal available)				
7)	CF card cover	Open or close when inserting or removing the CF card.				
8)	Battery cover	Open or close when replacing the battery.				
9)	Power terminal	Power terminal and FG terminal (for power supply (24VDC) to GOT and grounding)				
10)	CF card interface	Interface for installing the CF card to GOT				
11)	CF card eject button	Button for removing the CF card				
12) Battery and recipe data		GT11-50BAT battery for storing clock data, alarm history and recipe data (The project data is stored in the built-in flash memory.)				
or th	or the connection to the programmable controller or personal computer, refer to the					

For the connection to the programmable controller or personal computer, refer to the

 \rightarrow GOT1000 Series Connection Manual (Mitsubishi Products) for GT Works3

*1 Bright dots (always lit) and dark dots (unlit) may appear on a liquid crystal display panel. It is impossible to completely avoid this symptom, as the liquid crystal display comprises of a great number of display elements. Flickers may be observed depending on the display color. Please note that these dots appear due to its characteristic and are not caused by product defect.

*2 The GOT screen saving/backlight off function prevents images from becoming per nanently etched on the display screen and increases the backlight life

3.5 External Dimensions

28.5 110 (1.12) 21 (0.83)

-]!⊕

(1.12)

ń

· Authorized representative in Europe

152 (5.98)

167 (6.57)

110 (4.33)

110 (4.33)

(0.16) (0.20

0000 0 00000

4. EMC AND LOW VOLTAGE DIRECTIVE

Authorized representative in Europe is shown below Name :Mitsubishi Electric Europe BV Address :Gothaer strase 8, 40880 Ratingen, Germar 4.1 Requirements for Conformance to EMC Directive

4.1.1 Standards applicable to the EMC Directive

not unduly affected by electromagnetic interference (immunity)". The applicable products are requested to meet these requirements.

Telele

GT1155-QTBDQ, GT1155-QSBDQ, GT1150-QLBDQ

1===

00000000

#==E)

56)

- M2 (Metric screw type)

4-40UNC

(Inch screw type)

20 00000000

10.39

Panel thickn

5mm(0.2") or less

*3 ROM in which new data can be written without deleting the written data.

- *4 Compliant with IP67 when the USB environmental protection cover is attached. Not compliant when a USB cable is connected. Note that this does not guarantee all users' operation environment
- *5 For the GT1155-QSBDA, use GT Designer2 Version2 with the version 2.59M or later
- *6 For the GT1155-QSBDQ, when its hardware version is Z or earlier, the specifications of the liquid crystal display are as follows. Left/Right: 55 degrees, Top: 65 degrees, Bottom: 70 degrees For the GT1155-QSBDA, when its hardware version is X or earlier, the specifications of the liquid crystal display are as follows. Left/Right: 55 degrees, Top: 65 degrees, Bottom: 70 degrees

3.3 Built-in Interface Specifications

		Specifications		
	Item	GT1155-QTBDQ	GT1155-QTBDA	
	hem	GT1155-QSBDQ	GT1155-QSBDA	
		GT1150-QLBDQ	GT1150-QLBDA	
BUS		Bus interface for connecting to the QCPU (Q mode) and motion controller CPU (Q series) 1ch Application : For communicating with a programmable controller	-	
	603	-	Bus interface for connecting to the QnACPU, ACPU, and motion controller CPU (A series) 1ch Application : For communicating with a programmable controller	
Built-in interface RS-232 Connector Stape : D-sub 9-pin (Male) Application : Bar code reader connection, Personal computer communication (Project data upload/download, OS installation, transparent function)		uter communication		
	USB	Conforming to serial USB (Full Speed 12Mbps), device, 1ch Application: Personal computer communication (Project data uplo	ad/download, OS installation, transparent function)	
	CF card	Conforming to PCMCIA, compact flash slot, 1ch Connector shape : Dedicated for TYPE I Application : Data transfer, data storage		

3.4 Power Supply Specifications

	Specifications				
Item	GT1155-QTBDQ	GT1155-QSBDQ	GT1150-QLBDQ		
	GT1155-QTBDA	GT1155-QSBDA	GT1150-QLBDA		
Input power supply voltage	24VDC (+10% -15%), ripple voltage 200m	V or less			
Fuse (built-in, not exchangeable)	1.0A				
Power consumption	11.16W (465mA/24VDC) or less	9.72W (405mA/24VDC) or less	7.92W (330mA/24VDC) or less		
At backlight off	5.04W (210mA/24VDC) or less	•	•		
Inrush current	26A or less (26.4V) 4ms				
Permissible instantaneous power failure time*1	Within 10ms				
Noise immunity	Noise voltage: 500Vp-p, Noise width: 1µs (by noise simulator of 25to 60Hz noise frequency)				
Dielectric withstand voltage*2	500VAC for 1 minute (across power supply	terminals and earth)			
Insulation resistance*2	$10M\Omega$ or larger by a 500VDC insulation res	istance tester (across power supply terminals	s and earth)		
Applicable wire size	0.75 to 2[mm ²]				
Applicable solderless terminal	Solderless terminal for M3 screw RAV1.25-3, V2-N3A, FV2-N3A				
Applicable tightening torque (Terminal block terminal screw)	0.5 to 0.8[N-m]				

*1 The GOT continues to operate even upon 5ms or shorter instantaneous power failure. The GOT stops operating if there is extended power failure or voltage drop, while it auto

tically resumes operation as soon as the power is restored

*2 A surge absorber is connected between the power supply and earth terminal so that the GOT does not malfunction due to applied lightning surge noise. Values without a surge absorber are described for the dielectric withstand voltage and the insulation resistance.

- 4.1.1 Standards applicable to the EMC Directive
 The following products have shown compliance through direct testing (to the identified standards) and design analysis (forming a technical construction file) to the European
 Directive for Electromagnetic Compatibility (89/336/EEC) when used as directed by the appropriate documentation
 Type Programmable Controller (Open Type Equipment)
 Models : MELSEC GOT series products, identified here, manufactured from January 7th, 2008
 GT1155-QTBDQ, GT1155-QTBDA, GT1155-QSBDA, GT1150-QLBDA, GT1150-QLBDA.

Standard		Remark
EN61131-2 : 2007 Programmable controllers - Equipment, requirement and tests	EMI	Compliance with all relevant aspects of the standard. (Radiated Emissions)
	EMS	Compliance with all relevant aspects of the standard. (ESD, RF electromagnetic field, EFTB, Surge, RF conducted disturbances and Power frequency magnetic field)

4.1.2 Control cabinet

The GOT is an open type device (device installed to another device) and must be installed in a conductive control panel or cabinet. It not only assure the safety but also has a large effect to shut down the noise generated from GOT, on the control panel.

1) Control cabinet

- Use a conductive control cabinet a) b)
- When attaching the control cabinet: When attaching the control cabinet's top plate or base plate, mask painting and weld so that good surface contact can be made between the cabinet and plate. To ensure good electrical contact with the control cabinet, mask the paint on the installation bolts of the inner plate in the control cabinet. c) so that contact between surfaces can be ensured over the widest
- possible area. Earth the control cabinet with a thick wire so that a low impedance d) connection to ground can be ensured even at high frequencies (22mm 2 wire or thicker is recommended.)
- Holes made in the control cabinet must be 10 cm (3.94") diameter or e) less. If the holes are 10cm (3.94") or larger, radio frequency noise
- may be emitted. In addition, because radio waves leak through a clearance between the control panel door and the main unit, reduce the clearance as

much as practicable.

The leakage of radio waves can be suppressed by the direct applica-tion of an EMI gasket on the paint surface.

 Connection of power and ground wires Ground and power supply wires for the GOT must be connected as described below.

Provide an earthing point near the GOT. Earth the power supply's FG terminal (FG: Frame Ground) with the thickest and shortest wire possible. (The wire length must be 30cm (11.81") or shorter.) The FG terminal function is to pass the noise generated in the GOT to the ground, so an impedance that is as low as possible must be ensured. As the wires are used to relieve the noise, the wire itself carries a large noise content and thus short wing means that the wire is prevented from acting as an antenna. a) prevented from acting as an antenna. Note) A long conductor will become a more efficient antenna at high

frequency.

- 3) Electrical shock prevention In order to such as the operators from electric shocks, the control box must have the following functions :
 - a) The control cabinet must be equipped with a lock so that only skilled or qualified personnel.
 - The control cabinet must be fitted with advice which automatically b) stops the power supply when the cabinet is opened

4.2 Wiring Precautions the Part which Matches the EMC Directives

Connect and wire GOT equipment as instructed below. If the GOT equipment is configured in a way that differs from the following instructions then the system will not comply with EMC directives.

4.2.1 About the cable used

EX.1

EX.3


4.2.1 About the cable used Connect and wire GOT equipment as instructed below. If the GOT equipment is configured in a way that differs from the following instruc-tions then the system will not comply with EMC directives. Bus connection cable The following products are used in the EMC specification compatibility test con-ducted by Mitsubishi Electric Corporation.

- ZCAT3035-1330 ferrite core manufactured by TDK corporation
- AD75CK-type cable clamp manufactured by MITSUBISHI
- Zipper tube SHNJ type manufactured by Zippertubing(Japan),Ltd

GOT Unit	Existing Cables	User Made Cables
GT1155- QTBDQ, GT1155- QSBDQ, GT1150- QLBDQ	GT15-QC□B,GT15-QC□BS modified as shown in EX.1. Peel the sheath at both ends of the cable, and expose the shield braided wire for grounding. (For grounding with clamps.(refer to Section 4.2.3.))	The cable need to
GT1155- QTBDA.	GT15-C BS, cGT15-C EXSS-S1 modified as shown in EX2. Peel the sheath at both ends of the cable, and expose the shield braided wire for grounding. (For grounding with clamps.(refer to Section 4.2.3.))	be independently tested by the user to demonstrate EMC compatibility when they are used with the GOT, the PLC of MELSEC-Q series, MELSEC-
GT1155- QSBDA. GT1150- QLBDA	Other bus connection cables modified as shown in EX.3. Wind cable shield material around the cable, and pull out the grounding braided wire of the cable shield material. Attach the ferrite core to the cable in the specified position and insert the braided wire for arounding into the ferrite core.	QnA series, and MELSEC-A series.

4.2.2 Method to connect the power wire and ground wire

The ferrite filter is not required for the 24VDC cables. the GT1155-QTBDQ, GT1155-QTBDA, GT1155-QSBDQ, GT1155-QSBDA, GT1150-QLBDQ, and GT1150-QLBDA unit requires an additional ferrite filter to be attached to the 24V DC power supply cables. The filter should be attached in a similar manner as shown in the figure opposite, i.e. the power cables are wrapped around the filter. However, as with all EMC situations the more correctly applied precautions the better the systems Electro-magnetic Compatibility. The ferrite recommended is a TDX CZCAT3036-1330 or similar. The ferrite should be placed as near to the 24V DC terminals of the the GT1155-QTBDQ, GT1155-QTBDA, GT1155-QSBDQ, GT1155-QSBDA, GT1150-QLBDQ, and GT1150-QLBDA as possible (which should be within 75mm of the GOT terminal). (which should be within 75mm of the GOT terminal).



5.1 Control Panel Inside Dimensions for Mounting GOT

Mount the GOT onto the control panel while considering the control

GT1155-QTBDA, GT1155-QSBDA, GT1150-QLBDA

THE O

00000000

00000000

THE T

F

Panel thickne

5mm(0.2") or less

10 39

#4-40UNC

(Inch : type)

Unit: mm (inch)

167 (6.57)

110 (4.33)

110 (4.33)

(0.16) (0.2

0000 0 00000

28.5 110 1.12) 21 (0.83)

°▮∎⊕

28.5

ħ


152 (5.98)

62 (2.44

For the products sold in European countries, the conformance to the EMC Directive, which is one of the European Directives, has been a legal obligation since 1996. Also, conformance to the Low Voltage Directive, another European Directives, has been a legal obligation since 1997. Manufacturers who recognize their products must conform to the EMC and Low Voltage Directive are required to declare that their products conform to these Directives and put a "CE mark" on their products.

The EMC Directive specifies that products placed on the market must "be so constructed that they do not cause excessive electromagnetic interference (emissions) and are

The applicable products are requirements. The sections 4.1.1 through 4.1.3 summarize the precations on conformance to the EMC Directive of the machinery constructed using the GOT. The details of these precautions has been prepared based on the requirements and the applicable standards control. However, we will not assure that the overall machinery manufactured according to these details conforms to the above-mentioned directives. The method of conformance to the EMC Directive and the judgment on whether or not the machinery conforms to the EMC Directive must be determined finally by the manufacturer of the machinery.




Unit: mm (inch)


Model Name	Α	В
GT1155-QTBDQ GT1155-QSBDQ GT1150-QLBDQ	56 (2.20)	40 (1.57)
GT1155-QTBDA GT1155-QSBDA GT1150-QLBDA	38 (1.50)	40 (1.57)

Î	No	Name
	1)	Bus connection cable

2) Personal computer connection cable/bar code reader connection cable

Applicable cable Application cables Some cables may need to be longer than the specified dimensions when connecting to the GOT. Therefore, consider the connector dimensions and bending radius of the cable as well for installation.






4.2.3 Grounding the cable

ð

Lise the hus conn

GOT units



4) Dustproof and waterproof features

The control box also has the dustproof and waterproof functions. Insufficient dustproof and waterproof features lower the insulation withstand voltage resulting in insulation destruction.

The insulation in our GOT is designed to cope with the pollution level 2, so use in an environment with pollution level 2 or better.

Pollution level 1:An environment where the air is dry and conductive dust

not exist. Pollution level 2:An environment where conductive dust does not usually exist,

but occasional temporary conductivity occurs due to the accumulated dust. Generally, this is the level for inside the control box equiva-

lent a


control room or on the floor of a typical factory Pollution level 3: An environment where conductive dust exits and conductive itv


, may be generated due to the accumulated dust. An environment for a typical factory floor. Pollution level 4:Continuous conductivity may occur due to rain, snow, etc. An outdoor environment.


4.1.3 Grounding


It is necessary to use the GOT grounding terminal only when it is in the grounded condition. Be sure to ground the grounding for the safety reasons and EMC Directives.

Functional grounding ____: Improves the noise resistance.









M)

us connection cable to ground the cable and grounding wire to the control ore the GOT and base unit are installed.

/ Braided shield

1) Ground the braided shield portion of the cable to

the control panel with the cable clamp (AD75CK)

Bus cor **19** cable ÷ FG wire


GOT FG termina

b) For other bus connection cables Ground the braided wire for grounding to the contro panel by tightening a screw

bendir

5.2 Panel Cutting Dimensions

Make holes in the panel according to the dimensions list below. Also, ensure 10mm spaces in upper and lower parts of the panel for mounting fixtures



IB-0800385ENG-K-2/2

5.3 Mounting Position When mounting the GOT, the clearances shown on the right must be left from a structure or the other device.


Secure 50mm (1.97") or more on the left, right and bottom sides of the GOT to structures or other devices Secure 80mm (3.15") or more on the

Secure 80mm (3.15") or more on the top of the GOT from structures or other devices to allow good ventiliation. If devices (such as a contactor) generating radiated noise or those generating heat are arranged around the GOT, secure 100mm (3.94") or more on the back panel. When using the CF card, secure a utificient distance on the left side to allo 1 To use the CE card leave sufficient distances for removal and installation of the CF card.

sufficient distance on the left side to allow installation and removal of the CF card. [Securing 100mm (3.94") or more is recommended.]

5.4 Control Panel Inside Temperature and Mounting Angle

When mounting the main unit to a control panel or similar, set the display section as shown below. When the temperature inside the control panel is 40 to $55^\circ\!\text{C}$ (Horizontal mount), 40 to 50°C (Vertical mount), the mounting angle should be in the range 60° to 105



5.5 Installation Procedure

The GOT is designed to be embedded into a panel. Mount the GOT by following the procedure below. For panel cutting dimensions, refer to Section 4.2. Note that the panel thickness should be within 5mm.

1) Inserting into the panel face Insert the GOT from the front side of the panel.

Mounting hole Magnified illustration

Mour

untin

80mm (3.15") or mor

50mm (1.97") or more

2) Fixing the GOT

Fixing the GOT Engage the hook of the mounting fitting (accessory) to the unit fixing hole of the GOT and tighten the screw until the GOT is fixed with the mounting bolt (accessory). The GOT will be fixed in 4 upper

parts. Tighten the mounting screw with the specified torque. (Failure to do so may distort the panel


and make a surface waviness on the protective sheet.)

3) A protection film is attached on the display section of GOT prior to shipment nove the film when the installation is completed.

5. INSTALLATION

5.1 Dimensions intérieures du tableau de commande pour le montage du GOT

Montez le GOT sur le tableau de commande en tenant compte des dime intérieures du tableau de commande ci-dessous.



Nom du modèle Α В

GT1155-QTBDQ GT1155-QSBDQ GT1150-QLBDQ	56 (2,20)	40 (1,57)
GT1155-QTBDA GT1155-QSBDA GT1150-QLBDA	38 (1,50)	40 (1,57)


N	Nom
1)	Câble de connexion du bus
2)	Câble de connexion de l'ordinateur individuel/câble de connexion du lecteur de code-barres


Câble applicable

Certains câbles peuvent être plus longs que les dimensions spécifiées lors de la connexion au GOT. Par conséquent, prenez également en compte les dimensions du connecteur et le rayon de courbure du câble pour l'installation.

5.2 Cotes de découpe du panneau

Faites des trous dans le panneau en suivant les dimensions ci-dessous. Veillez à laisser des espaces de 10mm dans les parties supérieure et inférieure du panneau pour les fixations.





Lors du montage du GOT, il est nécessaire de laisser les espaces indiqués à droite pour une structure ou un autre dispositif. Laissez 50mm (1,97") ou plus sur les côtés gauche, droit et inférieur du GOT pour des structures ou d'autres dispositifs.


dispositifs. Laissez 80mm (3.15") ou plus sur le côté supérieur du GOT pour des structures ou d'autres dispositifs afin d'assurer une bonne ventiliation. Si des dispositifs (comme un contacteur) générant des émissions sonores ou de la chaleur sont placés autour du GOT, laissez 100mm (3.94") ou us sur le paneau arritér

(3,94") ou plus sur le panneau arrière. Lors de l'utilisation de la carte CF, laissez une distance suffisante sur le côté gauche pour pouvoir insérer et retirer la carte CF. [Il est recommandé de laisser 100mm (3,94") ou plus.]

la carte CF.

5.4 Température intérieure et angle de montage du tableau de commande

Lors du montage du châssis de base sur un tableau de commande ou autre, réglez la zone d'affichage comme indiqué ci-dessous. Lorsque la température à l'intérieur du tableau de commande est comprise entre 40 et 55 °C (montage horizontal), 40 à 50 °C (montage vertical), l'angle de montage doit être compris entre 60 et 105 °.



5.5 Procédure d'installation

Le GOT est conçu pour s'intégrer dans un panneau. Montez le GOT en suivant la procédure ci-dessous. Pour connaître les cotes de découpe du panneau, réfe vous à la section 5.2 Notez que l'épaisseur du panneau doit être d'environ 5mm.

Insertion dans la façade du panneau Insérez le GOT sur la face antérieure du panneau.

2) Fixation du GOT

Placez le crochet de l'attache de fixation (accessoire) dans le trou de fixation du GOT et serrez la vis jusqu'à ce que le

Un film de protection est placé sur la zone d'affichage du GOT avant livraison. Retirez le film lorsque l'installation est terminée.



50mm (1.97*)

50mm (1.97") ou plus


*1 Pour utiliser la carte CF, laissez une

distance suffisante pour retirer et inséren

6.1 Power Supply Wiring


Connect the power terminal on the GOT rear face with the 24VDC terminal of the external power

Use 0.75mm² or more cables so as not to produce voltage drops. Use olderless terminals for M3 screws, and be sure to tighten the screws with a tightening torque of 0.5 to 0.8N-m.



 The index ident grounding is basically requ Ground the GOT with a ground resistance of 100Ω or less.

- If the independent grounding is impossible, carry out the shared grounding as shown in fig.2) below.
- Use the cable of 2mm² or more for grounding. Set the grounding point closer to the GOT to make the grounding cable short as possible



7. MAINTENANCE AND INSPECTION The GOT does not include consumable components that will cause the shorten

life However, note that battery life is 5 years and LCD life is 50,000 hours. The life of backlight in GT1155-QTBDQ, GT1155-QTBDA, GT1155-QSBDQ, GT1155-QSBDA is 75,000 hours and that in GT1150-QLBDQ, GT1150-QLBDA is 54,000

It is recommended to replace the battery periodically. (For the replacement of the liquid crystal screen and backlight, please consult your nearest sales office or FA Center.)

7.1 Daily Inspection

Daily inspection items					
No.	Inspection Item		Inspection Method	Criterion	Action
1	GOT mounting status		Check for loose mounting screws.	Securely mounted	Retighten screws within the specified torque range
Connection status	atus	Loose terminal screws	Retighten screws with screwdriver	Not loose	Retighten terminal screws
	Connection st	Proximate solderless terminals	Visual check	Proper intervals	Correct
		Loose connectors	Visual check	Not loose	Retighten connector fixing screws
3	Usage status	Dirt on protection sheet	Visual check	Not outstanding	Replace with new one
		Foreign material attachment	Visual check	No foreign matter sticking	Remove clean
Refer	to	the following for th	ne model name	s of the protec	tion sheet or the

onowing for model names of the the → GT11 User's Manual

7.2 Periodic Inspection

Yearly or half-yearly inspection items The following inspection should also be performed when equipment has been moved or modified or the wiring changed.

7.3 Battery Replacement

The battery backs up clock data, alarm history and recipe data. Screen data is stored in the flash memory and data is retained even if the battery is dead.

•	Battery model name
	GT11 III is shipped with the following battery

	°,
Product name	Model
Battery	GT11-5

Bat

1) T 2) 3) F

4)[

for 30 seconds.)

and close the back cover

Conn

· How to confirm production year and month


Ŀ

the purchased GOT can be The cor the GOT main unit

e production year a firmed by the produ				
	AMITSUBIS	SHI		1
	GRAPHIC OPERA		NAL.	
	MODEL GT1155	-OTBDQ		
	IN 24VDC			
l" ()++→	POWER MAX 0 SERIAL 000073	201020000	1.4	
1			1.75	
	MITSUBISHI E	LECTRIC	MADE IN JAPAN	
				1
	IN 24VDC POWER MAX O SERIAL 000077	0W_ 201DP0000		

٠	Battery model name
	GT11 G is shipped with the following battery.

Product name	Model name
Battery	GT11-50BAT
ttery replacement procedur. Turn the GOT power off. Open the back cover of the Remove the old battery holder. Disconnect the old battery and insert the new battery within 30s. (Clock data, alarm history, data is retained by the GOT for 30 eccorde).	GOT. from the connector connector and recipe



	GOT soit fixé avec le boulon de fixation (accessoire).	<u> </u>
ou plus	Le GOT est fixé en 4 points en haut et en bas.	
	Serrez la vis de fixation au couple spécifié.	
	(Ne pas le faire peut déformer le panneau et faire onduler le film de protection.)	•

Gros plan

Attache de

de fixatio

Warranty

Mitsubishi will not be held liable for damage caused by factors found not to be the cause of Mitsubishi; machine damage or lost profits caused by faults in the Mitsubishi products; damage, secondary damage, accident compensation caused by special factors unpredictable by Mitsubishi; damages to products other than Mitsubishi products; and to other duties.

≜For safe use

- This product has been manufactured as a general-purpose part for general industries, and has not been designed or manufactured to be incorporated in a device or system used in purposes related to human life
- Before using the product for special purposes such as nuclear power, electric power, aerospace, medicine or passenger movement ehicles, consult with Mitsubishi.
- This product has been manufactured under strict quality control. However, when installing the product where major accidents or losses could occur if the product fails, install appropriate backup or failsafe functions in the system.

Country/Region Sales office/Te

Italy

Snain

France

- Mitsubishi Electric Automation, Inc. 500 Corporate Woods Parkway, Vernon Hills, IL 60061, U.S.A. USA
- Mandooni Lei Woods Parkway, Vernon Hills, IL 60061, U.S.A. Tel: +1-847-478-2100 Mitsubshit Fleedric do Brasil Comercio e Servicos Ltda. Avenida Adelino Cardana, 293, 21 andar, Bethaville, Barueri SP, Brasil CEP 06401-477 Tel: +55-11-4689-3000 Mitsubshi Electric Automation, Inc. Mexico Branch Mariano Escobedo #69, Col. Zona Industrial, Tlainepantia Edo. Mexico, C.P.54030 Tel: +525-53-0067-7511 Mitsubshit Electric-Platz 1, 40802 Ratingen, Germany Tel: +43-2102-486-0 Mitsubshi Electric Furupe B, V. UIK Branch
- Mexico
- Germany
- Tel: +49-2102-486-0 at: Mitsubishi Electric Europe B.V. (UK Branch Travellers Lane, Hatfield, Hertfordshire, AL10 8XB, U.K. Tel: +44-1707-28-8780 Mitsubshi Electric Europe B.V. Italian Branch Centro Direzionale Collooni Palazzo Sino, Vale Colleoni 7, Agrate Branza (Mb), Italy Tel: +39-435-4034 Mitsubshi Electric Europe B.V. Spanish Branch Carnetera de Ruhi 78-80-Apdo.420, 08190 Sant Cugat del Valles (Barcelona), Spain Tel: +34-935-65-311 Mitsubshi Electric Europe B.V. French Branch 25, Boulevard des Bouvets, 92741 Nanterre Cedex, France Tel: +33-435-68-55-68 Mitsubshi Electric Europe B.V. Czech Branch UK

No.	Inspect	ion Item	Inspection Method	Criterion		Criterion Action		Action
	Surrounding		Make measurement with thermometer	Display section	0 to 50°C	For use in		
1 Surrounding environment				Other portions	0 to 55°C	control panel, temperature inside control		
	environment	Ambient humidity	or hygrometer Measure corrosive gas	10 to 90%RH		panel is ambient temperature		
		Atmosphere	corrosive gas	No corrosive gas				
2	Power supply voltage 24VDC Measure voltage across terminals. 20.4 to 26.4VDC		Change supply power					
		Loose terminal screws	Retighten screws with screwdriver	Not loose		Retighten terminal screws		
3	Connection status	Proximate solderless terminals	Visual check	Proper intervals		Correct		
		Loose connectors	Visual check	Not loose	e	Retighten connector fixing screws		



 Battery life Approximate battery life: 5 years (ambient temperature: 25°C) [Guaranteed for 1 year] Battery replacement: In 4 to 5 years

Approximate life is 5 years, but life may be shorter depending on the ambient temperature, therefore, note that the battery must be replaced in 4 to 5 years. Make sure to purchase a new battery as needed as it self-discharges.

Battery status can be confirmed on a GOT utility screen. For details of battery status or how to output alarm, refer to the following: \rightarrow GT11 User's Manual

Czecn	Mitsubishi Electric Europe B.V. Gzech Branch
	Avenir Business Park, Radlicka 751/113e, 158 00 Praha 5, Czech Republic
	Tel: +420-251-551-470
Turkey	Mitsubishi Electric Turkey A.S. Umraniye Branch
	Serifali Mahallesi Nutuk Sokak No:5, TR-34775 Umraniye / Istanbul, Turkey
	Tel: +90-216-526-3990
Poland	Mitsubishi Electric Europe B.V. Polish Branch
	ul. Krakowska 50, 32-083 Balice, Poland
	Tel: +48-12-347-65-00
Russia	Mitsubishi Electric (Russia) LLC St. Petersburg Branch
100010	Piskarevsky pr. 2, bld 2, lit "Sch", BC "Benua", office 720;
	RU-195027 St. Petersburg, Russia
	Tel: +7-812-633-3497
South Africa	Adroit Technologies
South Africa	20 Waterford Office Park. 189 Witkoppen Road. Fourways. Johannesburg. South Africa
	Tel: +27-11-658-8100
China	Mitsubishi Electric Automation (China) Ltd.
Unina	
	No.1386 Hongqiao Road, Mitsubishi Electric Automation Center, Shanghai, China
	Tel: +86-21-2322-3030
Taiwan	SETSUYO ENTERPRISE CO., LTD.
	6F, No.105, Wugong 3rd Road, Wugu District, New Taipei City 24889, Taiwan
	Tel: +886-2-2299-2499
Korea	Mitsubishi Electric Automation Korea Co., Ltd.
	7F-9F, Gangseo Hangang Xi-tower A, 401, Yangcheon-ro, Gangseo-Gu,
	Seoul 07528, Korea
	Tel: +82-2-3660-9530
Singapore	Mitsubishi Electric Asia Pte. Ltd.
	307 Alexandra Road, Mitsubishi Electric Building, Singapore 159943
	Tel: +65-6473-2308
Thailand	Mitsubishi Electric Factory Automation (Thailand) Co., Ltd.
	12th Floor, SV.City Building, Office Tower 1, No. 896/19 and 20 Rama 3 Road,
	Kwaeng Bangpongpang, Khet Yannawa, Bangkok 10120, Thailand
	Tel: +66-2682-6522 to 31
Indonesia	PT. Mitsubishi Electric Indonesia
	Gedung Jaya 11th Floor, JL. MH. Thamrin No.12, Jakarta Pusat 10340, Indonesia
	Tel: +62-21-3192-6461
Vietnam	Mitsubishi Electric Vietnam Co., LTD. Ho Chi Minh Head Office
	Unit 01-04, 10th Floor, Vincom Center, 72 Le Thanh Ton Street, District 1,
	Ho Chi Minh City, Vietnam
	Tel: +84-8-3910-5945
India	Mitsubishi Electric India Pvt. Ltd. Pune Branch
	Emerald House, EL -3, J Block, M.I.D.C., Bhosari, Pune - 411026, Maharashtra, India
	Tel: +91-20-2710-2000
Australia	Mitsubishi Electric Australia Pty. Ltd.
-	348 Victoria Road, P.O. Box 11, Rydalmere, N.S.W. 2116, Australia
	Tel: +61-2-9684-7777

MITSUBISHI ELECTRIC CORPORATION

HEAD OFFICE : TOKYO BUILDING, 2-7-3 MARUNOUCHI, CHIYODA-KU, TOKYO 100-8310, JAPAN NAGOYA WORKS : 1-14, YADA-MINAMI 5-CHOME, HIGASHI-KU, NAGOYA, JAPAN

When exported from Japan, this manual does not require application to the Ministry of Economy, Trade and Industry for service transaction permission.

Specifications subject to change without notice Printed in Japan, July 2019.