


For your all production needs

# **MELSERVO-J4 Solutions**

**Eco-friendly Conveyors and Product Handling Equipment** 





- 1 Robot 1 X-axis
- 2 Robot 1 Y-axis (Linear)
- 3 Robot 1 Z-axis
- 4 Robot 2 X-axis
- 5 Robot 2 Y-axis (Linear)
- 6 Robot 2 Z-axis
- 7 Line 1 Belt Conveyor Drive Axis
- **B** Line 2 Belt Conveyor Drive Axis
- (a) Robot 1
  - (b) Robot 2
  - (c) Line 1
  - (d) Line 2

## **Control Flow**

All axes

Robot 1 (X, Y, Z-axis) moves to its wait position.

Robot 2 (X, Y, Z-axis) moves to its wait position.

Robot 1 (X, Y, Z-axis)

Robot 1 grabs a workpiece and place it on the pallet.

Robot 2 (X, Y, Z-axis)

Robot 2 grabs the workpiece in the pallet and move it to Line 2.

Operation is then repeated

Issues at production sites

Managing of total power consumption

Power Monitor Function

Issue 2

Reduction of power consumption


Multi-axis Servo
Amplifier

Issue 3

Minimizing waste of power

Capacity Selection Software

## **System Example**



PLC CPU :Q06UDEHCPU GOT :GOT 1000 series Main base unit:Q35DB Simple Motion : QD77MS16 I/O module : QX40,QY40P

Servo amplifier : MR-J4W3-B,MR-J4W2-B Servo motor : HG-KR

Servo motor : HG-KH Linear servo motor : LM-H3

#### **《Application》**

- Conveyors and handling equipment
- Packing machine
- Motion alignment
- Pick and place robot

Step1

Setup Procedure System Configuration Settings

Step2

Settings for Optional Data Monitor Step3

Creation of a Sequence Program for GOT Display

## Offering the **Best Solution**



**Power Monitor Function** 

## **Managing Power Consumption with** a Visualization System

The MR-J4 series servo amplifiers can calculate power consumption itself without a power measuring instrument, and can send the data to controllers for monitoring.

· Peak load ratio

 Equivalent disturbance torque

- Bus voltage

• Parameter setting (Optional data selection)

Data that can be Monitored

The following are some examples of the data.


- · Effective load ratio
- · Regenerative load ratio · Position loop gain 1
- · Load to motor inertia ratio

Optional data monitor:

Data type setting with GX Works2

- Module power consumption
- Module integral power consumption
  - Module power consumption (W) · Module integral power consumption (Wh)

Displaying power consumption



alculating the data without a power

Solution 2


Multi-axis Servo **Amplifier** 

## **Contributing Energy Conservation Using Regenerative Energy**

The multi-axis servo amplifier can store regenerative energy when motors decelerate.

Those regenerative energy is used to drive another motor, contributing to energy conservation of the machine.

In this system, the regenerative energy from the Y-axis is used to accelerate the Z-axis.



Solution 3


**Capacity Selection Software** 

**Easy Selection of a Suitable Motor** for Your Machine

The "Capacity selection software" (free software) selects a suitable rotary servo motor, linear servo motor, and direct drive motor for your machine using various data, such as mass of the table and the load, the operation pattern, etc.

After the selection, it shows the calculation process and results.






Selecting

# Setup Procedure




Set servo amplifier.






Set the "Optional data monitor" with the parameter. If you select "Module power consumption" or "Module integral power consumption", the amplifier power consumption is monitored.






Creation of
a Sequence Program
for GOT Display

Create a sequence program to calculate the data to be displayed on GOT, such as, "Peak power consumption", "Peak integral power consumption", and "Peak motor current".





consumption

# MELSERI/O-J4 Features

## **Saving Total Power Consumption with Various Functions for Energy-conservation**


**Energy Saving** 

## **Optimal Energy-conservative Machine System**

## PN Bus Voltage Connection + Power Regeneration Common Converter

Regenerative energy is used efficiently when multiple servo amplifiers and inverters are connected through common PN bus to the power regeneration common converter.

- \* System only with common PN bus connection is also possible to be configured without using the power regeneration common converter. However, there are restrictions depending on the system. Contact your local sales office for more details.
- \* Refer to MR-J4-B(-RJ)/A(-RJ) Servo Amplifier Instruction Manual for selection of power regeneration common converter FR-CV series.



**Energy Saving** 

## **Advanced Function and Performance for More Energy-conservation**

#### **Reduced Energy Loss of Servo Amplifier and Servo Motor**

#### < Servo amplifier >

Efficiency is increased by the use of a new power module.


#### < Servo motor >

Motor efficiency is increased by optimized design of magnetic circuit.



## Energy-conservation Due to the Improved Machine Performance

Thanks to the driving system configured by servo amplifier and servo motor with industry-leading level of high performance, machine tact time and operation time are reduced, achieving energy-conservation.



**Energy Saving** 


## **Energy-conservation Achieved by LM-H3 Linear Servo Motor Series**

NEW

#### **Reduced Motor Driving Power**


LM-H3 has achieved a reduction of 25% in motor driving current due to a new magnetic design with optimized magnet form, contributing to power conservation for machines. The motor coil is lighter as compared to the prior model, which also contributes to saving energy for driving the moving part.

\* For 720 N rated linear servo motor



#### **Space Saving**

For LM-H3, widths of the motor coil and the magnet are reduced by 10% from the prior model. Increased thrust to current ratio results in using the servo amplifier in smaller capacity, contributing to more compact machine (the reduction of materials).



Man, machine and environment in perfect harmony

Solution \( \square\)





## MITSUBISHI ELECTRIC CORPORATION

HEAD OFFICE: TOKYO BUILDING, 2-7-3, MARUNOUCHI,CHIYODA-KU,TOKYO 100-8310,JAPAN NAGOYA WORKS: 1-14, YADA-MINAMI 5,HIGASHI-KU,NAGOYA,JAPAN