

## GT15 CF card unit User's Manual

#### GT15-CFCD

Thank you for choosing Mitsubishi Electric Graphic Operation Terminal (GOT).

Prior to use, please read both this manual and detailed manual thoroughly to fully understand the product.

MODEL	GT15-CFCD-U
MODEL CODE	1D7M62
IB(NA)-0800365-K(1806)MEE	



© 2006 MITSUBISHI ELECTRIC CORPORATION

#### ●SAFETY PRECAUTIONS●

(Be sure to read these instructions before use.)

Before using this product, read this and relevant manuals carefully and handle the product correctly with full attention to safety. Note that these precautions apply only to this product.

In this manual, ●SAFETY PRECAUTIONS● are classified into 2 levels: "WARNING" and "CAUTION".

Indicates that incorrect handling may cause **↑WARNING** hazardous conditions, resulting in death or severe injury

Indicates that incorrect handling may cause ⚠ CAUTION hazardous conditions, resulting in medium or slight personal injury or physical damage.

Under some circumstances, failure to observe the  $\Delta {\rm CAUTION}$  level instructions may also lead to serious accidents. Be sure to observe the instructions of both levels to ensure the

safety.

Please keep this manual in a safe place for future reference and also pass this manual on to the end user

#### [Installation precautions]

#### **MARNING**

- Be sure to shut off all phases of the external power supply used by the system before mounting or removing this unit to/from the GOT. Not doing so can cause the unit to fail or malfunction.
- When installing this unit, wear a wrist strap to prevent the unit
- from being damaged by static electricity.
- Be sure to shut off all phases of the external power supply of the GOT main unit before connecting the cable to this unit. Not doing so can cause the unit to fail or malfunction.

#### **⚠ CAUTION**

- Use this unit in the environment that satisfies the general specifications described in the User's Manual for the GOT used Not doing so can cause an electric shock, fire, malfunction or product damage or deterioration.
- When installing this unit, fit it to the connection interface of the GOT and tighten the mounting screws. If the screw is too loose, it may cause a drop of the unit, a failure or malfunctions. Tightening the screw excessively may damage the screw and/or the unit, resulting in a drop of the unit, a failure or malfunctions.
- When installing a CF card into this unit, insert it into the card slot of this unit until the CF card eject button pops out. Failure to do so may cause a malfunction due to poor contact.
- Before inserting or removing a CF card into/from this unit, turn the CF card access switch off.
  Failure to do so may corrupt data on the CF card.
- When removing a CF card from the GOT, support it by hand, as it may pop out. Failure to do so may cause the CF card to drop from the unit, resulting in a damage or failure.

#### [Wiring precautions]

#### **MARNING**

Be sure to shut off all phases of the external power supply used by the system before wiring. Failure to do so may result in an electric shock, product damage

## **⚠ CAUTION**

Carefully prevent foreign matter such as dust or wire chips from Failure to do so may cause a fire, failure or malfunctions

#### [Startup and maintenance precautions]

#### **MARNING**

Be sure to shut off all phases of the external power supply of the GOT main unit before starting cleaning.

Not doing so can cause the unit to fail or malfunction.

## **⚠ CAUTION**

- Do not disassemble or modify this unit and CF card. Doing so can cause failure, malfunctions, personal injuries and/or a fire.
- Do not touch the conductive and electronic parts of this unit directly. Doing so can cause a unit malfunction or failure.
- Do not drop or apply strong impact to this unit or the CF card. Doing so may damage the unit or CF card.
- Before handling this unit, touch a grounded metal object to discharge the static electricity from the human body. Failure to do so may cause failure or malfunctions of the unit.

#### [Disposal precautions]

## **⚠ CAUTION**

• When disposing of the product, treat it as an industrial waste.

#### [Transportation precautions]

### **⚠ CAUTION**

Make sure to transport this unit in the manner it will not be exposed to the impact exceeding the impact resistance described in the general specifications of the User's Manual for the GOT used, as it is a precision device. Failure to do so may cause the unit to fail Check if the unit operates correctly after transportation

#### MANUAL

The following shows manuals relevant to this product

Detailed Manual

Manual name		Manual number (Model code)
GT16 User's Manual (	SH-080928ENG (1D7MD3)	
GT15 User's Manual	(Sold separately)	SH-080528 (1D7M23)

Relevant Manuals

For relevant manuals, refer to the PDF manuals stored in the DVD-ROM for the drawing software used.

## Compliance with the EMC and Low Voltage

#### <u>Directives</u>

To configure a system meeting the requirements of the EMC and Low Voltage Directives when incorporating the Mitsubishi GOT (EMC and Low Voltage Directives compliant) into other machinery or equipment, refer to "EMC AND LOW VOLTAGE DIRECTIVES" of the General Description included with the GOT used.

The CE mark, indicating compliance with the EMC and Low Voltage Directives, is printed on the rating plate of the GOT

#### Compliance with the new China RoHS directive

GOT 相关的基于 " 电器电子产品有害物质限制使用管理办法 " 要求的表示方法



Note: This symbol mark is for China only.

有有害 6 物质的名称、含有量、含有部件 产品中所含有的有害 6 物质的名称、含有量、含有部件如下表所示。 产品中有害物质的名称及含量

	有害物质					
部件名称	铅 (Pb)	汞 (Hg)	镉 (Cd)	六价铬 (Cr(VI))	多溴联苯 (PBB)	多溴二苯醚 (PBDE)
电路板组件	×	0	0	0	0	0
树脂壳体、电缆、膜材	0	0	0	0	0	0
钣金部件、螺丝等金属部件	0	0	0	0	0	0

本表格依据 SJ/T11364 的規定編制。 〇:表示该有害物质在该部件所有均质材料中的含量均在 GB/T26572 規定的限量要 求以下。 ×:表示该有害物质至少在该部件的某一均质材料中的含量超出 GB/T26572 規定的

#### Referenced Standard: GB/T15969.2 (Requirement of Chinese standardized law)

#### Packing List

The following items are included

Model name	Product name	Quantity
	CF card unit	1
GT15-CFCD	Screw set (2 screws)	1
	GT15 CF card unit User's Manual (This manual)	1

#### 1. OVERVIEW

B drive of the GOT.

This User's Manual describes the GT15 CF card unit (hereinafter referred to as CF card unit).

For the GOTs to which the units can be installed and usable CF cards, refer to the User's Manual for the GOT used.
When using an additional drive, the CF card unit can be used as the

The extension units used as the B drive of the GOT are a CF card unit and a CF card extension unit. The CF card unit and the CF card extension unit cannot be used at


To use the CF card unit, make the Communication Settings For setting details, refer to the User's Manual for the GOT used.

## 2. SPECIFICATIONS

The performance specifications of the CF card unit are shown below. For the general specifications of the CF card unit, refer to the User's Manual for the GOT used.

Item	Specifications	
Internal current consumption (5VDC)	0.07A	
Protective structure	IP2X	
Weight	0.15kg (0.33lb)	

#### 3. PART NAMES AND EXTERNAL **DIMENSIONS**



Difficultions of X which installing the drift of the GOT		
GOT	GT16	GT15
15"	18.5 (0.73)	20 (0.79)
12.1"	17 (0.67)	17 (0.67)
10.4"	20 (0.79)	20 (0.79)
8.4"	22 (0.87)	22 (0.87)
5.7"	22 (0.87)	22 (0.87)

Unit: mm(inch)


No.	Name	Description
1)	CF card access LED	LED lamp lit when the CF card is accessed
2)	CF card access switch	Switch for disabling the access to the CF card ON: Access to the CF card enabled OFF: Access to the CF card disabled
3)	Eject button	Button for removing the CF card
4)	CF card cover	Cover opening/closing at CF card installation/ removal
5)	CF card connector	Connector for installing the CF card
6)	Rating plate	-
7)	CF card unit	Mounting screw fixed with a front extension unit or the GOT

## 4. INSTALLATION PROCEDURE


The installation procedure for the CF card unit is explained using the

## 4.1 CF Card Unit Installation

- 1) Power off the GOT.
- 2) Remove one of the extension unit covers of the GOT and fit the CF card unit along the gloove of the GOT case.



3) Fix the CF card unit by tightening its fixing screws (2 places) with a tightening torque of 0.36 to 0.48N•m.



## 4.2 Installation and Removal Precautions

- (1) Any extension units cannot be installed on the CF card unit.
  - When installing other extension units, install the CF card unit at the last
- (2) When installing the CF card unit on extension interface 1 (left side), do not install more units on extension interface 2 (right side) than on extension interface 1 (left side).
- If doing so, the CF card cannot be installed or removed. (3) When removing the CF card unit, detach it from the
- specified direction ( $\triangle PULL$ ) so as not to break the connector

#### 5. CF CARD INSTALLATION/REMOVAL **PROCEDURE**

## 5.1 Installation

1) Open the CF card cover and turn off the CF card access switch



2) Insert the CF card into the CF card connector with the face out.




3) Turn on the CF card access switch

## 5.2 Removal

1) Open the CF card cover. Turn off the CF card access switch and check that the CF card access LED turns off.
(When the CF card access LED turns off, the CF card can be removed even while the GOT power is on.)



2) Press the CF card eject button to pop out the CF card and remove it.



## Warranty

Mitsubishi Electric will not be held liable for damage caused by factors found not to be the cause of Mitsubishi Electric; machine damage or lost profits caused by faults in the Mitsubishi Electric products; damage, secondary damage, accident compensation caused by special factors unpredictable by Mitsubishi Electric; damages to products other than Mitsubishi Electric products; and to other duties.

## ⚠For safe use

- This product has been manufactured as a general-purpose part for general industries, and has not been designed or manufactured to be incorporated in a device or system used in purposes related to
- Before using the product for special purposes such as nuclear
- power, electric power, aerospace, medicine or passenger movement vehicles, consult with Mitsubishi Electric.

  This product has been manufactured under strict quality control. However, when installing the product where major accidents or losses could occur if the product fails, install appropriate backup or failed for motions in the persons. failsafe functions in the system.

#### Country/Region Sales office/Tel Mitsubishi Electric Automation, Inc. 500 Corporate Woods Parkway, Vernon Hills, IL 60061, U.S.A Tel: +1-847-478-2100 USA Brazi

18:: +1-84-4/8-2100 Milsubish IEectric do Brasil Comercio e Servicos Ltda. Avenida Adelino Cardana, 293, 21 andar, Bethaville, Barueri SP, Brasil CEP 06401-147 Tel: +55-11-4689-3000 Milsubish Electric Automation, Inc. Maylos Branch

Mitsubishi Electric Automation, Inc. Mexico Branch
Mariano Escobed #99, Col. Zona Industrial, Tlalnepantla Edo. Mexico, C.P.54030
Tel: +25-53-3067-7511
Mitsubishi Electric Furence 9 V.C. 

ishi Electric Europe B.V. Spanish Branch era de Rubi 76-80-Apdo.420, 08190 Sant Cugat del Valles (Barcelona), Spair Tel: +34-935-65-3131
Mitsubishi Electric Europe B.V. French Branch
25, Boulevard des Bouvets, 92741 Nanterre Cedex, France

55-58-55-68 Electric Europe B.V. Czech Branch ness Park, Radlicka 751/113e, 158 00 Praha 5, Czech Republic

Serifali Mahallesi Nutuk Sokak No.5, TR-34775 Umraniye / Istanbul, Turkey Tel: +90-216-526-3990 Mitsuhishi Electric Furnos R.V. Polish Branch missubishi Electric Europe B.V. Polish Braul. Krakowska 50, 32-083 Balice, Poland Tel: +48-12-347-65-00 Mitsubishi Flectric (Puesia) 11.0 o. pe B.V. Polish Branch

1el: +48-12-347-65-00 Mitsubishi Electric (Russia) LLC St. Petersburg Branch Piskarevsky pr. 2, bld 2, lit "Sch", BC "Benua", office 720; RU-195027 St. Petersburg, Russia

Adroit Technologies 20 Waterford Office Park, 189 Witkoppen Road, Fourways, Johannesburg, South Africa 20 Waterford Office Park, 189 Witkoppen Road, Fourways, Johannesburg, South Africa Tet +27-11-658-8100 Mitsubishi Electric Automation (China) Ltd. No. 1386 Hongrian Road, Mitsubishi Electric Automation Center, Shanghai, China Tet +86-21-2322-3030 SETSUYO ENTERPRISE CO., LTD. 6F. No. 105, Wugong 304 Road, Wugu District, New Taipei City 24889, Taiwan Tet +868-22298-2489 SETSUYO ENTERPRISE CO., Ltd.

Milsubishi Electric Automation Korea Co., Ltd.
7F-9F, Gangseo Hangang Xi-tower A, 401, Yangcheon-ro, Gangseo-Gu, Seoul 07528, Korea
Tel: ∗82-2-3660-9530 Singapore

Tel: +82-2-3680-9530
Mitsubishi Electric Asia Pte. Ltd.
307 Aloxandra Road, Mitsubishi Electric Building, Singapore 159943
Tel: +65-6473-2308
Mitsubishi Electric Factory Automation (Thailand) Co., Ltd.
21x Floor, SV. City Building, Office Tower 1, No. 8961/9 and 20 Rama 3 Road,
Kwaeng Bangpongpang, Khet Yannawa, Bangkok 10120, Thailand
Tel: +66-2882-652/20 a1
PT. Mitsubishi Electric Indonesia
Gedung Jaya 11th Floor, Jt. MH. Thamrin No.12, Jakarta Pusat 10340, Indonesia
Tel: +62-21-3192-6461
Mitsubishi Electric Vietnam Co., LTD. Ho Chi Minch Head Office
Unit 01-04, 10th Floor, Vincom Center, 72 Le Thanh Ton Street, District 1,
Ho Chi Minc (Civ. Vietnam
Tel: +848-3910-5945

rer: +64-8-3910-5945 Misubishi Electric India Pvt. Ltd. Pune Branch Emerald House, El. -3. J Block, M.I.D.C., Bhosari, Pune - 411026, Maharashtra, India Tel: +91-20-2710-2000

# Misubishi Electric Australia Py. Ltd. Misubishi Electric Australia Py. Ltd. All Victoria Road, P.O. Box 11, Rydalmere, N.S.W. 2116, Australia Tel: +61-2-9684-7777

MITSUBISHI ELECTRIC CORPORATION FICE : TOKYO BUILDING, 2-7-3 MARUNOUCHI, CHIYODA-KU, TOKYO 100-8310 A WORKS : 1-14, YADA-MINAMI 5-CHOME, HIGASHI-KU, NAGOYA, When exported from Japan, this manual does not require application to the Ministry

of Economy, Trade and Industry for service transaction per

Specifications subject to change without notice Printed in Japan, June 2018.