



Programmable Controller MELSEC iO-F





MELSEC iQ-F FX5-16FT/FΠ-H

Hardware Manual



Manual Number	JY997D64401
Revision	E
Date	July 2023

This manual describes the part names, dimensions, and specifications of the product. Before use, read this manual and manuals of relevant products fully to acquire proficiency in handling and operating the product. Make sure to learn all the product information, safety information, and precautions

And, store this manual in a safe place so that you can take it out and read it whenever necessary. Always forward it to the end user.

The company name and the product name to be described in this manual are the registered trademarks or trademarks of each company.

Specifications are subject to change without notice.

© 2016 MITSUBISHI ELECTRIC CORPORATION

Safety Precautions (Read these precautions before use.)

This manual classifies the safety precautions into two categories:

MARNING and MCAUTION

<u></u> <u>MARNING</u>	Indicates that incorrect handli conditions, resulting in death of
∴ CAUTION	Indicates that incorrect handli conditions, resulting in mino property damage.

ing may cause hazardou or severe injury.

ing may cause hazardous or moderate injury

Depending on the circumstances, procedures indicated by ACAUTION may also cause severe injury.

It is important to follow all precautions for personal safety

Associated Manuals

Manual name	Manual No.	Description
MELSEC iQ-F FX5S/ FX5UJ/FX5U/FX5UC User's Manual (Hardware)	SH-082452ENG	Describes the details of hardware of the CPU module, including performance specifications, wiring, installation, and maintenance.
MELSEC iQ-F FX5 User's Manual (Application)	JY997D55401	Describes the basic knowledge required for program design, functions of the CPU module, devices/labels, and parameters.

How to obtain manuals

For the necessary product manuals or documents, consult with your local Mitsubishi Electric representative

Applicable standards

FX5-16ET/ES-H, FX5-16ET/ESS-H comply with the EU Directive (EMC Directive), UL standards (UL, cUL) and UKCA marking.

→ MELSEC iQ-F FX5S/FX5UJ/FX5U/FX5UC User's Manual (Hardware) Regarding the standards that relate to the CPU module, please refer to either the product catalog or consult with your nearest Mitsubishi product provider.

This product is designed for use in industrial applications

1 Outline

FX5-16ET/ED-H high-speed pulse input/output module (hereinafter called high-speed pulse input/output module) connects to the FX5 CPU module to expand the high-speed input/output function. High-speed input/output module can be used as general input/

For details including installation, wiring, and system configuration, refer to the following

→ MELSEC iQ-F FX5S/FX5UJ/FX5U/FX5UC User's Manual (Hardware)

1.1 Incorporated Items

Model	Included Items	
	Product	1 module
FX5-16ET/ES-H FX5-16ET/ESS-H	Dust proof protection sheet	1 sheet
	Hardware manual (This manual)	1 manual


1.2 Function

For function details, parameter settings, and program examples, refer to the following

→ MELSEC iQ-F FX5 User's Manual (Application)

1.3 External Dimensions and Part Names

Unit: mm



[8] Extension connector

[10] DIN rail mounting groove

[11] DIN rail mounting hooks


(DIN rail: DIN46277, 35 mm wide)

[9] Name plate

- [1] Output display LED (green) [7] Terminal block (M3 screw)
- [2] Top cover
- [3] Pullout tab
- [4] Extension cable
- [5] POWER LED (green) [6] Input display LED (green)

1.4 Terminal Layout

FX5-16FT/FS-H



2. Specifications

STARTUP AND MAINTENANCE **↑** CAUTION RECAUTIONS Do not disassemble or modify the PLC

Doing so may cause fire, equipment failures, or malfunctions. For repair, contact your local Mitsubishi Electric representative.

Do not drop the product or exert strong impact to it. Doing so may cause damage

DISPOSAL PRECAUTIONS **↑**CAUTION

Please contact a certified electronic waste disposal company for the environmentally safe recycling and disposal of your device.

↑CAUTION RECAUTIONS

The product is a precision instrument. During transportation, avoid impacts large than those specified in the general specifications by using dedicated packaging boxes and shock-absorbing palettes.

Failure to do so may cause failures in the product After transportation, verify operation of the product and check for damage of the mounting part, etc.

2.1 Applicable CPU module

Model name	Applicability
FX5UJ CPU module	Ver. 1.030 or later
FX5U CPU module	Ver. 1.030 or later
FX5UC CPU module*1	Ver. 1.030 or later

*1 EX5-CNV-IEC or EX5-C1PS-5V is necessary to connect EX5-16ET/EII-H with the EX5LIC CPLI module

2.2 General Specifications

The general specifications are same with the CPU module specifications to be

For general specifications, refer to the following manuals

→ MELSEC iQ-F FX5S/FX5UJ/FX5U/FX5UC User's Manual (Hardware)

2.3 Power Supply Specification

Item	Specification
Rated voltage	5 V DC (internal power) 24 V DC (24 V DC service power supply or external power supply)
Current consumption	100 mA/5 V DC 125 mA/24 V DC (The current of the input circuit is included.)

2.4 Input Specification

ITE	em	Specif	ication
No. of input points		8 points	
Connection type		Terminal block (M3 screw	1)
Input type		Sink/source	
Input signal volta	age	24 V DC +20%, -15%	
Input signal curr	ent	5.3 mA/24 V DC	
Input impedance	•	4.3 kΩ	
ON input sensiti	vity current	3.5 mA or more	
OFF input sensi	tivity current	1.5 mA or less	
Input response	X□ to X□+5*1	200 kHz	
frequency	X□+6, X□+7*1	10 kHz	
Pulse waveform	Waveform	<u>* T1 * T1 * </u>	
wavelolili		T1 (pulse width)	T2 (rise/fall time)
	X□ to X□+5*1	2.5 μs or more	1.25 μs or less
	X□+6, X□+7*1	50 μs or more	25 μs or less

Item		Specification	
Input response	X□ to X□+5*1	ON: 2.5 μs or less OFF: 2.5 μs or less	
time (H/W filter delay)	X□+6, X□+7 ^{*1}	ON: 30 μs or less OFF: 50 μs or less	
Input response time (Digital filter setting value)		None, $10~\mu s$, $50~\mu s$, $0.1~m s$, $0.2~m s$, $0.4~m s$, $0.6~m s$, $1~m s$, $5~m s$, $10~m s$ (initial values), $20~m s$, $70~m s$ When using this product in an environment with much noise, set the digital filter.	
Input signal format		No-voltage contact input Sink: NPN open collector transistor Source: PNP open collector transistor	
Input circuit insulation		Photo-coupler insulation	
Indication of input operation		LED is lit when input is on	

*1 D: Head input number of each high-speed pulse input/output module

2.5 Output Specification

	Item	Specification	
No. of output points		8 points	
Connection ty	/ре	Terminal block (M3 screw)	
0	FX5-16ET/ES-H	Transistor/sink output	
Output type	FX5-16ET/ESS-H	Transistor/source output	
Maximum free	quency	200 kpps	
External power	er supply	5 to 30 V DC	
Max. load		1.6 A/8 points common	
Open circuit leakage current		0.1 mA or less/30 V DC	
Voltage drop	Y□, Y□+1, Y□+4, Y□+5 ^{*1}	1.0 V or less	
when ON	Y□+2, Y□+3, Y□+6, Y□+7 ^{*1}	1.5 V or less	
Response time	Y□, Y□+1, Y□+4, Y□+5*1	2.5 μs or less/10 mA or more (5 to 24 V DC)	
	Y□+2, Y□+3, Y□+6, Y□+7 ^{*1}	0.2 ms or less/200 mA or more (24 V DC)	
Output circuit insulation		Photo-coupler insulation	
Indication of output operation		LED is lit when output is on	
*1 □: Head	output number of each high-s	peed pulse input/output module.	

This manual confers no industrial property rights or any rights of any other kind. nor does it confer any patent licenses. Mitsubishi Electric Corporation cannot be held responsible for any problems involving industrial property rights which may occur as a result of using the contents noted in this manual.

Exclusion of loss in opportunity and secondary loss from warranty liability Regardless of the gratis warranty term, Mitsubishi shall not be liable for compensation to:

- (1) Damages caused by any cause found not to be the responsibility of Mitsubishi.
- (2) Loss in opportunity, lost profits incurred to the user by Failures of Mitsubishi products.
- (3) Special damages and secondary damages whether foreseeable or not, compensation for accidents, and compensation for damages to products other than Mitsubishi products.
- (4) Replacement by the user, maintenance of on-site equipment, start-up test run and other tasks

- This product has been manufactured as a general-purpose part for general industries, and has not been designed or manufactured to be incorporated in a device or system used in purposes related to human life.
- Before using the product for special purposes such as nuclear power, electric power, aerospace, medicine or passenger movement vehicles, consult with
- This product has been manufactured under strict quality control. However when installing the product where major accidents or losses could occur if the product fails, install appropriate backup or failsafe functions in the system

MITSUBISHI ELECTRIC CORPORATION