

# MINI DIIPM Ver.4 Series APPLICATION NOTE

## PS21765 / PS21767 / PS21767-V

### Table of contents

CHAPTER 1	Mini DIIPM Ver.4 INTRODUCTION .....	2
1.1	Target Applications .....	2
1.2	Product Line-up .....	2
1.3	Functions and Features .....	2
CHAPTER 2	SPECIFICATIONS AND CHARACTERISTICS .....	4
2.1	Mini DIIPM Ver.4 Specifications .....	4
2.1.1	Maximum Ratings .....	4
2.1.2	Thermal Resistance .....	5
2.1.3	Electric Characteristics (Power Part) .....	5
2.1.4	Electric Characteristics (Control Part) .....	6
2.1.5	Recommended Operating Conditions .....	7
2.1.6	Mechanical Characteristics and Ratings .....	8
2.2	Protective Functions and Operating Sequence .....	8
2.2.1	Short Circuit Protection .....	8
2.2.2	Control Supply UV Protection .....	9
2.3	Package Outlines .....	11
2.3.1	Package Outline Drawing .....	11
2.3.2	Laser Marking .....	12
2.3.3	Terminal Description .....	13
2.4	Mounting Method .....	15
2.4.1	Electric Spacing .....	15
2.4.2	Mounting Method and Precautions .....	15
2.4.3	Soldering Conditions .....	16
CHAPTER 3	SYSTEM APPLICATION HIGHLIGHT .....	17
3.1	Application Guidance .....	17
3.1.1	System connection .....	17
3.1.2	Interface Circuit (Direct Coupling Interface. One shunt) .....	18
3.1.3	Interface Circuit (Opto-coupler Isolated Interface) .....	19
3.1.4	External SC Protection Circuit with Using Three Shunt Resistors .....	20
3.1.5	Circuits of Signal Input terminals and Fo Terminal .....	20
3.1.6	Snubber Circuit .....	23
3.1.7	Recommended Wiring method around Shunt Resistor .....	23
3.1.8	Precaution for wiring on PCB .....	25
3.1.9	Parallel operation of DIIPM .....	26
3.1.10	SQA of Mini DIIPM Ver.4 .....	26
3.1.11	SCSOA .....	27
3.1.12	Power Life Cycles .....	28
3.2	Power Loss and Thermal Dissipation Calculation .....	29
3.2.1	Power Loss Calculation .....	29
3.2.2	Temperature Rise Considerations and Calculation Example .....	31
3.3	Noise Withstand Capability .....	32
3.3.1	Evaluation Circuit .....	32
3.3.2	Countermeasures and Precautions .....	32
3.3.3	Static Electricity Withstand Capability .....	33
CHAPTER 4	KEY PARAMETERS SELECTING GUIDANCE .....	34
4.1	Determination of Shunt Resistance .....	34
4.2	Bootstrap Circuit Operation .....	35
4.2.1	Bootstrap Circuit Operation .....	35
4.2.2	Bootstrap Supply Circuit Current at Switching State .....	36
4.2.3	Note for designing the bootstrap circuit .....	36
CHAPTER 5	Interface Demo Board .....	38
5.1	Mini DIIPM Ver.4 Interface Demo Board .....	38
5.2	Pattern Wiring .....	39
5.3	Circuit Schematic and Parts List .....	40
CHAPTER 6	PACKAGE HANDLING .....	42
6.1	Packaging Specification .....	42
6.2	Handling Precautions .....	43