



# **Auxiliary Power Supply System**



## **Ensuring High Levels of Safety and Reliability**

#### **Compact and Lightweight**

Size/Weight reduced 34% compared to conventional auxiliary power supply (APS) system

- Dimensions: 1,900×900×500mm(L×W×D)
- Weight: Approx. 640kg
- More compact high-frequency transformer
- Function module adopted

### **High Efficiency**


# Advanced power device achieving up to 95%\* efficiency

- High-efficiency system contributing to energy savings and low operating costs
- \*\* Maximum efficiency using AC output only; may vary depending on system configuration and service conditions.

#### **Excellent Output Voltage Control**

# Ensures stable output voltage in response to load changes

 High-speed instantaneous voltage waveform control realizing stable operation even after sudden load changes or short circuits



## Specifications for APS (including low-voltage power supply)


#### 50kVA model


Normal input voltage:	750VDC	Three-phase AC output: Output voltage Output power	208 to 400VAC ±5% (selectable) 50kVA (rated)
Dimensions (mm): L×W×D	1,900×900×500 (when roof-mounted)		
Weight:	Approx. 640kg		
Cooling system:	Forced air cooling		
Mounting:	Roof-mounted or Under floor	Degree of protection for electrical equipment:	IP65
Applicable standards:	IEC60077-1 IEC61287-1 EN50121-3-2	Options: (not included in standard specifications)	<ul><li>Single-phase AC output</li><li>Power supply to start flat battery</li><li>AC output parallel synchronous function</li><li>Shore power supply function</li></ul>

### **High-redundancy Design (Option)**

# Prevents interruption of power supply to load and enables simple back-up operation

- Compatible with AC output parallel synchronous operation
  - → No interruption of power supply to loads even if one APS unit stops due to a loss of contact between the pantograph and contact wire





#### MITSUBISHI ELECTRIC CORPORATION

www.MitsubishiElectric.com