





Auxiliary Power Supply System



Ensuring High Levels of Safety and Reliability

Compact and Lightweight

Size/Weight reduced 34% compared to conventional auxiliary power supply (APS) system

- Dimensions: 1,900×900×500mm(L×W×D)
- Weight: Approx. 640kg
- More compact high-frequency transformer
- Function module adopted

High Efficiency


Advanced power device achieving up to 95%* efficiency

- High-efficiency system contributing to energy savings and low operating costs
- ** Maximum efficiency using AC output only; may vary depending on system configuration and service conditions.

Excellent Output Voltage Control

Ensures stable output voltage in response to load changes

 High-speed instantaneous voltage waveform control realizing stable operation even after sudden load changes or short circuits



Specifications for APS (including low-voltage power supply)


50VA model


Normal input voltage:	750VDC	_ '	208 to 400VAC ±5% (selectable) 50kVA (rated)
Dimensions (mm): LxWxD	1,900×900×500 (when roof-mounted)		
Weight:	Approx. 640kg		
Cooling system:	Forced air cooling		
Mounting:	Roof-mounted or Under floor	Degree of protection for electrical equipment:	IP65
Applicable standards:	IEC60077-1 IEC61287-1 EN50121-3-2	Options: (not included in standard specifications)	- Single-phase AC output - Power supply to start flat battery - AC output parallel synchronous function - Shore power supply function

High-redundancy Design (Option)

Prevents interruption of power supply to load and enables simple back-up operation

- Compatible with AC output parallel synchronous operation
 - → No interruption of power supply to loads even if one APS unit stops due to a loss of contact between the pantograph and contact wire





MITSUBISHI ELECTRIC CORPORATION

http://www.MitsubishiElectric.com