



IDH - S - L2 HYDRAULIC ELEVATORS

REVERSE ENTRANCE HOLELESS ELEVATORS

STANDARD SPEEDS: 100 FPM AND 125 FPM



NOTES:

1. Complies with ASME A17.1 code. Confirm dimensions comply with local codes and standards.
2. Provide 4" wide divider beam between hoistways if adjacent elevators for rail support.
- ✦ 3. 2100 capacity does not accommodate stretcher.
- ✦✦ 4. 2500 and 3000 capacity only accommodates stretcher when single slide doors are provided.
5. Provide hoisting beam capable of holding 5000 lb. load. Remove after installation if required.

HOLELESS AND SEMI-HOLELESS HOISTWAY DIMENSIONS							
CAPACITY LBS.	HOISTWAY		PLATFORM		INSIDE CLEAR		ENTRANCE
	Width	Depth	Width	Depth	Width	Depth	Width
2100	7' - 6"	6'-7 1/2"	6' - 0"	5' - 7"	5' - 8"	4' - 3"	3' - 0"
2500	8' - 6"	6'-7 1/2"	7' - 0"	5' - 7"	6' - 8"	4' - 3"	3' - 6"
3000	8' - 6"	7'-0 1/2"	7' - 0"	6' - 0"	6' - 8"	4' - 8"	3' - 6"
3500	8' - 6"	7'-8 1/2"	7' - 0"	6' - 8"	6' - 8"	5' - 4"	3' - 6"
4000	9' - 6"	7'-8 1/2"	8' - 0"	6' - 8"	7' - 8"	5' - 4"	4' - 0"

FORM 535-2 041706D