

HIGH POWER SWITCHING USE INSULATED PACKAGE



APPLICATION

AC motor control of forklift (battery power source), UPS



HIGH POWER SWITCHING USE **INSULATED PACKAGE**

ABSOLUTE MAXIMUM RATINGS (Tj = 25°C unless otherwise specified.)

Symbol	Item	Conditions	Rating	Unit
VDSS	Drain-source voltage	G-S Short	150	V
Vgss	Gate-source voltage	D-S Short	±20	V
lD	Drain current	$Tc' = 122^{\circ}C^{*3}$	100	Α
lом	Torain current	Pulse*2	200	Α
IDA	Avalanche current	$L = 10\mu H \text{ Pulse}^{*2}$	100	Α
Is*1	Source current		100	Α
Ism*1	Source current	Pulse*2	200	Α
PD* ⁴	Maximum nawar dissination	Tc = 25°C	410	W
Po*4	Maximum power dissipation	$Tc' = 25^{\circ}C^{*3}$	560	W
Tch	Channel temperature		-40 ~ +150	°C
Tstg	Storage temperature		-40 ~ +125	°C
Visol	Isolation voltage	Main terminal to base plate, AC 1 min, f=60Hz, RMS	2500	V
_	Mounting torque	Main Terminal M6	3.5 ~ 4.5	N∙m
		Mounting to heat sink M6	3.5 ~ 4.5	N∙m
_	Weight	Typical value	600	g

$\textbf{ELECTRICAL CHARACTERISTICS} \ (T_{j} = 25^{\circ}\text{C unless otherwise specified.})$

Courselle ed	ltem	Conditions		Limits			Unit
Symbol				Min.	Тур.	Max.	Unit
IDSS	Drain cutoff current	VDS = VDSS, VGS = 0V		_	_	1	mA
VGS(th)	Gate-source threshold voltage	ID = 10mA, VDS = 10V		4.7	6	7.3	V
Igss	Gate leakage current	VGS = VGSS, VDS = 0V		_	_	1.5	μΑ
rDS(on)	Static drain-source	ID = 100A T _j = 25°C		_	4.8	6.6	0
(chip)	On-state resistance	VGS = 15V	Tj = 125°C	_	9.1	_	mΩ
VDS(on)	Static drain-source	ID = 100A	Tj = 25°C	_	0.48	0.66	V
(chip)	On-state voltage	VGS = 15V	Tj = 125°C	_	0.91	_	
	Internal lead resistance	ID = 100A	Tj = 25°C	_	1.2	_	mΩ
RDD'-SS'		terminal-chip	Tj = 125°C	_	1.68	_	
Ciss	Input capacitance	VDS = 10V VGS = 0V VDD = 80V, ID = 100A, VGS = 15V		_	_	50	nF
Coss	Output capacitance			_	_	7	
Crss	Reverse transfer capacitance			_	_	4	
QG	Total gate charge			_	820	_	nC
td(on)	Turn-on delay time	VDD = 80V, $ID = 100A$, $VGS1 = VGS2 = 15VRG = 13\Omega, Inductive load switching operationIS = 100A$		_	_	400	- ns
tr	Rise time			_	_	250	
td(off)	Turn-off delay time			_	_	450	
tf	Fall time			_	_	200	
trr*1	Reverse recovery time			_	_	200	ns
Qrr*1	Reverse recovery charge			_	6.5	_	μС
Vsp*1	Source-drain voltage	Is = 100A, VGS = 0V		_	_	1.3	V
Rth(j-c)	Thermal resistance	MOSFET part (1/6 module)*7 MOSFET part (1/6 module)*3		_	_	0.30	K/W
Rth(j-c')	Thermal resistance			_	_	0.22	
Rth(c-s)	Contact the sum of vaciots	Case to fin, Thermal grease Applied*8 (1/6 module)		_	0.1	_	
Rth(c'-s')	Contact thermal resistance Case to fin, Thermal grease Applied		³ (1/6 module)	_	0.09	_	

NTC THERMISTOR PART

Symbol	Parameter	Conditions	Limits			I India
			Min.	Тур.	Max.	Unit
R ₂₅ *6	Resistance	$TTH = 25^{\circ}C^{*5}$	_	100	_	kΩ
B*6	B Constant	Resistance at TTH = 25°C, 50°C*5	_	4000		K

^{*7:} Tc measured point is shown in page OUTLINE DRAWING. *8: Typical value is measured by using thermally conductive grease of λ =0.9 W/(m·K).



^{*11:} It is characteristics of the anti-parallel, source to drain free-wheel diode (FWDi).
*2: Pulse width and repetition rate should be such that the device junction temperature (Tj) does not exceed Tj max rating.


^{*3:} Tc' measured point is just under the chips. If use this value, Rth(s-a) should be measured just under the chips. *4: Pulse width and repetition rate should be such as to cause negligible temperature rise.


^{*5:} TTH is thermistor temperature.

^{*6:} B = (InR1-InR2)/(1/T1-1/T2) R1: Resistance at T1(K), R2: Resistance at T2(K)


HIGH POWER SWITCHING USE INSULATED PACKAGE


PERFORMANCE CURVES







DRAIN-SOURCE VOLTAGE VDS (V)












DRAIN-SOURCE VOLTAGE VDS (V)





HIGH POWER SWITCHING USE INSULATED PACKAGE











101

0 20 40 60 80


HALF-BRIDGE


DRAIN CURRENT ID (A)



Inductive load

100 120 140






HIGH POWER SWITCHING USE INSULATED PACKAGE

REVERSE RECOVERY CHARACTERISTICS OF FREE-WHEEL DIODE (TYPICAL) 10³ 3 10² 7 5 Irr (A), trr (ns) 3 Conditions: 10¹ VDD = 80V5 $VGS = \pm 15V$ $Rg = 13\Omega$ 3 Tj = 25°C 100 L 101 Inductive load 2 3 5 7 **10**² SOURCE CURRENT Is (A)

CHIP LAYOUT



The company name and product names herein are the trademarks and registered trademarks of the respective companies.



Important Notice

The information contained in this datasheet shall in no event be regarded as a guarantee of conditions or characteristics. This product has to be used within its specified maximum ratings, and is subject to customer's compliance with any applicable legal requirement, norms and standards.

Except as otherwise explicitly approved by Mitsubishi Electric Corporation in a written document signed by authorized representatives of Mitsubishi Electric Corporation, our products may not be used in any applications where a failure of the product or any consequences of the use thereof can reasonably be expected to result in personal injury.

In usage of power semiconductor, there is always the possibility that trouble may occur with them by the reliability lifetime such as Power Cycle, Thermal Cycle or others, or when used under special circumstances (e.g. condensation, high humidity, dusty, salty, highlands, environment with lots of organic matter / corrosive gas / explosive gas, or situations which terminals of semiconductor products receive strong mechanical stress). Therefore, please pay sufficient attention to such circumstances. Further, depending on the technical requirements, our semiconductor products may contain environmental regulation substances, etc. If there is necessity of detailed confirmation, please contact our nearest sales branch or distributor.

The contents or data contained in this datasheet are exclusively intended for technically trained staff. Customer's technical departments should take responsibility to evaluate the suitability of Mitsubishi Electric Corporation product for the intended application and the completeness of the product data with respect to such application. In the customer's research and development, please evaluate it not only with a single semiconductor product but also in the entire system, and judge whether it's applicable. As required, pay close attention to the safety design by installing appropriate fuse or circuit breaker between a power supply and semiconductor products to prevent secondary damage. Please also pay attention to the application note and the related technical information.

Keep safety first in your circuit designs!

Mitsubishi Electric Corporation puts the maximum effort into making semiconductor products better and more reliable, but there is always the possibility that trouble may occur with them. Trouble with semiconductors may lead to personal injury, fire or property damage. Remember to give due consideration to safety when making your circuit designs, with appropriate measures such as (i) placement of substitutive, auxiliary circuits, (ii) use of non-flammable material or (iii) prevention against any malfunction or mishap.

Notes regarding these materials

- •These materials are intended as a reference to assist our customers in the selection of the Mitsubishi Electric Semiconductor product best suited to the customer's application; they do not convey any license under any intellectual property rights, or any other rights, belonging to Mitsubishi Electric Corporation or a third party.
- •Mitsubishi Electric Corporation assumes no responsibility for any damage, or infringement of any thirdparty's rights, originating in the use of any product data, diagrams, charts, programs, algorithms, or circuit application examples contained in these materials.
- •All information contained in these materials, including product data, diagrams, charts, programs and algorithms represents information on products at the time of publication of these materials, and are subject to change by Mitsubishi Electric Corporation without notice due to product improvements or other reasons. It is therefore recommended that customers contact Mitsubishi Electric Corporation or an authorized Mitsubishi Electric Semiconductor product distributor for the latest product information before purchasing a product listed herein.

The information described here may contain technical inaccuracies or typographical errors. Mitsubishi Electric Corporation assumes no responsibility for any damage, liability, or other loss rising from these inaccuracies or errors.

Please also pay attention to information published by Mitsubishi Electric Corporation by various means, including the Mitsubishi Electric Semiconductor home page (http://www.MitsubishiElectric.com/semiconductors/).

- •When using any or all of the information contained in these materials, including product data, diagrams, charts, programs, and algorithms, please be sure to evaluate all information as a total system before making a final decision on the applicability of the information and products. Mitsubishi Electric Corporation assumes no responsibility for any damage, liability or other loss resulting from the information contained herein.
- •Mitsubishi Electric Corporation semiconductors are not designed or manufactured for use in a device or system that is used under circumstances in which human life is potentially at stake. Please contact Mitsubishi Electric Corporation or an authorized Mitsubishi Electric Semiconductor product distributor when considering the use of a product contained herein for any specific purposes, such as apparatus or systems for transportation, vehicular, medical, aerospace, nuclear, or undersea repeater use.
- •The prior written approval of Mitsubishi Electric Corporation is necessary to reprint or reproduce in whole or in part these materials.
- •If these products or technologies are subject to the Japanese export control restrictions, they must be exported under a license from the Japanese government and cannot be imported into a country other than the approved destination.
- Any diversion or re-export contrary to the export control laws and regulations of Japan and/or the country of destination is prohibited.
- •Please contact Mitsubishi Electric Corporation or an authorized Mitsubishi Electric Semiconductor product distributor for further details on these materials or the products contained therein.

Generally the listed company name and the brand name are the trademarks or registered trademarks of the respective companies.