

Logging Unit for Energy Measuring Unit (EcoMonitorLight, EcoMonitorPlus)

If you are considering using this unit for special purpose such as nuclear power plants User's Manual (Digest) | aerospace, medical care or passenger vehicles please refer to our sales representative.

·Before using this unit, please read both this manual and Details carefully and pay attention to

safety to handle this unit correctly.

·Make sure that the end users read this manual and then keep the

manual in a safe place for future reference

ABOUT MANUALS

You can download User's manual (Details) of this unit from the following site. http://www.mitsubishielectric.com/fa/worldwide/index.html

(1) This unit can memorize the data of various quantities related to electricity such as voltage, current, power and energy (hereinafter referred to as measured data) measured by Energy Measuring Unit (EcoMonitorLight), EcoMonitorPlus for a certain period.

(2) Memorized measured data can be output to an SD memory card in CSV format.

(3) You can check the data files output to the SD memory card by Microsoft Excel or GX LogViewer (Version 1.30G or

Microsoft Excel is the registered trademark of the U.S. Microsoft Corporation in the U.S.

The SD and SDHC logos are either registered trademarks or trademarks of SD-3C, LLC.



The following items for this device are included in package. Check that no items are missing (1) Logging Unit x1 (2) Battery (EMU4-BT) x1 *Stored in the battery box (3) User's Manual (Digest) x1

3, Safety Precautions

2. Checking package contents

3.1 Precautions for Operating Environment and Conditions This Unit is premised on being used in pollution degree II environment. When used in higher pollution degree, protect this unit from pollution on another device side to be incorporated. (For the definition of the pollution degree and the over

voltage category, refer to EN6(1010-1/2010.)

Do not use this product in the places listed below. Failure to follow the instruction may cause malfunctions and a life decrease of product

Places the operating humidity exceeds the range from 30 to 85%RH or places with dewfall

Places in strong electromagnetic field or places large amounts of external noise exist
 Places the operating temperature exceeds the range from -5 to +55°C
 Places exposed to direct sunlight

Operating altitude exceeds 2000m ·Vibration and impact exceed the specifications

· Places exposed to rain or water drop

· Places metal fragments or conductive substance are flying

Rack view

This unit is the open type device, which are designed to be housed within another device for prevention of electric

shock. House this unit within the device such as the control panel before use. (Indoor use)

3.2 Matters concerning the precaution before use Use the unit in specified usage environment and conditions

3.3 Installation and Wiring Precautions

⚠ Danger	 Do not touch the electrically charged portion. It may cause electric shock, electric burn injury or burnout of the device. Work under the electric outage condition when installing.
≜ Caution	-Any person who is involved in installation and winnig of this unlabould be fully competent to do his work. Work under electric uduage condition when installing and witing. Failure to do so may cause electric shock, a failure of the unit, a fire etc. "When tapping or whiting below care not to enter any foreign objects such as object and we pieces into this unit. "Check the connection way when connecting to the Energy Measuring Unit. Wrong wiring may cause failure of the unit all for or relettric shock."


Removed lithium batteries may have electric charge. Store them separately so as not to touch other metal, otherwise evolution of heat, burst or ignition may occur.

Left_side view

3.8 About packaging materials and this manual

For reduction of environment load, packaging materials are produced with cardboard

Front view



< Name and function of each part >

No.	Name	Function			
This indicates a state of logging operation. Tum or Logging in comparing Tum of Logging is stopped Birk slowly In-10 (5 especials) (Change of logging condition settings finished Birk quidely In-2 (30 seconds) (Change of logging condition settings finished Birk quidely In-2 (In-10 consumera) (In-10 c					
2)	SD C. LED	This indicates a state of communication with the SD memory card. Turn on: Communicating Turn off: Stop communicating Blink quickly N=2 : SD memory card error (N=4 3)			
3)	BAT. LED	This indicates a state of battery voltage. Turn on: Low battery voltage (Note 4) Turn off: Normal battery voltage			
4)	Battery box	This stores a battery to back up present time data, logging data and system log data.			
5)	SD memory card slot	This is a slot to insert an SD memory card.			
6)	Battery connector	This connects a battery.			
7)	IEC rail stop	This is used to fix to an IEC rail.			
8)	Connection stop	This is used to connect the Logging Unitto the Energy Measuring Unit.			
9)	Connector	This is used to connect the Energy Measuring Unit.			

[Note 1] Blink slowly: Repetition of 0.5-second on and 0.5-second off

[Note 2] Blink quickly: Repetition of 0.25-second on and 0.25-second off

[Note 3] Refer to "Error display and measures" if this indicates.
[Note 4] resent time data and logging data are erased by power-off with battery voltage low. ("Logging ID" "Logging mode", "Logging start time", "Detailed data logging cycle" and "Logging item" are not eras which are memorized in the nonvolatile memory.) If BAT.LED turns on, change a battery.

3.4 Precautions for Use

· Before operating the product, check that active bare wire and so on does not exist around the product. If any exposed conductor is found, stop the operation immediately, and take an appropriate action such as isolation protection. In the event of a power outage during the setting, the unit is not set correctly. Please set again after power recovery.

During communication with the SD memory card, the operations such as power-off, reset and ejection of the memory card may cause data corruption of the memory card or failure of this unit or the memory card. Power off or reset the

unit, or eject the SD memory card afterchecking that SD CLED turns off.

Make sure to use the SD memory card afterchecking Missubsit Electric Corporation (Model EMU4-SD2GB).

Using the other types of the SD memory card may cause the trouble such as data destruction of the memory card or system failure. For the SD memory card on the market, please refer to the Sales and Service No YAMA192 from our

system nature. For the SU friethery card on the inflated, please return the Saltes after Service Nov. Nov. 1s. crim to Friedram (1) and the Service Nov. 1s. crim to the Service Nov. 1s. crim to the Service Nov. 1s. crim to Friedram at SID memory card the two syspecified in this manual Format is done already as of the purchase, so a SD memory card made by Misubishi Electric Corporation (Model EMLH-SD2CSB) has use just as it is, and is no problem -insert the SD memory card with the wite protect switch "OFF. If the write protect switch "OFF," read-write to the SD memory card is stonned

Present time data and logging data are erased by power-off with BAT. LED on. ("Logging ID", "Logging mode", "Logging start time", "Detailed data logging cycle" and "Logging item" are not erased, which are memorized in the nonvolatile memory) IEBAT. LED turns on, cutput logging data to the SD memory card and change a battery.

All logging data of the Logging Unitis erased when you change the setting of "Phase wire system", "Primary voltage (Use or non-use of VT, Direct Voltage, "Primary voltage with VT, Special primary voltage; "Primary cut (Direct sensor, 3-6 sensor, Special primary current.)" or "Sensor type" of the Energy Measuring Unit(EcoMontlot).git Model. EMU4-BD1-MB/EMU4-HD1-MB. EcoMonitorPlus Model: EMU4-BM1-MB/EMU4-HM1-MB/EMU4-VA2/EMU4-A2) All logging data of the Logging Unitis erased when you change the setting of "Phase wire system" and "Measurement mode" of the Energy Measuring Unit with Insulation Monitoring (EcoMonitorPlus Model: EMU4-LG1-MB). Before changing the setting of the Energy Measuring Unit, output the logging data to the SD memory card and check the output data in the PC whether the logging data is memorized properly

All loggling data of the Loggling billise crased when you change the setting of "Present time", "Loggling mode", "Loggling slart iner", "Detailed data loggling cycle" or "Loggling Item" of the Loggling Unit. Before changing the setting of the Loggling Unit, output the loggling data to the SD memory card and check the output data in the Po whether the logging data is memorized properly

The Logging Unit should not be used for multiple Energy Measuring Units. Otherwise all logging data of the Logging Unit may be erased, or there may be some data for different Energy Measuring Units in the Logging Unit.

. ,	,	,	3,	9	55 5	
<u> </u>	of the device.	electrically charged p lectric outage condition	,	electric shock	k, electric burn injury o	or burnout
∆ Caution	Do not disassemb	le or modify this unit.	It may cause failure,	malfunction,	injury or fire.	

3.5 Maintenance Precautions

 Use a soft dry cloth to clean off dirt of the unit surface. Do not let a chemical cloth remain on the surface for an extended period of time nor wipe the surface with thinner or benzine.

· Check for the following items to use this unit properly for long time.

<Daily maintenance> (1) No damage on this unit

(2) No abnormality with LED indicators

(3) No abnormal noise smell or heat 3.6 Storage Precautions

To store this unit, put it in a plastic bag.

For long-time storage, avoid the following places. Failure to follow the instruction may cause a failure and reduced life of

 Places the relative humidity exceeds the range from 30 to 85% or places with dewfall Places the storage temperature exceeds the range from -10 to +60°C


·Places the average daily temperature exceeds +35°C ·Vibration and impact exceed the specifications · Dust, corrosive gas, saline and oil smoke exist · Places exposed to rain, water drop or direct sunlight

·Places metal fragments or conductive substance are flying

3.7 Disposal Precautions

When disposing of this unit treat it as industrial waste.





Information for end-users Annex II. This symbol means that electrical and electronic equipment, batteries and accumulators, at their end-of-life should be disposed of separately from your household waste

5. Procedure for operation Procedure for operation of this unit is as follows: Please refer to User's Manual (Details)

No.	Procedure	Content				
1)	Connect the battery to the Logging Unit	Refer to this manual 6.1 "How to connect the battery".				
2)	Connect the Logging Unit to the Energy Measuring Unit	y Refer to this manual 6.2 "How to connect the Logging Unit".				
3)	Mount the Energy Measuring Unit and the Logging Unit to the panel	Refer to this manual 7 "Installation". * Refer to User's manual (Details) of Logging Unit about "Panel mounting".				
4)	Turn on the Energy Measuring Unit					
5)	Set the present time of the Logging Unit	EcoMonitorLight : Refer to User's manual (Details) "Set the present time" o Energy Measuring Unit				
		EcoMonitorPlus : Refer to User's manual (Details) "Clock setup—the settings for the clock" of Small Type Display Unit for Energy Measurin Unit				
6)	Set logging ID of the Logging Unit	EcoMonitorLight: Refer to User's manual (Details) "Setting menu 5: Logging setting" of Energy Measuring Unit.				
		EcoMonitorPlus : Refer to User's manual (Details) "Logging setup—the setting for the logging ID" of Small Type Display Unit for Energ Measuring Unit.				
7)	Set logging condition in the Logging Unit	Refer to User's manual (Details) 7 Directions "Set condition in the Logging Unit" of Logging Unit.				
		 For setting, it is necessary to create a setting file using Logging unit utility Microsoft Excel 				
		 Setting is necessary when connecting to Energy Measuring Unit with Insulation Monitoring. If not setting, an error occurs (system log codes: 902). 				

6.1 How to connect the battery



(3)Fix the battery box to the Logging Unit.




Work under the electric outage condition when connecting and disconnecting battery. Failure to do so may cause electric shock, a failure of the unit, a fire

6.2 How to connect the Logging Unit

*This unit can be attached to EcoMonitorLight in below. This unit can be attached to EcoMonitorPlus as well. *In EcoMonitorPlus, connect to the base unit (model name: EMU4-BM1-MB/EMU4-HM1-MB/EMU4-LG1-MB/

(1) Remove the blank label stuck to the left side of the Energy (2) Insert the connector of the Logging Unit into that of the Energy Measuring Unit and contact the unit




pside and downside of the Logging Unit to lock it.



6.3 How to insert the SD memory card

ory card straight into the slot until it clicks into place




Make sure to use the SD memory card manufactured by Mitsubishi Electric Corporation (Model EMU4-SD2GB). Using the other types of the SD memory card may cause the trouble such as data destruction of the memory card or system failure.

Format an SD memory card in the way specified in this manual.

Insert the SD memory card with the write protect switch "OFF". Otherwise read/write to the SD memory


6.4 How to eject the SD memory card

Push the SD memory card in until it clicks into place. The SD memory card comes out by itself.



During communication with the SD memory card, ejection of the memory card may cause data corruption of the memory card or failure of this unit or the memory card. Check that SD C.LED tums off to eject the SD memory card.

8. Dimensions



<Basic specifications>

	ILEITI	Specifications					
Mo	del	EMU4-LM					
Rating		6.4V DC (powered by the Energy Measuring Unit)					
Co	mpensation for power ure	Battery (EMU4-BT) Total time of compensation is 1 year (average daily temperature is not more than +35°C). It is recommended that the battery is changed every 3 years.					
	Setting values	Memorized in FRAM (nonvolatile memory) The data is not erased during power failure.					
	Logging data	Memorized in SRAM (volatile memory)					
	System log data Timing	Data is erased if power failure occurs under low battery voltage condition (BATLED turns on). Timing is stopped if power failure occurs under low battery voltage condition (BATLED turns on). After power recovery, triming is started from Jan 1, 2013 00:00:00.					
	ick accuracy	1 minute per month					
Memory media for data output [Note 1]		SD memory card (SD, SDHC)					
Accommodating model		Energy Measuring Unit EcoMonitorLight Model: EMU4-BD1-MB/EMU4-HD1-MB EcoMonitorPlus Model: EMU4-BD1-MB/EMU4-HD1-MB ECOMonitorPlus Model: EMU4-BD1-MB/EMU4-HD1-MB EMU4-V2/EMU4-PX4/EMU4-AX4					
Standard		EMC: EN-61326-1: 2013					
Us	age environment						
	Operating temperature	-5°C to +55°C (average daily temperature is not more than +35°C)					
	Operating humidity	30% to 85%RH (No condensation)					
	Storage temperature	-10°C to +60°C					
	Operating altitude	2000m or lower					
Mass		0.1kg (Mass of the Logging Unit only)					
Optional part		SD memory card (EMU4-SD2GB) [Note 1] [Note 2]					
Op	tional supplies	Battery (EMU4-BT) (Note 2)					
Not	e 1] Make sure to use t	he SD memory card manufactured by Mitsubishi Electric Corporation (Model EMU4-SD2GE					


Using the other types of the SD memory card may cause the trouble such as data destruction of the memory card or system failure. For the SD memory card on the market, please refer to the Sales and Service No.YAMA192 from our site. [Note 2] For purchase of optional parts or supplies, contact the shop you bought this product.

There are two installation methods, surface mounting and panel mounting. Refer to User's manual (Details) of Logging Unit about "Panel mounting

(1) How to mount to an IEC rail

Applicable IEC rail

*This unit can be attached to EcoMonitorLight in below. This unit can be attached to EcoMonitorPlus as well.



(2) JIS agreement type attachment

*This unit can be attached to EcoMonitorLight in below. This unit can be attached to EcoMonitorPlus as well.



1	em			Spec	difications					
	Auto updating	Logging is started after comple	ete setup							
Logging mode	Date nomination	Auto start and stop by start tim	ne setting							
Type of logging	Detailed data	Memorize measured data in t 10 minutes, 15 minutes or 30 Data is output as detailed data	minutes).	ed "Detaile	ed data log	ging cycle"	(1 second,	1 minute,	5 minutes	
data	One-hour data	Memorize measured data in one-hour cycle. Data is output as One-hour data file and One-day data file.								
The number of logging items	Detailed data	If the detailed data logging cyc If the detailed data logging cyc				ems				
logging items	One-hour data	Up to 10 items								
					logging pe					
		Number of expansion [Nata]	1 Circuit	2 Circuit	3 Circuit	4 Circuit	5 Circuit	6 Circuit	7 Circuit	
Internal memory logging period	Detailed data	Logging cycle: 1 sec Logging cycle: 1 min Logging cycle: 5 min Logging cycle: 10 min Logging cycle: 15 min Logging cycle: 30 min	20hour 20days 100days 200days 300days 600days	6d 30d 60d 90d 180	6hour 6days 30days 60days 90days 180days		3hour 3days 15days 30days 45days 90days		2hour 2days 10days 20days 30days 60days	
				Maximum	logging pe	riod				
	One-hour data	Number of expansion ^{[N:A(3)}	1 Circuit	2 Circuit	3 Circuit	4 Circuit	5 Circuit	6 Circuit	7 Circuit	
			620days		idays	93d			lays	
		Number of expansion ^[Not(3)]	1 Circuit	2 Circuit	3 Circuit	4 Circuit	5 Circuit	6 Circuit	7 Circuit	
Logging period	with SD memory	Logging cycle: 1 sec	About 10month		About 5month	About 4month	About 3month	About 2month	About 2month	
card (2GB) Note	,	Logging cycle: 1 min	Over 10 years	Over 10 years	Over 10 years	About 8 yeas	About 6 yeas	About 5 yeas	About 4 yeas	
		Logging cycle: 5, 10, 15, 30 m	in → Ove	r 10 years						
System log data	3	3600 records								
Output format of and system log	data	CSV format (ASCII)								

[Note 3] The number of measurement circuits varies depending on the connected unit. For details, please refer to the manual (detail).

[Note 4] It is the period until capacity of 2GB SD memory card is filled in always-on connection. Data amount depends on the number of characters. It is the logging period when data is output in maximum volume. When saving data from multiple Energy Measuring Units on a single SD memory card, make sure that the total period of the saved data does not exceed the maximum logging period.

10. Contained harmful substances (1) 电器电子产品有害物质限制使用标识



根据《电器电子产品有害物质限制使用管理办法》,该标记适用于在中国销售的电器电子产品, 、其中的数字为产品的环保使用期限。只要遵守本产品在安全和使用方面的注意事项,从生产日 ■ 算起的环保使用期限内不会造成环境污染或对人体,财产产生深刻的影响。

注)产品正常使用废弃后,应按照国家和地方的法律法规完成该电器电子产品的回收和再利用。 此环保使用期限不涵盖随产品附带的电池。产品所附带的电池, 其环保使用期限为3年。

(2) 产品中有害物质的名称及含量

本产品中所含有的 6 种有害物质的名称、含有信息及含有部件如下表所示。

产品中有害物质的名称及含量

	有害物质							
部件名称	铅 (Pb)	汞 (Hg)	镉 (Cd)	六价铬 (Cr(VI)	多溴联苯 (PBB)	多溴二苯醚 (PBDE)		
基板	×	0	0	0	0	0		
箱子		0	0	0	0			
铭牌	0	0	0	0	0	0		
电池	0	0	0	0	0	0		
接线	0	0	0	0	0	0		
接线皮	0	0	0	0	0	0		

本表格依据 SJ/T11364 的规定编制。

○:表示该有案物质在该部件所有均质材料中的含量均在 GB/T 26572 规定的限量要求以下 :表示该有害物质至少在该部件的某一均质材料中的含量超出 GB/T26572 规定的限量要求。

且虽然目前业界没有成熟的替代方案, 但是符合欧盟 RoHS 指令要求。

If you have any questions or the product is broken down, contact our sales representative near you. (For details, please see at the end of this manual).

**Graits warranty is effective until the earlier of 1 year after the date of your purchase or 18 months after manufacturing.

**The graits warranty shall apply if the product fails even though it is being used property in the conditions, with the methods and under the environments in accordance with the terms and precuditive described in the callage, the instruction manual, caution label on the

product, etc.

• Repair shall be changed for the following cases even during the gratis warranty period.

• Failures occurring due to your improper storage or handling, carelessness or fault

• Failures due to faulty workmanning

• Failures due to faults in use and undue modification

Failures due to accidental force such as a fire, abnormal voltage, etc. and force maleure such as an earthquake, wind, flood, etc.

- Failures due to matters unpredictable based on the level of solicinos technology at the time of product

• Our company shall not be liable to compensate for any loss arising from events not attributable to our company, opportunity loss and lost
earning of the usotnerer due to failure of the product, and loss, secondary loss, accident compensation, damage to other products besides our products and other operations caused by a special reason regardless of our company's predictability.

If the equipment is used in a manner not specified by the manufacturer, the protection provided by the equipment may be impaired.

⚠ Caution If an abnormal sound, bad-smelling smoke, fever break out from this unit, switch it off promptly and don't use it.

MITSUBISHI ELECTRIC CORPORATION

Please refer to "catalog" or "user's manual (Details)" for more detail.