

Table of Contents

1. Features of the 7th Generation Module	2
1.1. FEATURES OF THE 7TH GENERATION IGBT AND DIODE CHIP	3
1.2. PACKAGING TECHNOLOGY	5
1.3. STRUCTURE (PARTS AND MATERIALS)	7
2. Glossary	9
2.1. COMMON	9
2.2. MAXIMUM RATINGS	10
2.3. TEMPERATURE RATINGS	10
2.4. THERMAL RATINGS AND CHARACTERISTICS	10
2.5. ELECTRICAL CHARACTERISTICS	11
3. Product label information	12
3.1. CONFIGURATION OF THE PART NUMBER	12
3.2. LABELING	13
3.3. TWO-DIMENSIONAL BARCODE CONFIGURATION	13
4. Safety standard (UL Standard)	14
5. Handling Precautions	15
5.1. HANDLING PRECAUTIONS	15
5.2. FLAME RETARDANCE	16
6. Precautions on Actual use	17
6.1. METHOD OF ATTACHING THE MODULE TO THE HEAT SINK	17
6.2. POWER MODULE IMPLEMENTATION	19
6.3. STAND-OFF RECOMMENDED USE (NX TYPE)	21
6.4. THERMALLY CONDUCTIVE (HEAT DISSIPATING) GREASE APPLICATION EXAMPLE	22
6.5. CONCEPT OF THERMAL RESISTANCE	23
6.6. EXAMPLE OF THERMOCOUPLE ATTACHMENT	24
6.7. SNUBBER CIRCUIT	26
6.8. USE OF THERMISTOR	29
6.9. OTHERS	30
7. How to use the IGBT module	31
7.1. IGBT MODULE SELECTION	31
7.2. RECOMMENDED DRIVING CONDITIONS AND DRIVING CIRCUIT	31
7.3. GATE DRIVE POWER SUPPLY	33
7.4. DEAD TIME SETTING	35
7.5. SHORT CIRCUIT PROTECTION	36
7.6. PARALLEL CONNECTION OF IGBT MODULES	39
8. Power loss and heat dissipation design	42
8.1. HOW TO CALCULATE THE POWER LOSS	42
8.2. CALCULATION OF TEMPERATURE RISE	45