MITSUBISHI ELECTRIC INVERTER TECHNICAL NEWS

NAGOYA WORKS

File No.: MF-S-177

Date of issue: 2020-11-4

Modified date: —

MODELS: FR-E800

TITLE: EMC DATA EXAMPLE (FR-E860)

EMC data example when using the filter compliant with the EU EMC Directive shows as below.

FR-E840

Conditions

The inverter conforms to EN61800-3/IEC61800-3 product standard.

The measurement was conducted based on the measurement conditions of 2nd Environment Category C3 described in EN61800-3/IEC61800-3.


(NOTE)The following EMC data example is under the determination value of EN61800-3 as the most strict condition.

Output interconnection (motor) length: 20m

Output cable type :Shielded cable

Inverter frequency :30Hz

Carrier frequency :Indicated above each graph



MITSUBISHI ELECTRIC INVERTER TECHNICAL NEWS

NAGOYA WORKS

File No.: MF-S-177

Date of issue: 2020-11-4


Modified date: —

MODELS: FR-E800

TITLE: EMC DATA EXAMPLE (FR-E860)


EXAMPLE OF MEASUREMENT RESULTS FR-E860-2.2K、FN3288HV-10-44-C34-R65

Conducted noise



(Note) The QP value will not exceed the peak value

Radiated noise (10m site)



(Note) The QP value will not exceed the peak value

MITSUBISHI ELECTRIC INVERTER TECHNICAL NEWS

NAGOYA WORKS

File No.: MF-S-177

Date of issue: 2020-11-4


Modified date: —

MODELS: FR-E800

TITLE: EMC DATA EXAMPLE (FR-E860)


EXAMPLE OF MEASUREMENT RESULTS FR-E860-7.5K、FN3288HV-20-33-C36-R65

Conducted noise



(Note) The QP value will not exceed the peak value

Radiated noise (10m site)



(Note) The QP value will not exceed the peak value