

MITSUBISHI ELECTRIC CORPORATION
PUBLIC RELATIONS DIVISION
7-3, Marunouchi 2-chome, Chiyoda-ku, Tokyo, 100-8310 Japan

FOR IMMEDIATE RELEASE

No. 2791

Customer Inquiries

Media Inquiries

LCD Marketing Dept. Sect. A
Mitsubishi Electric Corporation

Public Relations Division
Mitsubishi Electric Corporation

<http://www.MitsubishiElectric.com/semiconductors/>

prd.gnews@nk.MitsubishiElectric.co.jp
<http://www.MitsubishiElectric.com/news/>


Mitsubishi Electric to Add Two Wide-Screen Touch Panels to Lineup of Color TFT-LCD Modules

TOKYO, October 9, 2013 – [Mitsubishi Electric Corporation](http://www.MitsubishiElectric.com) (TOKYO: 6503) announced today the addition of 7.0-inch WVGA and 12.1-inch WXGA models to their lineup of industrial-use color TFT-LCD modules capable of intuitive operation even with gloved hands. Sales will begin on October 25 at Mitsubishi Electric offices worldwide (www.MitsubishiElectric.com/semiconductors/). Initial production has been set at 2,000 units per month for each new model.

The two additions to Mitsubishi Electric’s color TFT-LCD module lineup of high quality touch-panel screens combining excellent visual clarity with durable cover glass will expand the options for wide-aspect screens, bringing the total number of available display sizes to 10, ranging from 6.5 to 19.0 inches.



AA070ME11-PCAP



AA121TD11-PCAP

Highly reliable and widely applicable touch-panel solutions

- Wide range of solutions, including TFT-LCD, PCAP touch panel, touch controller and driver software, for diverse industrial applications.
- Factory-installed TFT-LCD, PCAP touch panel, cover glass and touch controller for excellent reliability.
- To adapt to diversified operational environments, many options are available, including optical bonding (resin bonding between the TFT-LCD module, touch-panel sensor and cover glass) for clearer images in bright environments, tempered cover glass and anti-reflection/anti-smudge surface treatments.

Excellent visual clarity combined with tactile operation via cover glass

- Proprietary detective processing for smooth, accurate response to finger movements even gloved fingers.
- Ultra-thin, highly conductive sensor lines with proprietary TFT array technologies for excellent clarity.

Expanded lineup for broader range of industrial applications


- Two new touch-panel modules offer wide-aspect ratios for more varied industrial applications.

Lineup of color TFT-LCD modules with projected capacitive touch panel (new models in bold)

Display Size	Resolution	Model
4:3	6.5-inch	VGA
	8.4-inch	SVGA
	10.4-inch	XGA
	12.1-inch	XGA
	15.0-inch	XGA
5:4	19.0-inch	SXGA
Wide	7.0-inch	WXGA
	9.0-inch	WXGA
	10.6-inch	WXGA
	12.1-inch	WXGA

Projected Capacitive Touch (PCAP)

Capacitive touch is a touchscreen technology that uses two perpendicular layers of conductive material to form a grid. When a current is applied, it forms a uniform electrostatic field. The touch of a finger or other conductive object will distort the field, allowing the system to accurately track movement across the screen at multiple points. This technology is used commonly for smartphones and tablets.



Specifications

Model		AA070ME11-PCAP	AA121TD11-PCAP
Display size/resolution		17.8cm (7.0 inch) WVGA	31cm (12.1 inch) WXGA
Display area (mm)		152.4 (H) × 91.44 (V)	261.12 (H) × 163.2 (V)
Number of dots		800 (H) × 480 (V)	1280 (H) × 800 (V)
Pixel pitch (mm)		0.1905 (H) × 0.1905 (V)	0.204 (H) × 0.204 (V)
Contrast ratio		600:1	700:1
Luminance (cd/m ²)		(1,200)	(1,200)
Viewing angle (CR>10)(°)		(-80 ~ +80) (H) (-80 ~ +60) (V)	-80 ~ +80 (H) -60 ~ +80 (V)
Colors		262k (6 bits/color), 16.7M (8 bits/color)	262k (6 bits/color), 16.7M (8 bits/color)
Electrical interface		LVDS 6/8 bits	LVDS 6/8 bits
Size (mm)	W	189.8 (LCD: 169.8)	303.0 (LCD: 283.0)
	H	129.7 (LCD: 109.7)	205.1 (LCD: 185.1)
	D	13.6(LCD: 8.9) (1.1 mm cover glass thickness)	15.3(LCD:9.7) (1.8 mm cover glass thickness)
Operational temperatures (°C)		-30 ~ +70	-30 ~ +70
Storage temperatures (°C)		-30 ~ +80	-30 ~ +80
Glass thickness (mm)		Up to 2.8mm (thicker specimens available upon request)	
Black mask printing		Available	
Strengthening treatment		Available	
Low-reflection treatment		Available	
Anti-smudge treatment		Available	
Optical bonding		Available	
Controller interface		UART, USB	
OS*		Windows 7 and Linux 3.0	

* If support for other OS is necessary, please contact Mitsubishi Electric sales representatives.

Environmental awareness

The color TFT-LCD modules are fully compliant with the European restriction of the use of certain hazardous substances in electrical and electronic equipment (RoHS), and are completely mercury-free.

###

About Mitsubishi Electric Corporation

With over 90 years of experience in providing reliable, high-quality products, Mitsubishi Electric Corporation (TOKYO: 6503) is a recognized world leader in the manufacture, marketing and sales of electrical and electronic equipment used in information processing and communications, space development and satellite communications, consumer electronics, industrial technology, energy, transportation and building equipment. Embracing the spirit of its corporate statement, Changes for the Better, and its environmental statement, Eco Changes, Mitsubishi Electric endeavors to be a global, leading green company, enriching society with technology. The company recorded consolidated group sales of 3,567.1 billion yen (US\$ 37.9 billion*) in the fiscal year ended March 31, 2013. For more information visit <http://www.MitsubishiElectric.com>

*At an exchange rate of 94 yen to the US dollar, the rate given by the Tokyo Foreign Exchange Market on March 31, 2013

Windows is a registered trademark of Microsoft Corporation in the United States and other countries.

Linux is the registered trademark of Linus Torvalds in the U.S. and other countries.