

### GT25 Ḥa̞ndy GOT General Description

GT2505HS-VTBD

Thank you for choosing Mitsubishi Electric Graphic Operation Terminal (GOT).

	MODEL	GT2505HS-V-U-GD-E
	MODEL CODE	1D7MU3
IB(NA)-0800614ENG-E(2212)		0800614ENG-E(2212)MEE

This manual describes the part names, dimensions, mounting, and specifications of the product. Before use, read this manual and manuals of rele fully to acquire proficiency in handling and operating the product. Make sure to learn all the product information, safety information, and precautions. And, store this manual in a safe place so that you can take it out and read it whenever necessary. Always forward it to the end user.

Ethernet is a trademark of Xerox Corporation in the United States. MODBUS is a trademark of Schneider Electric SA. Unicode is a trademark or registered trademark of Unicode, Inc. in the United States and other countries. The company name and the product name to be described in this manual are the registered trademarks or trademarks of each company.

Effective Dec. 2022

Specifications are subject to change without notice

© 2018 MITSUBISHI ELECTRIC CORPORATION Safety Precaution (Read these precautions before using.)

Before using this product, please read this manual and the relevant manuals introduced in this manual carefully and pay full attention to safety to handle the

product correctly.
The precautions given in this manual are concerned with this product.
In this manual, the safety precautions are ranked as "WARNING" and "CAUTION".

<b><u>^</u></b> MARNING	Indicates that incorrect handling may cause hazardous conditions, resulting in death or severe injury.	
<b>↑</b> CAUTION	Indicates that incorrect handling may cause hazardous conditions, resulting in medium or slight personal injury or physical damage.	
Depending on circumstances, procedures indicated by "CAUTION" may also be		

linked to serious results.

In any case, it is important to follow the directions for usage

#### **DESIGN PRECAUTIONS <u>∧</u>** WARNING

- Some failures of the GOT or cable may keep the outputs on or off. Al external monitoring circuit should be provided to check for output signal which may lead to a serious accident. Not doing so can cause an acciden due to false output or malfunction.
- Do not use the GOT as the warning device that may cause a serior accident. An independent and redundant hardware or mechanical interloan required to configure the device that displays and outputs serious warnin Failure to observe this instruction may result in an accident due to incorreoutput or malfunction.
- locuput of maintainer.

  Incorrect operation of the touch switch(s) may lead to a serious accident if the GOT backlight is gone out. When the GOT backlight goes out, the POWER LED flickers (blue/orange) and the display section turns black and causes the monitor screen to appear blank, while the input of the touch switch(s) remain active. This may confuse an operator in thinking that the GOT is in "screensaver" mode, who then tries to release the GOT from this mode touching the display section, which may cause a touch switch to operal Note that the following occurs on the GOT when the backlight goes out. The POWER LED flickers (blue/orange) and the monitor screen appear

#### **↑** WARNING DESIGN PRECAUTIONS

- The display section is an analog-resistive type touch panel. If you touch the display section simultaneously in 2 points or more, the switch that is locate around the center of the touched point, if any, may operate. Do not touch the display section in 2 points or more simultaneously. Doing so may cause all accident due to incorrect output or malfunction.
- When programs or parameters of the controller (such as a PLC) that is monitored by the GOT are changed, be sure to reset the GOT or shut off the power of the GOT at the same time. Not doing so can cause an accident due to false output or malfunction.
- malfunction.

  If a communication fault (including cable disconnection) occurs during monitoring on the GOT, communication between the GOT and PLC CPU is suspended and the GOT becomes inoperative. A system where the GOT is used should be configured to perform any significant operation to the system by using the switches of a device other than the GOT on the assumption that a GOT communication fault will occur. Not doing so can cause an accident due to false output or malfunction.
- To maintain the security (confidentiality, integrity, and availability) of the GOT and the system against unauthorized access, DoS<sup>11</sup> attacks, computer viruses, and other cyberattacks from unreliable networks and devices via network, take appropriate measures such as firewalls, virtual private networks (VPNs), and

antivirus solutions. Mitsubishi Electric shall have no responsibility or liability for any problems involving GOT trouble and system trouble by unauthorized access, DoS attacks computer viruses, and other cyberattacks.

\*1 DoS: A denial-of-service (DoS) attack disrupts services by overloading systems or exploiting vulnerabilities, resulting in a denial-of-service (DoS) state.

#### DESIGN PRECAUTIONS **⚠CAUTION**

- Do not bundle the control and communication cables with main-circuit, power of other wiring. Run the above cables separately from such wiring and keep them minimum of 100mm (3.94in.) apart.Not doing so noise can cause a malfunction. Do not press the GOT display section with a pointed material as a pen or driver boing so can result in a damage or failure of the display section.
- When the GOT is connected to the Ethernet network, the available IP address i
- restricted according to the system configuration.

  When multiple GOTs are connected to the Ethernet network:
  Do not set the IP address (192.168.3.18) for the GOTs and the controllers in the
- network.
  When a single GOT is connected to the Ethernet network:
  Do not set the IP address (192.168.3.18) for the controllers except the GOT i
- Doing so can cause the IP address duplication. The duplication can negatively affect the communication of the device with the IP address (192.168.3.18). The operation at the IP address duplication depends on the devices and the system.
- Turn on the controllers and the network devices to be ready for communication before they communicate with the GOT. Failure to do so can cause communication error on the GOT.
- When the GOT is subject to shock or vibration, or some colors appear on the screen of the GOT, the screen of the GOT might flicker.

### MOUNTING PRECAUTIONS WARNING

- Be sure to shut off all phases of the external power supply used by the syste before mounting or removing the GOT to/from the panel. Not doing so can caus the unit to fail or malfunction.
- Make sure to turn off the connector conversion box (GT11H-CNB-37S, GT16H CNB-37S, or GT16H-CNB-42S) before connecting or disconnecting the GOT. Connecting or disconnecting the GOT with the power being turned on may resu in damage to the unit or malfunctions.

### MOUNTING PRECAUTIONS (CAUTION

- Use the GOT in the environment that satisfies the general specifications described in this manual. Not doing so can cause an electric shock, fire, malfunction or product damage or deterioration.

  Remove the protective film of the GOT. When the user continues using the GOT with the protective film, the film may not be removed.

  Operate and store the GOT in environments without direct sunlight, high temperature, dust, humidity, and vibrations.

  Never drop cutting chips and electric wire chips into the ventilation window of the Handy GOT when you drill screw holes or perform wiring. Otherwise, fire, failure or malfunction may be caused.

  Connect connection cables securely to the specified connectors while the power is turned OFF. Imperfect connection may cause malfunction or failure.

#### **MARNING** IRING PRECAUTIONS

- Be sure to shut off all phases of the external power supply used by the syste before wiring. Failure to do so may result in an electric shock, product damager malfunctions
- Make sure to attach the back cover to the Handy GOT before turning on the power and starting operation after the installation or wiring work. Otherwis electrical shock may be caused.
- Use a DC power supply for this product. The power supply in the specific range must be applied for the power supply, the operation switch, and the emergency stop switch. If they are connected to the power supply of the different specification, it may cause a fire or failure.
- Correctly wire the GOT power supply section after confirming the rated voltage and terminal arrangement of the product. Not doing so can cause a fire o failure.
- Please make sure to ground FG terminal of the GOT power supply section by applying 100 or less which is used exclusively for the GOT. Not doing so may cause an electric shock or malfunction.
- Exercise care to avoid foreign matter such as chips and wire offcuts entering th GOT. Not doing so can cause a fire, failure or malfunction.

#### VIRING PRECAUTIONS **⚠CAUTION**

- When tightening the terminal screws, use a Phillips-head screwdriver No.2.
- Use applicable solderless terminals for terminal processing of a wire and tighter them with the specified torque. Not doing so can cause a fire, failure o
- Correctly wire the GOT power supply section after confirming the rated voltage and terminal arrangement of the product. Not doing so can cause a fire o
- Tighten the terminal screws of the GOT power supply section in the following
- specified torque range.
   Specified torque range (0.5 N·m to 0.8 N·m)
  Undertightening can cause a short circuit or malfunction. Overtightening cause a short circuit or malfunction due to the damage of the screws or the GOT.
- The cables connected to the unit must be run in ducts or clamped. Not doing s can cause the unit or cable to be damaged due to the dangling, motion of accidental pulling of the cables or can cause a malfunction due to a cable connection fault.
- When unplugging the cable connected to the unit, do not hold and pull the cab portion. Doing so can cause the unit or cable to be damaged or can cause malfunction due to a cable connection fault.
- Plug the communication cable into the connector of the connected unit and tighten the mounting and terminal screws in the specified torque range. Undertightening can cause a short circuit or malfunction. Overtightening can cause a short circuit or malfunction due to the damage of the screws or unit.

## EST OPERATION

Before performing the test operations of the user creation monitor screen (such as turning ON or OFF bit device, changing the word device current value, changing the settings or current values of the timer or counter, and changing the buffer memory current value), read through the manual carefully and make yourself familiar with the operation method. During test operation, never change the data of the devices which are used to perform significant operation for the system. False output or malfunction can cause an accident.

**⚠WARNING** 

**∴**WARNING

#### STARTUP/MAINTENANCE RECAUTIONS

- When power is on, do not touch the terminals. Doing so can cause an electronic
- Connect the battery correctly. Do not discharge, disassemble, heat, sho solder or throw the battery into the fire. Incorrect handling may cause the batter to generate heat, burst or take fire, resulting in injuries or fires.
- Before starting cleaning or terminal screw retightening, always switch off the power externally in all phases. Not switching the power off in all phases car cause a unit failure or malfunction. Undertightening can cause a short circuit or malfunction. Overtightening can cause a short circuit or malfunction due to the damage of the screws or unit.

#### STARTUP/MAINTENANCE **⚠CAUTION**

- Do not disassemble or modify the unit. Doing so can cause a failur malfunction, injury or fire.
- Do not touch the conductive and electronic parts of the unit directly. Doing s can cause a unit malfunction or failure.
- Do not drop the module or subject it to strong shock. A module damage ma

#### STARTUP/MAINTENANCE **∴**CAUTION

- Do not drop or give an impact to the battery mounted to the unit. Doing so ma damage the battery, causing the battery fluid to leak inside the battery. If th battery is dropped or given an impact, dispose of it without using.
- Before touching the unit, always touch grounded metals, etc. to discharge stati-electricity from human body, etc. Not doing so can cause the unit to fail o
- matunction. Replace battery with GT11-50BAT by Mitsubishi electric Co. only. Use of another battery may present a risk of fire or explosion. Dispose of used battery promptly. Keep away from children. Do not disassemble and do not dispose of in fire.

  Before replacing the battery, shut off all phases of the external power supply Not doing so can cause the unit to fail or malfunction by static electricity.

#### TOUCH PANEL **⚠**CAUTION

- For the analog-resistive film type touch panels, normally the adjustment is no required. However, the difference between a touched position and the object position may occur as the period of use elapses. When any difference between a touched position and the object position occurs, execute the touch panel attention of the period of use the period of use the period of use the period of the period of use the period of th
- When any difference between a touched position and the object position or other object may be activated. This may cause an unexpected operation do incorrect output or malfunction.

## PRECAUTIONS WHEN THE ATTACKS OF THE PRECAUTIONS WHEN THE WARNING

If the SD card is removed from drive A of the GOT while being accessed by the GOT, the GOT may stop processing data for about 20 seconds. The GO cannot be operated during this period. The functions that run in the backgroun including a screen updating, alarm, logging, scripts, and others are als interrupted. Before removing the SD card, check the following items. Make sun to turn off the SD card access switch before removing the SD card. Not doing s may damage the SD card or files.

# PRECAUTIONS WHEN THE ACTION DATA STORAGE IS IN USE

- If the data storage is removed from the GOT while being accessed by the GOT
  the data storage and files may be damaged. Before removing the data storag
  from the GOT, check the SD card access LED, system signal, or others to make sure that the data storage is not accessed.
- When inserting/removing a SD card into/from the GOT, turn the SD card accesswitch off in advance. Failure to do so may corrupt data within the SD card. Turning off the GOT while it accesses the SD card results in damage to the SE card and files.

- card and files.

  When inserting a SD card into the GOT, make sure to close the SD card cover. Failure to do so causes the data not to be read or written.

  When removing the SD card from the GOT, make sure to support the SD card by hand as it may pop out. Not doing so may cause the SD card to drop from the GOT, resulting in a failure or break.
- GOT, resulting in a failure or break.

  When inserting a USB device into a USB interface of the GOT, make sure to insert the device into the interface firmly. Not doing so may cause the USB device to drop from the GOT, resulting in a failure or break.

  Before removing the data storage from the GOT, follow the procedure fremoval on the utility screen of the GOT. After the successful completion dialog is displayed, remove the USB device by hand carefully. Not doing so may cause the USB device to drop from the GOT, resulting in a failure or break.
- PRECAUTIONS FOR USE \_\_\_\_\_\_CAUTION
- When you operate the Handy GOT while holding it, slide your hand through the hand strap on the back of the GOT to prevent falling. The hand strap length
- When you remove a cable from the Handy GOT, do not pull the cable portion Doing so may damage the unit or cable, or cause a malfunction due to a cab connection fault. Do not drop or strike the Handy GOT. Doing so may damage the GOT.
- When you carry or operate the Handy GOT, hold its body. Carrying or operati the Handy GOT while holding its cable may damage the unit or cable.
- Determine whether to use the emergency stop switch of the Handy GO according to your risk assessment.
- If you use a parallel circuit (to avoid entering the emergency stop status whi the Handy GOT is removed), the system may not conform to the safety standards. Check the safety standards required for your system before use.
- If the Handy GOT is exposed to any impact beyond the general specifications chattering may occur in the emergency stop switch for its structural reasons Check that your use conditions are proper
- Do not touch the edges of the touch panel (display section) repeatedly. Doing s may result in a failure.

#### RECAUTIONS FOR USE **∴**CAUTION

Do not turn off the GOT while data is being written to the storage memor (ROM) or SD card. Doing so may corrupt the data, rendering the GO

#### PRECAUTIONS FOR **⚠**CAUTION

Remote control is available through a network by using GOT function including the SoftGOT-GOT link function, the remote personal comput operation function, the VNC server function, and the GOT Mobile function these functions are used to perform remote control of control equipment, field operator may not notice the remote control, possibly leading to an accide the delivery of the proposed of the control of the proposed of the propo In addition, a communication delay or interruption may occur depending on the network environment, and remote control of control equipment cannot be performed normally in some cases. Before using the above functions to perform remote control, fully grasp the circumstances of the field site and ensure safety.

## PRECAUTIONS FOR EXCLUSIVE AUTHORIZATION

## **⚠**CAUTION

Make sure to fully understand the GOT network interaction function before usin make sure to fully inderstand the SQT inetwork interaction function better this function to control the authorization among pieces of equipment to prever simultaneous operations. The exclusive authorization control of the GO network interaction function can be enabled or disabled for each screen. [For a screens, the exclusive authorization control is disabled by default.) Proper determine the screens for which the exclusive authorization control is required and set the control by screen. A screen for which the exclusive authorization control is disabled can be operated simultaneously from pieces of equipmen before the determine the screen in the screen for which the exclusive authorization control is disabled can be operated simultaneously from pieces of equipmen. Make sure to determine the operation period for each operator, fully grasp th circumstances of the field site, and ensure safety to perform operations.

When disposing of the product, handle it as industrial waste. When disposing o batteries, separate them from other wastes according to the local regulations (For details of the battery directive in EU member states, refer GOT User's Manual.)

## **CAUTION**

DISPOSAL PRECAUTIONS \_\_\_\_\_CAUTION

- When transporting lithium batteries, make sure to treat them based on the transport regulations. (Refer to User's Manual for details of the regurated Before transporting the GOT, turn the GOT power on and check that the batter
- voltage status is normal on the Time setting & display screen (utilities screen). addition, confirm that the adequate battery life remains on the rating plat Transporting the GOT with the low battery voltage or the battery the reache battery life may unstabilize the backup data unstable during transportation. oatterly lie may unstabilize the abackup data unstable during transportation. When furnigants that contain halogen materials such as fluorine, chlorin bromine, and lodine are used for disinfecting and protecting wooden packagir from insects, they cause maffunction when entering our products. Please tal necessary precautions to ensure that remaining materials from furnigant do nenter our products, or treat packaging with methods other than furnigation (he
- Make sure to transport the GOT main unit and/or relevant unit(s) in the man they will not be exposed to the impact exceeding the impact resistandescribed in the general specifications of this manual, as they are precis devices. Failure to do so may cause the unit to fail. Check if the unit operate

## Certification of UL, cUL standards

- GT16H-CNB-42S
- External cable (GT14H-C30-42P, GT14H-C60-42P, GT14H-C100-42P)  $^{^{\prime 2}}$  GT16H-CNB-37S External cable (GT11H-C30-37P, GT11H-C60-37P, GT11H-C100-37P)\*3
- Cable must be properly installed and routed to ensure protection of the Cable.
- \*1 Hardware version D or later \*2 Version B or later
- \*3 Version D or late

## General notes on power supply This equipment must be supplied by a UL Listed or Recognized 24 V dc rated power supply and UL Listed or Recognized fuse rated not higher than 4A, or a UL Listed Class 2 power supply.

Compliance with EC directive (CE Marking) This note does not guarantee that an entire mechanical module produced in accordance with the contents of this note will comply with the following standards.

Compliance to EMC directive for the entire mechanical module should be checked by the user/manufacturer. For more details please contact the local Mitsubishi Electric sales site. Attention

· This product is designed for use in industrial applications

## Requirement for Compliance with EMC directive

The following products have shown compliance through direct testing (to the identified standards) and design analysis (forming a technical construction file) to the European Directive for Electromagnetic Compatibility when used as directed by the appropriate documentation.

. This product is designed for use in industrial applications Type: Graphic operation terminal

Models: GOT2000 series

Standard	Remark	
EN61131-2 : 2007	Compliance with all relevant aspects of the standard. (Radiated Emissions)	
Programmable controllers-Equipment,	Compliance with all relevant aspects of the standard. (ESD, RF electromagnetic field, EFTB	

Surge, RF conducted disturbances and Power frequency magnetic field) For more details please contact the local Mitsubishi Electric sales site.

or details of CE marking, refer to the following. →GOT2000 Series User's Manual (Hardware) Compliant with the UKCA marking

Directives (CE marking

Notes for compliance to EMC regulation General notes on the control panel
 Make sure to combine the GT2505HS-VTBD with the Connector Conversion Box to comply with the EMC directive. The Connector Conversion Box is an open type device (device installed to another device) and must be installed in a conductive

ents for compliance with the UKCA marking are the same with the EC


- 2) General notes on the use of communication cables
- External cable - GT14H-C30-42P, GT14H-C60-42P, GT14H-C100-42P
- GT11H-C30-37P, GT11H-C60-37P, GT11H-C100-37P (Ver.C or later)

Direct connection cable		
Existing Cables	User Made Cables	
GT01-C30R4-8P GT11H-C30R2-6P	The cable need to be independently tested by the user to demonstrate EMC compatibility when they are used with the GOT, the PLC of MELSEC-Q series, MELSEC-L series, MELSEC-L series, MELSEC-PX series.	

- Ethernet connection cable Shielded twisted pair cable (STP)
- PLC (manufactured by other company), microcomputer, temperature controller, inverter, servo amplifier, CNC, MODBUS(R)/RTU or MODBUS(R)/TCP

Produce the cable (RS-232 cable, RS-422 cable) for connecting the GOT to a

 General notes on Power supply
 The Connector Conversion Box requires an additional ferrite filter to be attached to the 24V DC power supply cables. The filter should be attached in a similar manner as shown in the figure opposite, i.e. the power cables are wrapped around the filter. However, as with all EMC situations the more correctly applied precautions the better the systems Electromagnetic Compatibility. The ferrite recommended is a TDK ZCAT3035-1330 or similar. The ferrite should be placed as near to the 24V DC terminals of the Connector Conversion Box as possible (which should be within 75mm of the GOT terminal). figure opposite, i.e. the power cables are



## **Detailed Manual**

Ī	Manual name	Manual Number(Model Code)
	GOT2000 Series User's Manual (Hardware)	SH-081194ENG (1D7MJ5)
-	GOT2000 Series User's Manual (Utility)	SH-081195ENG (1D7MJ6)

For detailed manuals, refer to the PDF manuals stored in the DVD-ROM for the drawing software used.


# For relevant manuals, refer to the Help or the PDF manuals stored in the DVD-ROM for the drawing software used. The latest manuals are also available from MITSUBISHI ELECTRIC FA Global Website (www.mitsubishielectric.com/fa/). **Bundled Items**

Relevant Manuals

Product Name	Model Name	Specifications
GOT	GT2505HS-VTBD	$[640\times480\ dots],$ TFT color (65536 colors), built-in battery


Bundled item  GT25 Handy GOT General Description (This manual)	Quantity
	1
Selector switch keys	2

#### 1. Part Name 1.1 Front Panel




		(5)
No	Name	Specifications
(1)	Emergency stop switch	Switch for external direct wiring (independent contact)
(2)	Display section	Displays the utility screen and the user creation screen.
(3)	Touch panel	For touch switch operation on the utility screen and the user creation screen.
(4)	Display LED for grip switch	Display LED for grip switch (green) (lighting control from display section)
(5)	Operation switch (6 switches)	Switch for external direct wiring (independent contact)
(6)	POWER LED	Lit in blue: Power is correctly supplied. Lit in orange: Screen saving and backlight not lit. Blinks in orange/blue: Blown back light bulb. Not lit: Power is not supplied.
(7)	Keylock switch (2-position switch)	Switch for external direct wiring (independent contact)

# 1.2 Back Panel



No	Name	Specifications
(1	Hook for hanging on walls	Hook when the Handy GOT is used hanging on walls.
(2	Environmental protection back cover screw	For opening and closing the environmental protection back cover (drop prevention screw)
(3	Hand strap	Used to hold the Handy GOT in hand by putting a hand under the strap. Length adjustable.


No	Name	Specifications
(4)	Environmental protection back cover	Opened and closed when the PLC communication type is changed (Ethernet ⇔RS-422 ⇔RS-232 before shipping: Ethernet), or the battery is replaced.
(5)	Rating plate	-
(6)	Battery	Battery for backup of SRAM data, clock data, and system status log data.
(7)	Connector for battery connection	For battery connection
	RS-422 connector	Connector for PLC communication using RS-422*1
(8)	RS-232 connector	Connector for PLC communication using RS-232*1
	Ethernet connector	Connector for PLC communication using Ethernet*1



		(6) (5) (4) <b>1111111</b>
No	Name	Specifications
(1)	Interface environmental protection cover	Opened and closed when the USB port is used or the SD card is inserted.
(2)	Emergency stop switch guard cover installing hole	Threaded hole for mounting the GT14H-50ESCOV type emergency stop switch guard (option) (M3)
(3)	USB interface (Host)	For data transfer, data storage (connector type: TYPE-A)
(4)	SD card access switch	Prohibits accessing the SD card removing the card from the Handy GOT.  ON: SD card being accessed (SD card removal prohibited)  OFF: SD card not accessed (SD card removal possible)
(5)	SD card access LED	Lit: SD card being accessed, Not lit: SD card is not accessed.
(6)	SD card interface	For installing the SD card to the GOT
(7)	Ethernet communication status LED	LED1: Turns on during data transfer/reception. LED2: Turns on during 100Mbps transmission.
	LICD interfece	

The Ethernet connector is set at factory shipment.

## 1.3 Top Face (Interface)



	Humo	Opcomoditions .
(1)	Interface environmental protection cover	Opened and closed when the USB port is used or the SD card is inserted.
(2)	Emergency stop switch guard cover installing hole	Threaded hole for mounting the GT14H-50ESCOV type emergency stop switch guard (option) (M3)
(3)	USB interface (Host)	For data transfer, data storage (connector type: TYPE-A)
(4)	SD card access switch	Prohibits accessing the SD card removing the card from the Handy GOT.  ON: SD card being accessed (SD card removal prohibited)  OFF: SD card not accessed (SD card removal possible)
(5)	SD card access LED	Lit: SD card being accessed, Not lit: SD card is not accessed.
(6)	SD card interface	For installing the SD card to the GOT
(7)	Ethernet communication status LED	LED1: Turns on during data transfer/reception. LED2: Turns on during 100Mbps transmission.
(8)	USB interface (Device)	For PC connection (connector type: MINI-B)

### 2. Specifications

### 2.1 General Specifications

Item	Specifications							
Operating ambient temperature	0°C to 40°C	0°C to 40°C						
Storage ambient temperature	-20°C to 60°C							
Operating ambient humidity	10% RH to 90% RH	H, non-condensing						
Storage ambient humidity	10% RH to 90% RH	H, non-condensing						
			Frequency	Acceleration	Half-amplitude	Sweep Count		
	Conforms to JIS	Under intermittent	5 to 8.4Hz		3.5mm	10 times each in X, Y and Z directions		
Vibration resistance	B3502 and	vibration	8.4 to 150Hz	9.8m/s <sup>2</sup>				
	IEC61131-2	Under continuous vibration	5 to 8.4Hz		1.75mm			
			8.4 to 150Hz	4.9m/s <sup>2</sup>	-			
Shock resistance	Conforms to JIS B3	Conforms to JIS B3502, IEC 61131-2 (147 m/s <sup>2</sup> , 3 times each in X, Y and Z directions)						
Operating atmosphere		Must be free of lamp black, corrosive gas, flammable gas, or excessive amount of electroconductive dust particles and must be no direct sunlight. (Same as for saving)						
Operating altitude*1	2000 m (6562 ft) m	2000 m (6562 ft) max.						
Overvoltage category*2	II or less	II or less						
Pollution degree*3	2 or less	2 or less						
Cooling method	Self-cooling	Self-cooling						
Grounding	more.	Grounding with a ground resistance of $100 \Omega$ or less by using a ground cable that has a cross-sectional area of $2 \text{ mm}^2$ or more.  If impossible, connect the ground cable to the control panel.						
Type rating	10.754	UL Type 1						

- When the air inside the control panel is purged by pressurization, the surface sheet may be lifted by high pressure. As a result, the touch panel may be difficult to press, and the sheet may be peeled off.
- \*2 This indicates the section of the power supply to which the equipment is assumed to be connected between the public electrical power distribution network and the machinery within the premises. Category II applies to equipment for which electrical power is supplied from fixed facilities. The surge voltage withstand level for up to the raged voltage of 300 V is 2500 V.
- \*3 This index indicates the degree to which conductive material is generated in the environment where the equipment is used. In pollution degree 2, only non-conductive pollution occurs but temporary conductivity may be produced due to condensation.

#### 2.2 Performance Specifications

14		Specifications			
	Item	GT2505HS-VTBD			
	Туре	TFT color liquid crystal display			
	Screen size	5.7"			
	Resolution	VGA: 640 × 480 dots			
B	Display size	115.2(4.54) (W) × 86.4(3.40) (H) mm (inch)			
Display section *1*2	Display character	16-dot standard font: 40 characters × 30 lines, 12-dot standard font: 53 characters × 40 lines			
0000011	Display color	65536 colors			
	Brightness adjustment	32 levels			
	Backlight	LED (Not replaceable)			
	Backlight life *4	Approximately 60000 hours (Operating ambient temperature: 25°C, display intensity: 50%)			
	Туре	Analog resistive film			
T1 *2	Key size	Minimum 2 × 2 dots *7 (per key)			
Touch panel *3	The number of simultaneous press	Not available *5 (Only 1 point can be touched.)			
	Life	1 million touches or more (Operating force: 0.98 N or less)			
Buzzer output		Single tone (tone length adjustable)			
Protective struct	ure*6	IP65F *6*8 (valid when the external cable is connected, except for the connector conversion box side			
External dimens	ions	145(5.70)(W)×185(7.27) (H)×79.3(3.12)(D)mm(inch) (Excluding projections such as the emergence stop switch)			
Weight		0.79kg (GT25 Handy main unit only)			
Compatible soft	vare package	GT Works3 Version1.195D or later			
	Operation switch	6 switches (6 contacts/common), N/O contact, Maximum rating 10mA/24VDC, Life: 1,000,000 times			
Switch		1 switch (single wiring) (IDEC HE3B-M2PB)			
	Grip switch	Enable switch (deadman switch) 3-position system of OFF ⇔ ON ⇔ OFF 2 N/O contacts Maximum rating 1A/24VDC (resistance load), Maximum rating 0.3A/24VDC (induction load), Life: 100,000 times			
	Emergency stop switch	1 switch (single wiring) (IDEC XA1E-BV303R) 3 N/C contacts Maximum rating 1A/24VDC (resistance load), Maximum rating 0.3A/24VDC (induction load), Life: 100,000 times			

Item		Specifications			
	Kem	GT2505HS-VTBD			
Switch	Keylock switch (2-position switch)	switch (single wiring) (IDEC AS6M-2KT-IPB)     -notch type (Manual stop at each position/A key can be inserted and removed on only the left side./Or the right side, a key cannot be removed./Two keys are provided.)     -position, Maximum rating 1A/24VDC (resistance load), Maximum rating 0.3A/24VDC (induction load) Life: 100,000 times			
	POWER LED	1 LED Lit in blue: Power is correctly supplied. Lit in orange: Screen saving and backlight not lit. Blinks in orange/blue: Blown back light bulb. Not lit: Power is not supplied.			
LED	LED for grip switch display	1 LED, green (lighting control from display unit part)			
	SD card access LED	ON: SD card installed Bilink: SD card accessed OFF: SD card not installed or SD card installed but removal possible			
	Ethernet communication status LED	LED1: Turns on during data transfer/reception. LED2: Turns on during 100Mbps transmission.			
User Memory	User memory capacity	Memory for storage (ROM): 32 MB Memory for operation (RAM): 80 MB			
	Life (number of write times)	100000 times			
Battery		GT11-50BAT lithium battery			
battery	Life	Approx. 5 years (Operating ambient temperature of 25°C)			
	RS-232 *9	1 channel Transmission speed: 115200/57600/38400/19200/9600/4800bps Connector shape : Round type 32pins (Male)			
	RS-422 *9	1 channel Transmission speed: 115200/57600/38400/19200/9600/4800bps Connector shape : Round type 32pins (Male) Terminating resistor : 3300 (Fixed)			
Built-in	Ethernet *9	1 channel Data transfer method: 100BASE-TX, 10BASE-T Connector shape : Round type 32pins (Male)			
built-in interface	USB (Host)	1 channel (Top face) USB version: USB 2.0 (High-Speed 480 Mbps) Connector shape: USB-A			
		1 channel (Top face)			
	USB (Device)	USB version: USB 2.0 (High-Speed 480 Mbps) Connector shape: USB Mini-B			
	SD card	1 channel, SDHC compliant (maximum 32GB)			

- a great number of display elements, the appearance of bright and dark dots cannot be reduced to zero. Individual differences in liquid crystal display panels may cause differences in color, uneven brightness and flickering. Note that these phenomena are characteristics of liquid crystal display panels and it does not mean the products are defective or dama
- \*2 Flickering may occur due to vibration, shock, or the display colors.
- \*3 When a stylus is used, the touch panel has a life of 100 thousand touches.
  The stylus must satisfy the following specifications.

   Material: Polyacetal resin
- \*4 To prevent the display section from burning in and lengthen the backlight life, enable the screen save function and turn off the backlight.
- \*5 If you touch two points or more simultaneously on the touch panel, a switch in an unintended location may operate Do not touch two points or more simultaneously on the touch panel.
- \*6 Note that the structure does not guarantee protection in all users' environments.


  The protection is not applied when the interface environment protection cover or environment protection back cover is removed.

  The GOT may not be used in an environment where the GOT is exposed to oil or chemicals for a long time, or where oil mist fills the air.
- The minimum size of a key that can be arranged.
   To ensure safe use of the product, the following settings are recommended.
   Key size: 16 x 16 dots or larger
   Distance between keys: 16 dots or more
- \*8 The suffix "F" of IP65F is a symbol that indicates protection rate against oil. It is described in the Appendix of JIS C 0920 of the Japanese Industrial Standards.
- \*9 Select either RS-232, RS-422 or Ethernet when used. The channel is set to Ethernet before shipping.

### 2.3 Power Supply Specifications

Item	Specifications			
iteiii	GT2505HS-VTBD			
Input power supply voltage	24V DC (+10% -15%)			
Power consumption	.4W or less			
At backlight off	7.0W or less			
Inrush current	30 A or less (2 ms, ambient temperature: 25 °C, under the maximum load)			
Permissible instantaneous power failure time*1	Within 5ms			
Noise immunity	Noise voltage: 1000Vp-p, Noise width: 1µs (by noise simulator of 30 to 100Hz noise frequency)			
Dielectric withstand voltage	500 V DC for 1 minute across power supply terminals and earth			
Insulation resistance	500 V DC across power supply terminals and earth, 10 MΩ or more by an insulation resistance tester			

## 2.4 External Dimensions



## 3. Maintenance and Inspection

ole components that will cause the shorten life. However, the battery, liquid crystal display screen and backlight have each life

It is recommended to replace the battery periodically. (For the replacement of the liquid crystal screen, please consult your nearest sales office or FA Center.)

#### 3.1 Daily Inspection Daily inspection items

		y mapection items					
	No.	Inspection Item Installation status of GOT		Inspection Method	Criterion	Action	
	1			Check for loose mounting screws.	Securely mounted	Retighten screws within the specified torque range.	
•		status	Loose terminal screws Retighten scr with screwdri		Not loose	Retighten terminal screws.	
	2	Connection st	Proximate solderless terminals	Visual check	Proper intervals	Correct.	
			Conne	Loose connectors	Visual check	Not loose	Retighten connector fixing screws.
	3	Usage status	Dirt on protection sheet	Visual check	Not outstanding	Replace with new one	
	3		Foreign material attachment	Visual check	No foreign matter sticking	Remove clean	

replacement procedure

## 3.2 Periodic Inspection

Yearly or half-yearly inspection items

The following inspection should also be performed when equipment has been moved or modified or the wiring changed.

No.	Inspection Item		Inspection Method	Criterion	Action	
	Surrounding environment	Ambient temperature	Make measurement with	0 to 40°C	For use in control	
1		Ambient humidity	thermometer or hygrometer	10 to 90%RH	panel, temperature inside control panel is	
		Atmosphere	Measure corrosive gas	No corrosive gas	ambient temperature	
2	Power supply voltage check		24V DC Measure voltage across terminals.	20.4 to 26.4V DC	Change supply power	
3	Mounting status	Looseness	Looseness Move module. Shor		Retighten screws.	
3		Foreign material attachment	Visual check	No foreign matter sticking	Remove, clean	
	Connection status	Loose terminal screws	Retighten screws with screwdriver.	Not loose	Retighten terminal screws.	
4		Proximate solderless terminals	Visual check	Proper intervals	Correct.	
		Loose connectors	Visual check	Not loose	Retighten connector fixing screws.	
5	Battery		Check GOT internal battery voltage status in [Time Setting & Display] of the Utility.	No alarm displayed	Replace with new battery when the current battery has reached the specified life span, even if battery voltage is not displayed.	

## 3.3 Battery Replacement

The battery retains RAM data, clock data, and system status log data. Screen data is stored in the flash memory and data is retained even if the battery is


Battery model name Handy GOT is shipped with the following battery. Use it at replacement.

•	
Product name	Model name
Battery	GT11-50BAT


Dates y replacement procedure


1) After keeping the GOT turned ON more than 10 minutes, turn OFF the GOT.

Perform steps 2) to 7) within five minutes after turning off the GOT. 2) Loosen the environmental protection back cover screws at four points on GOT



4) Insert the connector of the new battery.






6) Attach the environmental protection Tightening torque: 0.36 to 0.48 N•m tion back cover and tighten the screws

7) Turn the GOT power on

7) Turning GOT power on.
8) Check if the battery condition is normal with the utility.
Refer to the following for the details of battery status display.
→ GOT2000 Series User's Manual (Utility)



Battery life
 Approximate battery life: 5 years (ambient temperature: 25°C)
 Battery replacement: In 4 to 5 years
 The battery is susceptible to natural discharge. Order one when necessary.
 Battery status can be confirmed on a GOT utility screen.
 For details of battery status or how to output alarm, refer to the following.
 → GOT2000 Series User's Manual (Hardware)

## 4.1 Cautions on Using Emergency Stop Switch

In When using the emergency stop switch in the handy GOT, judge the validity to use the emergency stop switch in accordance with the risk assessment in your

2) When using the parallel circuit (which disables the emergency stop status while the handy GOT is removed), the system may not conform to the safety standards. Check the safety standards required in the system, and then judge the validity to use the emergency stop switch.

3) If a shock which exceeds the general specifications of the Handy GOT is applied, a chattering may occurs in the emergency stop switch due to the structure of the switch. Check your usage condition and decide whether to use

「电器电子产品有害物质限制使用标识要求」的表示方式



Note: This symbol mark is for China only.

含有有害6物质的名称,含有量,含有部品

本产品中所含有的有害6物质的名称,含有量,含有部品如下表

产品中有害物质的名称及含量

		Г.	1 1 1 1 1 1 1 1 1 1 1 1 1 1 1 1 1 1 1						
Ī	部件名称			有害物质					
			铅 (Pb)	汞 (Hg)	镉 (Cd)	六价铬 (Cr(VI))	多溴联苯 (PBB)	多溴 二苯醚 (PBDE)	
_	显示器 GOT	外壳	0	0	0	0	0	0	
		印刷基板	×	0	0	0	0	0	
		由继	Y						

本表格依据SJ/T 11364的规定编制。

〇:表示该有害物质在该部件所有均质材料中的含量均在GB/T

26572規定的限量要求以下。 ※:表示该有害物质至少在该部件的某一均质材料中的含量超出GB/

T 26572规定的限量要求。

Referenced Standard: GB/T15969.2 (Requirement of Chinese standardized law)

This manual confers no industrial property rights or any rights of any other kind, nor does it confer any patent licenses. Mitsubish Electric Corporation cannot be held responsible for any problems involving industrial property rights which may occur as a result of using the contents noted in this manual.

Warranty
Exclusion of loss in opportunity and secondary loss from warranty liability
Regardless of the gratis warranty term, Mitsubishi Electric shall not be liable for

compensation to:
(1) Damages caused by any cause found not to be the responsibility of Mitsubishi Electric.

(2) Loss in opportunity, lost profits incurred to the user by Failures of Mitsubishi Electric products.

Electric products.

(3 Special damages and secondary damages whether foreseeable or not, compensation for accidents, and compensation for damages to products other than Mitsubish Electric products.

(4) Replacement by the user, maintenance of on-site equipment, start-up test run and other tooks.

## ⚠ For safe use

This product has been manufactured as a general-purpose part for general

industries, and has not been designed or manufactured to be incorporated in a device or system used in purposes related to human life.

Before using the product for special purposes such as nuclear power, electric 

This product has been manufactured under strict quality control. However mis product has been maintained under strict quality control. nowever when installing the product where major accidents or losses could occur if product fails, install appropriate backup or failsafe functions in the system.