

# **GOT2000 Series CC-Link IE TSN Communication Unit**

User's Manual

G072000

GT25-J71GN13-T2

Thank you for choosing Mitsubishi Electric Graphic Operation Terminal (GOT).

Prior to use, please read both this manual and detailed manual thoroughly to fully understand the product.

MODEL	GT25-J71GN13-T2-U		
MODEL CODE	1D7MV7		
IB(NA)-0800633-E(2307)MEE			

© 2019 MITSUBISHI ELECTRIC CORPORATION

## ●SAFETY PRECAUTIONS●

(Always read these precautions before using this equipment.)

Before using this product, please read this manual and the relevant manuals introduced in this manual carefully and pay full attention to safety to handle the product

The precautions given in this manual are concerned with this product. In this manual, the safety precautions are ranked as "WARNING" and "CAUTION".

Indicates that incorrect handling may cause hazardous conditions, resulting in death or severe injury.

Indicates that incorrect handling may cause hazardous conditions, resulting in medium or slight personal injury or physical damage.

Note that the A CAUTION level may lead to a serious accident according to the

Always follow the precautions of both levels because they are important to per-Please save this manual to make it accessible when required and always forward it to the end use

#### [DESIGN PRECAUTIONS]

### **∆WARNING**

- If a communication fails in data link, the faulty station holds the data link data generated before the communication error. Create an interlock circuit in the sequenc program using the communication status information in order that the system will operate safely. Failure to do so may cause mis-outputs or malfunctions, resulting in accidents. Check the faulty station and the operation status during communication error by referring to the relevant manuals. Some failures of cable or communication unit may cause the GOT to keep the outputs on or off.
- it oil.

  An external circuit for monitoring output signals that may lead to serious accidents.
  Failure to do so may cause mis-outputs or malfunctions, resulting in accidents.

# **MARNING**

If a communication fault (including cable disconnection) occurs during monitoring on the GOT, communication between the GOT and PLC CPU is suspended and the GOT becomes inoperative.

For bus connection (GT27 and GT25 only): The GOT becomes inoperative. Power on the PLC CPU again to reestablish communication.

For bus connection (GT27 and GT25 only): The GOT becomes inoperative. Power on the PLC CPU again to reestablish communication.

For other than bus connection: The GOT becomes inoperative.

A system where the GOT is used should be configured to perform any significant operation to the system by using the switches of a device other than the GOT on the assumption that a GOT communication fault will occur.

Not doing so can cause an accident due to false output or malfunction.

To maintain the security (confidentiality, integrity, and availability) of the GOT and the system against unauthorized access, DoS¹ fatacks, computer viruses, and other opberatlacks from unreliable networks and devices via network, take appropriate measures such as firewalls, virtual private networks (VPNs), and antivirus solutions. Missubishi Electric shall have no responsibility or liability for any problems involving Mitsubishi Electric shall have no responsibility or liability for any problems involving GOT trouble and system trouble by unauthorized access, DoS attacks, computer visuses, and other cyberattacks.

1 DoS: A denial-of-service (DoS) attack disrupts services by overloading systems or exploiting vulnerabilities, resulting in a denial-of-service (DoS) state.

# **⚠ CAUTION**

Do not bunch the control wires or communication cables with the main circuit or pow wires, or lay them close to each other.

As a quide, separate the lines by a distance of at least 100 mm (3.94 inches) otherwise maifunctions may occur due to noise.

# [MOUNTING PRECAUTIONS]

# **∆WARNING**

Be sure to shut off all phases of the external power supply used by the system befo mounting or removing this unit to/from the GOT.

Not doing so can cause a unit failure or malfunction.

# **⚠** CAUTION

- Use this unit in the environment that satisfies the general specifications described in the User's Manual for the GOT used. Not doing so can cause an electric shock, fire, malfunction or product damage or deterioration.
- detenoration.

  When installing this unit to the GOT, fit it to the connection interface of the GOT and tighten the mounting screws in the specified torque range (0.36 N·m to 0.48 N·m) witt a Phillips-head screwdriver No.2.
- a Phillips-head screwdriver No.2.

  Undertightening can cause a drop, failure or malfunction.

  Overtightening can cause a drop, failure or malfunction due to screw or unit damage

  Do not directory touch the conductive part or electronic components of the unit.

  This may cause the unit to fail or malfunction.

#### [WIRING PRECAUTIONS]

# **≜WARNING**

Be sure to shut off all phases of the external power supply used by the system before the sure of the sure of the system before the sure of the sure of the sure of the system before the sure of the sure of the system before the sure of the sure of the sure of the system before the sure of the wiring.
Failure to do so may cause electric shock, product damage or malfunctions.

# **⚠** CAUTION

- Be careful not to let foreign matter such as dust or wire chips get inside the unit. This may cause a fire, failure or malfunctions.

  Make sure to securely connect the cable to the connector of unit. Incorrect connection may cause malfunctions.
- Make sure to house the communication cables connected to the unit in ducts, or fix them with clamps. Failure to do so may cause damage of the unit or the cables due to accidental pull or unintentional shifting of the cables, or malfunctions due to poor contact of the cables.

## [STARTUP/MAINTENANCE PRECAUTIONS]

#### **∆WARNING**

- Do not touch the connector while power is on. Failure to do so may cause electric shock or malfunctions
- Before starting cleaning or terminal screw retightening, always switch off the power

Not switching the power off in all phases can cause a unit failure or malfunction.
Undertightening can cause a short circuit or malfunction.
Overtightening can cause a short circuit or malfunction due to the damage of the screws or unit.

# **⚠ CAUTION**

- Do not disassemble or modify the unit.
  This will cause failure, malfunction, injuries, or fire.
  Do not touch the conductive areas and electronic parts of this unit directly.
  Doing so can cause a unit malfunction or failure.
  When unplugging the cable connected to the unit, do not hold and pull from the cable portion.
  Doing so can cause the unit or cable to be damaged or can cause a malfunction due to a cable connection fault.
- Make sure to touch the grounded metal to discharge the electricity charged in the body, etc., before touching the unit.

  Failure to do so may cause a failure or malfunctions of the unit.

#### [DISPOSAL PRECAUTIONS]

## **♠ CAUTION**

Dispose of this product as industrial waste.

# [TRANSPORTATION PRECAUTIONS]

# **⚠** CAUTION

- Make sure to transport the GOT main unit and/or relevant unit(s) in the manner they will not be exposed to the impact exceeding the impact resistance described in the general specifications of the User's Manual for the GOT used, as they are precision devices.
- devices.
  Failure to do so may cause the unit to fail.
  Check if the unit operates correctly after transportation.
  When furnigants that contain halogen materials such as fluorine, chlorine, bromine, and iodine are used for disinfecting and protecting wooden packaging from insects, they cause malfunction when entering our products. Please take necessary precautions to ensure that remaining materials from furnigant do not enter our products, or test packaging with methods other than furnigation (heat method). Additionally, disinfect and protect wood from insects before packing products.

# <u>Manual</u>

Manual name	Manual number (Model code)
GOT2000 Series User's Manual (Hardware) (Sold separately)	SH-081194ENG (1D7MJ5)
GOT2000 Series User's Manual (Monitor) (Sold separately)	SH-081196ENG (1D7MJ7)
GOT2000 Series Connection Manual (Mitsubishi Electric Products) For GT Works3 Version1 (Sold separately)	SH-081197ENG (1D7MJ8)

# Compliance with the EMC and Low Voltage

To configure a system meeting the requirements of the EMC and Low Voltage Directives when incorporating the Mitsubishi GOT (EMC and Low Voltage Directives compliant) into other machinery or equipment, refer to "EMC AND LOW VOLTAGE DIRECTIVES" of the General Description included with the GOT used. The CE mark, indicating compliance with the EMC and Low Voltage Directives, is printed on the rating plate of the GOT.

#### Compliance with the new China RoHS directive GOT 相关的基于 " 电器电子产品有害物质限制使用管理办法 " 要求的表示方法



Note: This symbol mark is for China only.

含有有害 6 物质的名称、含有量、含有部件 本产品中所含有的有害 6 物质的名称、含有量、含有部件如下表所示。 产品中有害物质的名称及含量

	有害物质						
部件名称	铅 (Pb)	汞 (Hg)	镉 (Cd)	六价铬 (Cr(VI))	多溴联苯 (PBB)	多溴二苯醚 (PBDE)	
路板组件	×	0	0	0	0	0	
脂壳体、电缆、膜材	0	0	0	0	0	0	
金部件、螺丝等金属部件	×	0	0	0	0	0	

- 本表格依据 SJ/T11364 的规定编制。 〇:表示该有害物质在该部件所有均质材料中的含量均在 GB/T26572 规定的限量要 求以下。 表示该有害物质至少在该部件的某一均质材料中的含量超出 GB/T26572 规定的
- 限量要求

# Referenced Standard: GB/T15969.2

# (Requirement of Chinese standardized law)

### Packing List

After unpacking the box, check that the following products are included

Model	Product	Quantity
	CC-Link IE TSN communication unit	1
	Mounting screw set (2 screws, 2 stickers)	2
T2	GOT2000 Series CC-Link IE TSN	1
	Communication Unit User's Manual (This manual)	
	Communication offic osci 3 Mandai (11113 mandai)	

## 1. OVERVIEW


For compatible GOTs, refer to the GOT user's manual

When using the CC-Link IE TSN connection, make the corperform communication with programmable controllers.

### 2. SPECIFICATIONS

Item			Specifications
Station type			Local station (device station)
	RX		16K points (16384 points, 2Kbytes)
RY		RY	16K points (16384 points, 2Kbytes)
Max. link de points per i		RWr	8K points (8192 points, 16Kbytes)
points per i	ietwork	RWw	8K points (8192 points, 16Kbytes)
		LB	32K points (32768 points, 4Kbytes)
		LW	16K points (16384 points, 32Kbytes)
		RX	16K points (16384 points, 2Kbytes)
		RY	16K points (16384 points, 2Kbytes)
Max. link de points per (		RWr	8K points (8192 points, 16Kbytes)
points per v	301	RWw	8K points (8192 points, 16Kbytes)
		LB	32K points (32768 points, 4Kbytes)
		LW	16K points (16384 points, 32Kbytes)
	Communication speed		1 Gbps, 100 Mbps
	Connection cable		standard: Category 5e or higher (double shielded, STP), straight cable  • An Ethernet cable that meets the 100BASE-T. standard: Category 5 or higher (double shielde STP), straight cable
Transmis sion	Max. station-to- station distance		100 m (conform to ANSI/TIA/EIA-568-B (category 5e))
specifica tions	Overall cable distance		Line topology: 12000 m (for connecting 1 maste station and 120 device stations) Ring topology: 12100 m (for connecting 1 maste station and 120 device stations) Other: Depending on the system configuration
	Max. num cascaded stages		20
	Transmiss path		Line topology, star topology, line-star topology, oring topology
Authentication class			CC-Link IE TSN Class B (Synchronized Realtime Communication)
Max. number of stations per network			121 (1 master station and 120 device stations)
Max. number of networks			239
Communication method			Time division method
transient transmission capacity			maximum 1920 bytes
Internal current concumption			0.00.4

# 3. PART NAMES AND EXTERNAL **DIMENSIONS**



No.	Name	Description	
1)	Indicator LED	⇒ (1) Indicator LED	
2)	Connection interface (PORT1 side)	For connecting Ethernet cables  (2) LEDs on a connection interface	
3)	Connection interface (PORT2 side)		
4)	Interface connector	Extension connector installed to a front extension unit or the GOT	
5)	Extension connector	Extension connector to which a back extension unit is installed	
6)	Mounting screw	Mounting screws fixed with a front extension unit or the GOT	
7)	Rating plate	-	

A LED indicates the status of the CC-Link IE TSN communication unit and the

	LED name	Description
	RUN LED	Indicates the operation status. ON: Normal OFF: Error
	P1 SD/RD LED	Indicates the data transmission and reception status.  ON: Sending or receiving data  OFF: Not sending or receiving data
RUN	P2 SD/RD LED	
P1 SD/RD P2 SD/RD ERR.	ERR LED	Indicates the unit status. ON: Unit error or errors in all stations Blink (200 ms interval): Unit error Blink (500 ms interval): Data link faulty station detected "1 OFF: Normal The LED is off when the GOT is in offline mode. Check the error in [Network Status Display] in the GOT utility. For details on [Network Status Display], refer to the following.

\*1 This is available only in the multicast mode.

Note that the LED remains off when a CC-Link IE TSN Class A (Synchroni Realtime Communication) device on a remote station has a data link error

# (2) LEDs on a connection interface

A LED indicates the link status of the CC-Link IE TSN communication unit and the

iec	reception status.				
Г	7 5	LED name	Description		
	LINKLED	L ER LED	Indicates the data receiption status. ON: Abnormal data received OFF: Normal data received The LED is off when the GOT is in offline mode.		
L	ER LED	LINK LED	Indicates the link status. ON: Link-up OFF: Link-down		

# 4. INSTALLATION PROCEDURE


# **⚠ CAUTION**

- When installing this unit to the GOT, fit it to the connection interface of the GOT and tighten the mounting screws in the specified torque range (0.36 N·m to 0.48 N·m) with a Phillips-head screwdriver No.2. Undertightening can cause a drop, failure or malfunction. Overtightening can cause a drop, failure or malfunction due to screw or unit damage.


The following shows how to mount the CC-Link IE TSN communication unit on GT2712 as an example.

Mount the CC-Link IE TSN communication unit on the first stage of the extension


1) Turn off the GOT.



3) Connect the CC-Link IE TSN communication unit to the extension interface on



on interface of the CC-Link IE SN communication unit, do not attach the accessory sticke /hen mounting no extension unit on the extension interface ver four mounting screws with the accessory stickers to gu lostricity. Leave the stickers in place



- 1) Confirm the followings on the Ethernet cable used.
  If there is no disconnection
  If there is no short circuit
  If there is no connection problem at the connectors
  Do not use Ethernet cables with broken latches.
  Using Ethernet cables with broken latches may cause cable disconnection or malfunction.
- Ethernet cable connector securely with the hands.
  4) Connect the Ethernet cable connector and unit connector securely until you hear

# Warranty

Weight

Mitsubishi Electric will not be held liable for damage caused by factors found not to be the cause of Mitsubishi Electric; machine damage or lost profits caused by faults in the Mitsubishi Electric products; damage, secondary damage, accident compensation caused by special factors unpredictable by Mitsubishi Electric: damages to products other than Mitsubishi Electric products; and to other duties.

# ♠ For safe use

- This product has been manufactured as a general-purpose part for general industries, and has not been designed or manufactured to be incorporated in a device or system used in purposes related to
- Before using the product for special purposes such as nuclear power, electric power, aerospace, medicine or passenger movement vehicles, consult with Mitsubishi Electric.
- This product has been manufactured under strict quality control. However, when installing the product where major accidents or losses could occur if the product fails, install appropriate backup or failed for the product fails. failsafe functions in the system.

# Sales office/Tel

Americas
Mitsubishi Electric Automation, Inc.
500 Corporate Woods Parkway, Vernon Hills, IL 60061, U.S.A.
Tel: +1-847-478-2100

Mitsubishi Electric do Brasil Comercio e Servicos Ltda. Avenida Adelino Cardana, 293, 21 andar, Bethaville, Barueri SP, Brazil Tel: +55-11-4689-3000

Misubalhi Electric Automation, Inc. Mexico Branch Boulevard Miguel de Cervantes Saavedra 301. Torre Norte Piso 5, Ampliacion Granada, Miguel Hidalajo. Cludd de Mexico, Mexico, C.P.11520

Europe Mitsubishi Electric Europe B.V. German Branch Mitsubishi-Electric-Platz 1, 40882 Ratingen, Germany Tel: +49-2102-486-0

rei. +49-2 (UZ-486-0 Mitsubishi Electric Europe B.V. UK Branch Travellers Lane, UK-Hatfleld, Hertfordshire, AL10 8XB, U.K. Tel: +44-1707-28-8780

18. 144-1707-20-0700
B.V. Italian Branch
Centro Direzionale Colleoni - Palazzo Sirio, Viale Colleoni 7, 20864 Agrate Brianza (MB), Italy
Tel: +39-039-90531

Mitsubishi Electric Europe B.V. Spanish Branch Carretera de Rubi, 76-80-Apdo. 420, E-08190 Sant Cugat del Valles (Barcelona), Spain Tel: +34-935-65-3131

Mitsubishi Electric Europe B.V. French Branch 25, Boulevard des Bouvets, 92741 Nanterre Cedex, France Tel: +33-1-55-68-55-68

Mitsubishi Electric Europe B.V. Czech B Pekarska 621/7, 155 00 Praha 5, Czech Tel: +420-255 719 200

Mitsubishi Electric Turkey A.S. Umraniye Branch Serifali Mahallesi Nutuk Sokak No:5, TR-34775 Umraniye / Istanbul, Turkey Tel: +90-216-526-3990

Mitsubishi Electric Europe B.V. Polish Branch ul. Krakowska 48, 32-083 Balice, Poland Tel: +48-12-347-65-00

Adroit Technologies 20 Waterford Office Park, 189 Witkoppen Road, Fourways, South Africa Tel: +27-11-658-8100

Asia-Pacific

Mitsubishi Electric Automation (China) Ltd. Mitsubishi Electric Automation Center, No.1386 Hongqiao Road, Shanghai, China Tei: +86-21-2322-3030

SETSUYO ENTERPRISE CO., LTD.
6F, No.105, Wugong 3rd Road, Wugu District, New Taipei City 24889, Taiwan Tel: +886-2-2299-2499

Mitsubishi Electric Automation Korea Co., Ltd. 7F to 9F, Gangseo Hangang XI-tower A, 401, Yangcheon-ro, Gangseo-Gu, Seoul 07528, Korea Tel: +82-2-3660-9669

Mitsubishi Electric Asia Pte. Ltd. 307 Alexandra Road, Mitsubishi Electric Building, Singapore 159943 Tel: +65-6473-2308

Milksubish Electric Factory Automation (Thailand) Co., Ltd. 12th Floor, SV.City Building, Office Tower 1, No. 896/19 and 20 Rama 3 Road, Kwaeng Bangpongpang, Khet Yannawa, Bangkok 10120, Thailand Tei: +66-2682-6522 to 31

PT. Mitsubishi Electric Indonesia Gedung Jaya 8th Floor, JL. MH. Thamrin No.12, Jakarta Pusat 10340, Indonesia Tel: +62-21 3192-6461

Mitsubishi Electric Vietnam Company Limited 11th & 12th Floor, Viettel Tower B, 285 Cach Mang Thang 8 Street, Ward 12, District 10,

Misubishi Electric India Pvt. Ltd. Pune Branch Emerald House, EL-3, J Block, M.I.D.C., Bhosari, Pune - 411026, Maharashtra, India Tei: +91-20-2710-2000

348 Victoria Road, P.O. Box 11, Rydalmere, N.S.W 2116, Australia Tel: +61-2-9684-7777

# MITSUBISHI ELECTRIC CORPORATION

HEAD OFFICE: TOKYO BLDG., 2-7-3, MARUNOUCHI, CHIYODA-KU, TOKYO 100-8310, JAP NAGOYA WORKS: 1-14, YADA-MINAMI 5-CHOME, HIGASHI-KU, NAGOYA 461-8670, JAP

of Economy, Trade and Industry for service transaction permission

Specifications subject to change without notice Printed in Japan, July 2023.

This user's manual describes the CC-Link IE TSN communication unit.
The CC-Link IE TSN communication unit allows GOT2000 series to function as a local station (device station) on the CC-Link IE TSN

The general specifications of the CO-Link IE TSN communication unit indicated below.

Station type			Local station (device station)
			16K points (16384 points, 2Kbytes)
			16K points (16384 points, 2Kbytes)
Max. link device RWr			8K points (8192 points, 16Kbytes)
points per r	network	RWw	8K points (8192 points, 16Kbytes)
		LB	32K points (32768 points, 4Kbytes)
		LW	16K points (16384 points, 32Kbytes)
		RX	16K points (16384 points, 2Kbytes)
		RY	16K points (16384 points, 2Kbytes)
Max. link de points per (		RWr	8K points (8192 points, 16Kbytes)
points per v	301	RWw	8K points (8192 points, 16Kbytes)
		LB	32K points (32768 points, 4Kbytes)
		LW	16K points (16384 points, 32Kbytes)
	Communication speed		1 Gbps, 100 Mbps
	Connection cable	on	An Ethernet cable that meets the 1000BASE-T standard: Category 5e or higher (double shielded, STP), straight cable     An Ethernet cable that meets the 100BASE-TX standard: Category 5 or higher (double shielded STP), straight cable
Transmis sion	Max. station-to- station distance		100 m (conform to ANSI/TIA/EIA-568-B (category 5e))
specifica tions	Overall cable distance		Line topology: 12000 m (for connecting 1 maste station and 120 device stations) Ring topology: 12100 m (for connecting 1 maste station and 120 device stations) Other: Depending on the system configuration
	Max. number of cascaded stages  Transmission path		20
			Line topology, star topology, line-star topology, o ring topology
Authentication class			CC-Link IE TSN Class B (Synchronized Realtime Communication)
Max. number of stations per network			121 (1 master station and 120 device stations)
Max. number of networks			239
Communication method			Time division method
transient transmission capacity			maximum 1920 bytes
Internal current consumption			0.92 A
			1

0.17 kg

# 5. PRECAUTIONS FOR WIRING CABLES

- malfunction.

  3) When connecting or removing the Ethernet cables to/from the unit, hold the

# a click sound. S) For connecting Ethernet cables to the unit, the bending radius of the cables must be within the specified range. For details, check the specifications of the cables to be used. G) When connecting an Ethernet cable, do not touch the cable pins or the port pins on the unit, and prevent dirt or dust from adhering to the pins. Otherwise, there may be further losses in transmission, causing a communication error in the data link. We the connector to the Ethernet cable correctly. After wiring, perform a loop test or station-to-station test or others to confirm if the setting and wiring of CC-Link IE TSN communication unit have been done properly.