

< Silicon RF Power Module >

# RA13H1317M1

RoHS Compliance, 135-175MHz 13W 12.5V, 2 Stage Amp. For MOBILE Radio

## DESCRIPTION

The RA13H1317M1 is a 13-watt RF MOSFET Amplifier Module for 12.5-volt mobile radios that operate in the 135- to -175 MHz range.

The battery can be connected directly to the drain of the enhancement-mode MOSFET transistors.

The output power and drain current increase as the gate voltage increases. With a gate voltage around 3.5V (minimum), output power and drain current increases substantially.

The nominal output power becomes available at 4V (typical) and 5V (maximum).

This module is designed for non-linear FM modulation, but may also be used for linear modulation by setting the drain quiescent current with the gate voltage and controlling the output power with the input power.

## FEATURES


- Enhancement-Mode MOSFET Transistors  
( $I_{DD} \approx 0$  @  $V_{DD}=12.5V$ ,  $V_{GG}=0V$ )
- $P_{out} > 13W$   $\eta_T > 40\%$  @  $V_{DD}=12.5V$ ,  $V_{GG}=5V$ ,  $P_{in}=50mW$
- Broadband Frequency Range: 135-175MHz
- Module Size: 67 x 19.4 x 9.9 mm
- Linear operation is possible by setting the quiescent drain current with the gate voltage and controlling the output power with the input power.

## RoHS COMPLIANCE

- RA13H1317M1 is a RoHS compliant products.
- This product include the lead in the Glass of electronic parts and the lead in electronic Ceramic parts. However, it is applicable to the following exceptions of RoHS Directions.
  1. Lead in the Glass of a cathode-ray tube, electronic parts, and fluorescent tubes.
  2. Lead in electronic Ceramic parts.

## ORDERING INFORMATION:

ORDER NUMBER	SUPPLY FORM
RA13H1317M1-501	Antistatic tray, 10 modules/tray



**RA13H1317M1**

RoHS Compliance, 135-175MHz 13W 12.5V, 2 Stage Amp. For MOBILE Radio

**MAXIMUM RATINGS** ( $T_{\text{case}}=+25^{\circ}\text{C}$ ,  $Z_G=Z_L=50\Omega$  unless otherwise specified)

SYMBOL	PARAMETER	CONDITIONS	RATING	UNIT
$V_{DD}$	Drain Voltage	$V_{GG} \leq 5V$	17	V
$V_{GG}$	Gate Voltage	$V_{DD} \leq 12.5V$ , $P_{in}=50mW$	6	V
$I_{DD}$	Total Current	-	5	A
$P_{in}$	Input Power	$f=135-175MHz$ , $V_{GG} \leq 5V$	100	mW
$P_{out}$	Output Power		20	W
$T_{\text{case(OP)}}$	Operation Case Temperature Range		-30 to +100	$^{\circ}\text{C}$
$T_{\text{stg}}$	Storage Temperature Range	-	-40 to +110	$^{\circ}\text{C}$

The above parameters are independently guaranteed.

**ELECTRICAL CHARACTERISTICS** ( $T_{\text{case}}=+25^{\circ}\text{C}$ ,  $Z_G=Z_L=50\Omega$ , unless otherwise specified)




SYMBOL	PARAMETER	CONDITIONS	MIN	TYP	MAX	UNIT
f	Frequency Range		135	-	175	MHz
$P_{out}$	Output Power	$V_{DD}=12.5V$ , $V_{GG}=5V$ , $P_{in}=50mW$	13	-	-	W
$\eta_T$	Total Efficiency		40	-	-	%
$2f_o$	2 <sup>nd</sup> Harmonic		-	-	-25	dBc
$3f_o$	3 <sup>rd</sup> Harmonic		-	-	-30	dBc
$\rho_{in}$	Input VSWR		-	-	3:1	—
$I_{DD}$	Leakage Current	$V_{DD}=17V$ , $V_{GG}=0V$ , $P_{in}=0W$	-	-	1	mA
—	Stability	$V_{DD}=10.0-15.2V$ , $P_{in}=25-70mW$ , $P_{out} \leq 20W$ ( $V_{GG}$ control), Load VSWR=3:1 (All Phase)	No parasitic oscillation		—	
—	Load VSWR Tolerance	$V_{DD}=15.2V$ , $P_{in}=50mW$ , $P_{out}=13W$ ( $V_{GG}$ adj.), Load VSWR=20:1 (All Phase)	No degradation or destroy		—	

All parameters, conditions, ratings, and limits are subject to change without notice.

# RA13H1317M1

RoHS Compliance, 135-175MHz 13W 12.5V, 2 Stage Amp. For MOBILE Radio




TYPICAL PERFORMANCE (Tcase=+25°C, Zg=Zl=50Ω, unless otherwise specified)



# RA13H1317M1

RoHS Compliance, 135-175MHz 13W 12.5V, 2 Stage Amp. For MOBILE Radio




TYPICAL PERFORMANCE (Tcase=+25°C, Zg=Zl=50Ω, unless otherwise specified)



# RA13H1317M1

RoHS Compliance, 135-175MHz 13W 12.5V, 2 Stage Amp. For MOBILE Radio


**TYPICAL PERFORMANCE** ( $T_{case}=+25^{\circ}C$ ,  $Z_g=Z_l=50\Omega$ , unless otherwise specified)



# RA13H1317M1

RoHS Compliance, 135-175MHz 13W 12.5V, 2 Stage Amp. For MOBILE Radio


TYPICAL PERFORMANCE (Tcase=+25°C, Zg=Zl=50Ω, unless otherwise specified)



# RA13H1317M1

RoHS Compliance, 135-175MHz 13W 12.5V, 2 Stage Amp. For MOBILE Radio

TYPICAL PERFORMANCE (T<sub>case</sub>=+25°C, Z<sub>g</sub>=Z<sub>l</sub>=50Ω, unless otherwise specified)







# RA13H1317M1

RoHS Compliance, 135-175MHz 13W 12.5V, 2 Stage Amp. For MOBILE Radio

## TEST BLOCK DIAGRAM



## EQUIVALENT CIRCUIT



- ① INPUT TERMINAL ( $P_{in}$ )
- ② GATE BIAS DC SUPPLY TERMINAL ( $V_{GG}$ )
- ③ DRAIN BIAS DC SUPPLY TERMINAL ( $V_{DD}$ )
- ④ OUTPUT TERMINAL ( $P_{out}$ )
- ⑤ FIN (GND)

# RA13H1317M1

RoHS Compliance, 135-175MHz 13W 12.5V, 2 Stage Amp. For MOBILE Radio

---

## RECOMMENDATIONS and APPLICATION INFORMATION:

### Construction:

This module consists of a glass-epoxy substrate soldered onto a copper flange. For mechanical protection, a metal cap is attached (which makes the improvement of RF radiation easy). The MOSFET transistor chips are die bonded onto metal, wire bonded to the substrate, and coated with resin. Lines on the substrate (eventually inductors), chip capacitors, and resistors form the bias and matching circuits. Wire leads soldered onto the glass-epoxy substrate provide the DC and RF connection.

Following conditions must be avoided:

- Bending forces on the glass-epoxy substrate (for example, by driving screws or from fast thermal changes)
- Mechanical stress on the wire leads (for example, by first soldering then driving screws or by thermal expansion)
- Defluxing solvents reacting with the resin coating on the MOSFET chips (for example, Trichloroethylene)
- ESD, surge, overvoltage in combination with load VSWR, and oscillation

### ESD:

This MOSFET module is sensitive to ESD voltages down to 1000V. Appropriate ESD precautions are required.

### Mounting:

A thermal compound between module and heat sink is recommended for low thermal contact resistance. The module must first be screwed to the heat sink, then the leads can be soldered to the printed circuit board. M3 screws are recommended with a tightening torque of 4.0 to 6.0 kgf-cm.

### Soldering and Defluxing:

This module is designed for manual soldering.

The leads must be soldered after the module is screwed onto the heat sink.

The temperature of the lead (terminal) soldering should be lower than 350°C and shorter than 3 second.

Ethyl Alcohol is recommend for removing flux. Trichloroethylene solvents must not be used (they may cause bubbles in the coating of the transistor chips which can lift off the bond wires).

### Thermal Design of the Heat Sink:

At  $P_{out}=13W$ ,  $V_{DD}=12.5V$  and  $P_{in}=50mW$  each stage transistor operating conditions are:

Stage	$P_{in}$ (W)	$P_{out}$ (W)	$R_{th(ch-case)}$ (°C/W)	$I_{DD} @ \eta_T=40\%$ (A)	$V_{DD}$ (V)
1 <sup>st</sup>	0.05	3	2.57	0.5	12.5
2 <sup>nd</sup>	3	13	1.6	2.1	

The channel temperatures of each stage transistor  $T_{ch} = T_{case} + (V_{DD} \times I_{DD} - P_{out} + P_{in}) \times R_{th(ch-case)}$  are:

$$T_{ch1} = T_{case} + (12.5V \times 0.5A - 3W + 0.05W) \times 2.57°C/W = T_{case} + 8.5 °C$$

$$T_{ch2} = T_{case} + (12.5V \times 2.1A - 13W + 3W) \times 1.6°C/W = T_{case} + 26 °C$$

For long-term reliability, it is best to keep the module case temperature ( $T_{case}$ ) below 90°C. For an ambient temperature  $T_{air}=60°C$  and  $P_{out}=50W$ , the required thermal resistance  $R_{th(case-air)} = (T_{case} - T_{air}) / ((P_{out} / \eta_T) - P_{in})$  of the heat sink, including the contact resistance, is:

$$R_{th(case-air)} = (90°C - 60°C) / (13W/40\% - 13W + 0.05W) = 1.53 °C/W$$

When mounting the module with the thermal resistance of 1.53 °C/W, the channel temperature of each stage transistor is:

$$T_{ch1} = T_{air} + 38.5 °C$$

$$T_{ch2} = T_{air} + 56 °C$$

The 175°C maximum rating for the channel temperature ensures application under derated conditions.

# RA13H1317M1

RoHS Compliance, 135-175MHz 13W 12.5V, 2 Stage Amp. For MOBILE Radio

---

## **Keep safety first in your circuit designs!**

Mitsubishi Electric Corporation puts the maximum effort into making semiconductor products better and more reliable, but there is always the possibility that trouble may occur with them. Trouble with semiconductors may lead to personal injury, fire or property damage. Remember to give due consideration to safety when making your circuit designs, with appropriate measures such as (i) placement of substitutive, auxiliary circuits, (ii) use of non-flammable material or (iii) prevention against any malfunction or mishap.

## **Notes regarding these materials**

- These materials are intended as a reference to assist our customers in the selection of the Mitsubishi Electric Semiconductor product best suited to the customer's application; they do not convey any license under any intellectual property rights, or any other rights, belonging to Mitsubishi Electric Corporation or a third party.
- Mitsubishi Electric Corporation assumes no responsibility for any damage, or infringement of any third-party's rights, originating in the use of any product data, diagrams, charts, programs, algorithms, or circuit application examples contained in these materials.
- All information contained in these materials, including product data, diagrams, charts, programs and algorithms represents information on products at the time of publication of these materials, and are subject to change by Mitsubishi Electric Corporation without notice due to product improvements or other reasons. It is therefore recommended that customers contact Mitsubishi Electric Corporation or an authorized Mitsubishi Electric Semiconductor product distributor for the latest product information before purchasing a product listed herein.  
The information described here may contain technical inaccuracies or typographical errors. Mitsubishi Electric Corporation assumes no responsibility for any damage, liability, or other loss rising from these inaccuracies or errors.  
Please also pay attention to information published by Mitsubishi Electric Corporation by various means, including the Mitsubishi Electric Semiconductor home page (<http://www.MitsubishiElectric.com/semiconductor/>).
- When using any or all of the information contained in these materials, including product data, diagrams, charts, programs, and algorithms, please be sure to evaluate all information as a total system before making a final decision on the applicability of the information and products. Mitsubishi Electric Corporation assumes no responsibility for any damage, liability or other loss resulting from the information contained herein.
- Mitsubishi Electric Corporation semiconductors are not designed or manufactured for use in a device or system that is used under circumstances in which human life is potentially at stake. Please contact Mitsubishi Electric Corporation or an authorized Mitsubishi Electric Semiconductor product distributor when considering the use of a product contained herein for any specific purposes, such as apparatus or systems for transportation, vehicular, medical, aerospace, nuclear, or undersea repeater use.
- The prior written approval of Mitsubishi Electric Corporation is necessary to reprint or reproduce in whole or in part these materials.
- If these products or technologies are subject to the Japanese export control restrictions, they must be exported under a license from the Japanese government and cannot be imported into a country other than the approved destination.  
Any diversion or re-export contrary to the export control laws and regulations of Japan and/or the country of destination is prohibited.
- Please contact Mitsubishi Electric Corporation or an authorized Mitsubishi Electric Semiconductor product distributor for further details on these materials or the products contained therein.