

< DIPIPM > PSS10S73FT

TRANSFER MOLDING TYPE INSULATED TYPE

OUTLINE



MAIN FUNCTION AND RATINGS

- 3 phase DC/AC inverter
- 1200V / 10A (CSTBT)
- N-side IGBT open emitter
- Built-in bootstrap diodes with current limiting resistor


APPLICATION

 AC 400Vrms(DC voltage:800V or below) class low power motor control

INTEGRATED DRIVE, PROTECTION AND SYSTEM CONTROL FUNCTIONS

- For P-side : Drive circuit, High voltage high-speed level shifting, Control supply under-voltage (UV) protection
- For N-side : Drive circuit, Control supply under-voltage protection (UV), Short circuit protection (SC),
- Fault signaling : Corresponding to SC fault (N-side IGBT), UV fault (N-side supply)
- Temperature output : Outputting LVIC temperature by analog signal
- Input interface : 3, 5V line, Schmitt trigger receiver circuit (High Active)
- UL Recognized : UL1557 File E323585

INTERNAL CIRCUIT



Publication Date: March 2022

TRANSFER MOLDING TYPE **INSULATED TYPE**

MAXIMUM RATINGS (T_j = 25°C, unless otherwise noted)

INVERTER PART

Symbol	Parameter	Condition		Ratings	Unit
Vcc	Supply voltage	Applied between P-NU,NV,NW		900	V
V _{CC(surge)}	Supply voltage (surge)	Applied between P-NU,NV,NW		1000	V
V _{CES}	Collector-emitter voltage			1200	V
±l _C	Each IGBT collector current	TC= 25°C	(Note 1)	10	Α
±I _{CP}	Each IGBT collector current (peak)	T _C = 25°C, less than 1ms		20	Α
T _{jop}	Operation junction temperature	Continuous operation	(Note 2)	-30~+150	°C
T _{jmax}	Maximum junction temperature	Temporally operation (e.g. overload)		175	°C


CONTROL (PROTECTION) PART

Symbol	Parameter	Condition	Ratings	Unit
V_D	Control supply voltage	Applied between V _{P1} -V _{NC} , V _{N1} -V _{NC}	20	V
V_{DB}	Control supply voltage	Applied between V _{UFB} -V _{UFS} , V _{VFB} -V _{VFS} ,V _{WFB} -V _{WFS}	20	V
V_{IN}	Input voltage	Applied between U _P , V _P , W _P , U _N , V _N , W _N -V _{NC}	-0.5~V _D +0.5	V
V_{FO}	Fault output supply voltage	Applied between Fo-VNC	-0.5~V _D +0.5	V
I _{FO}	Fault output current	Sink current at F ₀ terminal	5	mA
V _{sc}	Current sensing input voltage	Applied between CIN-V _{NC}	-0.5~V _D +0.5	V

TOTAL SYSTEM

Symbol	Parameter	Condition	Ratings	Unit
V _{CC(PROT)}	Self protection supply voltage limit (Short circuit protection capability)	V _D = 13.5~16.5V, Inverter Part T _i = 150°C, non-repetitive, less than 2μs	800	V
T _C	Module case operation temperature	Measurement point of Tc is provided in Fig.1	-30~+125	°C
T _{stg}	Storage temperature		-40~+125	°C
V _{iso}	Isolation voltage	60Hz, Sinusoidal, AC 1min, between connected all pins and heat sink plate	2500	V _{rms}

Fig. 1: T_C MEASUREMENT POINT



THERMAL RESISTANCE

Cumbal	Danamatan	Condition		Limits		
Symbol Parameter		Condition		Тур.	Max.	Unit
R _{th(j-c)Q}	Junction to case thermal	Inverter IGBT part (per 1/6 module)	-	-	1.50	K/W
R _{th(j-c)F}	resistance (Note 3)	Inverter FWDi part (per 1/6 module)	-	-	1.80	K/W

Note 3: Grease with good thermal conductivity and long-term endurance should be applied evenly with about +100µm~+200µm on the contacting surface of DIPIPM and heat sink. The contacting thermal resistance between DIPIPM case and heat sink Rth(c-f) is determined by the thickness and the thermal conductivity of the applied grease. For reference, Rth(c-f) is about 0.3K/W (per 1/6 module, grease thickness: 20µm, thermal conductivity: 1.0W/m•k).

Note 1: Pulse width and period are limited due to junction temperature.

Note 2: The maximum junction temperature rating of built-in power chips is 175°C(@Tc≤125°C). However, to ensure safe operation of DIPIPM, the average junction temperature should be limited to Tj(Ave)≤150°C (@Tc≤125°C).

TRANSFER MOLDING TYPE INSULATED TYPE

ELECTRICAL CHARACTERISTICS ($T_j = 25^{\circ}C$, unless otherwise noted) **INVERTER PART**


Cumah al	Daramatar	Condition	Limits			1.1
Symbol	Parameter	Condition		Тур.	Max.	Unit
$V_{\text{CE(sat)}}$	Collector-emitter saturation voltage	$V_D = V_{DB} = 15V$, $I_C = 10A$, $V_{IN} = 5V$	-	1.50	2.20	V
V _{EC}	FWDi forward voltage	V _{IN} = 0V, -I _C = 10A	-	1.90	2.40	V
t _{on}			0.85	1.50	2.20	μs
t _{c(on)}		V_{CC} = 600V, V_{D} = V_{DB} = 15V	-	0.30	0.60	μs
t _{off}	Switching times	I _C = 10A, T _j = 25°C, V _{IN} = 0↔5V	-	1.60	2.00	μs
$t_{c(off)}$		Inductive Load (upper-lower arm)	-	0.25	0.50	μs
t _{rr}			-	0.40	-	μs
I _{CES}	Collector-emitter cut-off current	V _{CE} =V _{CES}	-	-	1	mA


CONTROL (PROTECTION) PART

Cumbal	Deremeter	Condition		Limits			Unit
Symbol	Parameter	Cond	Condition		Тур.	Max.	Unit
1		Total of \/ \/ \/ \/	V _D =15V, V _{IN} =0V	-	-	5.60	
I _D	Circuit current	Total of V_{P1} - V_{NC} , V_{N1} - V_{NC}	V _D =15V, V _{IN} =5V	-	-	5.60	
-	- Circuit current	Each part of V _{UFB} - V _{UFS} ,	$V_D=V_{DB}=15V, V_{IN}=0V$	-	-	0.55	mA
I _{DB}		V _{VFB} - V _{VFS} , V _{WFB} - V _{WFS}	$V_D=V_{DB}=15V$, $V_{IN}=5V$	-	-	0.55	
$V_{\text{SC(ref)}}$	Short circuit trip level	V _D = 15V	(Note 4)	0.450	0.480	0.510	V
UV_DBt	P-side Control supply	Trip level		10.0	-	12.0	V
UV_DBr	under-voltage protection(UV)	Reset level	10.5	-	12.5	V	
UV _{Dt}	N-side Control supply under-voltage protection(UV) Trip level Reset level		10.3	-	12.5	V	
UV _{Dr}				10.8	-	13.0	V
V_{OT}	Temperature Output	LVIC Temperature=85°C, Pull down R=5.1kΩ (Note 5)		2.51	2.64	2.76	V
V_{FOH}	Fault output voltage	V_{SC} = 0V, F_O terminal pulled	up to 5V by $10k\Omega$	4.9	-	-	V
V_{FOL}	Fault output voltage	V_{SC} = 1V, I_{FO} = 1mA		-	-	0.95	V
t_{FO}	Fault output pulse width	C _{FO} =22nF	(Note 6)	1.6	2.4	-	ms
I _{IN}	Input current	V _{IN} = 5V	V _{IN} = 5V		1.00	1.50	mA
$V_{th(on)}$	ON threshold voltage	Annlied between LL, V., W.	The Ver WestVer	-	-	2.60	V
$V_{th(off)}$	OFF threshold voltage	Applied between U _P , V _P , W _P , U _N , V _N , W _N -V _{NC}		0.80	-	-	•
V_{F}	Bootstrap Di forward voltage	I _F =10mA including voltage drop by limiting resistor (Note 7)		0.5	0.9	1.3	V
R	Built-in limiting resistance	Included in bootstrap Di		16	20	24	Ω

Note 4 : SC protection works only for N-side IGBT. Please select the external shunt resistance such that the SC trip-level is less than 2.0 times of the current rating.
5 : DIPIPM don't shutdown IGBTs and output fault signal automatically when temperature rises excessively. When temperature exceeds the protective level that user defined, controller (MCU) should stop the DIPIPM. Temperature of LVIC vs. VOT output characteristics is described in Fig. 3. These minimum and maximum curves are based on theoretical designed value excluding LVIC temperature=85°C limits.

Fig. 2 Characteristics of bootstrap Di V_F-I_F curve (@Ta=25°C) including voltage drop by limiting resistor (Right chart is enlarged chart.)





^{6 :} Fault signal Fo outputs when SC or UV protection works. Fo pulse width is different for each protection modes. At SC failure, Fo pulse width is a fixed width which is specified by the capacitor connected to C_{FO} terminal. (C_{FO}=9.1 x 10⁻⁶ x t_{FO} [F]), but at UV failure, Fo outputs continuously until recovering from UV state. (But minimum Fo pulse width is the specified time by C_{FO}.)

^{7 :} The characteristics of bootstrap Di is described in Fig.2.

TRANSFER MOLDING TYPE INSULATED TYPE

Fig. 3 Temperature of LVIC vs. VoT output characteristics





Fig. 4 VoT output circuit



- (1) It is recommended to insert $5.1k\Omega$ pull down resistor for getting linear output characteristics at low temperature below room temperature. When the pull down resistor is inserted between V_{OT} and V_{NC} (control GND), the extra circuit current, which is calculated approximately by V_{OT} output voltage divided by pull down resistance, flows as LVIC circuit current continuously. In the case of using V_{OT} for detecting high temperature over room temperature only, it is unnecessary to insert the pull down resistor.
- (2) In the case of using V_{OT} with low voltage controller like 3.3V MCU, V_{OT} output might exceed control supply voltage 3.3V when temperature rises excessively. If system uses low voltage controller, it is recommended to insert a clamp Di between control supply of the controller and V_{OT} output for preventing over voltage destruction.
- (3) In the case of not using V_{OT} , leave V_{OT} output NC (No Connection).


Refer the application note for this product about the usage of Vot.

TRANSFER MOLDING TYPE **INSULATED TYPE**

MECHANICAL CHARACTERISTICS AND RATINGS

Parameter	Condition		Reference			Unit	
Falametei	Condition		Reference	Min.	Тур.	Max.	Offic
Mounting torque	Mounting screw : M3 (Note 8)	(Nata O)	JEITA-ED-4701	0.59	0.78	0.98	N·m
Mounting torque		(Note 8)	402 Method II	0.59			IN.III
Torminal atraneth null	Load 10N		JEITA-ED-4701	10	-	-	
Terminal strength pull			401 Method I				S
Townsia at atmospath, beautings	Lond CN COdes Dand		JEITA-ED-4701	2	-		4:
Terminal strength bending	Load 5N, 90deg. Bend		401 Method III			-	times
Weight			-	-	21	ı	g
Heat radiation part flatness		(Note 9)	-	-50	-	100	μm

Note 8: Plain washers (ISO 7089~7094) are recommended. Note 9: Measurement positions of heat radiation part flatness are as below.




RECOMMENDED OPERATION CONDITIONS

Symbol	Parameter	Condition	Limits			Unit
Symbol	Farameter	Condition	Min.	Тур.	Max.	Offic
Vcc	Supply voltage	Applied between P-NU, NV, NW	350	600	800	V
V_D	Control supply voltage	Applied between V _{P1} -V _{NC} , V _{N1} -V _{NC}	13.5	15.0	16.5	V
V_{DB}	Control supply voltage	Applied between V _{UFB} -V _{UFS} , V _{VFB} -V _{VFS} , V _{WFB} -V _{WFS}	13.0	15.0	18.5	V
ΔV_D , ΔV_{DB}	Control supply variation		-1	-	+1	V/µs
t _{dead}	Arm shoot-through blocking time	For each input signal	2.0	-	-	μs
f _{PWM}	PWM input frequency	T _C ≤ 125°C, T _j ≤ 150°C	-	-	20	kHz
PWIN(on)	Minimum input pulse width	(Note 10)	1.0	-	-	μs
PWIN(off)	Willimitani input puise widin	(Note 11)	2.0	-	-	μο
V _{NC}	V _{NC} variation	Between V _{NC} -NU, NV, NW (including surge)	-5.0	-	+5.0	V

Note 10: DIPIPM might not make response if the input signal pulse width is less than PWIN(on).

Note 11: DIPIPM might make no response or delayed response (P-side IGBT only) for input pulse width less than PWIN(off). Over rated collector current (Ic) operation, DIPIPM might make delayed response even if the input signal pulse width is PWIN(off) or more. The timing charts are described as below.




Real line: Normal response; turn on time t1 Broken line: Delayed response; turn on time t2 (t1:Normal switching time)

TRANSFER MOLDING TYPE INSULATED TYPE

Fig. 5 Timing Charts of The DIPIPM Protective Functions


[A] Short-Circuit Protection (N-side only with the external shunt resistor and RC filter)

- a1. Normal operation: IGBT ON and outputs current.
- a2. Short circuit current detection (SC trigger)
 - (It is recommended to set RC time constant 1.5~2.0µs so that IGBT shut down within 2.0µs when SC.)
- a3. All N-side IGBT's gates are hard interrupted.
- a4. All N-side IGBTs turn OFF.
- a5. F_0 outputs. The pulse width of the Fo signal is set by the external capacitor C_{FO} .
- a6. Input = "L": IGBT OFF
- a7. Fo finishes output, but IGBTs don't turn on until inputting next ON signal (L→H). (IGBT of each phase can return to normal state by inputting ON signal to each phase.)
- a8. Normal operation: IGBT ON and outputs current.



[B] Under-Voltage Protection (N-side, UVD)

- b1. Control supply voltage V_D exceeds under voltage reset level (UV_{Dr}), but IGBT turns ON by next ON signal (L→H). (IGBT of each phase can return to normal state by inputting ON signal to each phase.)
- b2. Normal operation: IGBT ON and outputs current.
- b3. V_D level drops to under voltage trip level. (UV_{Dt}).
- b4. All N-side IGBTs turn OFF in spite of control input condition.
- b5. Fo outputs for the period set by the capacitance C_{FO}, but output is extended during V_D keeps below UV_{Dr}.
- b6. V_D level reaches UV_{Dr} .
- b7. Normal operation: IGBT ON and outputs current.




< DIPIPM >

PSS10S73FT

TRANSFER MOLDING TYPE INSULATED TYPE


[C] Under-Voltage Protection (P-side, UV_{DB})

- c1. Control supply voltage V_{DB} rises. After the voltage reaches under voltage reset level UV_{DBr} , IGBT turns on by next ON signal (L \rightarrow H).
- c2. Normal operation: IGBT ON and outputs current.
- c3. V_{DB} level drops to under voltage trip level (UV_{DBt}).
- c4. IGBT of the correspond phase only turns OFF in spite of control input signal level, but there is no Fo signal output.
- c5. V_{DB} level reaches UV_{DBr} .
- c6. Normal operation: IGBT ON and outputs current.



TRANSFER MOLDING TYPE INSULATED TYPE


Fig. 6 Example of Application Circuit



- (1) If control GND is connected with power GND by common broad pattern, it may cause malfunction by power GND fluctuation. It is recommended to connect control GND and power GND at only a point N1 (near the terminal of shunt resistor).
- (2) It is recommended to insert a Zener diode D1(24V/1W) between each pair of control supply terminals to prevent surge destruction.
- (3) To prevent surge destruction, the wiring between the smoothing capacitor and the P, N1 terminals should be as short as possible. Generally a 0.1-0.22µF snubber capacitor C3 between the P-N1 terminals is recommended.
- (4) R1, C4 of RC filter for preventing protection circuit malfunction is recommended to select tight tolerance, temp-compensated type. The time constant R1C4 should be set so that SC current is shut down within 2µs. (1.5µs~2µs is recommended generally.) SC interrupting time might vary with the wiring pattern, so the enough evaluation on the real system is necessary.
- (5) To prevent malfunction, the wiring of A, B, C should be as short as possible.
- (6) The point D at which the wiring to CIN filter is divided should be near the terminal of shunt resistor. NU, NV, NW terminals should be connected at near NU, NV, NW terminals when it is used by one shunt operation. Low inductance SMD type with tight tolerance, temp-compensated type is recommended for shunt resistor.
- (7) All capacitors should be mounted as close to the terminals as possible. (C1: good temperature, frequency characteristic electrolytic type and C2:0.22μ-2μF, good temperature, frequency and DC bias characteristic ceramic type are recommended.)
- (8) Input logic is High-active. There is a 3.3kΩ(min.) pull-down resistor in the input circuit of IC. To prevent malfunction, the input wiring should be as short as possible. When using RC coupling, make the input signal level meet the turn-on and turn-off threshold voltage.
- (9) Fo output is open drain type. Fo output will be max 0.95V(@I_{FO}=1mA,25°C), so it should be pulled up to MCU or control power supply (e.g. 5V,15V) by a resistor that makes I_{FO}up to 1mA. (In the case of pulled up to 5V, 10kΩ is recommended.) About driving opto coupler by Fo output, please refer the application note of this series
- (10) Fo pulse width can be set by the capacitor connected to CFO terminal. $C_{FO}(F) = 9.1 \times 10^{-6} \times t_{FO}$ (Required Fo pulse width).
- (11) If high frequency noise superimposed to the control supply line, IC malfunction might happen and cause DIPIPM erroneous operation. To avoid such problem, line ripple voltage should meet dV/dt ≤+/-1V/μs, Vripple≤2Vp-p.
- (12) For DIPIPM, it isn't recommended to drive same load by parallel connection with other phase IGBT or other DIPIPM.

TRANSFER MOLDING TYPE INSULATED TYPE

Fig. 7 MCU I/O Interface Circuit




Note)

Design for input RC filter depends on PWM control scheme used in the application and wiring impedance of the printed circuit board.

DIPIPM input signal interface integrates a minimum $3.3k\Omega$ pull-down resistor. Therefore, when inserting RC filter, it is necessary to satisfy turn-on threshold voltage requirement.

Fo output is open drain type. It should be pulled up to the positive side of 5V or 15V power supply with the resistor that limits Fo sink current I_{Fo} under 1mA. In the case of pulling up to 5V supply, over $5.1k\Omega$ is needed. (10k Ω is recommended.)


Fig. 8 Pattern Wiring Around the Shunt Resistor



Low inductance shunt resistor like surface mounted (SMD) type is recommended.

Fig. 9 Pattern Wiring Around the Shunt Resistor (for the case of open emitter)

When DIPIPM is operated with three shunt resistors, voltage of each shunt resistor cannot be input to CIN terminal directly. In that case, it is necessary to use the external protection circuit as below.




- (1) It is necessary to set the time constant R_fC_f of external comparator input so that IGBT stops within 2μs when short circuit occurs. SC interrupting time might vary with the wiring pattern, comparator speed and so on.
- (2) It is recommended for the threshold voltage Vref to set to the same rating of short circuit trip level (Vsc(ref): typ. 0.480V).
- (3) Select the external shunt resistance so that SC trip-level is less than specified value (=2.0 times of rating current).
- (4) To avoid malfunction, the wiring A, B, C should be as short as possible.
- (5) The point D at which the wiring to comparator is divided should be close to the terminal of shunt resistor.
- (6) OR output high level when protection works should be over 0.510V (=maximum Vsc(ref) rating).
- (7) GND of Comparator, GND of Vref circuit and Cf should be not connected to power GND but to control GND wiring.

TRANSFER MOLDING TYPE INSULATED TYPE

Fig. 10 Package Outlines

Dimensions in mm



Important Notice

The information contained in this datasheet shall in no event be regarded as a guarantee of conditions or characteristics. This product has to be used within its specified maximum ratings, and is subject to customer's compliance with any applicable legal requirement, norms and standards.

Except as otherwise explicitly approved by Mitsubishi Electric Corporation in a written document signed by authorized representatives of Mitsubishi Electric Corporation, our products may not be used in any applications where a failure of the product or any consequences of the use thereof can reasonably be expected to result in personal injury.

In usage of power semiconductor, there is always the possibility that trouble may occur with them by the reliability lifetime such as Power Cycle, Thermal Cycle or others, or when used under special circumstances (e.g. condensation, high humidity, dusty, salty, highlands, environment with lots of organic matter / corrosive gas / explosive gas, or situations which terminals of semiconductor products receive strong mechanical stress). Therefore, please pay sufficient attention to such circumstances. Further, depending on the technical requirements, our semiconductor products may contain environmental regulation substances, etc. If there is necessity of detailed confirmation, please contact our nearest sales branch or distributor.

The contents or data contained in this datasheet are exclusively intended for technically trained staff. Customer's technical departments should take responsibility to evaluate the suitability of Mitsubishi Electric Corporation product for the intended application and the completeness of the product data with respect to such application. In the customer's research and development, please evaluate it not only with a single semiconductor product but also in the entire system, and judge whether it's applicable. As required, pay close attention to the safety design by installing appropriate fuse or circuit breaker between a power supply and semiconductor products to prevent secondary damage. Please also pay attention to the application note and the related technical information.

Publication Date: March 2022

Keep safety first in your circuit designs!

Mitsubishi Electric Corporation puts the maximum effort into making semiconductor products better and more reliable, but there is always the possibility that trouble may occur with them. Trouble with semiconductors may lead to personal injury, fire or property damage. Remember to give due consideration to safety when making your circuit designs, with appropriate measures such as (i) placement of substitutive, auxiliary circuits, (ii) use of non-flammable material or (iii) prevention against any malfunction or mishap.

Notes regarding these materials

- •These materials are intended as a reference to assist our customers in the selection of the Mitsubishi Electric Semiconductor product best suited to the customer's application; they do not convey any license under any intellectual property rights, or any other rights, belonging to Mitsubishi Electric Corporation or a third party.
- •Mitsubishi Electric Corporation assumes no responsibility for any damage, or infringement of any third-party's rights, originating in the use of any product data, diagrams, charts, programs, algorithms, or circuit application examples contained in these materials.
- •All information contained in these materials, including product data, diagrams, charts, programs and algorithms represents information on products at the time of publication of these materials, and are subject to change by Mitsubishi Electric Corporation without notice due to product improvements or other reasons. It is therefore recommended that customers contact Mitsubishi Electric Corporation or an authorized Mitsubishi Electric Semiconductor product distributor for the latest product information before purchasing a product listed herein.

The information described here may contain technical inaccuracies or typographical errors. Mitsubishi Electric Corporation assumes no responsibility for any damage, liability, or other loss rising from these inaccuracies or errors.

Please also pay attention to information published by Mitsubishi Electric Corporation by various means, including the Mitsubishi Electric Semiconductor home page (http://www.MitsubishiElectric.com/semiconductors/).

- •When using any or all of the information contained in these materials, including product data, diagrams, charts, programs, and algorithms, please be sure to evaluate all information as a total system before making a final decision on the applicability of the information and products. Mitsubishi Electric Corporation assumes no responsibility for any damage, liability or other loss resulting from the information contained herein.
- •Mitsubishi Electric Corporation semiconductors are not designed or manufactured for use in a device or system that is used under circumstances in which human life is potentially at stake. Please contact Mitsubishi Electric Corporation or an authorized Mitsubishi Electric Semiconductor product distributor when considering the use of a product contained herein for any specific purposes, such as apparatus or systems for transportation, vehicular, medical, aerospace, nuclear, or undersea repeater use.
- •The prior written approval of Mitsubishi Electric Corporation is necessary to reprint or reproduce in whole or in part these materials.
- •If these products or technologies are subject to the Japanese export control restrictions, they must be exported under a license from the Japanese government and cannot be imported into a country other than the approved destination.
- Any diversion or re-export contrary to the export control laws and regulations of Japan and/or the country of destination is prohibited.
- •Please contact Mitsubishi Electric Corporation or an authorized Mitsubishi Electric Semiconductor product distributor for further details on these materials or the products contained therein.

© MITSUBISHI ELECTRIC CORPORATION. ALL RIGHTS RESERVED. DIPIPM and CSTBT are trademarks of MITSUBISHI ELECTRIC CORPORATION.

Publication Date : March 2022 MITSUBISHI ELECTRIC CORPORATION