

< DIIPM >

# Compact DIIPM Series APPLICATION NOTE

## PSSxxSF1F6

### Table of contents

CHAPTER 1 INTRODUCTION .....	2
1.1 Features of Compact DIIPM .....	2
1.2 Functions .....	2
1.3 Target Applications .....	3
1.4 Product Line-up .....	3
1.5 The Differences between Compact DIIPM and Mini DIIPM Series .....	4
CHAPTER 2 SPECIFICATIONS AND CHARACTERISTICS .....	5
2.1 Compact DIIPM Specifications .....	5
2.1.1 Maximum Ratings .....	5
2.1.2 Thermal Resistance .....	7
2.1.3 Electric Characteristics and Recommended Conditions .....	8
2.1.4 Mechanical Characteristics and Ratings .....	10
2.2 Protective Functions and Operating Sequence .....	11
2.2.1 Short Circuit Protection .....	11
2.2.2 Control Supply UV Protection .....	13
2.2.3 Temperature output function $V_{OT}$ .....	15
2.2.4 Interlock function .....	18
2.3 Package Outlines .....	19
2.3.1 Package outlines and PCB Through-hole Pattern .....	19
2.3.2 Marking .....	21
The Lot number indicates production year, month, running number and country of origin. ....	21
2.3.3 Terminal Description .....	22
2.4 Mounting Method .....	24
2.4.1 Electric Spacing .....	24
2.4.2 Mounting Method and Precautions .....	24
2.4.3 Soldering Conditions .....	25
CHAPTER 3 SYSTEM APPLICATION GUIDANCE .....	27
3.1 Application Guidance .....	27
3.1.1 System connection .....	27
3.1.2 Interface Circuit (Direct Coupling Interface example for using one shunt resistor) .....	28
3.1.3 Interface Circuit (Example of Opto-coupler Isolated Interface) .....	29
3.1.4 External SC Protection Circuit with Using Three Shunt Resistors .....	30
3.1.5 Circuits of Signal Input Terminals and Fo Terminal .....	30
3.1.6 Snubber Circuit .....	32
3.1.7 Recommended Wiring Method around Shunt Resistor .....	32
3.1.8 Precaution for Wiring on PCB .....	34
3.1.9 Parallel operation of DIIPM .....	35
3.1.10 SOA of Compact DIIPM .....	35
3.1.11 SCSOA .....	36
3.1.12 Power Life Cycles .....	37
3.2 Power Loss and Thermal Dissipation Calculation .....	38
3.2.1 Power Loss Calculation .....	38
3.2.2 Temperature Rise Considerations and Calculation Example .....	40
3.2.3 Installation of thermocouple .....	41
3.3 Noise and ESD Withstand Capability .....	42
3.3.1 Evaluation Circuit of Noise Withstand Capability .....	42
3.3.2 Countermeasures and Precautions .....	42
3.3.3 Static Electricity Withstand Capability .....	43
CHAPTER 4 Bootstrap Circuit Operation .....	44
4.1 Bootstrap Circuit Operation .....	44
4.2 Bootstrap Supply Circuit Current at Switching State .....	45
4.3 Note for designing the bootstrap circuit .....	46
4.4 Initial charging in bootstrap circuit .....	47
CHAPTER 5 Interface Demo Board .....	48
5.1 Compact DIIPM Interface Demo Board .....	48
5.2 Circuit Schematic, Parts List and Board pattern .....	50
CHAPTER 6 PACKAGE HANDLING .....	52
6.1 Packaging Specification .....	52
6.2 Handling Precautions .....	53