

High Voltage Diode Module

HIGH POWER SWITCHING USE INSULATED TYPE



APPLICATION

Traction drives, High Reliability Converters / Inverters, DC choppers



High Voltage Diode Module



HIGH POWER SWITCHING USE INSULATED TYPE

High Voltage Diode Module

MAXIMUM RATINGS

Symbol	Item	Conditions	Ratings	Unit
VRRM	Repetitive peak reverse voltage	T _j = 25 °C	4500	V
VRSM	Non-repetitive peak reverse voltage	T _j = 25 °C	4500	V
VR(DC)	Reverse DC voltage	T _j = 25 °C	3000	V
lF	DC forward current	Tc = 25 °C	900	Α
IFSM	Surge forward current	Tj = 25 °C start, tw = 8.3 ms Half sign wave	6400	А
l ² t	Current-squared, time integration	T _j = 25 °C start, tw = 8.3 ms Half sign wave	170	kA ² s
Viso	Isolation voltage	Charged part to the baseplate RMS sinusoidal, 60Hz 1min.	6000	V
Tj	Junction temperature	_	-40 ~ +150	°C
Тор	Operating temperature	_	-40 ~ +125	°C
Tstg	Storage temperature	_	-40 ~ +125	°C

ELECTRICAL CHARACTERISTICS

Cumphal	Item	Canditions		Limits			Unit
Symbol	item	Conditions		Min	Тур	Max	
IRRM	Repetitive reverse current	$V_{RM} = V_{RRM}$ $T_{j} = 25 ^{\circ}C$ $T_{j} = 125 ^{\circ}C$	_	_	8	mA	
			Tj = 125 °C	_	8	20	""
\/=\4	Forward voltage (Note 1)	I= 000 A	Tj = 25 °C	— 4.00 ·	_	V	
VFM		IF = 900 A	Tj = 125 °C	_	3.60	_] ' [
trr	Reverse recovery time	VR = 2250 V, IF = 900 A di/dt = -1800 A/μs Ls=100nH, Tj = 125 °C		_	0.9	_	μs
Irr	Reverse recovery current			_	900	_	Α
Qrr	Reverse recovery charge			_	650	_	μС
Erec	Reverse recovery energy (Note 2)			_	0.7	_	J/P

Note 1. It doesn't include the voltage drop by internal lead resistance. 2. Erec is the integral of 0.1VRx0.1Irrxdt.



High Voltage Diode Module

HIGH POWER SWITCHING USE INSULATED TYPE


THERMAL CHARACTERISTICS

Symbol	Item	Conditions	Limits			Limit
		Conditions	Min	Тур	Max	Unit K/kW
Rth(j-c)	Thermal resistance	Junction to case (per 1/2 module)	_	_	20.0	K/kW
Rth(c-f)	Contact thermal resistance	Case to Fin, λgrease = 1W/m·K D(c-f)=100μm, (per 1/2 module)	_	16.0	_	K/kW


MECHANICAL CHARACTERISTICS

Symbol	Item	Conditions	Limits		Limit	
		Conditions	Min	Тур	Max	Unit
Mt	Mounting torque	M8: Main terminals screw	7.0	_	13.0	N⋅m
Ms		M6: Mounting screw	3.0	_	6.0	N⋅m
m	Mass	_	_	1.5	_	kg
CTI	Comparative tracking index	_	600	_	_	_
Da	Clearance	_	19.5	_	_	mm
Ds	Creepage distance	_	32	_	_	mm
LP CE	Internal inductance	_	_	35	_	nH
RCC'+EE'	Internal lead resistance	Tc = 25 °C	_	0.25	_	mΩ

PERFORMANCE CURVES




REVERSE RECOVERY ENERGY CHARACTERISTICS (TYPICAL)



High Voltage Diode Module




HIGH POWER SWITCHING USE INSULATED TYPE



REVERSE RECOVERY SAFE OPERATING AREA (RRSOA) 2500 $VR \le 3000V$, di/dt $\le 2600A/\mu s$ Tj = 125°C REVERSE RECOVERY CURRENT Irr (A) REVERSE RECOVERY CURRENT Irr (A) 2000 1500 1000 500 1000 2000 3000 4000 5000 REVERSE VOLTAGE VR (V)

TRANSIENT THERMAL IMPEDANCE CHARACTERISTICS 1.2 Rth(j-c) = 20K/kW 0.8 0.0 0.0 0.1 0.0 0.1 0.2 0.3 0.3 0.3 0.4 0.5 TIME (s)



High Voltage Diode Module



Important Notice

The information contained in this datasheet shall in no event be regarded as a guarantee of conditions or characteristics. This product has to be used within its specified maximum ratings, and is subject to customer's compliance with any applicable legal requirement, norms and standards.

Except as otherwise explicitly approved by Mitsubishi Electric Corporation in a written document signed by authorized representatives of Mitsubishi Electric Corporation, our products may not be used in any applications where a failure of the product or any consequences of the use thereof can reasonably be expected to result in personal injury.

In usage of power semiconductor, there is always the possibility that trouble may occur with them by the reliability lifetime such as Power Cycle, Thermal Cycle or others, or when used under special circumstances (e.g. condensation, high humidity, dusty, salty, highlands, environment with lots of organic matter / corrosive gas / explosive gas, or situations which terminals of semiconductor products receive strong mechanical stress). Therefore, please pay sufficient attention to such circumstances. Further, depending on the technical requirements, our semiconductor products may contain environmental regulation substances, etc. If there is necessity of detailed confirmation, please contact our nearest sales branch or distributor.

The contents or data contained in this datasheet are exclusively intended for technically trained staff. Customer's technical departments should take responsibility to evaluate the suitability of Mitsubishi Electric Corporation product for the intended application and the completeness of the product data with respect to such application. In the customer's research and development, please evaluate it not only with a single semiconductor product but also in the entire system, and judge whether it's applicable. As required, pay close attention to the safety design by installing appropriate fuse or circuit breaker between a power supply and semiconductor products to prevent secondary damage. Please also pay attention to the application note and the related technical information.

Keep safety first in your circuit designs!

Mitsubishi Electric Corporation puts the maximum effort into making semiconductor products better and more reliable, but there is always the possibility that trouble may occur with them. Trouble with semiconductors may lead to personal injury, fire or property damage. Remember to give due consideration to safety when making your circuit designs, with appropriate measures such as (i) placement of substitutive, auxiliary circuits, (ii) use of non-flammable material or (iii) prevention against any malfunction or mishap.

Notes regarding these materials

- •These materials are intended as a reference to assist our customers in the selection of the Mitsubishi Electric Semiconductor product best suited to the customer's application; they do not convey any license under any intellectual property rights, or any other rights, belonging to Mitsubishi Electric Corporation or a third party.
- •Mitsubishi Electric Corporation assumes no responsibility for any damage, or infringement of any third-party's rights, originating in the use of any product data, diagrams, charts, programs, algorithms, or circuit application examples contained in these materials.
- •All information contained in these materials, including product data, diagrams, charts, programs and algorithms represents information on products at the time of publication of these materials, and are subject to change by Mitsubishi Electric Corporation without notice due to product improvements or other reasons. It is therefore recommended that customers contact Mitsubishi Electric Corporation or an authorized Mitsubishi Electric Semiconductor product distributor for the latest product information before purchasing a product listed herein.
- The information described here may contain technical inaccuracies or typographical errors. Mitsubishi Electric Corporation assumes no responsibility for any damage, liability, or other loss rising from these inaccuracies or errors.
- Please also pay attention to information published by Mitsubishi Electric Corporation by various means, including the Mitsubishi Electric Semiconductor home page (https://www.MitsubishiElectric.com/semiconductors/).
- •When using any or all of the information contained in these materials, including product data, diagrams, charts, programs, and algorithms, please be sure to evaluate all information as a total system before making a final decision on the applicability of the information and products. Mitsubishi Electric Corporation assumes no responsibility for any damage, liability or other loss resulting from the information contained herein.
- •Mitsubishi Electric Corporation semiconductors are not designed or manufactured for use in a device or system that is used under circumstances in which human life is potentially at stake. Please contact Mitsubishi Electric Corporation or an authorized Mitsubishi Electric Semiconductor product distributor when considering the use of a product contained herein for any specific purposes, such as apparatus or systems for transportation, vehicular, medical, aerospace, nuclear, or undersea repeater use.
- •The prior written approval of Mitsubishi Electric Corporation is necessary to reprint or reproduce in whole or in part these materials.
- •If these products or technologies are subject to the Japanese export control restrictions, they must be exported under a license from the Japanese government and cannot be imported into a country other than the approved destination.
- Any diversion or re-export contrary to the export control laws and regulations of Japan and/or the country of destination is prohibited.
- •Please contact Mitsubishi Electric Corporation or an authorized Mitsubishi Electric Semiconductor product distributor for further details on these materials or the products contained therein.