


< High Voltage Insulated Gate Bipolar Transistor: HVIGBT >

CM1200HCB-66X


HIGH POWER SWITCHING USE INSULATED TYPE

5th-Version HVIGBT (High Voltage Insulated Gate Bipolar Transistor) Modules



APPLICATION

Traction drives, High Reliability Converters / Inverters, DC choppers



< High Voltage Insulated Gate Bipolar Transistor : HVIGBT >

CM1200HCB-66X HIGH POWER SWITCHING USE INSULATED TYPE

5th-Version HVIGBT (High Voltage Insulated Gate Bipolar Transistor) Modules

MAXIMUM RATINGS

Symbol	Item	Conditions	Ratings	Unit
V	Callantan amittan waltan	$V_{GE} = 0V, T_j = -40+150$ °C	3300	
V _{CES}	Collector-emitter voltage	$V_{GE} = 0V, T_{j} = -50^{\circ}C$	3200	V
V_{GES}	Gate-emitter voltage	$V_{CE} = 0V, T_j = 25^{\circ}C$	±20	V
Ic	Callantan assumant	DC, T _c = 105°C	1200	Α
I _{CRM}	Collector current	Pulse (Note 1)	2400	Α
I _E	Emitter current (Note 2)	DC, $T_c = 90$ °C	1200	Α
I _{ERM}	Emiller current	Pulse (Note 1)	2400	Α
P _{tot}	Maximum power dissipation (Note 3)	T _c = 25°C, IGBT part	11900	W
V _{iso}	Isolation voltage	RMS, sinusoidal, f = 60Hz, t = 1 min.	6000	V
V _e	Partial discharge extinction voltage	RMS, sinusoidal, f = 60Hz, Q _{PD} ≤ 10 pC	2600	V
T _i	Junction temperature		−50 ~ +150	°C
T _{jop}	Operating junction temperature		−50 ~ +150	°C
T _{stg}	Storage temperature		− 55 ~ + 150	°C
t _{psc}	Short circuit pulse width	$V_{CC} = 2500V, V_{CE} \le V_{CES}, V_{GE} = 15V, T_j = 150^{\circ}C$	10	μs

ELECTRICAL CHARACTERISTICS

Symbol	Item	Item Conditions			Limits		Unit
Cymbol	item			Min	Тур	Max	01111
I _{CES}			T _j = 25°C			4.0	
	Collector cutoff current	$V_{CE} = V_{CES}, V_{GE} = 0V$	T _j = 125°C	_	4.0		mA
			T _i = 150°C		24.0	_	
$V_{GE(th)}$	Gate-emitter threshold voltage	$V_{CE} = 10 \text{ V}, I_{C} = 120 \text{ mA}, T_{j} = 25^{\circ}\text{C}$		6.5	7.0	7.5	V
I_{GES}	Gate leakage current	$V_{GE} = V_{GES}$, $V_{CE} = 0V$, $T_j = 25$ °C		-0.5	_	0.5	μA
C _{ies}	Input capacitance	V _{CE} = 10 V, V _{GE} = 0 V, f = 100 kHz	,		139	_	
Coes	Output capacitance	$T_i = 25^{\circ}C$	-		9.3	_	nF
C _{res}	Reverse transfer capacitance	1) 20 0		_	1.3	_	
Q_G	Total gate charge	V_{CC} = 1800V, I_{C} = 1200A, V_{GE} = ±	15V	_	9.0		μC
		I _C = 1200A (Note 4)	T _j = 25°C	_	2.00	_	V
V_{CEsat}	Collector-emitter saturation voltage	$V_{GE} = 15V$	$T_j = 125^{\circ}C$		2.50	_	
		V GE - 13 V	$T_{j} = 150^{\circ}C$	_	2.60	3.10	
t _{d(on)}	Turn-on delay time		T _j = 150°C	_	_	0.90	μs
t _r	Turn-on rise time	V _{CC} = 1800V	T _j = 150°C	-	_	0.50	μs
	Turn-on switching energy (Note 7) (per pulse)	I _C = 1200A	T _j = 25°C	_	1.95	_	J
E _{on(10%)}		$V_{GE} = \pm 15V$	T _j = 125°C	_	2.15	_	
		$R_{G(on)} = 2.2 \Omega$	T _j = 150°C	_	2.25	_	
	Turn-on switching energy (Note 5) (per pulse)	L _s = 150nH	$T_j = 25^{\circ}C$	_	2.00	_	
E _{on}			T _j = 125°C	_	2.25	_	
			T _j = 150°C		2.35	_	
	Turn-off delay time		$T_j = 25^{\circ}C$	_	2.90	_	μs
$t_{d(off)}$			T _j = 125°C	_	3.20	_	
			T _j = 150°C		3.20	4.25	
	Turn-off fall time	V _{CC} = 1800V	$T_j = 25^{\circ}C$	_	0.40	_	
t _f		I _C = 1200A	T _j = 125°C	_	0.45	_	μs
		V _{GE} = ±15V	T _j = 150°C	_	0.50	1.00	
E _{off(10%)}	Turn-off switching energy (Note 7) (per pulse)	$R_{G(off)} = 18 \Omega$	T _j = 25°C	-	1.55	_	
		L _s = 150nH	T _j = 125°C		2.00	_	J
	(hei haise)	Inductive load	T _j = 150°C	_	2.05	_	
	Turn-off switching energy (Note 5)		T _j = 25°C		1.65	_	<u> </u>
E _{off}	Turn-off switching energy (Note 5) (per pulse)		T _j = 125°C	_	2.10	_	J
	(per puise)		T _j = 150°C	-	2.25	_	

< High Voltage Insulated Gate Bipolar Transistor : HVIGBT >

CM1200HCB-66X HIGH POWER SWITCHING USE INSULATED TYPE

5th-Version HVIGBT (High Voltage Insulated Gate Bipolar Transistor) Modules

ELECTRICAL CHARACTERISTICS (continuation)

Cymhal	Item		Conditions		Limits			Unit
Symbol					Min	Тур	Max	Offic
			I _E = 1200 A ^(Note 4)	T _j = 25°C		2.20	_	
V_{EC}	Emitter-collector voltage	(Note 2)		T _j = 125°C	_	2.40	_	V
			$V_{GE} = 0 V$	T _j = 150°C	_	2.50	3.00	
				T _j = 25°C	-	0.95	_	
t _{rr}	Reverse recovery time	(Note 2)		T _j = 125°C	1	1.10	_	μs
				T _j = 150°C	1	1.15	_	'
				T _j = 25°C	1	_	_	
Irr	Reverse recovery current	(Note 2)		T _j = 125°C	1	1550	_	Α
				T _j = 150°C	1	1650	_	
			V _{CC} = 1800 V	$T_j = 25^{\circ}C$		1050	_	
Q _{rr(10%)}	Reverse recovery charge	(Note 2,6)	I _C = 1200 A	T _j = 125°C		1600	_	μC
			V _{GE} = ±15 V	T _j = 150°C		1650	_	
			$R_{G(on)} = 2.2 \Omega$	T _j = 25°C	1	1200	_	
Q_{rr}	Reverse recovery charge	(Note 2,5)	L _s = 150 nH	T _j = 125°C	_	1750	_	μC
		Inductive load	T _j = 150°C	1	1800	_		
	(Note 2.7	(Note 2,7)		T _j = 25°C	1	1.15	_	
E _{rec(10%)}	Reverse recovery energy	····		T _j = 125°C		1.65	_	J
•	(per pulse)			T _j = 150°C		1.85	_	
	(Note 2.5)	(Note 2,5)		T _i = 25°C		1.25	_	
E _{rec}	Reverse recovery energy	(.1010 2,0)		T _i = 125°C		1.75	_	J
	(per pulse)			T _j = 150°C	_	1.95	_	

THERMAL CHARACTERISTICS

Cumbal	Item	Conditions	Limits			l lmi4
Symbol			Min	Тур	Max	Unit
$R_{th(j-c)Q}$	Thermal resistance	Junction to Case, IGBT part	-		10.5	K/kW
$R_{th(j-c)D}$		Junction to Case, FWDi part	-		16.5	K/kW
R _{th(c-s)}	Contact thermal resistance	Case to heat sink λ_{grease} = 1W/m*k, $D_{(c-s)}$ = 80 μ m		5.7	_	K/kW

MECHANICAL CHARACTERISTICS

Symbol	Item	Conditions		Unit		
		Conditions	Min	Тур	Max	Unit
M_t	Mounting torque	M8 : Main terminals screw	7.0	_	19.0	N·m
Ms	Mounting torque	M6 : Mounting screw	3.0	_	6.0	N·m
M_t	Mounting torque (Note 8)	M4 : Auxiliary terminals screw	1.0	_	3.0	N·m
М	Mass		_	1.2	_	kg
CTI	Comparative tracking index		600	_	_	_
da	Clearance		19.5	_	_	mm
d _s	Creepage distance		32.0	_	_	mm
L _{P CE}	Parasitic stray inductance		_	8.0	_	nΗ
R _{CC'+EE'}	Internal lead resistance	T _C = 25°C	_	0.09	_	mΩ

Note1. Pulse width and repetition rate should be such that junction temperature (T_j) does not exceed T_{jopmax} rating.

Note2. The symbols represent characteristics of the anti-parallel, emitter to collector free-wheel diode (FWD_i).

Note3. Junction temperature (T_j) should not exceed T_{jmax} rating (150°C).

Note4. Pulse width and repetition rate should be such as to cause negligible temperature rise.

Note5. Definition of all items is according to IEC 60747, unless otherwise specified.


Note6. The integration range of reverse recovery charge is from I_E = 0A to 10% I_E .


Note7. The integration range of switching energies is from 10%V_{CE} to 10%I_c(10%I_E).

Note8. The maximum specified value is under the condition of using PCB mounted on the power module.


In case no PCB is used this maximum torque for M4 screw is 2.0 N·m.

PERFORMANCE CURVES






COLLECTOR-EMITTER SATURATION VOLTAGE CHARACTERISTICS (TYPICAL)




FREE-WHEEL DIODE FORWARD CHARACTERISTICS (TYPICAL)




PERFORMANCE CURVES


CAPACITANCE CHARACTERISTICS (TYPICAL)




GATE CHARGE CHARACTERISTICS (TYPICAL)



HALF-BRIDGE SWITCHING ENERGY CHARACTERISTICS (TYPICAL)




HALF-BRIDGE SWITCHING ENERGY CHARACTERISTICS (TYPICAL)




PERFORMANCE CURVES


HALF-BRIDGE SWITCHING ENERGY CHARACTERISTICS (TYPICAL)




HALF-BRIDGE SWITCHING ENERGY CHARACTERISTICS (TYPICAL)



HALF-BRIDGE SWITCHING TIME CHARACTERISTICS (TYPICAL)




HALF-BRIDGE SWITCHING TIME CHARACTERISTICS (TYPICAL)




PERFORMANCE CURVES


FREE-WHEEL DIODE REVERSE RECOVERY CHARACTERISTICS (TYPICAL)



FREE-WHEEL DIODE REVERSE RECOVERY CHARACTERISTICS (TYPICAL)



TRANSIENT THERMAL IMPEDANCE CHARACTERISTICS




$$Z_{th(j-c)}(t) = \sum_{i=1}^{n} R_{i} \left\{ 1 - \exp\left(\frac{t}{\tau_{i}}\right) \right\}$$


	1	2	3	4
R_i [K/kW]:	0.0096	0.1893	0.4044	0.3967
τ_i [sec]:	0.0001	0.0058	0.0602	0.3512

PERFORMANCE CURVES


REVERSE BIAS SAFE OPERATING AREA (RBSOA)



SHORT CIRCUIT SAFE OPERATING AREA (SCSOA)



FREE-WHEEL DIODE REVERSE RECOVERY SAFE OPERATING AREA (RRSOA)



5th-Version HVIGBT (High Voltage Insulated Gate Bipolar Transistor) Modules

Important Notice

The information contained in this datasheet shall in no event be regarded as a guarantee of conditions or characteristics. This product has to be used within its specified maximum ratings, and is subject to customer's compliance with any applicable legal requirement, norms and standards.

Except as otherwise explicitly approved by Mitsubishi Electric Corporation in a written document signed by authorized representatives of Mitsubishi Electric Corporation, our products may not be used in any applications where a failure of the product or any consequences of the use thereof can reasonably be expected to result in personal injury.

In usage of power semiconductor, there is always the possibility that trouble may occur with them by the reliability lifetime such as Power Cycle, Thermal Cycle or others, or when used under special circumstances (e.g. condensation, high humidity, dusty, salty, highlands, environment with lots of organic matter / corrosive gas / explosive gas, or situations which terminals of semiconductor products receive strong mechanical stress). Therefore, please pay sufficient attention to such circumstances. Further, depending on the technical requirements, our semiconductor products may contain environmental regulation substances, etc. If there is necessity of detailed confirmation, please contact our nearest sales branch or distributor.

The contents or data contained in this datasheet are exclusively intended for technically trained staff. Customer's technical departments should take responsibility to evaluate the suitability of Mitsubishi Electric Corporation product for the intended application and the completeness of the product data with respect to such application. In the customer's research and development, please evaluate it not only with a single semiconductor product but also in the entire system, and judge whether it's applicable. As required, pay close attention to the safety design by installing appropriate fuse or circuit breaker between a power supply and semiconductor products to prevent secondary damage. Please also pay attention to the application note and the related technical information.

Dec. 2022 (HVM-1086-F)

5th-Version HVIGBT (High Voltage Insulated Gate Bipolar Transistor) Modules

Keep safety first in your circuit designs!

Mitsubishi Electric Corporation puts the maximum effort into making semiconductor products better and more reliable, but there is always the possibility that trouble may occur with them. Trouble with semiconductors may lead to personal injury, fire or property damage. Remember to give due consideration to safety when making your circuit designs, with appropriate measures such as (i) placement of substitutive, auxiliary circuits, (ii) use of non-flammable material or (iii) prevention against any malfunction or mishap.

Notes regarding these materials

- •These materials are intended as a reference to assist our customers in the selection of the Mitsubishi Electric Semiconductor product best suited to the customer's application; they do not convey any license under any intellectual property rights, or any other rights, belonging to Mitsubishi Electric Corporation or a third party.
- •Mitsubishi Electric Corporation assumes no responsibility for any damage, or infringement of any third-party's rights, originating in the use of any product data, diagrams, charts, programs, algorithms, or circuit application examples contained in these materials.
- •All information contained in these materials, including product data, diagrams, charts, programs and algorithms represents information on products at the time of publication of these materials, and are subject to change by Mitsubishi Electric Corporation without notice due to product improvements or other reasons. It is therefore recommended that customers contact Mitsubishi Electric Corporation or an authorized Mitsubishi Electric Semiconductor product distributor for the latest product information before purchasing a product listed herein.
- The information described here may contain technical inaccuracies or typographical errors. Mitsubishi Electric Corporation assumes no responsibility for any damage, liability, or other loss rising from these inaccuracies or errors.
- Please also pay attention to information published by Mitsubishi Electric Corporation by various means, including the Mitsubishi Electric Semiconductor home page (https://www.MitsubishiElectric.com/semiconductors/).
- •When using any or all of the information contained in these materials, including product data, diagrams, charts, programs, and algorithms, please be sure to evaluate all information as a total system before making a final decision on the applicability of the information and products. Mitsubishi Electric Corporation assumes no responsibility for any damage, liability or other loss resulting from the information contained herein.
- •Mitsubishi Electric Corporation semiconductors are not designed or manufactured for use in a device or system that is used under circumstances in which human life is potentially at stake. Please contact Mitsubishi Electric Corporation or an authorized Mitsubishi Electric Semiconductor product distributor when considering the use of a product contained herein for any specific purposes, such as apparatus or systems for transportation, vehicular, medical, aerospace, nuclear, or undersea repeater use.
- •The prior written approval of Mitsubishi Electric Corporation is necessary to reprint or reproduce in whole or in part these materials.
- •If these products or technologies are subject to the Japanese export control restrictions, they must be exported under a license from the Japanese government and cannot be imported into a country other than the approved destination.
- Any diversion or re-export contrary to the export control laws and regulations of Japan and/or the country of destination is prohibited.
- •Please contact Mitsubishi Electric Corporation or an authorized Mitsubishi Electric Semiconductor product distributor for further details on these materials or the products contained therein.

© MITSUBISHI ELECTRIC CORPORATION..