


<Full SiC Power Modules>

FMF300DXZ-34B

HIGH POWER SWITCHING USE
INSULATED TYPE



Dual switch (Half-Bridge)

Drain current I_D **300 A**
 Drain-Source voltage V_{DSX} **1700 V**
 Maximum junction temperature T_{vjmax} **175 °C**


- Silicon Carbide MOSFET + Silicon Carbide Schottky Barrier Diode
- Flat base Type
- Copper base plate
- RoHS Directive compliant
- Recognized under UL1557, File E323585

APPLICATION


AC Motor Control, Motion/Servo Control, Power supply, etc.

OUTLINE DRAWING & INTERNAL CONNECTION

Dimension in mm



INTERNAL CONNECTION



Terminal code

- | | |
|----|------|
| 1 | aP |
| 2 | aN |
| 3 | bN |
| 4 | N.C. |
| 5 | TH1 |
| 6 | TH2 |
| 7 | VDN |
| 8 | SCN |
| 9 | GN |
| 10 | EN |
| 11 | bOUT |
| 12 | aOUT |
| 13 | EP |
| 14 | GP |
| 15 | SCP |
| 16 | VDP |

Tolerance otherwise specified

| Division of Dimension | Tolerance |
|-----------------------|-----------|
| 0.5 to 3 | ±0.2 |
| over 3 to 6 | ±0.3 |
| over 6 to 30 | ±0.5 |
| over 30 to 120 | ±0.8 |
| over 120 to 400 | ±1.2 |

aN and bN, aOUT-bOUT must be connected externally.

FMF300DXZ-34B

HIGH POWER SWITCHING USE
INSULATED TYPEMAXIMUM RATINGS ($T_{vj}=25\text{ }^{\circ}\text{C}$, unless otherwise specified)

| Symbol | Item | Conditions | Rating | Unit |
|--------------------|--------------------------------|--|---------------|--------------------|
| V_{DSX} | Drain-source voltage | $V_{GS}=-15\text{ V}$ | 1700 | V |
| V_{GSS} | Gate-source voltage | D-S short-circuited | ± 20 | V |
| I_D | Drain current | DC, $T_C=48\text{ }^{\circ}\text{C}$ (Note.2) | 300 | A |
| I_{DRM} | | Pulse, Repetitive (Note.3), $T_{vj}=150\text{ }^{\circ}\text{C}$ | 450 | |
| P_{tot} | Total power dissipation | $T_C=25\text{ }^{\circ}\text{C}$ (Note. 2) | 1230 | W |
| I_S (Note.1) | Source current | DC | 300 | A |
| I_{SRM} (Note.1) | | Pulse, Repetitive (Note.3), $T_{vj}=150\text{ }^{\circ}\text{C}$ | 450 | |
| V_{isol} | Isolation voltage | Terminals to base plate, RMS, $f=60\text{ Hz}$, AC 1 min | 5000 | V |
| T_{vjmax} | Maximum junction temperature | Instantaneous event (overload) (Note.10) | 175 | $^{\circ}\text{C}$ |
| T_{vjop} | Operating junction temperature | Continuous operation (under switching) (Note.10) | $-40\sim+150$ | $^{\circ}\text{C}$ |
| T_{cmax} | Maximum case temperature | (Note.2, 10) | 125 | $^{\circ}\text{C}$ |
| T_{stg} | Storage temperature | - | $-40\sim+125$ | $^{\circ}\text{C}$ |

ELECTRICAL CHARACTERISTICS ($T_{vj}=25\text{ }^{\circ}\text{C}$, unless otherwise specified)

| Symbol | Item | Conditions (note9) | Limits | | | Unit | |
|---------------------------------|----------------------------------|---|--------------------------------------|------|------|---------------|---------------|
| | | | Min. | Typ. | Max. | | |
| I_{DSX} | Drain-source cut-off current | $V_{DS}=V_{DSX}$, $V_{GS}=-15\text{ V}$ | - | - | 5 | mA | |
| | | $V_{DS}=1000\text{ V}$, $V_{GS}=-15\text{ V}$ | - | - | 0.5 | | |
| $V_{GS(th)}$ | Gate-source threshold voltage | $I_D=113\text{ mA}$, $V_{DS}=10\text{ V}$ | 1.8 | 2.5 | 3.2 | V | |
| I_{GSS} | Gate-source leakage current | $V_{GS}=V_{GSS}$, D-S short-circuited | - | - | 0.5 | μA | |
| $V_{DS(on)}$ (terminal) | Drain-source on-state voltage | $I_D=300\text{ A}$, $V_{GS}=15\text{ V}$ (Note.6) | $T_{vj}=25\text{ }^{\circ}\text{C}$ | - | 1.65 | 2.60 | V |
| | | | $T_{vj}=125\text{ }^{\circ}\text{C}$ | - | 2.19 | - | |
| | | | $T_{vj}=150\text{ }^{\circ}\text{C}$ | - | 2.33 | - | |
| $V_{DS(on)}$ (chip) | Drain-source on-state voltage | $I_D=300\text{ A}$, $V_{GS}=15\text{ V}$ (Note.6) | $T_{vj}=25\text{ }^{\circ}\text{C}$ | - | 1.47 | - | V |
| | | | $T_{vj}=125\text{ }^{\circ}\text{C}$ | - | 2.01 | - | |
| | | | $T_{vj}=150\text{ }^{\circ}\text{C}$ | - | 2.15 | - | |
| $r_{DS(on)}$ (chip) | Drain-source on-state resistance | $I_D=300\text{ A}$, $V_{GS}=15\text{ V}$ (Note.6) | $T_{vj}=25\text{ }^{\circ}\text{C}$ | - | 4.90 | - | m Ω |
| | | | $T_{vj}=125\text{ }^{\circ}\text{C}$ | - | 6.70 | - | |
| | | | $T_{vj}=150\text{ }^{\circ}\text{C}$ | - | 7.16 | - | |
| C_{iss} | Input capacitance | $V_{DS}=10\text{ V}$, $V_{GS}=0\text{ V}$ | - | 27.4 | - | nF | |
| C_{oss} | Output capacitance | | - | 17 | - | | |
| C_{rss} | Reverse transfer capacitance | | - | 0.98 | - | | |
| Q_G | Gate charge | $V_{DD}=900\text{ V}$, $I_D=300\text{ A}$, $V_{GS}=0\rightarrow 15\text{ V}$ | - | 800 | - | nC | |
| $t_{d(on)}$ | Turn-on delay time | $V_{DD}=900\text{ V}$, $I_D=300\text{ A}$, $V_{GS}=\pm 15\text{ V}$, $T_{vj}=150\text{ }^{\circ}\text{C}$, $R_G=1.5\Omega$, $L_{s_ext}=16\text{ nH}$, Inductive load, per pulse | - | 200 | - | ns | |
| t_r | Rise time | | - | 50 | - | | |
| $t_{d(off)}$ | Turn-off delay time | | - | 220 | - | | |
| t_f | Fall time | | - | 30 | - | | |
| E_{on} | Turn-on switching energy | | - | 16 | - | | mJ |
| E_{off} | Turn-off switching energy | | - | 5 | - | | |
| Q_C | Drain-source charge | | - | 3.8 | - | | μC |
| V_{SD} (Note.1) (terminal) | Source-drain voltage | $I_S=300\text{ A}$ (Note.6) $V_{GS}=-15\text{ V}$ | $T_{vj}=25\text{ }^{\circ}\text{C}$ | - | 1.80 | 2.40 | V |
| | | | $T_{vj}=125\text{ }^{\circ}\text{C}$ | - | 2.45 | - | |
| | | | $T_{vj}=150\text{ }^{\circ}\text{C}$ | - | 2.69 | - | |
| V_{SD} (Note.1) (chip) | Source-drain voltage | $I_S=300\text{ A}$ (Note.6) $V_{GS}=-15\text{ V}$ | $T_{vj}=25\text{ }^{\circ}\text{C}$ | - | 1.64 | - | V |
| | | | $T_{vj}=125\text{ }^{\circ}\text{C}$ | - | 2.28 | - | |
| | | | $T_{vj}=150\text{ }^{\circ}\text{C}$ | - | 2.52 | - | |
| $R_{DD'+SS'}$ | Internal lead resistance | P-N | - | 0.6 | - | m Ω | |
| L_s | Internal stray inductance | P-N | - | 25 | - | nH | |
| r_g | Internal gate resistance | Per switch | - | 0.5 | - | Ω | |

FMF300DXZ-34B

HIGH POWER SWITCHING USE
INSULATED TYPE

THERMAL RESISTANCE CHARACTERISTICS

| Symbol | Item | Conditions | Limits | | | Unit |
|----------------|--|--|--------|------|------|------|
| | | | Min. | Typ. | Max. | |
| $R_{th(j-c)Q}$ | Thermal resistance ^(Note. 2) | Junction to case, per inverter switch | - | - | 121 | K/kW |
| $R_{th(j-c)D}$ | | Junction to case, per inverter FWD | - | - | 131 | |
| $R_{th(c-s)}$ | Contact thermal resistance ^(Note.2) | Case to heat sink, per 1 module, Thermal grease applied ^(Note.8, 10) | - | 12 | - | K/kW |

NTC THERMISTOR PART

| Symbol | Item | Conditions | Limits | | | Unit |
|---------------|-------------------------|---|--------|------|------|------|
| | | | Min. | Typ. | Max. | |
| R_{25} | Zero-power resistance | $T_C=25\text{ }^\circ\text{C}$ ^(Note.2) | 4.85 | 5.00 | 5.15 | kΩ |
| $\Delta R/R$ | Deviation of resistance | $T_C=100\text{ }^\circ\text{C}$ ^(Note.2) , $R_{100}=493\text{ }\Omega$ | -7.3 | - | +7.8 | % |
| $B_{(25/50)}$ | B-constant | Approximate by equation ^(Note.7) | - | 3375 | - | K |
| P_{25} | Power dissipation | $T_C=25\text{ }^\circ\text{C}$ ^(Note.2) | - | - | 10 | mW |


MECHANICAL CHARACTERISTICS

| Symbol | Item | Conditions | Limits | | | Unit |
|--------|---------------------------|--|--------|------|------|------|
| | | | Min. | Typ. | Max. | |
| M_t | Mounting torque | Main terminals M 6 screw | 3.5 | 4.0 | 4.5 | N·m |
| M_s | | Mounting to heat sink M 5 screw | 2.5 | 3.0 | 6.0 | |
| m | mass | - | - | 500 | - | g |
| d_a | Clearance | - | 10 | - | - | mm |
| d_s | Creepage distance | - | 17 | - | - | mm |
| e_c | Flatness of base plate | On the centerline X, Y ^(Note.5) | -100 | - | +100 | μm |
| - | Connector insertion force | 2 pin type | 0 | - | 25 | N |
| - | | 4 pin type | 0 | - | 35 | N |

*: This product is compliant with the Restriction of the Use of Certain Hazardous Substances in Electrical and Electronic Equipment (RoHS) directive 2011/65/EU and (EU)2015/863.

Note1. Represent ratings and characteristics of the anti-parallel, source-drain free wheeling diode (FWD).

- Case temperature (T_C) and heat sink temperature (T_s) are defined on the each surface (mounting side) of base plate and heat sink just under the chips. Refer to the figure of chip location.
- Pulse width and repetition rate should be such that the device junction temperature (T_{vj}) does not exceed T_{vjmax} rating.
- Junction temperature (T_{vj}) should not increase beyond T_{vjmax} rating.
- The base plate (mounting side) flatness measurement points (X, Y) are as follows of the following figure.



- Pulse width and repetition rate should be such as to cause negligible temperature rise.

$$7. B_{(25/50)} = \ln\left(\frac{R_{25}}{R_{50}}\right) / \left(\frac{1}{T_{25}} - \frac{1}{T_{50}}\right)$$

R_{25} : resistance at absolute temperature T_{25} [K]; $T_{25}=25\text{ }^\circ\text{C}+273.15=298.15$ [K]

R_{50} : resistance at absolute temperature T_{50} [K]; $T_{50}=50\text{ }^\circ\text{C}+273.15=323.15$ [K]

- Typical value is measured by using thermally conductive grease of $\lambda=0.9\text{ W/(m}\cdot\text{K)}/D_{(c-s)}=100\mu\text{m}$.

- Per switch (ex. Tr1 chips total in page.6)

- Long term performance related to thermal conductive grease (including but not limited to aspects such as the increase of thermal resistance due to pumping out, etc.) should be verified under your specific application conditions. Each temperature condition (T_{vjmax} , T_{vjop} , T_{Cmax}) must be maintained below the maximum rated temperature throughout consideration of the temperature rise even for long term usage.

FMF300DXZ-34B

HIGH POWER SWITCHING USE
INSULATED TYPE

RECOMMENDED OPERATING CONDITIONS

| Symbol | Item | Conditions | Limits | | | Unit | |
|----------------|---|--|-----------------------|-------|------|----------|-----|
| | | | Min. | Typ. | Max. | | |
| V_{DD} | (DC) Supply voltage | Applied across aP -aN+bN terminals | - | 900 | 1200 | V | |
| V_D | DC supply voltage (control) | Applied across VDP-EP/ VDN-EN terminals | 13.5 | 15.0 | 16.5 | V | |
| $V_{GS(+)}$ | Gate-Source positive drive voltage | Applied across GP-EP/ GN-EN terminals | 13.5 | 15.0 | 16.5 | V | |
| $V_{GS(-)}$ | Gate-Source negative drive voltage | Applied across GP-EP/ GN-EN terminals | -16.5 | -15.0 | -7.0 | V | |
| R_G | External gate resistance ^(Note.11) | Per switch | 1.5 | - | 7.5 | Ω | |
| f_c | Switching frequency | $V_{GS(+)}=15V, R_G=1.5\Omega, V_{DD}=900V, T_{vj}=150^\circ C$ | $V_{GS(-)} < -10V$ | - | - | 50 | kHz |
| | | | $V_{GS(-)} \geq -10V$ | - | - | 100 | kHz |
| $t_{d(SCoff)}$ | Gate cutoff delay time after SC output | $V_{GS}=15V, R_G=1.5\Omega, V_{DD} \leq 1200V, T_{vj}=150^\circ C$ | - | - | 3 | μs | |

Note 11. The value of external gate resistance should be considered the surge voltage not to exceed the rating voltage in the worst system condition.

SHORT CIRCUIT DETECTION & PROTECTION CHARACTERISTICS


| Symbol | Item | Conditions | Limits | | | Unit |
|--------------|-------------------------------------|--|--------|------|------|----------|
| | | | Min. | Typ. | Max. | |
| $I_{D(SC)}$ | SC detect drain current | $T_{vj}=150^\circ C, V_{GS}=15V$ | 450 | 600 | - | A |
| $t_{d(SC)}$ | SC detect delay time | $T_{vj}=150^\circ C, V_{DD} \leq 1200V, V_{GS}=15V, R_G=1.5\Omega$ | - | 1 | - | μs |
| $V_{GS(SC)}$ | SC protection gate limit voltage | $T_{vj}=150^\circ C, V_{GS}=15V, R_G=1.5\Omega$ | - | 0 | - | V |
| R1 | SC protection gate limit resistance | - | - | 0 | - | Ω |

Refer to the circuit in page.5


FMF300DXZ-34B

HIGH POWER SWITCHING USE
INSULATED TYPE

SHORT CIRCUIT DETECTION & PROTECTION



Example of application (Short circuit detection & protection)




FMF300DXZ-34B

HIGH POWER SWITCHING USE
INSULATED TYPE

CHIP LOCATION (Top view)

Dimension in mm, tolerance: ± 1 mm






Tr1,Tr2: SiC-MOSFET, Di1,Di2: SiC-SBD, Th: NTC thermistor

FMF300DXZ-34B


HIGH POWER SWITCHING USE
INSULATED TYPE

TEST CIRCUIT AND WAVEFORMS




Switching characteristics test circuit and waveforms(x: connected a* and b*)

Q_C test waveform




MOSFET Turn-on switching energy




MOSFET Turn-off switching energy

Turn-on / Turn-off switching energy test waveforms (Integral time instruction drawing)

TEST CIRCUIT




Tr1




Tr2

V_{DS(on)} test circuit (x: Connected a* and b*)




Di1




Di2

V_{SD} test circuit, V_{GS}=-15V (x: Connected a* and b*)



Tr1&Di1



Tr2&Di2


V_{SD} test circuit, V_{GS}=15V (x: Connected a* and b*)

FMF300DXZ-34B


HIGH POWER SWITCHING USE
INSULATED TYPE

PERFORMANCE CURVES


OUTPUT CHARACTERISTICS (TYPICAL)



DRAIN-SOURCE ON STATE VOLTAGE CHARACTERISTICS (TYPICAL)



DRAIN-SOURCE ON STATE VOLTAGE CHARACTERISTICS (TYPICAL)




FMF300DXZ-34B


HIGH POWER SWITCHING USE
INSULATED TYPE

PERFORMANCE CURVES


FREE WHEELING DIODE
FORWARD CHARACTERISTICS
(TYPICAL)




SOURCE-DRAIN ON STATE VOLTAGE
CHARACTERISTICS
(TYPICAL)



CAPACITANCE
CHARACTERISTICS
(TYPICAL)



GATE CHARGE
CHARACTERISTICS
(TYPICAL)




FMF300DXZ-34B

HIGH POWER SWITCHING USE
INSULATED TYPE

PERFORMANCE CURVES


HALF-BRIDGE SWITCHING CHARACTERISTICS
(TYPICAL)

$V_{DD}=900\text{ V}$, $V_{GS}=\pm 15\text{ V}$, $R_G=1.5\ \Omega$, $T_{vj}=150\text{ }^\circ\text{C}$, $L_{s_ext}=16\text{ nH}$
INDUCTIVE LOAD, PER PULSE




HALF-BRIDGE SWITCHING CHARACTERISTICS
(TYPICAL)

$V_{DD}=900\text{ V}$, $V_{GS}=\pm 15\text{ V}$, $I_D=300\text{ A}$, $T_{vj}=150\text{ }^\circ\text{C}$, $L_{s_ext}=16\text{ nH}$
INDUCTIVE LOAD, PER PULSE




HALF-BRIDGE SWITCHING CHARACTERISTICS
(TYPICAL)

$V_{DD}=900\text{ V}$, $V_{GS}=\pm 15\text{ V}$, $R_G=1.5\ \Omega$, $T_{vj}=150\text{ }^\circ\text{C}$, $L_{s_ext}=16\text{ nH}$
INDUCTIVE LOAD, PER PULSE



HALF-BRIDGE SWITCHING CHARACTERISTICS
(TYPICAL)

$V_{DD}=900\text{ V}$, $V_{GS}=\pm 15\text{ V}$, $I_D=300\text{ A}$, $T_{vj}=150\text{ }^\circ\text{C}$, $L_{s_ext}=16\text{ nH}$
INDUCTIVE LOAD, PER PULSE




FMF300DXZ-34B

HIGH POWER SWITCHING USE

INSULATED TYPE


PERFORMANCE CURVES

TRANSIENT THERMAL IMPEDANCE CHARACTERISTICS (MAXIMUM)



NTC thermistor part

TEMPERATURE CHARACTERISTICS (TYPICAL)



Note: The characteristics curves are presented for reference only and not guaranteed by production test, unless otherwise noted.

Important Notice

The information contained in this datasheet shall in no event be regarded as a guarantee of conditions or characteristics. This product has to be used within its specified maximum ratings, and is subject to customer's compliance with any applicable legal requirement, norms and standards.

Except as otherwise explicitly approved by Mitsubishi Electric Corporation in a written document signed by authorized representatives of Mitsubishi Electric Corporation, our products may not be used in any applications where a failure of the product or any consequences of the use thereof can reasonably be expected to result in personal injury.

In usage of power semiconductor, there is always the possibility that trouble may occur with them by the reliability lifetime such as Power Cycle, Thermal Cycle or others, or when used under special circumstances (e.g. condensation, high humidity, dusty, salty, highlands, environment with lots of organic matter / corrosive gas / explosive gas, or situations which terminals of semiconductor products receive strong mechanical stress). Therefore, please pay sufficient attention to such circumstances. Further, depending on the technical requirements, our semiconductor products may contain environmental regulation substances, etc. If there is necessity of detailed confirmation, please contact our nearest sales branch or distributor.

The contents or data contained in this datasheet are exclusively intended for technically trained staff. Customer's technical departments should take responsibility to evaluate the suitability of Mitsubishi Electric Corporation product for the intended application and the completeness of the product data with respect to such application. In the customer's research and development, please evaluate it not only with a single semiconductor product but also in the entire system, and judge whether it's applicable. As required, pay close attention to the safety design by installing appropriate fuse or circuit breaker between a power supply and semiconductor products to prevent secondary damage. Please also pay attention to the application note and the related technical information.

Keep safety first in your circuit designs!

Mitsubishi Electric Corporation puts the maximum effort into making semiconductor products better and more reliable, but there is always the possibility that trouble may occur with them. Trouble with semiconductors may lead to personal injury, fire or property damage. Remember to give due consideration to safety when making your circuit designs, with appropriate measures such as (i) placement of substitutive, auxiliary circuits, (ii) use of non-flammable material or (iii) prevention against any malfunction or mishap.

Notes regarding these materials

- These materials are intended as a reference to assist our customers in the selection of the Mitsubishi Electric Semiconductor product best suited to the customer's application; they do not convey any license under any intellectual property rights, or any other rights, belonging to Mitsubishi Electric Corporation or a third party.
- Mitsubishi Electric Corporation assumes no responsibility for any damage, or infringement of any third-party's rights, originating in the use of any product data, diagrams, charts, programs, algorithms, or circuit application examples contained in these materials.
- All information contained in these materials, including product data, diagrams, charts, programs and algorithms represents information on products at the time of publication of these materials, and are subject to change by Mitsubishi Electric Corporation without notice due to product improvements or other reasons. It is therefore recommended that customers contact Mitsubishi Electric Corporation or an authorized Mitsubishi Electric Semiconductor product distributor for the latest product information before purchasing a product listed herein.
The information described here may contain technical inaccuracies or typographical errors. Mitsubishi Electric Corporation assumes no responsibility for any damage, liability, or other loss rising from these inaccuracies or errors.
Please also pay attention to information published by Mitsubishi Electric Corporation by various means, including the Mitsubishi Electric Semiconductor home page (<http://www.MitsubishiElectric.com/semiconductors/>).
- When using any or all of the information contained in these materials, including product data, diagrams, charts, programs, and algorithms, please be sure to evaluate all information as a total system before making a final decision on the applicability of the information and products. Mitsubishi Electric Corporation assumes no responsibility for any damage, liability or other loss resulting from the information contained herein.
- Mitsubishi Electric Corporation semiconductors are not designed or manufactured for use in a device or system that is used under circumstances in which human life is potentially at stake. Please contact Mitsubishi Electric Corporation or an authorized Mitsubishi Electric Semiconductor product distributor when considering the use of a product contained herein for any specific purposes, such as apparatus or systems for transportation, vehicular, medical, aerospace, nuclear, or undersea repeater use.
- The prior written approval of Mitsubishi Electric Corporation is necessary to reprint or reproduce in whole or in part these materials.
- If these products or technologies are subject to the Japanese export control restrictions, they must be exported under a license from the Japanese government and cannot be imported into a country other than the approved destination.
Any diversion or re-export contrary to the export control laws and regulations of Japan and/or the country of destination is prohibited.
- Please contact Mitsubishi Electric Corporation or an authorized Mitsubishi Electric Semiconductor product distributor for further details on these materials or the products contained therein.

Generally the listed company name and the brand name are the trademarks or registered trademarks of the respective companies.