




<IGBT Modules>  
CM300DX-34T/CM300DXP-34T  
HIGH POWER SWITCHING USE  
INSULATED TYPE

OUTLINE DRAWING



Tolerance otherwise specified

Division of Dimension		Tolerance
0.5	to 3	±0.2
over 3	to 6	±0.3
over 6	to 30	±0.5
over 30	to 120	±0.8
over 120	to 400	±1.2



## CM300DX-34T/CM300DXP-34T

HIGH POWER SWITCHING USE  
INSULATED TYPEMAXIMUM RATINGS ( $T_{vj}=25\text{ }^{\circ}\text{C}$ , unless otherwise specified)

## INVERTER PART IGBT/FWD

Symbol	Item	Conditions	Rating	Unit
$V_{CES}$	Collector-emitter voltage	G-E short-circuited	1700	V
$V_{GES}$	Gate-emitter voltage	C-E short-circuited	$\pm 20$	V
$I_C$	Collector current	DC, $T_C=85\text{ }^{\circ}\text{C}$ (Note2, 4)	300	A
$I_{CRM}$		Pulse, Repetitive (Note3)	600	
$P_{tot}$	Total power dissipation	$T_C=25\text{ }^{\circ}\text{C}$ (Note2, 4)	1515	W
$I_E$ (Note1)	Emitter current	DC (Note2)	300	A
$I_{ERM}$ (Note1)		Pulse, Repetitive (Note3)	600	

## MODULE

Symbol	Item	Conditions	Rating	Unit
$V_{isol}$	Isolation voltage	Terminals to base plate, RMS, f=60 Hz, AC 1 min	4000	V
$T_{vjmax}$	Maximum junction temperature	Instantaneous event (overload) (Note9)	175	$^{\circ}\text{C}$
$T_{Cmax}$	Maximum case temperature	(Note4, 9)	125	
$T_{vjop}$	Operating junction temperature	Continuous operation (under switching) (Note9)	-40 ~ +150	$^{\circ}\text{C}$
$T_{stg}$	Storage temperature	-	-40 ~ +125	

ELECTRICAL CHARACTERISTICS ( $T_{vj}=25\text{ }^{\circ}\text{C}$ , unless otherwise specified)

## INVERTER PART IGBT/FWD

Symbol	Item	Conditions		Limits			Unit
				Min.	Typ.	Max.	
I <sub>CES</sub>	Collector-emitter cut-off current	V <sub>CE</sub> =V <sub>CES</sub> , G-E short-circuited		-	-	1.0	mA
I <sub>GES</sub>	Gate-emitter leakage current	V <sub>GE</sub> =V <sub>GES</sub> , C-E short-circuited		-	-	0.5	μA
V <sub>GE(th)</sub>	Gate-emitter threshold voltage	I <sub>C</sub> =30 mA, V <sub>CE</sub> =10 V		5.4	6.0	6.6	V
V <sub>CEsat</sub> (Terminal)	Collector-emitter saturation voltage	I <sub>C</sub> =300 A, V <sub>GE</sub> =15 V, Refer to the figure of test circuit (Note5)	T <sub>vj</sub> =25 °C	-	2.05	2.45	V
			T <sub>vj</sub> =125 °C	-	2.45	-	
			T <sub>vj</sub> =150 °C	-	2.55	-	
V <sub>CEsat</sub> (Chip)		I <sub>C</sub> =300 A, V <sub>GE</sub> =15 V, (Note5)	T <sub>vj</sub> =25 °C	-	1.95	2.35	V
			T <sub>vj</sub> =125 °C	-	2.35	-	
			T <sub>vj</sub> =150 °C	-	2.45	-	
C <sub>ies</sub>	Input capacitance	V <sub>CE</sub> =10 V, G-E short-circuited		-	-	80	nF
C <sub>oes</sub>	Output capacitance			-	-	2.2	
C <sub>res</sub>	Reverse transfer capacitance			-	-	0.7	
Q <sub>G</sub>	Gate charge	V <sub>CC</sub> =1000 V, I <sub>C</sub> =300 A, V <sub>GE</sub> =15 V		-	2.35	-	μC
t <sub>d(on)</sub>	Turn-on delay time	V <sub>CC</sub> =1000 V, I <sub>C</sub> =300 A, V <sub>GE</sub> =±15 V, R <sub>G</sub> =0 Ω, Inductive load		-	-	800	ns
t <sub>r</sub>	Rise time			-	-	200	
t <sub>d(off)</sub>	Turn-off delay time			-	-	800	
t <sub>f</sub>	Fall time			-	-	600	
V <sub>EC</sub> (Note1) (Terminal)	Emitter-collector voltage	I <sub>E</sub> =300 A, G-E short-circuited, Refer to the figure of test circuit (Note5)	T <sub>vj</sub> =25 °C	-	2.75	3.35	V
			T <sub>vj</sub> =125 °C	-	2.95	-	
			T <sub>vj</sub> =150 °C	-	2.95	-	
V <sub>EC</sub> (Note1) (Chip)		I <sub>E</sub> =300 A, G-E short-circuited, (Note5)	T <sub>vj</sub> =25 °C	-	2.65	3.25	V
			T <sub>vj</sub> =125 °C	-	2.75	-	
			T <sub>vj</sub> =150 °C	-	2.75	-	
t <sub>rr</sub> (Note1)	Reverse recovery time	V <sub>CC</sub> =1000 V, I <sub>E</sub> =300 A, V <sub>GE</sub> =±15 V, R <sub>G</sub> =0 Ω, Inductive load		-	-	300	ns
Q <sub>rr</sub> (Note1)	Reverse recovery charge			-	12.5	-	μC
E <sub>on</sub>	Turn-on switching energy per pulse	V <sub>CC</sub> =1000 V, I <sub>C</sub> =I <sub>E</sub> =300 A,		-	74.5	-	mJ
E <sub>off</sub>	Turn-off switching energy per pulse	V <sub>GE</sub> =±15 V, R <sub>G</sub> =0 Ω, T <sub>vj</sub> =150 °C,		-	65.7	-	
E <sub>rr</sub> (Note1)	Reverse recovery energy per pulse	Inductive load		-	36.8	-	mJ
R <sub>CC'+EE'</sub>	Internal lead resistance	Main terminals-chip, per switch, T <sub>C</sub> =25 °C (Note4)		-	0.88	-	mΩ
r <sub>g</sub>	Internal gate resistance	Per switch		-	2.5	-	Ω

## CM300DX-34T/CM300DXP-34T

HIGH POWER SWITCHING USE  
INSULATED TYPEELECTRICAL CHARACTERISTICS (cont.;  $T_{vj}=25\text{ }^{\circ}\text{C}$ , unless otherwise specified)

## NTC THERMISTOR PART

Symbol	Item	Conditions	Limits			Unit
			Min.	Typ.	Max.	
$R_{25}$	Zero-power resistance	$T_C=25\text{ }^{\circ}\text{C}$ (Note4)	4.85	5.00	5.15	k $\Omega$
$\Delta R/R$	Deviation of resistance	$R_{100}=493\text{ }\Omega$ , $T_C=100\text{ }^{\circ}\text{C}$ (Note4)	-7.3	-	+7.8	%
$B_{(25/50)}$	B-constant	Approximate by equation (Note6)	-	3375	-	K
$P_{25}$	Power dissipation	$T_C=25\text{ }^{\circ}\text{C}$ (Note4)	-	-	10	mW

## THERMAL RESISTANCE CHARACTERISTICS

Symbol	Item	Conditions	Limits			Unit
			Min.	Typ.	Max.	
$R_{th(j-c)Q}$	Thermal resistance	Junction to case, per Inverter IGBT (Note4)	-	-	99	K/kW
$R_{th(j-c)D}$		Junction to case, per Inverter FWD (Note4)	-	-	149	
$R_{th(c-s)}$	Contact thermal resistance	Case to heat sink, per 1 module Thermal grease applied (Note4, 7, 9)	-	11.5	-	K/kW

## MECHANICAL CHARACTERISTICS

Symbol	Item	Conditions	Limits			Unit
			Min.	Typ.	Max.	
$M_t$	Mounting torque	Main terminals M 6 screw	3.5	4.0	4.5	N·m
$M_s$	Mounting torque	Mounting to heat sink M 5 screw	2.5	3.0	3.5	N·m
$d_s$	Creepage distance	Solder pin type (DX)	Terminal to terminal		17	mm
			Terminal to base plate		18.1	
		Pressfit pin type (DXP)	Terminal to terminal		17	mm
			Terminal to base plate		18.6	
$d_a$	Clearance	Solder pin type (DX)	Terminal to terminal		10	mm
			Terminal to base plate		16.2	
		Pressfit pin type (DXP)	Terminal to terminal		10	mm
			Terminal to base plate		16.2	
$e_c$	Flatness of base plate	On the centerline X, Y (Note8)	$\pm 0$	-	+200	$\mu\text{m}$
$m$	mass	-	-	300	-	g

\*: This product is compliant with the Restriction of the Use of Certain Hazardous Substances in Electrical and Electronic Equipment (RoHS) directive 2011/65/EU and (EU) 2015/863.

Note1. Represent ratings and characteristics of the anti-parallel, emitter-collector free-wheeling diode (FWD).

- Junction temperature ( $T_{vj}$ ) should not increase beyond  $T_{vj\text{max}}$  rating.
- Pulse width and repetition rate should be such that the device junction temperature ( $T_{vj}$ ) dose not exceed  $T_{vj\text{max}}$  rating.
- Case temperature ( $T_C$ ) and heat sink temperature ( $T_s$ ) are defined on the each surface (mounting side) of base plate and heat sink just under the chips.  
Refer to the figure of chip location.

- Pulse width and repetition rate should be such as to cause negligible temperature rise. Refer to the figure of test circuit.


$$6. B_{(25/50)} = \ln \left( \frac{R_{25}}{R_{50}} \right) / \left( \frac{1}{T_{25}} - \frac{1}{T_{50}} \right)$$

$R_{25}$ : resistance at absolute temperature  $T_{25}$  [K];  $T_{25}=25\text{ }^{\circ}\text{C}+273.15=298.15$  [K]

$R_{50}$ : resistance at absolute temperature  $T_{50}$  [K];  $T_{50}=50\text{ }^{\circ}\text{C}+273.15=323.15$  [K]

- Reference value. Thermally conductive grease of thermal conductivity  $\lambda=0.9\text{ W/(m}\cdot\text{K)}$  and thickness  $D_{(c-s)}=50\text{ }\mu\text{m}$ .

- The base plate (mounting side) flatness measurement points (X, Y) are shown in the following figure.



- Long term performance related to thermal conductive grease (including but not limited to aspects such as the increase of thermal resistance due to pumping out, etc.) should be verified under user's specific application conditions. Each temperature condition ( $T_{vj\text{max}}$ ,  $T_{vj\text{op}}$ ,  $T_{C\text{max}}$ ) must be maintained below the maximum rated temperature throughout consideration of the temperature rise even for long term usage.

**CM300DX-34T/CM300DXP-34T**

HIGH POWER SWITCHING USE  
INSULATED TYPE

Note10. Use the following screws when mounting the printed circuit board (PCB) on the standoffs.

PCB thickness : t1.6

Type	Manufacturer	Size	Tightening torque (N·m)	Recommended tightening method
(1) PT®	EJOT	K25×8	0.55 ± 0.055	by handwork (equivalent to 30 rpm by mechanical screw driver) ~ 600 rpm (by mechanical screw driver)
(2) PT®		K25×10	0.75 ± 0.075 N·m	
(3) DELTA PT®		25×8	0.55 ± 0.055 N·m	
(4) DELTA PT®		25×10	0.75 ± 0.075 N·m	
(5) B1 tapping screw	-	φ2.6×10	0.75 ± 0.075 N·m	
		φ2.6×12		

**RECOMMENDED OPERATING CONDITIONS**

Symbol	Item	Conditions	Limits			Unit
			Min.	Typ.	Max.	
$V_{CC}$	(DC) Supply voltage	Applied across C1-E2 terminals	-	1000	1200	V
$V_{GEon}$	Gate (-emitter drive) voltage	Applied across G1-Es1/G2-Es2 terminals	13.5	15.0	16.5	V
$R_G$	External gate resistance	Per switch	0	-	16	Ω

Dimension in mm, tolerance:  $\pm 1$  mm

Technical drawing of a 4-pin connector assembly, showing dimensions and labels. The drawing includes a top view and a side view. The top view shows a rectangular assembly with four pins. The side view shows the profile of the assembly. Dimensions are given in millimeters (mm). Labels include: (62), (50), 41.0, 37.1, 17.8, 15.4, 10.4, 0, 6.0, 18.6, 30.3, 43.0, 79.8, 91.8, 122, (110), 43.3, 56.2, 81.2, 93.3, 0, 42.3, 41.9, 22.4, 18.9, 6.0, 0, Di1, Tr1, Di2, Tr2, Th, LABEL SIDE, 110, 67, 2, 3, 4, 5, 6, 7, 8.

Technical drawing of a mechanical part, likely a bracket or plate, showing dimensions and features. The drawing includes a top view and a side view. Key dimensions include overall width (122), overall height (62), and various hole positions (Di1, Di2, Th). The drawing also shows a 'LABEL SIDE' and a 'TR' (thread) feature.

Dimensions and Features:


- Overall Width: 122
- Overall Height: 62
- Top View Dimensions:
  - Horizontal: 110, 43.3, 56.2, 81.2, 93.3
  - Vertical: 41.0, 37.1, 17.8, 15.4, 10.4
- Side View Dimensions:
  - Horizontal: 6.0, 18.6, 30.3, 43.0, 79.8, 91.8
  - Vertical: 42.3, 41.9, 22.4, 18.9, 6.0
- Features:
  - Di1, Di2: Hole positions.
  - Th: Threaded hole.
  - Tr1, Tr2: Threaded holes.
  - Tr: Threaded hole.
  - Label Side: Indicated by an arrow.

Tr1/Tr2: IGBT, Di1/Di2: FWD, Th: NTC thermistor


**CM300DX-34T/CM300DXP-34T**

HIGH POWER SWITCHING USE

INSULATED TYPE

**TEST CIRCUIT AND WAVEFORMS**

Switching characteristics test circuit and waveforms


 $t_{rr}$ ,  $Q_{rr}$  characteristics test waveform

IGBT Turn-on switching energy

IGBT Turn-off switching energy

FWD Reverse recovery energy

Switching energy and Reverse recovery energy test waveforms (Integral time instruction drawing)





**TEST CIRCUIT** $V_{CEsat}$  characteristics test circuit $V_{CE}$  characteristics test circuit



**CM300DX-34T/CM300DXP-34T**

HIGH POWER SWITCHING USE

INSULATED TYPE

**PERFORMANCE CURVES****INVERTER PART****OUTPUT CHARACTERISTICS  
(TYPICAL)****COLLECTOR-EMITTER SATURATION VOLTAGE  
CHARACTERISTICS  
(TYPICAL)****COLLECTOR-EMITTER VOLTAGE CHARACTERISTICS  
(TYPICAL)****FREE WHEELING DIODE  
FORWARD CHARACTERISTICS  
(TYPICAL)**





## CM300DX-34T/CM300DXP-34T

HIGH POWER SWITCHING USE

INSULATED TYPE

## PERFORMANCE CURVES


## INVERTER PART

HALF-BRIDGE SWITCHING CHARACTERISTICS  
(TYPICAL)
 $V_{CC}=1000\text{ V}$ ,  $R_G=0\ \Omega$ ,  $V_{GE}=\pm 15\text{ V}$ , INDUCTIVE LOAD  
 —:  $T_{vj}=150\text{ }^\circ\text{C}$ , - - - -:  $T_{vj}=125\text{ }^\circ\text{C}$ 
HALF-BRIDGE SWITCHING CHARACTERISTICS  
(TYPICAL)
 $V_{CC}=1000\text{ V}$ ,  $I_C=300\text{ A}$ ,  $V_{GE}=\pm 15\text{ V}$ , INDUCTIVE LOAD  
 —:  $T_{vj}=150\text{ }^\circ\text{C}$ , - - - -:  $T_{vj}=125\text{ }^\circ\text{C}$ 
HALF-BRIDGE SWITCHING CHARACTERISTICS  
(TYPICAL)
 $V_{CC}=1000\text{ V}$ ,  $R_G=0\ \Omega$ ,  $V_{GE}=\pm 15\text{ V}$ , INDUCTIVE LOAD,  
 —:  $T_{vj}=150\text{ }^\circ\text{C}$ , - - - -:  $T_{vj}=125\text{ }^\circ\text{C}$ , PER PULSE
HALF-BRIDGE SWITCHING CHARACTERISTICS  
(TYPICAL)
 $V_{CC}=1000\text{ V}$ ,  $I_C/I_E=300\text{ A}$ ,  $V_{GE}=\pm 15\text{ V}$ , INDUCTIVE LOAD,  
 —:  $T_{vj}=150\text{ }^\circ\text{C}$ , - - - -:  $T_{vj}=125\text{ }^\circ\text{C}$ , PER PULSE



PERFORMANCE CURVES

INVERTER PART


CAPACITANCE CHARACTERISTICS  
(TYPICAL)




FREE WHEELING DIODE  
REVERSE RECOVERY CHARACTERISTICS  
(TYPICAL)



GATE CHARGE CHARACTERISTICS  
(TYPICAL)




TRANSIENT THERMAL IMPEDANCE CHARACTERISTICS  
(MAXIMUM)




PERFORMANCE CURVES

INVERTER PART

TURN-OFF SWITCHING SAFE OPERATIONG AREA  
(REVERSE BIAS SAFE OPERATING AREA)  
(MAXIMUM)




SHORT-CIRCUIT SAFE OPERATING AREA  
(MAXIMUM)



NTC thermistor part

TEMPERATURE CHARACTERISTICS  
(TYPICAL)



Note: The characteristics curves are presented for reference only and not guaranteed by production test, unless otherwise noted.

### **Important Notice**

The information contained in this datasheet shall in no event be regarded as a guarantee of conditions or characteristics. This product has to be used within its specified maximum ratings, and is subject to customer's compliance with any applicable legal requirement, norms and standards.

Except as otherwise explicitly approved by Mitsubishi Electric Corporation in a written document signed by authorized representatives of Mitsubishi Electric Corporation, our products may not be used in any applications where a failure of the product or any consequences of the use thereof can reasonably be expected to result in personal injury.

In usage of power semiconductor, there is always the possibility that trouble may occur with them by the reliability lifetime such as Power Cycle, Thermal Cycle or others, or when used under special circumstances (e.g. condensation, high humidity, dusty, salty, highlands, environment with lots of organic matter / corrosive gas / explosive gas, or situations which terminals of semiconductor products receive strong mechanical stress). Therefore, please pay sufficient attention to such circumstances. Further, depending on the technical requirements, our semiconductor products may contain environmental regulation substances, etc. If there is necessity of detailed confirmation, please contact our nearest sales branch or distributor.

The contents or data contained in this datasheet are exclusively intended for technically trained staff. Customer's technical departments should take responsibility to evaluate the suitability of Mitsubishi Electric Corporation product for the intended application and the completeness of the product data with respect to such application. In the customer's research and development, please evaluate it not only with a single semiconductor product but also in the entire system, and judge whether it's applicable. As required, pay close attention to the safety design by installing appropriate fuse or circuit breaker between a power supply and semiconductor products to prevent secondary damage. Please also pay attention to the application note and the related technical information.

## **Keep safety first in your circuit designs!**

Mitsubishi Electric Corporation puts the maximum effort into making semiconductor products better and more reliable, but there is always the possibility that trouble may occur with them. Trouble with semiconductors may lead to personal injury, fire or property damage. Remember to give due consideration to safety when making your circuit designs, with appropriate measures such as (i) placement of substitutive, auxiliary circuits, (ii) use of non-flammable material or (iii) prevention against any malfunction or mishap.

## **Notes regarding these materials**

- These materials are intended as a reference to assist our customers in the selection of the Mitsubishi Electric Semiconductor product best suited to the customer's application; they do not convey any license under any intellectual property rights, or any other rights, belonging to Mitsubishi Electric Corporation or a third party.
- Mitsubishi Electric Corporation assumes no responsibility for any damage, or infringement of any third-party's rights, originating in the use of any product data, diagrams, charts, programs, algorithms, or circuit application examples contained in these materials.
- All information contained in these materials, including product data, diagrams, charts, programs and algorithms represents information on products at the time of publication of these materials, and are subject to change by Mitsubishi Electric Corporation without notice due to product improvements or other reasons. It is therefore recommended that customers contact Mitsubishi Electric Corporation or an authorized Mitsubishi Electric Semiconductor product distributor for the latest product information before purchasing a product listed herein.  
The information described here may contain technical inaccuracies or typographical errors. Mitsubishi Electric Corporation assumes no responsibility for any damage, liability, or other loss rising from these inaccuracies or errors.  
Please also pay attention to information published by Mitsubishi Electric Corporation by various means, including the Mitsubishi Electric Semiconductor home page (<https://www.MitsubishiElectric.com/semiconductors/>).
- When using any or all of the information contained in these materials, including product data, diagrams, charts, programs, and algorithms, please be sure to evaluate all information as a total system before making a final decision on the applicability of the information and products. Mitsubishi Electric Corporation assumes no responsibility for any damage, liability or other loss resulting from the information contained herein.
- Mitsubishi Electric Corporation semiconductors are not designed or manufactured for use in a device or system that is used under circumstances in which human life is potentially at stake. Please contact Mitsubishi Electric Corporation or an authorized Mitsubishi Electric Semiconductor product distributor when considering the use of a product contained herein for any specific purposes, such as apparatus or systems for transportation, vehicular, medical, aerospace, nuclear, or undersea repeater use.
- The prior written approval of Mitsubishi Electric Corporation is necessary to reprint or reproduce in whole or in part these materials.
- If these products or technologies are subject to the Japanese export control restrictions, they must be exported under a license from the Japanese government and cannot be imported into a country other than the approved destination.  
Any diversion or re-export contrary to the export control laws and regulations of Japan and/or the country of destination is prohibited.
- Please contact Mitsubishi Electric Corporation or an authorized Mitsubishi Electric Semiconductor product distributor for further details on these materials or the products contained therein.

Generally the listed company name and the brand name are the trademarks or registered trademarks of the respective companies.