


<Intelligent Power Modules>


PM35RG1A120

FLAT-BASE TYPE INSULATED PACKAGE



APPLICATION


General purpose inverter, servo drives and other motor controls



1

<Intelligent Power Modules> PM35RG1A120 HIGH POWER SWITCHING USE

INSULATED TYPE



MAXIMUM RATINGS (Tvj = 25°C, unless otherwise noted)

INVERTER PART

Symbol	Parameter	Conditions	Ratings	Unit
V _{CES}	Collector-Emitter Voltage	V _D =15 V, V _{CIN} =15 V	1200	V
I _C	Callester Coment	T _c =25 °C	35	
I _{CRM}	Collector Current	Pulse	70	A
P _{tot}	Total Power Dissipation	T _c =25 °C	290	W
IE	Emitter Current	T _c =25 °C	35	Α
I _{ERM}	(Free-wheeling Diode Forward current)	Pulse	70	
Tvj	Junction Temperature	(Note5)	-20 ~ +150	°C

*: Tc measurement point is just under the chip.

BRAKE PART

Symbol	Parameter	Conditions	Ratings	Unit
V _{CES}	Collector-Emitter Voltage	V _D =15 V, V _{CIN} =15 V	1200	V
I _C		T _c =25 °C	25	
I _{CRM}	Collector Current	Pulse	50	A
P _{tot}	Total Power Dissipation	T _c =25 °C	260	W
V _{R(DC)}	Diode Rated Reverse DC Voltage	T _c =25 °C	1200	V
l _F	Diode Forward Current	T _c =25 °C	25	А
Tvj	Junction Temperature	(Note5)	-20 ~ +150	°C

*: Tc measurement point is just under the chip.

CONTROL PART

Symbol	Parameter	Conditions	Ratings	Unit
VD	Supply Voltage	Applied between: V_{UP1} - V_{UPC} , V_{VP1} - V_{VPC} , V_{WP1} - V_{WPC} , V_{N1} - V_{NC}	20	V
V _{CIN}	Input Voltage	Applied between: U _P -V _{UPC} , V _P -V _{VPC} , W _P -V _{WPC} , U _N , V _N , W _N , Br -V _{NC}	20	V
V _{FO}	Fault Output Supply Voltage	Applied between: U_{FO} - V_{UPC} , V_{FO} - V_{VPC} , W_{FO} - V_{WPC} , FO- V_{NC}	20	V
I _{FO}	Fault Output Current	Sink current at U_{FO} , V_{FO} , W_{FO} , Fo terminals	20	mA

TOTAL SYSTEM

Symbol	Parameter	Conditions	Ratings	Unit			
V _{CC(PROT)}	Supply Voltage Protected by SC	V _D =13.5 V∼16.5 V, Inverter Part, Tvj=+125°C start	800	V			
T _{stg}	Storage Temperature	-	-40 ~ +125	°C			
Tc	Operating Case Temperature	(Note5)	-20 ~ +125	°C			
V _{isol}	Isolation Voltage	60Hz, Sinusoidal, Charged part to Base plate, AC 1min, RMS	2500	V			

*: Tc measurement point is just under the chip.

THERMAL RESISTANCE


Symbol	Parameter	Conditions	Limits			Unit
Symbol	Falameter	Conditions	Min.	Тур.	Max.	Unit
R _{th(j-c)Q}	Thermal Resistance	Inverter, Junction to case, IGBT, per 1 element (Note1)	-	-	0.43	
R _{th(j-c)D}		Inverter, Junction to case, FWD, per 1 element (Note1)	-	-	0.67	K/W
$R_{th(j-c)Q}$		Brake, Junction to case, IGBT, per 1 element (Note1)	-	-	0.48	N/ VV
$R_{th(j-c)D}$		Brake, Junction to case, FWD, per 1 element (Note1)	-	-	0.78	
$R_{th(c-s)}$	Contact Thermal Resistance	Case to heat sink, per 1 module, Thermal grease applied (Note.1, 2, 5)	-	19.1	-	K/kW

Note1. If you use this value, $R_{th(s-a)}$ should be measured just under the chips.

Note2. Typical value is by thermally conductive grease of λ =0.9W/(m·K), D_{(C-S)}=50 \ \mu m.

CHIP LOCATION (Top view)

Dimension in mm, torelance: ±1mm



Tr** Di**

ELECTRICAL CHARACTERISTICS (Tvj= 25°C, unless otherwise noted)

INVERTER PART

Currente e l	Devenueter	Conditions			1.1				
Symbol	/mbol Parameter Conditions				Min.	Тур.	Max.	Unit	
				Terminal	-	-	1.7		
V		V _D =15 V, I _C =35 A	Tvj=25 °C	Chip	-	1.3	-	v	
V _{CEsat}	Collector-Emitter Saturation Voltage	(0) (Duland (Fig. 1)	Tui-105 °C	Terminal	-	-	1.95	v	
		V _{CIN} =0 V, Pulsed, (Fig.1)	Tvj=125 °C	Chip	-	1.5	-		
		Emitter-Collector Voltage	Tui-25 °C	Terminal	-	-	2.35		
V			TVJ-25 C	Chip	-	1.75	-	v	
V _{EC}	Ũ	V_{CIN} = 15 V, pulsed, (Fig.2) Tvj=125 °C	с С	Tyi-125 °C	Terminal	-	-	2.6	v
			Chip	-	1.95	-			
t _{on}		V_{D} =15 V, V_{CIN} =0 V \leftrightarrow 15 V,		0.3	0.7	1.2			
t _{rr}		V _{CC} =600 V, I _C =35A,		-	0.13	0.4			
t _{c(on)}	Switching Time	Tvj=125 °C,		-	0.2	0.4	μs		
t _{off}		Inductive Load		-	1.0	2.8			
t _{c(off)}		(Fig.3, 4)			-	0.4	1.2		
	Collector-Emitter Cut-off Current	$V_{CE}=V_{CES}, V_{D}=15 V,$		Tvj=25 °C	-	-	1	m (
I _{CES}		V _{CIN} =15 V (Fig.5)		Tvj=125 °C	-	-	10	mA	

BRAKE PART

Symbol	Deremeter	Conditions		Limits			1.1	
Symbol	Parameter	Condition	S		Min.	Тур.	Max.	Unit
		V _D =15 V, I _C =25 A	Tvj=25 °C	Terminal	-	-	1.7	
V		VD-10 V, IC-20 A	10]=23 0	Chip	-	1.3	-	v
V _{CEsat}	Collector-Emitter Saturation Voltage	V _{CIN} =0 V, Pulsed, (Fig.1)	Tvj=125 °C	Terminal	-	-	1.95	V
				Chip	-	1.5	-	
			Tvj=25 °C	Terminal	-	-	2.35	- V
V				Chip	-	1.75	-	
V _{FM}	Diode Forward Voltage	I _F =25A	Tvi=125 °C	Terminal	-	-	2.6	
		I VJ:		Chip	-	1.95	-	
1	Collector-Emitter Cut-off Current	$V_{CE} = V_{CES}, V_D = 15 V, V_{CIN} = 15 V$ (Fig.5)		Tvj=25 °C	-	-	1	
I _{CES}				Tvj=125 °C	-	-	10	mA

ELECTRICAL CHARACTERISTICS (Tvj = 25°C, unless otherwise noted)

CONTROL PART

Symbol	Denemeter	Conditions	Conditions		Limits		
	Parameter	Conditions			Тур.	Max.	Unit
			V _{P1} -V _{PC}	-	4	6	
1		V_{D} =15 V, V_{CIN} =15 V	V _{N1} -V _{NC}	-	16	24	
ID	Circuit Current	V_D =15 V, V_{CIN} =0 V \leftrightarrow 15 V, V_{CC} =800 V	V _{P1} -V _{PC}	-	13	15	mA
		l _c =0A, Tvj=125 °C, f _c ≤20kHz	V _{N1} -V _{NC}	-	48	56	
$V_{th(ON)}$	Input ON Threshold Voltage	Applied between:		1.2	1.5	1.8	v
$V_{th(OFF)}$	Input OFF Threshold Voltage	$U_{P}\text{-}V_{UPC}, V_{P}\text{-}V_{VPC}, W_{P}\text{-}V_{WPC}, U_{N}, V_{N}, W_{N},$	Br-V _{NC}	1.7	2.0	2.3	V
	Short Circuit Trip Level	-20≤Tvj≤125 °C, V _D =15 V (Fig.3, 6)	Inverter	70	-	-	
SC			Brake	50	-	-	A
t _{d(SC)}	Short Circuit Current Delay Time	V _D =15 V, Tvj=125 °C (Fig.3, 6)		-	2.0	-	μs
ОТ			Trip level	150	-	-	*0
OT _(hys)	Over Temperature Protection	Detect temperature of IGBT chip surface	Hysteresis	-	20	-	°C
UVt	Supply Circuit		Trip level	11.0	12.0	12.7	
UVr	Under-Voltage Protection	-	Reset level	-	12.5	-	V
I _{FO(H)}	Fourth Outrout Outroant			-	-	0.01	
I _{FO(L)}	Fault Output Current	V _D =15 V, V _{FO} =15 V (Note3)		-	10	15	mA
			OT	-	8.0	-	
t _{FO}	Fault Output Pulse Width	V _D =15 V (Note3)	UV	-	4.0	-	ms
			SC	-	2.0	-	

Note3. Fault output is given only when the internal SC, OT & UV protections schemes of either upper or lower arm device operate to protect it.


MECHANICAL RATINGS AND CHARACTERISTICS

Symbol	Parameter	Conditions	Limits			Unit
		Conditions		Тур.	Max.	Unit
Ms	Mounting Torque	Mounting part screw : M4	1.5	1.7	2.0	N•m
Mt	Mounting Torque	Main terminal part screw : M4	1.5	1.7	2.0	IN•III
m	mass	-	-	175	-	g

RECOMMENDED CONDITIONS FOR USE

Symbol	Parameter	Conditions	Recommended value	Unit
V _{cc}	Supply Voltage	Applied across P-N terminals	≤ 800	V
V _D	Control Supply Voltage	Applied between : V _{UP1} -V _{UPC} , V _{VP1} -V _{VPC} , V _{WP1} -V _{WPC} ,V _{N1} -V _{NC} (Note4)	15.0±1.5	V
V _{CIN(ON)}	Input ON Voltage	Applied between :	≤ 0.8	v
V _{CIN(OFF)}	Input OFF Voltage	$U_{P}\text{-}V_{UPC}, V_{P}\text{-}V_{VPC}, W_{P}\text{-}V_{WPC}, U_{N}, V_{N}, W_{N}, Br\text{-}V_{NC}$	≥ 9.0	v
f _{PWM}	PWM Input Frequency	Using Application Circuit of Fig. 8	≤ 20	kHz
t _{dead}	Arm Shoot-through Blocking Time	For IPM's each input signals (Fig.7)	≥ 2.5	μs

Note4. With ripple satisfying the following conditions: dv/dt swing ≤ ±5 V/µs, Variation ≤ 2 V peak to peak



GND

Note5. Long term performance related to thermal conductive material such as thermal grease (including but not limited to aspects such as the increase of thermal resistance due to pumping out, etc.) should be verified under your specific application conditions. Each temperature condition (Tvj, Tc) must be maintained below the maximum rated temperature throughout consideration of the temperature rise even for long term usage.

PRECAUTIONS FOR TESTING

VD(a


VD(all


1. Before applying any control supply voltage (V_D), the input terminals should be pulled up by resistors, etc. to their corresponding supply voltage and each input signal should be kept off state.

After this, the specified ON and OFF level setting for each input signal should be done.


2. When performing "SC" tests, the turn-off surge voltage spike at the corresponding protection operation should not be allowed to rise above V_{CES} rating of the device.

(These test should not be done by using a curve tracer or its equivalent.)





<Intelligent Power Modules> PM35RG1A120 HIGH POWER SWITCHING USE INSULATED TYPE




NOTES FOR STABLE AND SAFE OPERATION ;

- Design the PCB pattern to minimize wiring length between opto-coupler and IPM's input terminal, and also to minimize the stray capacity between the input and output wirings of opto-coupler.
- Connect low impedance capacitor between the Vcc and GND terminal of each fast switching opto-coupler.
- Fast switching opto-couplers: t_{PLH} , $t_{PHL} \le 0.8 \mu s$, Use High CMR type.
- Slow switching opto-coupler: CTR > 100% (*can be applied to Brake part input signal, in this case, resistor should be selected properly).
- Use 4 isolated control power supplies (V_D). Also, care should be taken to minimize the instantaneous voltage charge of the power supply.
- Make inductance of DC bus line as small as possible, and minimize surge voltage using snubber capacitor between P and N terminal.

HIGH POWER SWITCHING USE

INSULATED TYPE



COLLECTOR CURRENT I_C (A)

0

10

20

EMITTER CURRENT IE (A)


40

30


2.0

40


<Intelligent Power Modules> PM35RG1A120 HIGH POWER SWITCHING USE INSULATED TYPE




TIME (s)



HIGH POWER SWITCHING USE **INSULATED TYPE**





Note:

The characteristics curves are presented for reference only and not guaranteed by production test, unless otherwise noted.

0.001

0.0001

0.01

TIME (s)

0.1

1

10

0.001

Important Notice

The information contained in this datasheet shall in no event be regarded as a guarantee of conditions or characteristics. This product has to be used within its specified maximum ratings, and is subject to customer's compliance with any applicable legal requirement, norms and standards.

Except as otherwise explicitly approved by Mitsubishi Electric Corporation in a written document signed by authorized representatives of Mitsubishi Electric Corporation, our products may not be used in any applications where a failure of the product or any consequences of the use thereof can reasonably be expected to result in personal injury.

In usage of power semiconductor, there is always the possibility that trouble may occur with them by the reliability lifetime such as Power Cycle, Thermal Cycle or others, or when used under special circumstances (e.g. condensation, high humidity, dusty, salty, highlands, environment with lots of organic matter / corrosive gas / explosive gas, or situations which terminals of semiconductor products receive strong mechanical stress). Therefore, please pay sufficient attention to such circumstances. Further, depending on the technical requirements, our semiconductor products may contain environmental regulation substances, etc. If there is necessity of detailed confirmation, please contact our nearest sales branch or distributor.

The contents or data contained in this datasheet are exclusively intended for technically trained staff. Customer's technical departments should take responsibility to evaluate the suitability of Mitsubishi Electric Corporation product for the intended application and the completeness of the product data with respect to such application. In the customer's research and development, please evaluate it not only with a single semiconductor product but also in the entire system, and judge whether it's applicable. As required, pay close attention to the safety design by installing appropriate fuse or circuit breaker between a power supply and semiconductor products to prevent secondary damage. Please also pay attention to the application note and the related technical information.

Keep safety first in your circuit designs!

Mitsubishi Electric Corporation puts the maximum effort into making semiconductor products better and more reliable, but there is always the possibility that trouble may occur with them. Trouble with semiconductors may lead to personal injury, fire or property damage. Remember to give due consideration to safety when making your circuit designs, with appropriate measures such as (i) placement of substitutive, auxiliary circuits, (ii) use of non-flammable material or (iii) prevention against any malfunction or mishap.

Notes regarding these materials

- •These materials are intended as a reference to assist our customers in the selection of the Mitsubishi Electric Semiconductor product best suited to the customer's application; they do not convey any license under any intellectual property rights, or any other rights, belonging to Mitsubishi Electric Corporation or a third party.
- •Mitsubishi Electric Corporation assumes no responsibility for any damage, or infringement of any thirdparty's rights, originating in the use of any product data, diagrams, charts, programs, algorithms, or circuit application examples contained in these materials.
- •All information contained in these materials, including product data, diagrams, charts, programs and algorithms represents information on products at the time of publication of these materials, and are subject to change by Mitsubishi Electric Corporation without notice due to product improvements or other reasons. It is therefore recommended that customers contact Mitsubishi Electric Corporation or an authorized Mitsubishi Electric Semiconductor product distributor for the latest product information before purchasing a product listed herein.

The information described here may contain technical inaccuracies or typographical errors. Mitsubishi Electric Corporation assumes no responsibility for any damage, liability, or other loss rising from these inaccuracies or errors.

Please also pay attention to information published by Mitsubishi Electric Corporation by various means, including the Mitsubishi Electric Semiconductor home page (http://www.MitsubishiElectric.com/semiconductors/).

- •When using any or all of the information contained in these materials, including product data, diagrams, charts, programs, and algorithms, please be sure to evaluate all information as a total system before making a final decision on the applicability of the information and products. Mitsubishi Electric Corporation assumes no responsibility for any damage, liability or other loss resulting from the information contained herein.
- •Mitsubishi Electric Corporation semiconductors are not designed or manufactured for use in a device or system that is used under circumstances in which human life is potentially at stake. Please contact Mitsubishi Electric Corporation or an authorized Mitsubishi Electric Semiconductor product distributor when considering the use of a product contained herein for any specific purposes, such as apparatus or systems for transportation, vehicular, medical, aerospace, nuclear, or undersea repeater use.
- •The prior written approval of Mitsubishi Electric Corporation is necessary to reprint or reproduce in whole or in part these materials.
- •If these products or technologies are subject to the Japanese export control restrictions, they must be exported under a license from the Japanese government and cannot be imported into a country other than the approved destination.
- Any diversion or re-export contrary to the export control laws and regulations of Japan and/or the country of destination is prohibited.
- •Please contact Mitsubishi Electric Corporation or an authorized Mitsubishi Electric Semiconductor product distributor for further details on these materials or the products contained therein.

Generally the listed company name and the brand name are the trademarks or registered trademarks of the respective companies.