

[Issue No.] GOT-A-0148-B

[Title] Precautions when Replacing GT11 Model with GT27 and GT25 Models for Overseas [Date of Issue] First Edition: November 2019 (Ver. B: July 2021)

[Relevant Models] GOT1000 Series (GT11 Model) \rightarrow GOT2000 Series (GT2705-VTBD, GT2505-VTBD, and GT2505HS-VTBD)

Thank you for your continued support of Mitsubishi Electric Graphic Operation Terminal (GOT). We released the GOT2000 series GT2705-VTBD in March 2015, GT2505-VTBD in August 2017, and GT2505HS-VTBD in March 2018 with high functions and performance as alternatives of the GT11 model. We highly recommend that you replace the GT11 model with GT2705-VTBD, GT2505-VTBD, or GT2505HS-VTBD for using new sophisticated features.

Contents

1. Recomr	nended models for replacement	2
1.1 GO	Т	2
1.2 Cor	nmunication unit	2
1.3 Opt	ion	3
1.4 Cat	Die	3
1.4.1	RS-232 cable	3
1.4.2	RS-422 cable	3
1.4.3	External connection cable for Handy GOT	4
1.4.4	Q bus connection cable	4
1.4.5	Other cables	4
1.5 Sof	tware	5
1.6 Cha	anging the connection type from the bus connection	5
1.6.1	Changing the connection type from the A bus connection	5
1.6.2	Changing the connection type from the Q bus connection	13
2. Compar	ison in specifications	19
2.1 Cor	nparison in hardware specifications	.19
2.1.1	Comparison in performance specifications between GT115□-Q□BD(□) and GT2705-VTBD,	
	GT2505-VTBD	19
2.1.2	Comparison in power supply section specifications between GT115□-Q□BD(□) and GT2705-VTBD_GT2505-VTBD	23
213	Comparison in performance specifications between GT115 HS-0 BD and GT2505HS-VTBD	24
2.1.0	Comparison in power supply section specifications between GT115 HS-Q BD and	.27
2.1.1	GT2505HS-VTBD	25
2.2 Cor	nparison in external dimensions	.26
2.3 Cor	nparison in panel cutting dimensions	29
2.4 Mor	unting intervals	
2.4.1	When replacing GT11 models with GT2705-VTBD	30
2.4.2	When replacing GT11 models with GT2505-VTBD	31
2.5 Fur	ction specifications	32
2.5.1	Comparison in function specifications	32
2.5.2	Detailed comparison in function specifications	33
2.6 Scr	een design software specifications	37
2.6.1	Preparation before converting the project data	37
2.6.2	Procedure for converting the project data	37
2.6.3	Unsupported screen design function	.39
2.6.4	Other major changes	39
REVISIONS		42

MITSUBISHI ELECTRIC CORPORATION

HEAD OFFICE : TOKYO BUILDING, 2-7-3 MARUNOUCHI, CHIYODA-KU, TOKYO 100-8310, JAPAN NAGOYA WORKS : 1-14 , YADA-MINAMI 5-CHOME , HIGASHI-KU, NAGOYA , JAPAN



[Issue No.] GOT-A-0148-B

1. Recommended models for replacement

Other models^{*1} can be selected depending on the usage conditions in your system. Select an appropriate model after checking the specifications of the current system.

For the specifications of GT2705-VTBD, GT2505-VTBD, and GT2505HS-VTBD, refer to the following.

→ GOT2000 Series User's Manual (Hardware) (SH-081194ENG)

*1 Replacing with GT2105 is not recommended because it has many restrictions. For the replacement with GT2105, contact your local sales office.

1.1 GOT

Table 1-1 List of replacement models from GT115_□(HS) with GT2705, GT2505(HS)

			o: Compatil	ble, ×: Not compatible
GOT1000 series in use	Recommended GOT2000 series for	Panel cut compatibility	Attachment necessity	Cable compatibility
	replacement			
GT1155-QTBD	GT2505-VTBD	0	Not necessary	0
GT1155-QSBD	_			
GT1155-QSBD-C				
GT1150-QLBD				
GT1150-QBBD-C				
GT1155-QTBDA	GT2505-VTBD *1*2			× *3
GT1155-QSBDA				
GT1150-QLBDA				
GT1155-QTBDQ	GT2705-VTBD *4			0
	GT2505-VTBD *1*2			× *3
GT1155-QSBDQ	GT2705-VTBD *4			0
	GT2505-VTBD *1*2			× *3
GT1150-QLBDQ	GT2705-VTBD *4			0
	GT2505-VTBD *1*2			× *3
GT1155HS-QSBD	GT2505HS-VTBD *5	-	Not necessary	0
GT1150HS-OLBD				

^{*}1 Consider replacing with the communication type other than the bas connection.

→ 1.6 Changing the connection type from the bus connection

*2 For GT2505-VTBD, a communication unit or option unit is not available.

- To use a communication unit or option unit, consider replacing the GOT with the GT2705-VTBD.
- *3 The cable to be used depends on the communication type to be used.
 - → 1.6 Changing the connection type from the bus connection

*4 For the replacement with GT2705-VTBD, a Q bus connection communication unit (any one of GT15-QBUS, GT15-QBUS2, GT15-75QBUSL, or GT15-75QBUS2L) is necessary.

*5 The cable connector for PLC communication of GT2505HS-VTBD is set to the "Ethernet" connection at factory default. To perform the serial connection with a peripheral such as a PLC, set the cable connector for PLC communication to "RS-232" or "RS-422".

The cable connector for PLC communication is inside of the environmental protection back cover.

→ GOT2000 Series Handy GOT Connection Manual For GT Works3 Version1 (SH-081867ENG)

1.2 Communication unit

The communication units for the GOT1000 series can be used with the GOT2000 series as-is. Check the availability in the following table.

Table 1-2 List of replacement models for communication units

			○: Available as-is, ×: Not available
Unit for GOT1000		Availability	Remarks
Product name	Model	-	
Serial multi-drop	GT01-RS4-M	0	For the GOT multi-drop connection
Connection conversion adapter	GT10-9PT5S	0	Conversion connector between D-sub 9-pin (male) and European terminal block 5-pin
CC-Link interface unit	GT11HS-CCL	0	CC-Link interface unit for Handy GOT
	GT11H-CCL		

[Issue No.] GOT-A-0148-B

1.3 Option

For options, use the products for the GOT2000 series. Some options can be used as-is. Check the availability in the following table.

Table 1-3 List of replacement models for options

		o: Available as-is, ×: Not available
Product name	Availability	Remarks
Option function board	×	Products for the GOT1000 series cannot be used. No option function board is necessary for the GOT2000 series.
Protective sheet	×	Products for the GOT1000 series cannot be used. Use the products for the GOT2000 series. (Models of the protective sheet for GT2705-VTBD: GT25-05PSGC, GT25-05PSCC Models of the protective sheet for GT2505-VTBD: GT25-05PSGC-2, GT25-05PSCC-2) * Because the design of the front face panel and the position of the USB port differ.
Protective sheet (for Handy GOT)	×	Products for the GOT1000 series (for GT11 Handy) cannot be used. Use the products for the GOT2000 series. (Model: GT14H-50PSC)
USB environmental protection cover	×	Products for the GOT1000 series cannot be used. Use the products for the GOT2000 series. (Model of the USB environmental protection cover for GT2705-VTBD: GT25-05UCOV Model of the USB environmental protection cover for GT2505-VTBD: GT21-WUCOV)
Protective cover for oil	×	Products for the GOT1000 series cannot be used. Use the products for the GOT2000 series. (Model of the protective cover for oil for GT2705-VTBD: GT25-05PCO Model of the protective cover for oil for GT2505-VTBD: GT25-05PCO-2)
Stand	0	Products for the GOT1000 series can be used as-is.
Memory card (CF card)	×	Products for the GOT1000 series cannot be used. Use the products (SD cards) for the GOT2000 series.
Attachment	0	The attachment used in the GOT1000 series can be used as-is. * At the replacement of the GOT1000 series with the GOT2000 series, no attachment is necessary because the panel cutting dimensions are the same.
Battery (spare)	0	Products for the GOT1000 series can be used as-is. * GT2705-VTBD, GT2505-VTBD, and GT2505HS-VTBD have a built-in battery at factory default.
Emergency stop switch guard cover	×	Products for the GOT1000 series (for GT11 Handy) cannot be used. Use the products for the GOT2000 series. (Model: GT14H-50ESCOV)
Connector conversion box	0	Products for the GOT1000 series can be used as-is. (Model: GT11H-CNB-37S)

1.4 Cable

1.4.1 RS-232 cable

The currently used cable for the GOT1000 series (including the cable for Handy GOT) can be used as-is for the GOT2000 series.

For the following cable for Handy GOT, use the one with version C or later.

- GT11H-C15R2-6P

1.4.2 RS-422 cable

The currently used cable for the GOT1000 series (including the cable for Handy GOT) can be used as-is for the GOT2000 series.

For the following cable for Handy GOT, use the one with version C or later.

- GT11H-C15R4-8P
- GT11H-C15R4-25P

[Issue No.] GOT-A-0148-B

1.4.3 External connection cable for Handy GOT

For the following cables among the currently used external connection cables for Handy GOT, use the ones with version C or later.

- GT11H-C30-37P
- GT11H-C60-37P
- GT11H-C100-37P
- GT11H-C30
- GT11H-C60
- GT11H-C100

1.4.4 Q bus connection cable

(1) Utilization of currently used cables

The currently used Q bus connection cable for the GOT1000 series can be used as-is for the GOT2000 series.

(2) Replacement of GOT when multiple units are connected by Q bus connection

When multiple GOT1000 series GOTs are connected by the Q bus connection, one or more of the units can be replaced with the GOT2000 series. In this case, the GOT1000 series and GOT2000 series can coexist.



* When multiple GOTs are connected by the Q bus connection, GT11 can be used at the terminal only.

1.4.5 Other cables

The currently used cables for the GOT1000 series (including the cable for Handy GOT) other than the above can be used as-is for the GOT2000 series.

[Issue No.] GOT-A-0148-B

1.5 Software

To create the project data, MELSOFT GT Designer3 (GOT2000) is necessary. The supported version of MELSOFT GT Designer3 (GOT2000) differs depending on the model. For the supported version and how to obtain, refer to Table 1-5.

Software	Supported version	How to obtain
GOT screen design software MELSOFT GT Works3	■Japanese/English/Chinese version MELSOFT GT Designer3 (GOT2000) enclosed with MELSOFT GT Works3 Version1.130L or later for creating the project data of GT2705-VTBD. MELSOFT GT Designer3 (GOT2000) enclosed with MELSOFT GT Works3 Version1.180N or later for creating the project data of GT2505-VTBD. MELSOFT GT Designer3 (GOT2000) enclosed with MELSOFT GT Works3 Version1.195D or later for creating the project data of GT2505HS-VTBD.	The versions shown on the left are supported. If your version is old, contact your local sales office for how to obtain the latest version.
GOT screen design software MELSOFT GT Works2 MELSOFT GT Designer2	Not supported	To create the project data for GOT2000, purchase MELSOFT GT Works3.
FA integrated engineering software MELSOFT iQ Works	■Japanese/English version Ver.2.11M or later for creating the project data of GT2705-VTBD. *1 Ver.2.48Q or later for creating the project data of GT2505-VTBD. *2 Ver.2.50C or later for creating the project data of GT2505HS-VTBD. *3	The versions shown on the left are supported. If your version is old, contact your local sales office for how to obtain the latest version.

*1 To use the interaction function of MELSOFT Navigator and MELSOFT GT Works3, update MELSOFT GT Works3 to Version1.136S or later.

*2 To use the interaction function of MELSOFT Navigator and MELSOFT GT Works3, update MELSOFT GT Works3 to Version1.185T or later.

*3 To use the interaction function of MELSOFT Navigator and MELSOFT GT Works3, update MELSOFT GT Works3 to Version1.197F or later.

1.6 Changing the connection type from the bus connection

1.6.1 Changing the connection type from the A bus connection

The A bus connection unit for the GOT2000 series has been discontinued since the end of January in 2015.

When the A bus connection is used with the GT11 model, change the communication type or replace the PLC.

To replace the PLC, refer to the following Technical Bulletin.

- Production discontinuation of MELSEC-AnS/QnAS (small type) series and MELSEC-I/OLINK (FA-A-0142)
 - Production discontinuation of MELSEC-A/QnA (large type) series (T99-0050)

When changing the communication type from the A bus connection, refer to the following.

- ➡ ■1. Setting of PLC and GOT
 - ■2. Communication type

■1. Setting of PLC and GOT

When changing the communication type, check the settings of the PLC and GOT.

(1) PLC

When the GOT in the bus connection is removed or communication units are added to the PLC, the setting of the PLC may need to be changed.

Change the parameter setting (such as I/O assignment), the I/O number in the sequence program, and others according to the configuration of the PLC.

[Issue No.] GOT-A-0148-B

(2) GOT

Change the controller setting. *1

When changing to the network connection (other than the Ethernet connection), set the network number and station number to the device number of each object. *2

1	Setting exampl When connecti	e of ng te	the co the M	ntroller ELSEC-A se	ries us	ing the dir	rect CP	U connecti	on (serial)
	🖶 Controller Setting						-		
	Controler Setting Ch1:MELSEC-A Ch2:None Ch2:None Ch4:None Ch4:None Ch4:None Ch4:None Ch4:None Ch4:None Ch4:None Ch4:None	Manufa Control I/F: Driver:	cturer: er Type:	MITSUBISHI ELECTRIC MELSEC-A Standard I/F(RS422/485) Serial(MELSEC)		× × ×	^		
	22 Gateway Serve	🙆 D	etail Setting				_		
			Property		Val	e			
	- FTP Server		Transmission S	peed(BPS)	115	200			
	MELSEC Redundan		Retry(Times)		0				
	Station No. Switch		Timeout Time(Sec)	3				
	Buffer Memory Unit No		Delay Time(ms)	0				
			Format		1				
			Monitor Speed		High	(Normal)			

Setting of the network No. and station No. *2

When monitoring D0 of the CPU with network No. 1 and station No. 2

Basic Settings / Device / Style / Extended / Trigger / Operation/Script	
Type: Numerical Display O Numerical Input	
Device: 1-2 D0 Data Type: Signed	BIN16 ~
Font: Signed birtor entimetacera	×
Device D E F Format: 0 0 0 E F Digits (Integr 4 5 6 A B C 1 2 3 Back, CL CL	Information [Kind] [VORD [Range] Device: 0-8999 9000-9255 9256-32767
Oloris (Fracti Network Oloris @ Other Network No.: 1 0 Station No.	: 2 🗘
Switch to the device comment dialog	OK Cancel

■2. Communication type

(1) Replacing with the serial connection

(a) Direct CPU connection (serial)

Configure the connection as follows.



1) Connecting to MELSEC-A (ACPU, AnCPU, AnSCPU) or MELSEC-QnA (QnACPU, QnASCPU)

PLC		Connection cable *1	GOT	
CPU module	Communic ation type	*	Option	GOT
MELSEC-A (ACPU) MELSEC-A (AnCPU)	RS-422	GT01-C30R4-25P (3 m) GT01-C100R4-25P (10 m)	(Built in the GOT)	GT2705-VTBD GT2505-VTBD
MELSEC-A (AnSCPU) MELSEC-Q (QnACPU) MELSEC-Q (QnASCPU)		GT01-C200R4-25P (20 m) GT01-C300R4-25P (30 m)	GT15-RS4-9S	GT2705-VTBD

When the distance between the connected devices exceeds 30 m, consider replacing with the network connection. *1

[Issue No.] GOT-A-0148-B

(b) Computer link connection

Configure the connection as follows.

When replacing with the computer link connection, a computer link module is required on the PLC.



1) Connecting to MELSEC-A (ACPU, AnCPU)

PLC		Connection cable *1*2	GOT	
Computer link module	Communic ation type		Option	GOT
AJ71UC24 *3	RS-232	GT09-C30R2-25P (3 m) User-created cable (15 m max.)	(Built in the GOT)	GT2705-VTBD GT2505-VTBD
			GT15-RS2-9P	GT2705-VTBD
	RS-422	GT09-C30R4-6C (3 m) GT09-C100R4-6C (10 m) GT09-C200R4-6C (20 m) GT09-C300R4-6C (30 m) User-created cable (500 m max.)	(Built in the GOT)	GT2705-VTBD GT2505-VTBD
			GT15-RS4-9S	GT2705-VTBD

*1 For the user-created cable, refer to the following.

→ GOT2000 Series Connection Manual (Mitsubishi Electric Products) For GT Works3 Version1 (SH-081197ENG)

*2 When the distance between the connected devices exceeds 30 m, consider replacing with the connection with user-created cables or the network connection.

*3 This module has been discontinued.

2) Connecting to MELSEC-A (AnSCPU, A0J2HCPU, A2CCPU)

PLC		Connection cable *1*2 GOT	GOT	
Computer link module	Communic ation type		Option	GOT
A1SJ71UC24-R2 *3	RS-232	GT09-C30R2-9P (3 m)	(Built in the GOT)	GT2705-VTBD
A1SJ71024-R2 3 A1SJ71UC24-PRF *3 A1SJ71C24-PRF *3		User-created cable (15 m max.)	GT15-RS2-9P	GT2705-VTBD
A1SJ71UC24-R4 *3 A1SJ71C24-R4 *3	RS-422	GT09-C30R4-6C (3 m) GT09-C100R4-6C (10 m)	(Built in the GOT)	GT2705-VTBD GT2505-VTBD
		GT09-C200R4-6C (20 m) GT09-C300R4-6C (30 m) User-created cable (500 m max.)	GT15-RS4-9S	GT2705-VTBD

*1 For the user-created cable, refer to the following.

→ GOT2000 Series Connection Manual (Mitsubishi Electric Products) For GT Works3 Version1 (SH-081197ENG)

*2 When the distance between the connected devices exceeds 30 m, consider replacing with the connection with user-created cables or the network connection.

*3 This module has been discontinued.

[Issue No.] GOT-A-0148-B

3) Connecting to MELSEC-QnA (QnACPU)

PLC		Connection cable *1*2	GOT	
Serial communication/comput er link module	Communic ation type	-	Option	GOT
AJ71QC24 *4 AJ71QC24N *4 AJ71QC24-R2 *4 AJ71QC24-R2 *4	RS-232	GT09-C30R2-25P (3 m) User-created cable (15 m max.)	(Built in the GOT) GT15-RS2-9P	GT2705-VTBD GT2505-VTBD GT2705-VTBD
AJ71QC24-R4 *4 AJ71QC24N-R4 *4	RS-422	GT01-C30R4-25P (3 m) GT01-C100R4-25P (10 m) GT01-C200R4-25P (20 m) GT01-C200R4-25P (30 m)	(Built in the GOT) GT15-RS4-9S	GT2705-VTBD GT2505-VTBD GT2705-VTBD
AJ71QC24 *4 AJ71QC24N *4 AJ71QC24-R4 *4 AJ71QC24N-R4 *4	RS-422	GT09-C30R4-6C (3 m) GT09-C100R4-6C (10 m) GT09-C200R4-6C (20 m) GT09-C200R4-6C (30 m) User-created cable (1200 m max.)	(Built in the GOT) GT15-RS4-9S	GT2705-VTBD GT2505-VTBD GT2705-VTBD
AJ71UC24 *3*4	RS-232	GT09-C30R2-25P (3 m) User-created cable (15 m max.)	(Built in the GOT) GT15-RS2-9P	GT2705-VTBD GT2505-VTBD GT2705-VTBD
AJ71UC24 *3*4	RS-422	GT09-C30R4-6C (3 m) GT09-C100R4-6C (10 m) GT09-C200R4-6C (20 m) GT09-C300R4-6C (30 m) User-created cable (500 m max.)	(Built in the GOT) GT15-RS4-9S	GT2705-VTBD GT2505-VTBD GT2705-VTBD

*1 For the user-created cable, refer to the following.

→ GOT2000 Series Connection Manual (Mitsubishi Electric Products) For GT Works3 Version1 (SH-081197ENG)

*2 When the distance between the connected devices exceeds 30 m, consider replacing with the connection with user-created cables or the network connection.

*3 The range of available device numbers is the device range of AnACPU.

*4 This module has been discontinued.

4) Connecting to MELSEC-QnA (QnASCPU)

PLC		Connection cable *1*2	GOT	
Serial communication/comput er link module	Communic ation type		Option	GOT
A1SJ71QC24 *4 A1SJ71QC24N *4 A1SJ71QC24N1 *4	RS-232	GT09-C30R2-9P (3 m) User-created cable (15 m max.)	(Built in the GOT)	GT2705-VTBD GT2505-VTBD
A1SJ71QC24-R2 *4 A1SJ71QC24N-R2 *4 A1SJ71QC24N1-R2 *4			GT15-RS2-9P	GT2705-VTBD
A1SJ71QC24 *4 A1SJ71QC24N *4 A1SJ71QC24N1 *4	RS-422	S-422 GT09-C30R4-6C (3 m) GT09-C100R4-6C (10 m) GT09-C200R4-6C (20 m)	(Built in the GOT)	GT2705-VTBD GT2505-VTBD
		GT09-C300R4-6C (30 m) User-created cable (1200 m max.)	GT15-RS4-9S	GT2705-VTBD
A1SJ71UC24-R2 *3*4 A1SJ71C24-R2 *3*4	RS-232	GT09-C30R2-9P (3 m) User-created cable (15 m max.)	(Built in the GOT)	GT2705-VTBD GT2505-VTBD
A1SJ71UC24-PRF *3*4 A1SJ71C24-PRF *3*4			GT15-RS2-9P	GT2705-VTBD
A1SJ71UC24-R4 *3*4 A1SJ71C24-R4 *3*4	RS-422	422 GT09-C30R4-6C (3 m) GT09-C100R4-6C (10 m) GT09-C200R4-6C (20 m) GT09-C300R4-6C (30 m) User-created cable (15 m max.)	(Built in the GOT)	GT2705-VTBD GT2505-VTBD
			GT15-RS4-9S	GT2705-VTBD

*1 For the user-created cable, refer to the following.

→ GOT2000 Series Connection Manual (Mitsubishi Electric Products) For GT Works3 Version1 (SH-081197ENG)

When the distance between the connected devices exceeds 30 m, consider replacing with the connection with user-created cables or the network connection.

*3 The range of available device numbers is the device range of AnACPU.

*4 This module has been discontinued.

*2

[Issue No.] GOT-A-0148-B

(2) Replacing with the network connection

(a) Ethernet connection

Configure the connection as follows.

When replacing with the Ethernet connection, an Ethernet module is required on the PLC.



1) Connecting to MELSEC-A (AnCPU, AnSCPU)

PLC		Connection cable GOT			
Ethernet module	Communication		Option	GOT	
	type				
AJ71E71N3-T *1*2	Ethernet	Twisted cable	(Built in the GOT)	GT2705-VTBD	
AJ71E71N-B5 *1*2		- 10BASE-T		GT2505-VTBD	
AJ71E71N-B2 *1*2		- 100BASE-TX			
AJ71E71N-T *1*2					
AJ71E71N-B5T *1*2					
AJ71E71-S3 *1*2					
A1SJ71E71N3-T *1*2					
A1SJ71E71N-B5 *1*2					
A1SJ71E71N-B2 *1*2					
A1SJ71E71N-T *1*2					
A1SJ71E71N-B5T *1*2					
A1SJ71E71-B5-S3 *1*2					
Δ1S I71E71_B2_S3 *1*2					

*1 This module has been discontinued.

*2 The applicable destination to connect the twisted pair cable depends on the configuration of the Ethernet network system to be used.

Connect to the Ethernet module, hub, transceiver, wireless LAN adapter (NZ2WL-JPA or NZ2WL-JPS), or other system equipment according to the Ethernet network system to be used.

Use the cable, connector, or hub that meets the IEEE802.3 10BASE-T/100BASE-TX standards.

To connect to the Ethernet module, a cross cable can be used.

For the controller to which the wireless LAN adapter can be connected and how to configure the settings for the wireless LAN adapter, refer to the manual of the wireless LAN adapter to be used.

[Issue No.] GOT-A-0148-B

2) Connecting to MELSEC-QnA (QnACPU, QnASCPU)

PLC		Connection cable GOT			
Ethernet module	Communication		Option	GOT	
	type				
AJ71QE71N3-T *1 AJ71QE71N-B5 *1 AJ71QE71N-B2 *1 AJ71QE71N-B2 *1 AJ71QE71N-T *1 AJ71QE71N-B5T *1 AJ71QE71-B5 *1 A1SJ71QE71N-B5 *1 A1SJ71QE71N-B2 *1 A1SJ71QE71N-B5 *1 A1SJ71QE71N-B5 *1 A1SJ71QE71-B5 *1 A1SJ71QE71-B5 *1 A1SJ71QE71-B5 *1	Éthernet	Twisted cable - 10BASE-T - 100BASE-TX	(Built in the GOT)	GT2705-VTBD GT2505-VTBD	

^{*}1 This module has been discontinued.

*2 The applicable destination to connect the twisted pair cable depends on the configuration of the Ethernet network system to be used.

Connect to the Ethernet module, hub, transceiver, wireless LAN adapter (NZ2WL-JPA or NZ2WL-JPS), or other system equipment according to the Ethernet network system to be used.

Use the cable, connector, or hub that meets the IEEE802.3 10BASE-T/100BASE-TX standards.

To connect to the Ethernet module, a cross cable can be used.

For the controller to which the wireless LAN adapter can be connected and how to configure the settings for the wireless LAN adapter, refer to the manual of the wireless LAN adapter to be used.

(b) CC-Link connection (Intelligent device station)

Configure the connection as follows.

When replacing with the CC-Link (intelligent device station) connection, a CC-Link module is required on the PLC.



1) Connecting to MELSEC-A (ACPU ^{*1}, AnCPU, AnSCPU)

PLC		Connection cable	GOT	
CC-Link module	Communication type		Option	GOT
AJ61BT11 *3	CC-Link	CC-Link dedicated cable	GT15-J61BT13 *2	GT2705-VTBD
A1SJ61BT11	(Ver.1)			

*1 Only A0J2HCPU, A0J2HCPUP21, A0J2HCPUR21, and A0J2HCPU-DC24 can be connected.

*2 In the controller setting, set the mode to Ver.1.

*3 This module has been discontinued.

2) Connecting to MELSEC-QnA (QnACPU, QnASCPU)

PLC		Connection cable	GOT		
CC-Link module	Communication type		Option	GOT	
AJ61QBT11 *2	CC-Link	CC-Link dedicated cable	GT15-J61BT13 *1	GT2705-VTBD	
A1SJ61QBT11	(Ver.1)				
A la the explored anti- and the weeds to Verd					

*1 In the controller setting, set the mode to Ver.1.

*2 This module has been discontinued.

[Issue No.] GOT-A-0148-B

(c) MELSECNET/10 connection

Configure the connection as follows.

When replacing with the MELSECNET/10 connection, a MELSECNET/10 module is required on the PLC. On the GOT, a MELSECNET/H communication module (used in the MNET/10 mode) is required.



1) Connecting to MELSEC-A (AnCPU *1, AnSCPU *1) (optical loop system)

PLC		Connection cable	GOT		
	MELSECNET/10 module	Communication type		Option	GOT
	AJ71LP21 *3 A1SJ71LP21 *3	MELSECNET/10	Fiber-optic cable	GT15-J71LP23-25 *2	GT2705-VTBD

*1 A2UCPU, A2UCPU-S1, A3UCPU, A4UCPU, A2USCPU, A2USCPU-S1, and A2USHCPU-S1 can be connected.

*2 In the controller setting, set the MNET/10 mode.

*3 This module has been discontinued.

2) Connecting to MELSEC-QnA (QnACPU, QnASCPU) (optical loop system)

PLC		Connection cable	GOT	
MELSECNET/10 module	Communication type		Option	GOT
AJ71QLP21 *2 AJ71QLP21S *2 A1SJ71QLP21 *2 A1SJ71QLP21 *2 A1SJ71QLP21S *2	MELSECNET/10	Fiber-optic cable	GT15-J71LP23-25 *1	GT2705-VTBD

*1 In the controller setting, set the MNET/10 mode.

*2 This module has been discontinued.

3) Connecting to MELSEC-A (AnCPU *1, AnSCPU *1) (coaxial bus system)

PLC		Connection cable	GOT	
MELSECNET/10 module	Communication type		Option	GOT
AJ71BR11 *3 A1SJ71BR11 *3	MELSECNET/10	Coaxial cable	GT15-J71BR13 *2	GT2705-VTBD

*1 A2UCPU, A2UCPU-S1, A3UCPU, A4UCPU, A2USCPU, A2USCPU-S1, and A2USHCPU-S1 can be connected.

*2 In the controller setting, set the MNET/10 mode.

*3 This module has been discontinued.

4) Connecting to MELSEC-QnA (QnACPU, QnASCPU) (coaxial bus system)

PLC		Connection cable	GOT	
MELSECNET/10	Communication type		Option	GOT
AJ71QBR11 *2 A1SJ71QBR11 *2	MELSECNET/10	Coaxial cable	GT15-J71BR13 *1	GT2705-VTBD

*1 In the controller setting, set the MNET/10 mode.

*2 This module has been discontinued.

[Issue No.] GOT-A-0148-B

(3) Replacement when multiple units are connected

Consider the following connection types for the replacement of the configuration in which multiple units are connected.

- Network connection
 - → 1.6.1 ■2. (2) Replacing with the network connection
- Multi-drop connection
 - → (a) Multi-drop connection
- (a) Multi-drop connection *1

Configure the connection as follows.

When replacing with the multi-drop connection, the following options and cables are required.



*1 If the number of connected slave GOTs or the number of devices of each GOT increase, the device update cycle on the screen may be delayed.

In this case, it is recommended to reduce the number of devices of each GOT.

(The standard number of devices is 250 per GOT, and 750 in total.)

If a timeout error occurs, extend the timeout time with the controller setting of the slave GOT.

1) Connecting to MELSEC-A (ACPU, AnCPU, AnSCPU) *1*2, MELSEC-QnA (QnACPU *3, QnASCPU) *4

For the system configuration between the serial multi-drop connection unit and the PLC, refer to each connection type.

Multi-drop connection unit		Cable *5	GOT	
Serial multi-drop connection unit	Communication type		Option	GOT
GT01-RS4-M RS-485	RS-485	S-485 User-created cable (500 m max. *6)	(Built in the GOT)	GT2705-VTBD GT2505-VTBD
			GT15-RS4-9S	GT2705-VTBD
			GT15-RS4-TE	GT2705-VTBD

*1 Cannot be connected when the PLC and serial multi-drop connection unit are connected by the computer link connection.

*2 The SB, SW, Ww, Wr, ER, and BM devices cannot be monitored.

*3 Q4ARCPU cannot be connected.

*4 The Ww and Wr devices cannot be monitored.

*5 For the user-created cable, refer to the following.

→ GOT2000 Series Connection Manual (Mitsubishi Electric Products) For GT Works3 Version1 (SH-081197ENG)

*6 This is the maximum distance between the PLC and the GOT (terminal).

[Issue No.] GOT-A-0148-B

1.6.2 Changing the connection type from the Q bus connection

When changing the communication type from the Q bus connection, refer to the following.

- ➡ ■1. Setting of PLC and GOT
 - ■2. Communication type

■1. Setting of PLC and GOT

When changing the communication type, check the settings of the PLC and GOT.

(1) PLC

When the GOT in the bus connection is removed or communication units are added to the PLC, the setting of the PLC may need to be changed. Change the parameter setting (such as I/O assignment), the I/O number in the sequence program, and others according to the configuration of the PLC.

(2) GOT

Change the controller setting. *1

When changing to the network connection (other than the Ethernet connection), set the network number and station number to the device number of each object. *2

*1 Example of the controller setting



*2 Setting of the network No. and station No. When monitoring D0 of the CPU with network No. 1 and station No. 2



[Issue No.] GOT-A-0148-B

■2. Communication type

(1) Replacing with the serial connection

(a) Direct CPU connection (serial)

Configure the connection as follows.



PLC			Connection cable *1	GOT	
CPU module	RS-422 conversion cable	Communication type	-	Option	GOT
MELSEC-Q (Q mode) MELSEC-Q (A mode)	-	RS-232	GT01-C30R2-6P (3 m)	(Built in the GOT)	GT2705-VTBD GT2505-VTBD
C Controller module				GT15-RS4-9S	GT2705-VTBD
(Q Series)	FA-CNV2402CBL (0.2m)	RS-422	GT01-C30R4-25P (3 m) GT01-C100R4-25P (10 m)	(Built in the GOT)	GT2705-VTBD GT2505-VTBD
	FA-CNV2405CBL		GT01-C200R4-25P (20 m) GT01-C300R4-25P (30 m)	GT15-RS4-9S	GT2705-VTBD

*1 When the distance between the connected devices exceeds 30 m, consider replacing with the network connection.

(b) Serial communication connection

Configure the connection as follows.

When replacing with the serial communication connection, a serial communication connection module is required on the PLC.

Connecting to MELSEC-Q (Q mode)

PLC		Connection cable *1 GOT		
Computer link module	Communication type		Option	GOT
QJ71C24 *2	RS-232	GT09-C30R2-9P (3 m)	(Built in the GOT)	GT2705-VTBD
QJ/1C24N		User-created cable (15 m max.)		G12505-V1BD
QJ71C24-R2 *2			GT15-RS2-9P	GT2705-VTBD
QJ71C24N-R2				
QJ71CMO *2				
QJ71CMON *2				
QJ71C24 *2	RS-422	GT09-C30R4-6C (3 m)	(Built in the GOT)	GT2705-VTBD
QJ71C24N		GT09-C100R4-6C (10 m)		GT2505-VTBD
QJ71C24N-R4		GT09-C200R4-6C (20 m)	GT15-RS4-9S	GT2705-VTBD
		GT09-C300R4-6C (30 m)		
		User-created cable (500 m max.)		

*1 For the user-created cable, refer to the following.

→ GOT2000 Series Connection Manual (Mitsubishi Electric Products) For GT Works3 Version1 (SH-081197ENG)

*2 This module has been discontinued.

[Issue No.] GOT-A-0148-B

(2) Replacing with the network connection

(a) MELSECNET/10 connection

Configure the connection as follows.

When replacing with the MELSECNET/10 connection, a MELSECNET/10 module is required on the PLC. On the GOT, a MELSECNET/H communication module (used in the MNET/10 mode) is required.



1) Connecting to MELSEC-Q (optical loop system)

PLC		Connection cable	GOT	
MELSECNET/H module	Communication type		Option	GOT
QJ71LP21 *2 QJ71LP21-25	MELSECNET/10	Fiber-optic cable	GT15-J71LP23-25 *1	GT2705-VTBD
QJ71LP21S-25				

^{*}1 In the controller setting, set the MNET/10 mode.

*2 This module has been discontinued.

2) Connecting to MELSEC-Q (coaxial bus system)

PLC		Connection cable	GOT	
MELSECNET/H module	Communication type		Option	GOT
QJ71BR11	MELSECNET/10	Coaxial cable	GT15-J71BR13 *1	GT2705-VTBD

*1 In the controller setting, set the MNET/10 mode.

(b) MELSECNET/H connection

Configure the connection as follows.

When replacing with the MELSECNET/H connection, a MELSECNET/H module is required on the PLC. On the GOT, a MELSECNET/H communication module is required.



1) Connecting to MELSEC-Q (optical loop system)

PLC		Connection cable	GOT	
MELSECNET/H module	Communication type		Option	GOT
QJ71LP21 *1	MELSECNET/H	Fiber-optic cable	GT15-J71LP23-25	GT2705-VTBD
QJ71LP21S-25				

*1 This module has been discontinued.

[Issue No.] GOT-A-0148-B

2) Connecting to MELSEC-Q (coaxial bus system)

PLC		Connection cable	GOT	
MELSECNET/H module Communication			Option	GOT
QJ71BR11	MELSECNET/H	Coaxial cable	GT15-J71BR13	GT2705-VTBD

(c) CC-Link connection (intelligent device station)

Configure the connection as follows.

When replacing with the CC-Link (intelligent device station) connection, a CC-Link module is required on the PLC.



Connecting to MELSEC-Q

PLC		Connection cable	GOT	
CC-Link module *1	Communication type		Option	GOT
QJ61BT11 *5 QJ61BT11N	CC-Link(Ver.1)	CC-Link dedicated cable *2*3	GT15-J61BT15 *4	GT2705-VTBD

*1 For the system configuration for the CC-Link module, refer to the following manuals.

CC-Link System Master/Local Module User's Manual (SH-080016)

MELSEC-Q CC-Link System Master/Local Module User's Manual (SH-080394)

*2 For the specifications of CC-Link dedicated cables and contact, refer to the following.

- CC-Link Partner Association website: http://www.cc-link.org/
- *3 The maximum length of total extension cables and that of the cable between stations depends on the cable type to be used and the transmission speed.

For details, refer to the following manuals.

CC-Link System Master/Local Module User's Manual (SH-080016)

MELSEC-Q CC-Link System Master/Local Module User's Manual (SH-080394)

- *4 In the controller setting, set the mode to Ver.1.
 - For details, refer to the following manual.

→ GOT2000 Series Connection Manual (Mitsubishi Electric Products) For GT Works3 Version1 (SH-081197ENG)

*5 This module has been discontinued.

[Issue No.] GOT-A-0148-B

(d) Ethernet connection

Configure the connection as follows.

When replacing with the Ethernet connection, an Ethernet module is required on the PLC.



Connecting to MELSEC-Q

PLC		Connection cable	GOT	
Ethernet module	Communication type		Option	GOT
QJ71E71-100 QJ71E71-B5 *1 QJ71E71-B2 *1 QJ71E71 *1	Éthernet	Twisted cable - 10BASE-T - 100BASE-TX	(Built in the GOT)	GT2705-VTBD GT2505-VTBD

*1 This module has been discontinued.

[Issue No.] GOT-A-0148-B

(3) Replacement when multiple units are connected

Consider the following connection type when replacing the configuration where multiple units are connected.

- Network connection
 - → 1.6.2 ■2. (2) Replacing with the network connection
 - Multi-drop connection
 - → (a) Multi-drop connection
- (a) Multi-drop connection *1

Configure the connection as follows.

When replacing with the multi-drop connection, the following options and cables are required.



*1 If the number of connected slave GOTs or the number of devices of each GOT increase, the device update cycle on the screen may be delayed.

In this case, it is recommended to reduce the number of devices of each GOT.

(The standard number of devices is 250 per GOT, and 750 in total.)

If a timeout error occurs, extend the timeout time with the controller setting of the slave GOT.

1) Connecting to MELSEC-Q *1

For the system configuration between the serial multi-drop connection unit and the PLC, refer to each connection type.

Multi-drop connection unit		Cable *2	GOT		
Serial multi-drop connection unit	Communication type		Option	GOT	
GT01-RS4-M	RS-485	User-created cable (500 m max. *3)	(Built in the GOT)	GT2705-VTBD GT2505-VTBD	
			GT15-RS4-9S	GT2705-VTBD	
			GT15-RS4-TE	GT2705-VTBD	

*1 The Ww and Wr devices cannot be monitored.

*2 For the user-created cable, refer to the following.

→ GOT2000 Series Connection Manual (Mitsubishi Electric Products) For GT Works3 Version1 (SH-081197ENG)

*3 This is the maximum distance between the PLC and the GOT (terminal).

2. Comparison in specifications

2.1 Comparison in hardware specifications

2.1.1 Comparison in performance specifications between GT115□-Q□BD(□)(-C) and GT2705-VTBD, GT2505-VTBD

The specifications in the gray cells are not changed by replacement.

Table 2-1 Comparison chart of performance specifications (GT115□-Q□BD(-C) and GT2505-VTBD)

Item			Model in use			Recommended model for replacement	
		GT1155- QTBD	GT1155- QSBD(-C)	GT1150- QLBD, GT1150- QBBD-C	GT2505-VTBD		
Conforr	ming standard		CE (EMC), UL/c	UL, KC		<i>←</i>	
Displa y sectio	Туре		TFT color LCD	STN color LCD	STN monochrome (black/white) LCD	TFT color LCD	
n	Screen size		5.7"			←	
	Resolution		QVGA: 320 × 24	40 [dot]		VGA: 640 × 480 [dot]	
	Display size		115 (W) × 86 (H) [mm]		←	
	Number of dis characters	played	16-dot standard (two-byte chara 12-dot standard (two-byte chara	font: 20 characte cters) font: 26 characte cters)	ers × 15 lines ers × 20 lines	16-dot standard font: 40 characters × 30 lines (two- byte characters) 12-dot standard font: 53 characters × 40 lines (two- byte characters)	
Display color		256 colors GT QLI Moi (bla 16 J GT QB Moi (wr 16		GT1150- QLBD: Monochrome (black/white) 16 levels GT1150- QBBDC: Monochrome (white/blue) 16 levels	65536 colors		
Brightness			8 levels			32 levels	
Decklig	adjustment		Cold cathode fluorescent tube (not replace		ot replaceable)	LED (not replaceable)	
васкіід	Type		Backlight OFF				
nı	Function		Screen saving t	me settable			
	Life *1		Approx. 75,000 hours Approx. 54,000 hours		Approx. 54,000 hours	Approx. 60,000 hours	
Touch	Туре		Matrix resistive film			Analog resistive film	
panel	Key size		Minimum 16 × 16 dots (per key)			Minimum 2 × 2 dots (per key)	
	Simultaneous	press	Max. 2	Max. 2		Not available	
	Life		1 million touche [N] or less)	s or more (operat	ing force: 0.98	~	
Memo ry	User memory	ory Built-in flash memory: 3MB Life (number of writings): 100 thousand		Storage memory (ROM): 32MB Operation memory (RAM): 80MB Life (number of writings): 100 thousand			
	Built-in SRAM		Drive D: 512KB			SRAM user area: 500KB	
Battery	Туре		GT11-50BAT lithium battery			<i>←</i>	
	Life		Approx. 5 years (ambient temperature: 25°C)		ature: 25°C)	← 	
Built-in interfa ce	Bus	Spec ificat ion	-			←	
	RS-422/485	Spec ificat ion	1 channel, conn (female)	ector shape: D-si	ub 9-pin	←	
	RS-232	Spec ificat ion	1 channel, conn	ector shape: D-si	ub 9-pin (male)	←	

[Issue No.] GOT-A-0148-B

Item		Model in use			Recommended model for replacement	
		GT1155-	GT1155-	GT1150-	GT2505-VTBD	
		QTBD	QSBD(-C)	QLBD,		
				GT1150-		
				QBBD-C	1 channel, data transfer mothod: 100PASE	
Built-in	Ethernet	-				
interfa					connector shape: RJ-45 (modular jack)	
се	USB (host)	-			1 channel, maximum transfer rate: High-Speed 480	
					Mbps,	
					connector shape: USB-A (back)	
	USB (device)	1 channel, maxi	mum transfer rate	e: Full-Speed 12	1 channel, maximum transfer rate: High-Speed 480	
		MDps, connector shape: USB Mini-B (front)			connector shape: USB Mini-B (front)	
	SD/CE card	CF card: 1 chan	nel, FAT16 forma	at (max. 2GB)	SD card: 1 channel, SDHC-compatible (max.	
	50/Cr curd	Not available to	GT1155-QSBD-0	C and GT1150-	32GB)	
		QBBD-C.				
Buzzer output		Single tone (tone length adjustable)			Single tone (tone and tone length adjustable)	
POWER	LED	2 colors (green and orange)			2 colors (blue and orange)	
Protectiv	ve structure	IP67F (panel front face only)			←	
External	dimensions	164 (W) × 135 (H) × 56 (D) [mm]			164 (W) × 139 (H) × 55 (D) [mm]	
Panel cu	itting dimensions	153 (W) × 121 (H) [mm]		←	
Weight	(excluding installation	0.7 kg			0.6 kg	
fitting)						
Compatible software package		GT Designer3 V	/ersion1.00A or la	ter	GT Works3 Version1.180N or later	
		GT1155-QSBD-C, GG1150-QBBD-C: GT		D-C: GT		
		Designer3 Versi	on1.01B or later			
Installat	ion direction	Horizontal or ve	rtical		~	
Control	panel inside	Refer to the follo	owing.		Refer to the following.	
dimensi	ons for installation	→ 2.4 Mounting	intervals		→ 2.4 Mounting intervals	
Installati	ion position					

Installation position

*1 Period when operating ambient temperature is 25°C and display intensity is 50%

[Issue No.] GOT-A-0148-B

Table 2-2 Comparison chart of performance specifications

			_(GT115□-Q⊏	BD and GT2	705-VTBD, GT	[2505-VTBD)		
Item			Model in use			Recommended model	for replacement	
			GT1155- QTBDA, GT1155- QTBDQ	GT1155- QSBDA, GT1155- QSBDQ	GT1150- QLBDA, GT1150- QLBDQ	GT2705-VTBD	GT2505-VTBD	
Conform	ning standar	d	CE (EMC), UL/c	UL, KC	l'	<i>←</i>		
Displa y sectio	Type TFT color LCD STN color		STN color LCD	STN monochrome (black/white) LCD	TFT color LCD			
n	Screen size		5.7"	5.7"		←		
	Resolution [dot]	QVGA: 320 × 24	.0		VGA: 640 × 480		
	Display size		115 (W) × 86 (H)	115 (W) × 86 (H) [mm]		←		
	Number of		16-dot standard	font: 20 characte	ers × 15 lines	16-dot standard font: 4	0 characters × 30 lines	
	displayed		(two-byte charac	ters)	22 11	(two-byte characters)		
	characters		12-dot standard	tont: 26 characte	ers × 20 lines	12-dot standard font: 5	3 characters × 40 lines	
	Display color	r	256 colors		Monochrome (black/white) 16 levels	65536 colors		
	Brightness		8 levels			32 levels		
	adjustment	ıt						
Backlig	Туре		Cold cathode fluorescent tube (not replaceable)			LED (not replaceable)		
ht	Function		Backlight OFF Screen saving ti	me settable		←		
	Life *1		Approx. 75,000 hours		Approx. 54,000 hours	Approx. 60,000 hours		
Touch	Туре		Matrix resistive f	ilm		Analog resistive film		
panel	Key size		Minimum 16 × 1	6 dots (per key)		Minimum 2 × 2 dots (per	key)	
	Simultaneou	is press	Max. 2			Max. 2	Not available	
	Life		1 million touches or less)	s or more (operatin	ng force: 0.98 [N]	← ("DOM")	00145	
Memo ry	User memor	у	Life (number of v	mory: 3MB writings): 100 thou	sand	Storage memory (ROM): 32MB Operation memory (RAM): 80MB Life (number of writings): 100 thousand		
	Built-in SRAN	Ν	Drive D: 512KB	····· I 44 - ····		SRAM user area: 500KB		
Battery	Туре		GTTT-SUBAT IIII	ium ballery	human 05°C)			
	Life		Approx. 5 years		(UIE. 25 C)			
Built-in interfa ce	Bus	Speci ficati on	1 channel or QnA/ACPU/M channel	otion controller CF	PU (A series), 1	-		
	RS- 422/485	Speci ficati on	-	-		1 channel, connector sha	ape: D-sub 9-pin (female)	
	RS-232	Speci ficati on	1 channel, connector shape: D-sub 9-pin (male)		← 			
	Ethernet -		-			1 channel, data transfer TX/10BASE-T, connector shape: R.I-45	method: 100BASE- (modular.iack)	
	USB (host)		-			2 channels, maximum transfer rate: High- Speed 480 Mbps, connector shape: USB- A (front/back)	1 channel, maximum transfer rate: High- Speed 480 Mbps, connector shape: USB- A (back)	
	USB (device)		1 channel, maxir Mbps, connector shape	num transfer rate: :: USB Mini-B (fror	Full-Speed 12	1 channel, maximum tran 480 Mbps, connector shape: USB M	nsfer rate: High-Speed lini-B (front)	
	SD/CF card		connector shape: USB Mini-B (front) CF card: 1 channel, FAT16 format (max. 2GB)			SD card: 1 channel, SDF 32GB)	IC-compatible (max.	

[21 / 42]

[Issue No.] GOT-A-0148-B



Item	Model in use			Recommended model for replacement		
	GT1155-	GT1155-	GT1150-	GT2705-VTBD	GT2505-VTBD	
	QTBDA,	QSBDA,	QLBDA,			
	GT1155-	GT1155-	GT1150-			
	QTBDQ	QSBDQ	QLBDQ			
Buzzer output	Single tone (tone	e length adjustable	e)	Single tone (tone and tor	ne length adjustable)	
POWER LED	2 colors (green a	and orange)		2 colors (blue and orange	e)	
Protective structure	IP67F (panel front face only)			←		
External dimensions [mm]	167 (W) × 135 (H) × 65 (D)			167 (W) × 139 (H) × 60 (D)	164 (W) × 139 (H) × 55 (D)	
Panel cutting dimensions	153 (W) × 121 (I	H)		←		
[mm]						
Weight (excluding	0.9 kg			1.0 kg	0.6 kg	
installation fitting)						
Compatible software	GT Designer3 Version1.00A or later			GT Works3	GT Works3	
package				Version1.130L or later	Version1.180N or later	
Installation direction	Horizontal or vertical			←		
Control panel inside	Refer to the follo	wing.		Refer to the following.		
dimensions for installation	→ 2.4 Mounting	intervals		→ 2.4 Mounting intervals	;	
Installation position						

*1 Period when operating ambient temperature is 25°C and display intensity is 50%

[Issue No.] GOT-A-0148-B

2.1.2 Comparison in power supply section specifications between GT115-QBD() and GT2705-VTBD, GT2505-VTBD

The specifications in the gray cells are not changed by replacement.

Table 2-3 Comparison chart of power supply section specifications $(GT115\Box-Q\Box BD\Box$ and GT2705-VTBD, GT2505-VTBD)

Item	Model in use				<u></u> ,	Recommende replacement	d model for
	GT1155- QTBD, GT1155- QSBD, GT1155- QSBD-C	GT1150- QLBD, GT1150- QBBD-C	GT1155- QTBDA, GT1155- QTBDQ	GT1155- QSBDA, GT1155- QSBDQ	GT1150- QLBDA, GT1150- QLBDQ	GT2705- VTBD	GT2505- VTBD
Input power supply voltage	24 V DC (+10%,	, -15%) ripple volt	age 200 mV or lov	ver		←	
Power consumption (Under the maximum load)	9.84 W (410 mA/24 V)	9.36 W (390 mA/24 V)	11.16 W (465 mA/24 V)	9.72 W (405 mA/24 V)	7.92 W (330 mA/24 V)	30 W or less	8.4 W or less
Inrush current *1	15 A or lower (2	ms)	26 A or lower (4	26 A or lower (4 ms)			42A or lower (2 ms)
Permissible instantaneous power failure time	5 ms or less		10 ms or less			10 ms or less	
Noise immunity	Noise voltage: 1000 Vp-p, noise width: 1 µs (Measured by a noise simulator with noise frequency 30 to 100 Hz)		Noise Voltage: 500 Vp-p, noise Width: 1 µs (Measured by a noise simulator with noise frequency 25 to 60Hz)			Noise voltage: 500 Vp-p, noise width: 1 µs (Measured by a noise simulator with noise frequency 25 to 60Hz)	Noise voltage: 1000 Vp-p, noise width: 1 µs (Measured by a noise simulator with noise frequency 30 to 100 Hz)
Withstand voltage	500 V AC for 1 minute across power terminals and earth \leftarrow						
Insulation resistance	$10\ \text{M}\Omega$ or more across power terminals and earth by a 500V DC insulation resistance tester					←	
Applicable wire size	For power: 0.75	[mm2] or more, fo		←			
Applicable solderless terminal	Solderless termi	nal for M3 screw:	RAV1.25-3, V2-S	3.3, V2-N3A, FV2	-N3A	<i>←</i>	

*1 Ambient temperature: 25°C, under the maximum load

[Issue No.] GOT-A-0148-B

2.1.3 Comparison in performance specifications between GT115 HS-Q BD and GT2505HS-VTBD The specifications in the gray cells are not changed by replacement.

Table 2-4 Comparison chart of performance specifications (Handy GOT)

Item			Model in use		Recommended model for replacement	
			GT1155HS-QTBD	GT1150HS-QLBD	GT2505HS-VTBD	
Confor	Conforming standard		CE (EMC), UL/cUL, KC		←	
Displa	Туре		TFT color LCD	STN monochrome (black/white) LCD	TFT color LCD	
y	Screen size		5.7"		← →	
section	Resolution		QVGA: 320 × 240 [dot]		VGA: 640 × 480 [dot]	
	Display size		115 (W) × 86 (H) [mm]		←	
	Number of dis	played	16-dot standard font: 20	characters × 15 lines	16-dot standard font: 40 characters × 30 lines	
	characters		(two-byte characters)	abaraatara x 20 linaa	(two-byte characters)	
			(two-byte characters)	characters × 20 lines	(two-byte characters)	
	Display color		256 colors	Monochrome (black/white) 16 levels	65536 colors	
	Brightness		8 levels		32 levels	
	adjustment					
Backlig	Туре		Cold cathode fluorescent t	ube (not replaceable)	LED (not replaceable)	
nt	Function		Backlight OFF Screen saving time settab	le	←	
	Life *1		Approx. 75,000 hours	Approx. 54,000 hours	Approx. 60,000 hours	
Touch	Туре		Matrix resistive film		Analog resistive film	
panel	Key size		Minimum 16 × 16 dots (pe	r key)	Minimum 2 × 2 dots (per key)	
	Simultaneous	press	Max. 2		Not available	
	Life		1 million touches or more or less)	(operating force: 0.98 [N]	←	
Memor y	User memory		Built-in flash memory: 3MB Life (number of writings): 100 thousand		Storage memory (ROM): 32MB Operation memory (RAM): 80MB Life (number of writings): 100 thousand	
	Built-in SRAM		Drive D: 512KB		SRAM user area: 500KB	
Battery	attery Type		GT11-50BAT lithium battery		←	
	Life		Approx. 5 years (ambient temperature: 25°C)		←	
Built-in	Bus	Spec	-		←	
interfa		ificati				
се		on				
	RS-422	Spec	1 channel each		1 channel each	
		ificati	(Select 1 channel from RS	-422/RS-232 (for PLC	(Select 1 channel from RS-422/RS-232/Ethernet to use)	
		on	Connector shape: Round 3	32-pin (male)	Connector shape: Round 32-pin (male)	
	RS-232	Spec				
	(for PLC	ificati				
	communicati	on				
	on)					
	RS-232	Spec	1 channel MINI DIN 6 pip (female)		-	
	(for PC	ificati	winal-Din o-pin (lemale)			
	communicati	on				
	on)					
	Ethernet		-		1 channel (Select 1 channel from RS-422/RS-232/Ethernet to use)	
					Data transfer method: 100BASE-TX/10BASE-T Connector shape: Round 32-pin (male)	
	USB (host)		-		1 channel, maximum transfer rate: High-Speed 480 Mbps,	
	USB (device)		1 channel, maximum trans Mbps,	fer rate: Full-Speed 12	connector shape: USB-A 1 channel, maximum transfer rate: High-Speed 480 Mbps,	
			connector shape: USB Mir	ni-B	connector shape: USB Mini-B	

[25 / 42]

[Issue No.] GOT-A-0148-B

Item	Model in use GT1155HS-QTBD GT1150HS-QLBD		Recommended model for replacement	
			GT2505HS-VTBD	
Buzzer output	Single tone (tone length adjustable)		Single tone (tone and tone length adjustable)	
POWER LED	2 colors (green and orange)		2 colors (blue and orange)	
Protective structure	IP65F (when an external connection cable is connected)		←	
External dimensions	176 (W) × 220 (H) × 93 (D) [mm]	145 (W) × 185 (H) × 79.3 (D) [mm]	
Weight (Handy GOT only)	1.0 kg		0.79 kg	
Compatible software package	GT Designer3 Version1.00A or later		GT Works3 Version1.195D or later	

*1 Period when operating ambient temperature is 25°C and display intensity is 50%

2.1.4 Comparison in power supply section specifications between GT115□HS-Q□BD and GT2505HS-VTBD

The specifications in the gray cells are not changed by replacement.

Table 2-5 Comparison chart of power supply section specifications (Handy GOT)

Item	Model in use		Recommended model for replacement	
	GT1155HS-QTBD	GT1150HS-QLBDE	GT2505HS-VTBD	
Input power supply	24 V DC (+10%, -15%) ripple voltage 200 mV or lower		<i>←</i>	
voltage				
Power consumption	9.84 W (410 mA/24 V)	9.36 W (390 mA/24 V)	8.40 W or less	
(Under the				
maximum load)				
Inrush current *1	15 A or lower (2 ms)		30 A or lower (2 ms)	
Permissible	5 ms or less		<i>←</i>	
instantaneous				
power failure time				
Noise immunity	Noise voltage: 1000 Vp-p, noise	width: 1 µs	<i>←</i>	
	(Measured by a noise simulator Hz)	with noise frequency 30 to 100		
Withstand voltage	500 V AC for 1 minute across po	wer terminals and earth	<i>←</i>	
Insulation resistance	10 $M\Omega$ or more across power ter insulation resistance tester	minals and earth by a 500V DC	←	

*1 Ambient temperature: 25°C, under the maximum load

[Issue No.] GOT-A-0148-B

2.2 Comparison in external dimensions

■GT115□-Q□BD(-C)



∎GT115□-Q□BD□



[Issue No.] GOT-A-0148-B

■GT2705-VTBD



■GT2505-VTBD



[Issue No.] GOT-A-0148-B

■GT11 handy model



■GT2505HS-VTBD



[Issue No.] GOT-A-0148-B

2.3 Comparison in panel cutting dimensions



The specifications in the gray cells are not changed by replacement.

Item	Model in use	Recommended model for replacement		
	GT11 model	GT2705-VTBD	GT2505-VTBD	
А	153 ⁺² ₋₀ mm (6.02 ^{+0.08} inch)	←		
В	121 ⁺² ₋₀ mm (4.76 ^{+0.08} inch)	←		
С	10 mm or more (0.39 inch or more)	<i>←</i>		
Panel thickness	2 to 4 mm (0.08 to 0.16 inch)	1.6 to 4 mm (0.06 to 0.16 inch)		

[Issue No.] GOT-A-0148-B

2.4 Mounting intervals

2.4.1 When replacing GT11 models with GT2705-VTBD





Figure 2-4-1-1 GT11 model

∎Horizontal







Figure 2-4-1-2 GT2705-VTBD

The specifications in the gray cells are not changed by replacement.

Item	Model in use	Recommended model for replacement
	GT11 model	GT2705-VTBD
А	50 mm or more (20 mm or more)	59 mm or more
В	Vertical: 80 mm or more (20 mm or more) [3.15 inch or more (0.79 inch or more)] Horizontal: 50 mm or more (20 mm or more) [1.97 inch or more (0.79 inch or more)]	Vertical: 78 mm or more (18 mm or more) [3.07 inch or more (0.71 inch or more)] Horizontal: 48 mm or more (18 mm or more) [1.89 inch or more (0.71 inch or more)]
C	When the CF card is used: 100 mm or more (100 mm or more) [3.94 inch or more (3.94 inch or more)] When the CF card is not used: Vertical: 50 mm or more (20 mm or more) [1.97 inch or more (0.79 inch or more)] Horizontal: 80 mm or more (0.79 inch or more) [1.97 inch or more (0.79 inch or more)]	When the SD card is used:100 mm or more (100 mm or more)[3.94 inch or more (3.94 inch or more)]When the SD card is not used:50 mm or more (20 mm or more)[1.97 inch or more (0.79 inch or more)]
D	50 mm or more (20 mm or more)	Vertical: 50 mm or more (20 mm or more) [1.97 inch or more (0.79 inch or more)] Horizontal: 80 mm or more (20 mm or more) [3.15 inch or more (0.79 inch or more)]
E	100 mm or more (20 mm or more) [3.94 inch or more (0.79 inch or more)]	← ·

The dimensions within the parentheses apply when no equipment generating radiated noise (such as a contactor) or heat is installed near the GOT.

[Issue No.] GOT-A-0148-B

2.4.2 When replacing GT11 models with GT2505-VTBD





Figure 2-4-2-1 GT11 model

∎Horizontal







Figure 2-4-2-2 GT2505-VTBD The specifications in the gray cells are not changed by replacement.

Item	Model in use	Recommended model for replacement
	GT11 model	GT2505-VTBD
А	50 mm or more (20 mm or more)	←
	[1.97 inch or more (0.79 inch or more)]	
В	Vertical: 80 mm or more (20 mm or more)	←
	[3.15 inch or more (0.79 inch or more)]	
	Horizontal: 50 mm or more (20 mm or more)	
	[1.97 inch or more (0.79 inch or more)]	
С	When the CF card is used:	Vertical: 50 mm or more (20 mm or more)
	100 mm or more (100 mm or more)	[1.97 inch or more (0.79 inch or more)]
	[3.94 inch or more (3.94 inch or more)]	Horizontal: 80 mm or more (20 mm or more)
	When the CF card is not used:	[3.15 inch or more (0.79 inch or more)]
	Vertical: 50 mm or more (20 mm or more)	
	[1.97 inch or more (0.79 inch or more)]	
	Horizontal: 80 mm or more (20 mm or more)	
	[1.97 inch or more (0.79 inch or more)]	
D	50 mm or more (20 mm or more)	<i>←</i>
	[1.97 inch or more (0.79 inch or more)]	
E	100 mm or more (20 mm or more)	When the SD card is used:
	[3.94 inch or more (0.79 inch or more)]	100 mm or more (100 mm or more)
		[3.94 inch or more (3.94 inch or more)
		When the SD card is not used:
		100 mm or more (20 mm or more)
		[3.94 inch or more (0.79 inch or more)

The dimensions within the parentheses apply when no equipment generating radiated noise (such as a * contactor) or heat is installed near the GOT.

[Issue No.] GOT-A-0148-B

2.5 Function specifications

2.5.1 Comparison in function specifications

Most of the functions of the GOT1000 series can be used in the GOT2000 series, however, some functions are not supported or are integrated, or their names have been changed. For details, refer to "Table 2-6 Comparison in GOT2000 function specifications". For details of each function of the GOT2000 series, refer to the manual.

(1) Functions not supported by the GOT2000 series

- Data list display
- A list editor
- Connecting multiple GOTs

(2) Integrated functions and functions with changed names

Function name in the GOT1000 series	Function name in the GOT2000 series
Basic comment	Comment group
Comment group	
Alarm history, alarm history display	User alarm observation, alarm display (user)
Status observation function	Trigger action
Trigger action	
ASCII display, ASCII input	Text display, text input
User alarm display	Simple alarm display
Alarm scrolling	Alarm popup display
System monitor	Device monitor

[Issue No.] GOT-A-0148-B

2.5.2 Detailed comparison in function specifications

(1) Detailed comparison in function specifications

The following table shows the differences in the functions between the GOT1000 series and the GOT2000 series.

	Table 2-6 Comparison in GOT2000 function specifications					
Cat	ego	Function name in GOT1000	GT11	GT27,	Precautions for replacing GOT1000 series with GOT2000	
ry				GT25	series	
Shap	Shap	Shape	•	•	-	
e/obj	e	Logo text	•	•	-	
ect fu	Font	Standard font	•	•	- Refer to 2.6.4 (2).	
Inctic	type	HQ font	•	•	-	
ă		TrueType font	•	•	-	
		Windows font	•	•	-	
	Com	Text	•	•	-	
	mon	Trigger type	•	•	-	
		Offset device	•	•	- Refer to 2.6.4 (5).	
		Number of colors	•	•	-	
	Object	Touch switch	•	•	 The special function switches that are not supported by GOT2000 are replaced with [Utility]. When multiple actions including ones to which no device has been set have been set on a switch in the [Action] tab, touching the switch may not perform actions after the action to which no device has been set. 	
		Lamp	•	•	- The [Use Image Transparent] setting for when objects registered in the library are used will be deleted. Transparent color becomes effective in GOT2000 regardless of the settings in GOT1000.	
		Numerical display, numerical input	•	•	-	
		ASCII display, ASCII input	•	•	- Replaced with [Text Display] or [Text Input].	
		Date display, time display	•	•	-	
		Comment display	•	•	 When [16dot HQ Mincho] or [16dot HQ Gothic] is specified for the comment display (bit), the setting is replaced as follows. When the text size (width × height) is any of 0.5, 1, 3, 5, or 7: The font selected in [16dot Standard Font] in the type setting of GOT1000. 2, 4, 6, or 8: [16dot HQ Mincho] 	
		Basic comment	•	•	- Replaced with [Comment Group]. - [Basic Comment] is replaced with the comment group No. 256.	
		Comment group	•			
		Parts display	•	•	- When [Fixed Parts Display] is used, [Rise] and [Fall] of the trigger type setting are replaced with [ON] and [OFF].	
		Parts display	•	•	- When [Fixed Parts Display] is used, [Rise] and [Fall] of the trigger type setting are replaced with [ON] and [OFF].	
		Parts movement	•	•	-	
		Data list display	•	×	- Not supported by GOT2000.	

[Issue No.] GOT-A-0148-B

Cat rv	ego	Function name in GOT1000	GT11	GT27, GT25	Precautions for replacing GOT1000 series with GOT2000 series
Shape/object fun	Object	User alarm display	•	•	 Replaced with [Simple Alarm Display]. [Rise], [Fall], and [Sampling] of the trigger type setting are replaced with [Ordinary]. Text alignment of the comment setting (multiple rows) will be deleted. Texts are aligned [Left] in GOT2000 regardless of the setting of GOT1000. [Store Memory] is not supported. When [Store Memory] is used, replace it with [User Alarm Observation] or [Alarm Display(User)].
ctio		System alarm display	•	•	-
		Alarm history, alarm history display	•	•	 Replaced with [User Alarm Observation] or [Alarm Display(User)]. Replaced with [Time (hh:mm)] when [Text] is set as the date/time format for [Occurred], [Restored], and [Checks] of the displayed items in [Alarm History Display]. When [Create a CSV file simultaneously] is selected in [Alarm History], configure the setting again in [Alarm Common Setting] of [User Alarm Observation] on GOT2000. GT2505-V cannot be saved in the drive D Use the data storage since it is replaced with the drive X. For the available drives, refer to 2.6.4 (3).
		Alarm scrolling	•	•	- Replaced with [Alarm Popup Display].
		Level	•	•	-
		Panel meter	•	•	- [Top 1/4], [Bottom 1/4], [Left 1/4], and [Right 1/4] are replaced with [Top 1/6], [Bottom 1/6], [Left 1/6], and [Right 1/6] respectively. The display size is not changed.
		Line graph	•	•	- [Locus] is not supported.
		Trend graph	•	•	 Replaced with [Historical Trend Graph] or [Logging] when [Store Memory] is set. However, this function will be deleted when the number of logging settings exceeds the upper limit.
		Bar graph	•	•	-
		Statistics bar graph	•	•	-
		Statistics pie graph	•	•	-
		Scatter graph	•	•	-
		Key window object	•	•	-
Function running in a	Function running in t	Recipe	•	•	 The following functions are not supported. Creating a recipe file if no recipe file is found at startup Specifying the file register name The format of the recipe file (CSV/Unicode text) differs. When using the recipe file of GOT1000, change the format into the one for GOT2000. For details, refer to Section 2.2.2(2). GT2505-V cannot be saved in the drive D Use the data storage since it is replaced with the drive X. For the available drives, refer to 2.6.4 (3).
c c		Status observation function	•	•	- Replaced with [Trigger Action]. - Because the trigger action has no [Observation Cycle] setting the
ackground	ackaround	Trigger action	•		setting is replaced with one of [ON Sampling], [OFF Sampling], and [Ordinary] in the [Trigger Type] setting when the [Observation Cycle] setting has been set. Thus, the operation timing in the first cycle may change.
		Time action	•	•	- GT2505-V cannot be saved in the drive D Use the data storage since it is replaced with the drive X. For the available drives, refer to 2.6.4 (3).

[Issue No.] GOT-A-0148-B

Catego	Function name in GOT1000	GT11	GT27,	Precautions for replacing GOT1000 series with GOT2000
Function running in the background	Project/Screen script	•	•	 The setting of [Cancel internal device (GD/GB) assignment delay] will be deleted. In GOT2000, the result of assignment of internal devices (GD/GB) is reflected immediately regardless of the setting in GOT1000. [Perform script initial operation (screen/object) only when switching screens] is added to GOT2000. The setting will be replaced as follows. Not checked (compatible with GOT1000) The trigger type of a script is replaced as shown below. [Ordinary] → [Sampling] (Cycle time: 100 ms) [OFF] → [OFF Sampling] (Cycle time: 100 ms) When the drive D is specified with file operation function, change the destination drive. For the available drives, refer to 2.6.4 (3).
Fur usir	RFID function	●*1	•*2	-
nction ng ipheral	Barcode reader	●*1	•*2	-
GO	Base screen	•	•	-
r fur	Overlap window	•	•	-
nctio	Superimpose window	•	•	-
	Dialog window	•	•	-
	Key window	•	•	-
	Language switching	•	•	-
	Connecting multiple GOTs	•	×	-
	System information	•	•	-
	Security level authentication	•	•	- The password input dialog of the security level authentication differs In GT11, the dialog where 0 to 9 and A to F can be entered is displayed. In GOT2000, the dialog where 0 to 9, A to Z, and a to z can be entered is displayed.
	Startup logo	•	•	-
	FA transparent	•	•	- The modem connection and RS-232 connection between the GOT and a personal computer are not supported.
Debug	System monitor	•	•	 Replaced with [Device Monitor]. The display method for device comments is the same as the one for the sequence program monitor.
funct	A list editor	•*4	×	 Not supported by GOT2000. The special function switch [A List Editor] is replaced with [Utility].
ion	FX list editor	•*3	•	-

*1 Excluding GT11 Handy
*2 Excluding GT25 Handy
*3 Excluding GT11 dedicated to bus connection
*4 Excluding GT11Q dedicated to bus connection

•: Supported

×: Not supported by GOT2000

[Issue No.] GOT-A-0148-B

(2) Recipe files (CSV/Unicode text) of the recipe

The format of the recipe files (CSV/Unicode text) differs between the GOT1000 series and GOT2000 series. Thus, when using a recipe file (CSV/Unicode text) for the GOT1000 series in the GOT2000 series, change the format into the one for the GOT2000 series.

(a) Convert the project data into the one for the GOT2000 series, and execute the recipe.

(b) A recipe file for the GOT2000 series (CSV/Unicode text) is created in a specified drive.

(c) Copy the device values in the recipe file for the GOT1000 series onto the corresponding section in the recipe file for the GOT2000 series created in (b).

-	GOT1000 recipe f	ile

0074000

:DATE	2014/1/31 12:38
:GROUP No.	1
:GROUP NAME	RECIPE1
:DEVICE	8
ITEM NAME	VALUE
	234
	421
	52
	-23
	534
	-3
	32
	0

......

Copy and paste these values onto the GOT2000 recipe file.

-	GOT2000 recipe file	(number of record	s: 1)
	:GT2K_RECIPE		0	

:GT2K_RECIPE	0				
:RECIPE_ID	1				
:RECIPE_NAME	RECIPE1				
:DEVICE_NUM	8				
:RECORD_NUM	1				
	YYYY/MM/DD				
:DATE_ORDER	hh:mm:ss				
:LOCAL_TIME	GMT+09:00				
:TIME_INF_ORDER	L				
	DEV_COMMENT	DEV_TYPE	DISP_TYPE	DEV_SIZE	1
:RECORD_NAME					
:RECORD_ATTR					
:UPDATE					2014/131 12:38
1		BIN16	DEC		234
2		BIN16	DEC	1	421
3		BIN16	DEC	1	52
4		BIN16	DEC	1	-23
5		BIN16	DEC	1	534
6		BIN16	DEC	1	-3
7		BIN16	DEC	1	32
8		BIN16	DEC	1	0

[Issue No.] GOT-A-0148-B

2.6 Screen design software specifications

The project data used in the GOT1000 series can be converted into the project data for the GOT2000 series, and can be used as-is.

[Precautions]

This explanation is based on GT Works3 Version1.195D.

Once the project data is converted into the one for the GOT2000 series, it cannot be converted back into the one for the GOT1000 series.

2.6.1 Preparation before converting the project data

Install the following software into the personal computer in advance.

(1) When reading the project data for the GOT1000 series from a GOT

Install GT Designer3 (GOT1000) (GT Works3 Version1.195D or later) or Data Transfer Tool. * This operation is not necessary if any project data to be converted is already in the personal computer.

(2) When converting the project data for the GOT2000 series

Install GT Designer3 (GOT2000) (GT Works3 Version1.195D or later).

For how to install the software, refer to the following. (Download the manual from MITSUBISHI ELECTRIC FA Global Website.)

- GT Works3 Installation Instructions (DVD version) (BCN-P5999-0066)

If your version is old, contact your local sales office for how to obtain the latest version.

2.6.2 Procedure for converting the project data

(1) Checking and saving the project data to be converted

When the data to be converted is in the personal computer, check the storage location of the project data for the GOT1000 series. When no data to be converted is in the personal computer, connect the personal computer to the GOT1000 series, and read and save the project data using GT Designer3 (GOT1000) or Data Transfer Tool.

(2) Opening the project data to be converted

1) When the project data to be converted does not need to be edited

Open the project data to be converted with GT Designer3 (GOT2000), and select [Convert the project to GOT2000 data and edit it in GT Designer3 (GOT2000)].

MELSOFT	r GT Designer3 (GOT2000)	
	GOT1000 data is selected. Select the editing method.	
Start GT Designer3 (GOT1000) and edit the GOT1000 data as is		
 Convert the project to GOT2000 data and edit it in GT Designer3 (GOT2000) 		
Exit GT Designer3 (GOT2000)		
OK Cancel		

[Issue No.] GOT-A-0148-B

2) When converting the project data to be converted after editing

Open the project data to be converted in GT Designer3 (GOT1000), edit the data, select [Common] - [GOT Type Setting], and select [GOT2000] for [Series] in GOT Type. Then, click "OK".

Series:	GOT1000		•		
GOT Type:	GOT1000 GOT16**-S (800x600))			
<u>C</u> olor Setting:	256		•		
Default Drive Name:	A:Standard CF Card		•		
Project Folder:	Project1				
Standard Font					
Eont	Japanese		•		
16dot Standard Font:	 Gothic 	Mincho			
TrueType Numerical Fon	t 💿 Gothic	7-Segment			
Check for overlapping objects with	hin GOT				
Adjust object display order in GC	T to the one in GT Desi	gner3			
Use system labels in conjunction	with MELSOFT Navigat	or	About System La	bel	

GT Designer3 (GOT2000) is started up.

(3) Converting the project data to be converted Select the GOT2000 model to be replaced with and click "OK".

/pe Setting	
Original GOT Type:	GT16**-S (800x600)
GOT Type	
Series:	GOT2000 👻
Type:	GT27**-S (800x600)
Model:	GT2712-STBA GT2712-STBD GT2712-STWA GT2712-STWD GT2710-STBA GT2710-STBD
Setup Direction:	e Horizontal
Color Setting:	65536 Colors
Use the gesture functio	n
Enable the graphics a	accelerator
Package Folder Name:	G2PACKAGE¥ Project1
Language and Font Setting	
Standard Language:	Japanese 🔹
Use easily-distinguishable	e font for 0 (zero) and I
Outline Font	
The beauties of the second sec	Vanii 🕅 Hangul
V Alphaniimenc/kana	
Chinasa (Cirratificad) Char	
Chinese (Simplified) Char	acter Code:
Chinese (Simplified) Char	racter Code:
Chinese (Simplified) Char Enable the antialiasing	acter Code:
Appandment(Kana) Chinese (Simplified) Char Enable the antialasing Check for overlapping of Adjust object display orr	acter Code: © GB2312 © GBK to smooth jagged text edges bjects in the GOT fer in GOT to the one in GT Designer3
Chinese (Simplified) Chai Chaese (Simplified) Chai Chaese (Simplified) Chai Check for overlapping of Adjust object display or Use system labels in con	acter Code:

(4) The project data is converted for the GOT2000 series, and GT Designer3 (GOT2000) is started up. The changes can be checked in the output window.

	Output	Ψ×	
ĺ	Option Refinement:		
I	Project open processing has been started. 25/02/2014 14:31		
	GOT type conversion has been started. 25/02/2014 14:32		
	The GOT type has been converted. Refer to the Help for supported functions of each GOT type.		
I	GOT type conversion has been completed. 25/02/2014 14:32		
I	Project open processing has been completed. 25/02/2014 14:32		

[Issue No.] GOT-A-0148-B

2.6.3 Unsupported screen design function

The following screen design function is not supported.

Category	Screen design function	GT11	GT27, GT25	Precautions for replacing GOT1000 series with GOT2000 series
Screen design software	Communication between the screen design software and GOT (modem, RS-232)	•	×	The modem or RS-232 connection between the screen design software (personal computer) and GOT is not supported. Use the USB or Ethernet connection.

•: Supported

×: Not supported by GOT2000

[Precautions]

Note that the settings of the functions that are not supported in the GOT2000 series are deleted when the GOT1000 series project data is converted for the GOT2000 series.

For compatibility of the functions between the GOT2000 series and GOT1000 series, refer to Section 3.5.

2.6.4 Other major changes

Major changes in the screen design function are as follows.

(1) Name of the OS (standard monitor OS, extended function OS)

The name is changed as follows.

In the GOT2000 series, the data necessary for GOT operations including system applications, project data, and communication drivers are collectively called "package data".

Name in GOT1000	Name in GOT2000
OS	System application
Standard monitor OS	Standard system application
Extended function OS	Advanced system application

(2) Name of standard fonts

The name and type of the standard fonts are changed as follows.

Name in GOT1000	Precautions and names for replacing GOT1000 with GOT2000
Japanese *1	Japanese *3 * Replaced with a font equivalent to Japanese (supporting Europe) of the GOT1000 series.
Japanese (supporting Europe) *2	Japanese *3
Chinese (Simplified) *1	Chinese (Simplified) *3 * Replaced with a font equivalent to Chinese (Simplified) (supporting Europe) of the GOT1000 series.
Chinese (Simplified) (supporting Europe) *2	Chinese (Simplified) *3
Chinese (Traditional) (supporting European) *2	Chinese (Traditional) *3

European characters (Latin-1 Supplement, Latin Extended-A, Basic Greek, and Cyrillic) are displayed in two-byte characters.

*2 European characters (Latin-1 Supplement, Latin Extended-A, Basic Greek, and part of Cyrillic) are displayed in one-byte characters.

*3 European characters (Latin-1 Supplement, Latin Extended-A, Latin Extended-B, IPA Extensions, Latin Extended Additional, Basic Greek, Greek Extended, and part of Cyrillic) are displayed in one-byte characters.

(3) Drive configuration of the GOT The name and type (media) of drives are different as follows.

Drive name	Drive type		
	GT11	GT27	GT25
Drive A	Standard CF card	Standard SD card	←
Drive C	Built-in flash memory	Built-in flash memory	←
Drive D	Built-in SRAM	-	←
Drive E	-	USB (assigned in order of connection)	<i>←</i>
Drive F	-	USB (assigned in order of connection)	←
Drive G	-	USB (assigned in order of connection)	←
Drive X (current drive)	-	A drive that is running a project. (Note that it indicates the drive A when the project is started from the drive C.)	←

(4) Storage locations of data The storage locations of data are different as follows.

Data type	Storage drive				
	GT11	GT27	GT25		
OS Project data	Drive A, C Drive A, C * Only the drive A can be used when the OS is stored in the drive A.	Package data Drive A, C, E, F, G * The project data and system application cannot be stored in a different drive. * Only the drive A can be used for direct startup from a memory card.	←		
Resource data	Drive A, D * Storage locations differ depending on the type.	Drive A, E, F, G	<i>←</i>		

[Issue No.] GOT-A-0148-B

(5) Offset value setting

When offsets are used and the following conditions are satisfied, the values to be stored in the offset devices must be changed.

1) Conditions requiring changes

- Controller: OMRON PLC
- Connection type: Ethernet connection
- Offset-target device: Bit devices (.., LR, HR, WR, and AR)

2) Change method

Values to be stored in the offset devices can be calculated using the following expression. Store the calculated values in the offset devices.

Offset value for the GOT2000 series = (Offset value for the GOT1000 series) / 100 × 16

+ (Offset value for the GOT1000 series) % 100

* % means the division to calculate a remainder. (For "a % b", a remainder after "a" is divided by "b".)

Example) The following shows an example of offset values for the device LR00000.

Object setting in the GOT	Device number after the offset is added	Offset value for the GOT1000 series (decimal)	Offset value for the GOT2000 series (decimal) (calculated by the expression)
LR00000	LR00010	10	10
	LR00100	100	16
	LR00310	310	58
	LR010000	10000	1600

3) Differences in the specifications of the offsets of bit devices (.., LR, HR, WR, and AR)

In the GOT1000 series, values must be set corresponding to the device notation (channel number and bit position). In the GOT2000 series, values disregarding channel numbers are set while bit devices are considered continuous.

Example) The following shows an example for the GOT1000 series.

Offset	Device indicated by the monitor device
Offset value = 0 (no offset)	LR00000
Offset value = 1	LR00001
Offset value = 15	LR00015
Offset value = 16	322 (range error)
Offset value = 100	LR00100
Offset value = 115	LR00115

*1 The following shows the bit device representation. (LR is used as an example).

 $\mathsf{LR} \Box \Box \Box \Box \Delta \Delta$

Bit position
Channel number

*2 The lower two digits of the offset value are applied as an offset value for the bit position (*1). The valid value is 0 to 15. If 16 to 99 is set, the system alarm 322 "Dedicated device is out of range. Confirm device range." is displayed. The values excluding the lower two digits of the offset value are applied as an offset value for the channel number.

[Issue No.] GOT-A-0148-B

Example) The following shows an example for the GOT2000 series.

Offset	Device indicated by the monitor device
Offset value = 0 (no offset)	LR00000
Offset value = 1	LR00001
Offset value = 15	LR00015
Offset value = 16	LR00100
Offset value = 100	LR00604
Offset value = 115	LR00703

*1 The following shows the device representation for devices (.., LR, HR, WR, and AR). (LR is used as an example.) LR $\Box \Box \Box \Delta \Delta$

Bit position
Channel number

*2 As the offset value of the bit position is increased by 16, the channel number increases by 1.

REVISIONS

Version	Print Date	Revision
-	November 2019	- First edition (Japanese only)
А	December 2019	- Writing errors have been corrected.
В	July 2021	- Writing errors have been corrected.